

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: HALO

Report Number: P979206

Luminaire Tested: L820S10NF935XXXXBLSHBXXXX

Issue Date: 4/1/2025

Test Information

Test Method: LM-79-2019
Report Number: P979206
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (3DTHCNLSLWHSTLFWHST15LRNF30KWH)
Test Lab: INNOVATION CENTER
Issue Date: 4/1/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: L820S10NF935XXXXBLSHBXXXX
Description: 2IN Sustainable LED Track Luminaire with narrow flood optic
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1037.9 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.37
Luminous Opening: Circular (Dia: 0.22' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9
Total Harmonic Distortion (THDi): 20
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979206
CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	94	93	92
3	106	101	97	94	105	100	96	94	97	95	92	95	93	91	93	91	89	88
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84
5	99	93	88	85	98	92	88	85	90	87	84	89	86	83	87	85	83	81
6	96	89	85	81	95	88	84	81	87	83	81	86	83	80	85	82	80	78
7	93	86	81	78	92	85	81	78	84	80	78	83	80	77	82	79	77	76
8	90	83	78	75	89	82	78	75	81	78	75	80	77	75	80	77	74	73
9	87	80	76	73	86	80	75	73	79	75	72	78	75	72	77	74	72	71
10	85	78	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	1314872	1314872	1314872	1314872
5°	1050046	1120484	1147985	1078634
10°	637807	717031	750348	666396
15°	327267	376398	398091	343495
20°	188815	207483	215722	191926
25°	135342	143049	145110	134625
30°	94842	115473	109753	87777
35°	26736	51423	42368	21283
40°	5937	7421	7810	6432
45°	3982	4824	5475	4633
50°	3159	3748	4338	3706
55°	2785	3209	3634	3257
60°	2761	3086	3411	3086
65°	2947	3203	3331	2754
70°	3087	3641	3008	2533
75°	2720	3870	2615	1778
80°	3274	4833	3118	1871
85°	621	932	1242	621

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 100°
 Vertical Angle: 82.5°
 Luminance: 5600 cd/sqm



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	336.5	32.4
10°-20°	374.9	36.1
20°-30°	220.4	21.2
30°-40°	79.1	7.6
40°-50°	10.0	1.0
50°-60°	6.2	0.6
60°-70°	4.7	0.5
70°-80°	2.9	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.1	0.0
140°-150°	0.3	0.0
150°-160°	0.8	0.1
160°-170°	0.9	0.1
170°-180°	0.3	0.0
0°-30°	931.8	89.8
0°-40°	1010.9	97.4
0°-60°	1027.1	99.0
0°-90°	1035.6	99.8
90°-120°	0.0	0.0
90°-150°	0.3	0.0
90°-180°	2.0	0.2
0°-180°	1037.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	4857	4857	4857	4857	4857	
5°	3864	4123	4224	3969	3864	320
15°	1168	1343	1420	1226	1168	343
25°	453	479	486	451	453	212
35°	81	156	128	64	81	67
45°	10	13	14	12	10	8
55°	6	7	8	7	6	5
65°	5	5	5	4	5	4
75°	3	4	2	2	3	3
85°	0	0	0	0	0	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	2	2	2	2	2	1
165°	3	3	3	3	3	1
175°	3	3	3	3	3	0
180°	3	3	3	3	3	



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4516.8	4516.0	4515.5	4515.5	4516.0	4516.9	4518.2	4520.1	4522.4	4525.1	4528.4
5°	3864.0	3863.8	3864.5	3865.9	3868.2	3871.3	3875.2	3879.9	3885.4	3891.7	3898.7
7.5°	3084.9	3084.9	3086.1	3088.5	3092.0	3096.5	3102.2	3108.9	3116.7	3125.5	3135.3
10°	2320.2	2320.3	2321.6	2324.0	2327.5	2332.1	2337.7	2344.4	2352.1	2360.8	2370.6
12.5°	1671.0	1671.0	1671.9	1673.8	1676.6	1680.3	1684.9	1690.4	1696.9	1704.2	1712.4
15°	1167.7	1167.7	1168.5	1170.0	1172.2	1175.1	1178.6	1182.9	1187.8	1193.4	1199.7
17.5°	847.8	848.2	849.0	850.3	851.9	853.9	856.4	859.2	862.3	865.8	869.6
20°	655.4	655.5	655.9	656.6	657.5	658.7	660.2	661.9	663.9	666.2	668.7
22.5°	532.1	532.3	532.7	533.2	534.0	534.9	536.0	537.3	538.7	540.3	542.0
25°	453.1	453.2	453.4	453.7	454.1	454.7	455.3	456.1	456.9	457.9	458.9
27.5°	401.4	401.9	402.6	403.3	404.1	405.0	405.9	406.9	407.9	408.9	409.8
30°	303.4	305.2	307.2	309.4	311.7	314.3	317.0	319.9	322.9	326.2	328.9
32.5°	187.9	189.9	192.1	194.4	197.0	199.8	202.8	206.0	209.3	212.9	215.7
35°	80.9	82.2	83.8	85.5	87.5	89.6	91.9	94.4	97.2	100.1	102.6
37.5°	22.2	22.6	23.0	23.4	24.0	24.6	25.2	26.0	26.8	27.7	28.5
40°	16.8	16.9	16.9	17.0	17.1	17.1	17.2	17.3	17.4	17.5	17.5
42.5°	12.6	12.7	12.7	12.7	12.8	12.9	12.9	13.0	13.1	13.2	13.2
45°	10.4	10.4	10.4	10.4	10.4	10.4	10.5	10.5	10.5	10.6	10.6
47.5°	8.7	8.7	8.7	8.7	8.8	8.8	8.8	8.8	8.8	8.9	8.9
50°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.6	7.6
52.5°	6.4	6.4	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
55°	5.9	5.9	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
57.5°	5.6	5.6	5.6	5.5	5.5	5.5	5.5	5.5	5.4	5.4	5.4
60°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.2
62.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
65°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
67.5°	4.1	4.2	4.2	4.2	4.2	4.3	4.3	4.4	4.4	4.4	4.4
70°	3.9	3.9	4.0	4.0	4.0	4.1	4.1	4.2	4.2	4.2	4.3
72.5°	3.0	3.1	3.1	3.2	3.2	3.3	3.4	3.4	3.5	3.6	3.6
75°	2.6	2.7	2.7	2.7	2.8	2.8	2.9	2.9	3.0	3.0	3.0
77.5°	2.4	2.4	2.5	2.5	2.6	2.6	2.6	2.7	2.7	2.8	2.8
80°	2.1	2.2	2.2	2.2	2.3	2.3	2.4	2.4	2.5	2.5	2.5
82.5°	1.0	1.1	1.1	1.1	1.2	1.2	1.3	1.4	1.4	1.5	1.5
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.7
150°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.5	1.5	1.5	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
155°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.7	2.7	2.7	2.7	2.7	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5
175°	3.3	3.3	3.3	3.3	3.3	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.2	3.2	3.2	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4532.1	4536.3	4541.0	4546.3	4552.0	4558.2	4564.9	4572.1	4590.3	4585.0	4582.8
5°	3906.4	3914.9	3924.1	3929.1	3931.8	3961.0	3952.2	3945.0	3952.6	3960.9	3970.0
7.5°	3146.1	3157.0	3160.4	3164.9	3170.4	3192.7	3184.4	3193.3	3203.2	3214.0	3225.7
10°	2381.3	2386.0	2390.7	2396.7	2427.6	2419.4	2421.9	2431.1	2440.6	2450.5	2460.6
12.5°	1719.4	1722.1	1725.8	1730.5	1751.1	1743.6	1749.6	1756.6	1764.0	1771.5	1779.2
15°	1203.8	1206.3	1209.2	1212.3	1223.7	1219.7	1225.3	1231.4	1238.1	1245.4	1252.2
17.5°	871.1	872.3	873.8	885.1	881.8	880.7	884.2	888.1	892.1	896.4	899.4
20°	669.4	670.3	671.4	678.6	676.4	676.2	678.4	680.8	683.5	686.4	687.9
22.5°	542.4	542.9	543.6	547.9	546.4	546.3	547.6	549.0	550.5	551.8	556.7
25°	459.2	459.5	459.8	461.9	460.8	460.9	461.8	462.8	463.9	464.9	468.3
27.5°	410.1	410.4	410.8	412.6	412.0	412.1	412.6	413.1	413.7	414.1	415.7
30°	330.7	332.7	334.9	340.7	340.6	342.4	344.9	347.4	349.9	350.8	354.6
32.5°	217.6	219.6	222.0	228.3	228.2	230.4	233.3	236.3	239.4	240.5	244.7
35°	104.3	106.2	108.3	113.6	113.3	115.3	117.7	120.3	122.9	123.9	127.6
37.5°	29.0	29.7	30.4	32.0	32.0	33.1	34.6	36.2	37.8	38.6	40.6
40°	17.6	17.7	17.7	17.9	17.9	18.0	18.2	18.3	18.4	18.6	18.8
42.5°	13.3	13.4	13.5	13.7	13.7	13.8	13.9	14.1	14.2	14.3	14.6
45°	10.6	10.7	10.7	10.8	10.8	10.8	10.9	11.0	11.0	11.1	11.2
47.5°	8.9	8.9	9.0	9.0	9.0	9.1	9.1	9.2	9.2	9.3	9.4
50°	7.6	7.6	7.6	7.7	7.7	7.7	7.7	7.8	7.8	7.9	8.0
52.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.7	6.7	6.7	6.8	6.8
55°	5.8	5.8	5.9	5.9	5.9	5.9	5.9	5.9	6.0	6.0	6.1
57.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.5	5.5	5.5
60°	5.2	5.2	5.2	5.2	5.2	5.2	5.3	5.3	5.3	5.3	5.3
62.5°	4.7	4.7	4.7	4.8	4.8	4.8	4.8	4.8	4.9	4.9	4.9
65°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
67.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.6	4.6	4.6
70°	4.3	4.3	4.4	4.4	4.4	4.5	4.5	4.5	4.6	4.6	4.6
72.5°	3.6	3.7	3.7	3.8	3.8	3.8	3.9	3.9	4.0	4.0	4.1
75°	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.3	3.3	3.3	3.3
77.5°	2.8	2.9	2.9	3.0	3.0	3.0	3.1	3.1	3.1	3.1	3.2
80°	2.6	2.6	2.6	2.7	2.7	2.8	2.8	2.8	2.9	2.9	2.9
82.5°	1.6	1.6	1.7	1.8	1.9	1.9	2.0	2.0	2.1	2.1	2.2
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
155°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.5	3.4	3.4	3.4	3.5	3.5	3.5	3.5
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4586.6	4590.9	4595.5	4600.6	4605.9	4611.7	4635.3	4630.1	4629.8	4634.7	4639.9
5°	3979.9	3990.5	4001.9	4025.8	4025.7	4032.6	4038.7	4045.5	4053.1	4076.0	4069.5
7.5°	3238.3	3280.6	3265.7	3267.5	3273.8	3281.3	3289.7	3325.6	3309.7	3321.1	3332.6
10°	2470.9	2485.5	2483.5	2492.7	2502.3	2512.3	2522.6	2536.3	2545.1	2556.8	2568.3
12.5°	1801.5	1788.6	1798.1	1807.8	1817.6	1827.4	1851.7	1846.7	1855.9	1865.0	1872.3
15°	1267.6	1262.5	1267.6	1272.9	1278.3	1283.8	1293.4	1297.1	1305.0	1311.5	1317.4
17.5°	906.4	905.8	910.2	914.5	918.7	933.4	926.6	931.6	936.4	940.3	955.1
20°	691.3	691.4	693.6	695.8	698.1	705.9	702.9	705.4	707.5	709.2	715.8
22.5°	554.1	554.5	555.8	557.1	558.5	562.6	561.5	563.3	564.8	566.2	570.0
25°	466.7	467.5	468.4	469.4	470.3	472.5	472.0	473.0	473.8	474.6	476.6
27.5°	414.8	415.2	415.6	416.1	416.5	417.6	417.6	418.3	419.0	419.6	420.9
30°	352.8	353.9	355.1	356.5	357.9	360.8	361.1	362.2	362.6	363.1	364.5
32.5°	242.8	244.4	246.2	247.9	249.8	252.9	253.7	255.4	256.6	257.8	259.7
35°	126.2	128.3	130.5	132.7	134.9	138.2	139.5	141.3	143.0	144.6	146.5
37.5°	40.0	41.2	42.5	43.7	44.9	46.5	47.2	48.2	49.0	49.7	50.5
40°	18.9	19.0	19.1	19.2	19.4	19.6	19.7	19.8	20.0	20.1	20.2
42.5°	14.6	14.7	14.8	14.9	15.1	15.2	15.4	15.5	15.6	15.9	15.8
45°	11.3	11.4	11.4	11.5	11.6	11.7	11.8	11.9	11.9	12.1	12.1
47.5°	9.4	9.5	9.6	9.6	9.8	9.8	9.9	9.9	10.0	10.1	10.1
50°	8.0	8.1	8.1	8.2	8.3	8.3	8.4	8.4	8.5	8.6	8.7
52.5°	6.9	6.9	7.0	7.0	7.1	7.1	7.2	7.2	7.3	7.4	7.4
55°	6.1	6.1	6.2	6.2	6.3	6.3	6.4	6.4	6.5	6.5	6.6
57.5°	5.6	5.6	5.6	5.7	5.7	5.7	5.8	5.8	5.9	5.9	5.9
60°	5.3	5.4	5.4	5.4	5.4	5.4	5.5	5.5	5.5	5.6	5.6
62.5°	5.0	5.0	5.0	5.0	5.1	5.1	5.1	5.1	5.2	5.2	5.2
65°	4.6	4.7	4.7	4.7	4.7	4.7	4.7	4.8	4.8	4.9	4.9
67.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.7	4.7	4.7	4.7	4.8
70°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
72.5°	4.1	4.1	4.1	4.2	4.2	4.3	4.3	4.3	4.3	4.3	4.3
75°	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.6	3.6	3.6	3.6
77.5°	3.2	3.2	3.2	3.2	3.3	3.3	3.3	3.3	3.3	3.3	3.3
80°	2.9	2.9	3.0	3.0	3.0	3.0	3.1	3.1	3.1	3.1	3.1
82.5°	2.2	2.2	2.3	2.3	2.4	2.4	2.4	2.4	2.5	2.5	2.5
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4	0.4
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6	0.6
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9	0.9
152.5°	1.4	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.8	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.2	2.2	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.4	3.4
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.4	3.4
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4645.5	4651.5	4657.8	4669.9	4668.8	4673.0	4677.4	4682.3	4687.4	4698.9	4696.9
5°	4076.7	4084.4	4092.5	4123.2	4109.9	4121.6	4130.8	4140.1	4171.1	4157.0	4163.0
7.5°	3344.0	3355.4	3365.9	3371.9	3379.8	3387.8	3421.7	3404.1	3413.2	3422.6	3432.3
10°	2577.8	2591.0	2597.7	2608.4	2618.7	2656.2	2637.8	2645.6	2652.9	2659.8	2680.8
12.5°	1893.8	1887.3	1896.5	1905.5	1914.2	1929.8	1930.5	1937.8	1944.9	1975.6	1959.6
15°	1326.8	1329.9	1336.7	1343.0	1366.3	1354.0	1359.7	1365.1	1371.5	1386.4	1383.5
17.5°	947.5	951.9	956.1	960.0	971.2	967.5	971.7	976.2	980.3	986.3	987.6
20°	712.8	715.4	717.9	720.2	725.3	724.5	726.9	729.4	731.6	733.5	736.1
22.5°	568.5	569.8	571.1	572.4	574.6	575.3	577.3	579.2	585.1	582.3	583.9
25°	476.3	477.3	478.1	478.9	479.7	480.3	481.4	482.3	485.3	484.0	484.9
27.5°	420.9	421.4	421.9	422.3	422.7	423.2	423.7	424.2	425.7	425.0	425.4
30°	364.0	364.5	365.2	369.4	367.2	367.9	368.0	368.2	370.3	368.5	368.4
32.5°	259.8	260.8	261.8	266.8	264.1	265.1	265.7	266.4	269.0	267.6	268.0
35°	147.6	149.0	150.6	155.6	153.8	154.7	155.3	155.7	157.5	156.4	156.7
37.5°	51.9	53.2	54.3	57.3	56.2	57.5	58.6	59.5	60.9	60.7	61.3
40°	20.4	20.6	20.8	21.0	20.9	21.0	21.2	21.3	21.4	21.6	21.8
42.5°	16.0	16.1	16.3	16.5	16.5	16.6	16.7	16.8	16.9	17.0	17.1
45°	12.2	12.3	12.4	12.6	12.6	12.7	12.8	12.8	12.9	13.0	13.1
47.5°	10.2	10.3	10.4	10.5	10.6	10.6	10.7	10.7	10.8	10.8	10.9
50°	8.7	8.8	8.9	8.9	9.0	9.0	9.1	9.1	9.2	9.2	9.3
52.5°	7.5	7.6	7.6	7.7	7.7	7.8	7.8	7.9	7.9	8.0	8.0
55°	6.6	6.7	6.7	6.8	6.8	6.9	6.9	7.0	7.0	7.1	7.1
57.5°	6.0	6.0	6.1	6.1	6.2	6.2	6.2	6.3	6.3	6.4	6.4
60°	5.6	5.7	5.7	5.7	5.7	5.8	5.8	5.8	5.9	5.9	5.9
62.5°	5.2	5.3	5.3	5.3	5.3	5.4	5.4	5.4	5.4	5.4	5.5
65°	4.9	4.9	5.0	5.0	5.0	5.0	5.0	5.1	5.1	5.1	5.1
67.5°	4.8	4.8	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
70°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
72.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.2	4.2	4.2
75°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.6
77.5°	3.3	3.3	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3
80°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
82.5°	2.5	2.6	2.6	2.6	2.6	2.6	2.6	2.7	2.6	2.6	2.6
85°	0.3	0.4	0.4	0.3	0.4	0.4	0.5	0.5	0.5	0.5	0.5
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.3	1.3	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.7	1.7	1.7	1.7	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.0	2.0
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.4	2.4
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.8	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4699.6	4702.3	4705.3	4718.0	4711.5	4713.0	4715.7	4719.6	4724.6	4732.2	4732.3
5°	4169.8	4177.6	4198.3	4193.5	4199.9	4204.9	4210.4	4216.3	4220.3	4225.4	4231.0
7.5°	3456.6	3451.7	3460.2	3468.6	3476.6	3486.1	3489.6	3494.2	3498.3	3533.0	3512.0
10°	2674.3	2681.0	2687.2	2692.7	2700.8	2704.3	2710.4	2718.4	2726.3	2736.2	2737.6
12.5°	1967.1	1973.7	1979.4	1998.4	1988.2	1991.9	1998.0	2003.7	2022.6	2012.4	2016.9
15°	1390.1	1395.7	1400.1	1406.9	1406.2	1410.3	1415.2	1419.2	1427.3	1426.0	1429.6
17.5°	990.8	993.6	1007.2	997.4	999.6	1003.5	1006.8	1021.7	1012.1	1013.6	1014.9
20°	738.3	740.2	747.4	743.2	745.0	747.2	748.9	756.1	751.1	752.3	753.0
22.5°	585.3	586.6	590.6	588.7	589.9	591.0	591.8	595.4	592.8	593.4	593.7
25°	485.5	485.9	487.2	486.3	487.6	488.8	489.8	492.5	491.4	492.0	492.3
27.5°	425.6	425.7	426.2	425.9	426.5	427.1	427.7	429.1	428.7	429.2	429.7
30°	368.5	368.8	370.2	369.4	369.0	368.7	368.4	369.4	367.7	367.4	367.1
32.5°	268.4	268.6	269.5	268.8	268.8	268.7	268.6	270.0	268.1	267.6	266.9
35°	156.8	156.8	157.0	156.8	157.0	157.1	157.0	158.0	156.3	155.8	155.0
37.5°	61.7	61.8	61.8	62.2	62.7	62.9	62.9	63.3	62.4	62.0	61.4
40°	21.9	21.9	21.8	21.9	22.1	22.2	22.3	22.4	22.5	22.6	22.5
42.5°	17.2	17.5	17.4	17.4	17.5	17.6	17.6	17.7	17.8	17.8	17.9
45°	13.2	13.3	13.3	13.4	13.4	13.5	13.6	13.7	13.7	13.8	13.8
47.5°	11.0	11.1	11.1	11.2	11.2	11.3	11.3	11.4	11.4	11.5	11.5
50°	9.3	9.4	9.4	9.5	9.5	9.6	9.7	9.7	9.7	9.8	9.8
52.5°	8.1	8.1	8.1	8.2	8.2	8.3	8.3	8.3	8.4	8.4	8.4
55°	7.1	7.2	7.2	7.2	7.2	7.3	7.3	7.3	7.3	7.4	7.4
57.5°	6.4	6.5	6.5	6.5	6.6	6.6	6.6	6.6	6.7	6.7	6.7
60°	5.9	6.0	6.0	6.0	6.0	6.1	6.1	6.1	6.2	6.2	6.2
62.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.6
65°	5.1	5.1	5.1	5.1	5.1	5.1	5.2	5.2	5.2	5.2	5.2
67.5°	4.9	5.0	5.0	4.9	4.9	4.9	5.0	4.9	5.0	5.0	5.0
70°	4.6	4.6	4.6	4.6	4.5	4.5	4.5	4.4	4.4	4.4	4.4
72.5°	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.1	4.0	4.0	4.0
75°	3.6	3.6	3.6	3.5	3.5	3.4	3.4	3.4	3.3	3.3	3.2
77.5°	3.3	3.3	3.3	3.2	3.2	3.1	3.1	3.1	3.1	3.0	3.0
80°	3.1	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.8	2.8	2.8
82.5°	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5	2.5	2.4	2.4
85°	0.5	0.5	0.5	0.6	0.6	0.6	0.7	0.6	0.6	0.6	0.6
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3
147.5°	0.6	0.6	0.6	0.6	0.6	0.5	0.6	0.6	0.6	0.5	0.5
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.5	1.5
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4731.6	4731.7	4732.4	4734.1	4729.7	4725.9	4722.7	4720.7	4717.6	4713.6	4710.3
5°	4257.4	4242.1	4243.5	4245.5	4247.7	4273.7	4255.0	4250.2	4249.2	4248.4	4246.9
7.5°	3517.6	3521.3	3523.1	3522.8	3535.9	3521.2	3525.4	3527.7	3528.2	3526.7	3523.2
10°	2741.5	2744.5	2746.4	2771.8	2753.7	2754.6	2755.4	2755.1	2753.5	2750.5	2746.0
12.5°	2019.9	2021.4	2021.4	2038.6	2030.5	2034.6	2037.4	2038.7	2038.5	2036.8	2035.6
15°	1432.6	1434.8	1437.4	1447.1	1442.5	1443.0	1442.7	1441.6	1439.6	1436.8	1436.4
17.5°	1015.3	1014.9	1027.1	1019.5	1019.2	1020.4	1020.8	1020.5	1019.4	1017.5	1018.0
20°	753.3	753.3	760.7	756.1	756.6	757.2	757.4	757.2	756.5	755.3	755.9
22.5°	593.7	593.8	598.4	595.8	596.7	597.3	597.5	597.4	596.9	596.2	596.2
25°	492.3	492.4	494.6	492.8	493.0	493.0	492.9	492.7	492.2	491.8	491.7
27.5°	430.1	430.4	432.0	431.0	431.0	430.9	430.8	430.7	430.4	430.2	430.1
30°	366.9	366.9	368.9	366.6	366.2	365.8	365.3	364.7	364.0	363.3	362.4
32.5°	265.9	265.5	267.1	264.2	263.3	262.3	261.0	259.6	258.0	256.5	255.3
35°	154.0	153.7	155.2	152.6	151.8	150.8	149.5	148.1	146.4	144.9	143.5
37.5°	60.7	60.5	61.4	59.7	59.3	58.7	57.8	56.8	55.4	54.4	53.6
40°	22.3	22.3	22.5	22.5	22.6	22.6	22.6	22.6	22.5	22.4	22.4
42.5°	17.9	17.9	18.1	18.0	18.1	18.1	18.1	18.1	18.1	18.1	18.1
45°	13.9	13.9	14.0	14.0	14.1	14.1	14.2	14.2	14.2	14.2	14.2
47.5°	11.6	11.7	11.7	11.8	11.8	11.9	11.9	11.9	12.0	12.0	12.0
50°	9.8	9.9	10.0	10.0	10.0	10.1	10.1	10.2	10.2	10.2	10.2
52.5°	8.5	8.5	8.6	8.6	8.6	8.7	8.7	8.7	8.7	8.8	8.8
55°	7.4	7.5	7.5	7.5	7.5	7.6	7.6	7.6	7.6	7.7	7.7
57.5°	6.8	6.8	6.8	6.9	6.9	6.9	6.9	6.9	7.0	7.0	7.0
60°	6.2	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
62.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.7	5.7	5.7	5.7
65°	5.2	5.2	5.2	5.2	5.3	5.3	5.3	5.3	5.3	5.3	5.3
67.5°	5.0	5.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.8
70°	4.3	4.3	4.3	4.2	4.2	4.2	4.1	4.1	4.1	4.0	4.0
72.5°	3.9	4.0	3.9	3.9	3.8	3.8	3.7	3.7	3.7	3.6	3.6
75°	3.2	3.2	3.1	3.1	3.1	3.0	3.0	3.0	2.9	2.9	2.8
77.5°	2.9	2.9	2.9	2.8	2.8	2.7	2.7	2.6	2.6	2.6	2.5
80°	2.7	2.7	2.6	2.6	2.6	2.5	2.5	2.4	2.4	2.3	2.3
82.5°	2.4	2.4	2.3	2.3	2.2	2.2	2.1	2.1	2.1	2.0	2.0
85°	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.6
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
155°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4707.6	4705.4	4705.2	4706.2	4707.7	4709.8	4712.5	4713.9	4715.6	4717.8	4720.4
5°	4244.3	4240.5	4259.1	4250.6	4242.0	4233.2	4224.4	4226.5	4228.5	4230.6	4232.6
7.5°	3518.4	3546.9	3537.4	3527.8	3518.1	3508.4	3498.7	3500.3	3502.0	3503.7	3505.4
10°	2747.7	2772.6	2764.1	2755.5	2746.9	2738.2	2729.6	2730.6	2731.5	2732.5	2733.4
12.5°	2038.2	2059.2	2051.1	2042.9	2034.7	2026.5	2018.3	2018.1	2017.9	2017.7	2017.5
15°	1437.6	1452.0	1445.7	1439.4	1433.1	1426.7	1420.4	1421.4	1422.3	1423.3	1424.2
17.5°	1031.9	1027.8	1023.7	1019.7	1015.6	1011.5	1007.4	1007.5	1007.7	1007.9	1008.1
20°	764.1	761.6	759.0	756.5	753.9	751.4	748.8	748.7	748.5	748.3	748.1
22.5°	600.6	598.8	596.9	595.1	593.2	591.4	589.5	589.3	589.1	588.8	588.6
25°	494.4	493.0	491.6	490.1	488.7	487.3	485.8	485.5	485.1	484.8	484.4
27.5°	431.8	431.0	430.3	429.5	428.7	428.0	427.2	426.9	426.6	426.4	426.1
30°	365.3	362.9	360.5	358.2	355.8	353.5	351.1	350.3	349.5	348.6	347.8
32.5°	257.8	255.0	252.1	249.2	246.3	243.4	240.5	239.3	238.1	236.8	235.6
35°	145.7	142.8	139.9	136.9	134.0	131.1	128.2	126.5	124.9	123.3	121.7
37.5°	55.0	53.0	51.1	49.1	47.2	45.2	43.3	42.5	41.7	40.9	40.2
40°	22.6	22.5	22.4	22.4	22.3	22.2	22.1	22.1	22.1	22.1	22.0
42.5°	18.2	18.2	18.1	18.0	18.0	17.9	17.8	17.8	17.8	17.7	17.7
45°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.2	14.2
47.5°	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1
50°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3
52.5°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.7	8.7
55°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.6
57.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.9
60°	6.4	6.4	6.4	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
62.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.6
65°	5.3	5.2	5.2	5.2	5.2	5.2	5.2	5.1	5.1	5.1	5.1
67.5°	4.8	4.8	4.8	4.7	4.7	4.6	4.6	4.6	4.5	4.5	4.5
70°	4.0	4.0	3.9	3.9	3.9	3.9	3.8	3.8	3.8	3.8	3.7
72.5°	3.6	3.6	3.5	3.5	3.4	3.4	3.3	3.3	3.2	3.2	3.2
75°	2.8	2.8	2.7	2.7	2.6	2.5	2.5	2.5	2.4	2.4	2.3
77.5°	2.5	2.4	2.4	2.3	2.3	2.2	2.2	2.2	2.1	2.1	2.0
80°	2.3	2.2	2.2	2.1	2.1	2.0	2.0	1.9	1.9	1.9	1.8
82.5°	1.9	1.9	1.8	1.8	1.7	1.7	1.6	1.6	1.6	1.5	1.5
85°	0.6	0.6	0.6	0.5	0.5	0.4	0.4	0.4	0.4	0.4	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
155°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
157.5°	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4722.6	4718.5	4716.9	4716.3	4716.6	4719.2	4707.6	4702.7	4698.1	4693.9	4685.7
5°	4207.9	4205.6	4200.7	4193.2	4183.2	4173.3	4171.5	4188.3	4156.6	4148.3	4138.5
7.5°	3507.0	3467.9	3464.3	3459.8	3453.8	3446.3	3437.5	3427.6	3435.5	3410.8	3402.3
10°	2734.4	2701.3	2691.8	2688.8	2684.3	2678.2	2670.7	2661.9	2652.9	2664.0	2632.1
12.5°	2017.3	1989.9	1980.1	1975.8	1972.6	1968.0	1962.2	1955.1	1946.9	1949.9	1928.1
15°	1425.2	1405.6	1399.1	1393.9	1390.8	1386.6	1381.6	1375.6	1368.9	1367.2	1355.1
17.5°	1008.3	1008.5	990.9	986.6	985.0	982.8	979.9	976.5	972.5	970.1	974.5
20°	747.9	747.7	737.7	734.8	733.8	732.4	730.4	728.1	725.2	722.4	724.4
22.5°	588.3	588.1	580.9	578.6	577.4	576.1	574.5	572.7	570.5	568.2	569.4
25°	484.1	483.7	479.8	478.5	477.8	477.3	476.6	475.8	474.8	473.8	474.4
27.5°	425.8	425.5	422.6	421.6	421.0	420.5	419.8	419.1	418.2	417.2	417.4
30°	347.0	346.2	340.3	338.1	336.4	334.8	333.0	330.9	328.5	325.8	325.3
32.5°	234.3	233.1	226.7	223.9	221.7	219.7	217.4	214.9	212.1	209.1	208.1
35°	120.0	118.4	112.7	110.0	108.0	106.3	104.5	102.4	100.1	97.6	96.6
37.5°	39.4	38.6	36.1	34.9	34.0	33.4	32.8	32.1	31.3	30.5	30.2
40°	22.0	22.0	21.7	21.6	21.5	21.4	21.2	21.1	21.0	20.9	20.8
42.5°	17.7	17.6	17.4	17.2	17.1	17.0	16.9	16.8	16.6	16.5	16.4
45°	14.2	14.2	14.0	14.0	13.9	13.9	13.8	13.7	13.7	13.6	13.5
47.5°	12.1	12.0	11.9	11.9	11.8	11.8	11.7	11.7	11.6	11.5	11.5
50°	10.2	10.2	10.1	10.1	10.0	10.0	10.0	9.9	9.8	9.8	9.7
52.5°	8.7	8.7	8.6	8.6	8.6	8.6	8.5	8.5	8.5	8.4	8.4
55°	7.6	7.6	7.6	7.6	7.6	7.6	7.5	7.5	7.5	7.5	7.4
57.5°	6.9	6.9	6.9	6.8	6.8	6.8	6.7	6.7	6.7	6.6	6.6
60°	6.2	6.2	6.2	6.2	6.1	6.1	6.1	6.1	6.1	6.0	6.0
62.5°	5.6	5.6	5.6	5.5	5.5	5.5	5.5	5.4	5.4	5.4	5.4
65°	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.8	4.8	4.8	4.7
67.5°	4.5	4.4	4.4	4.3	4.3	4.2	4.2	4.1	4.1	4.0	4.0
70°	3.7	3.7	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.4
72.5°	3.1	3.1	3.0	2.9	2.9	2.8	2.8	2.8	2.7	2.7	2.7
75°	2.3	2.3	2.2	2.2	2.1	2.1	2.1	2.1	2.0	2.0	2.0
77.5°	2.0	2.0	1.9	1.9	1.8	1.8	1.8	1.8	1.7	1.7	1.7
80°	1.8	1.7	1.7	1.7	1.6	1.6	1.6	1.5	1.5	1.5	1.4
82.5°	1.5	1.4	1.4	1.3	1.3	1.2	1.2	1.2	1.1	1.1	1.1
85°	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.1	1.1	1.1	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.5	1.5	1.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
177.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4678.4	4671.8	4665.8	4662.4	4656.2	4651.7	4647.6	4643.8	4640.3	4646.3	4623.7
5°	4127.5	4141.8	4112.8	4103.7	4093.5	4083.2	4073.0	4064.6	4057.4	4053.0	4059.1
7.5°	3393.0	3382.9	3372.2	3388.7	3349.1	3342.4	3334.5	3327.4	3314.1	3302.2	3290.0
10°	2623.8	2614.0	2602.8	2593.9	2579.4	2567.1	2555.6	2547.0	2540.8	2530.0	2521.8
12.5°	1922.2	1915.1	1906.7	1897.2	1901.7	1876.1	1864.8	1854.1	1846.3	1852.2	1830.0
15°	1350.7	1346.9	1342.0	1336.0	1333.8	1321.3	1313.0	1303.9	1296.2	1293.6	1286.5
17.5°	958.8	955.5	951.7	947.5	943.4	950.0	934.0	928.5	922.3	918.5	926.0
20°	715.3	713.6	711.6	709.1	706.3	709.2	700.4	697.0	693.3	690.3	693.4
22.5°	563.9	562.3	560.9	559.2	557.1	558.2	553.6	551.6	549.4	547.2	548.2
25°	471.4	470.4	469.6	468.6	467.5	467.8	465.5	464.4	463.4	462.3	462.6
27.5°	414.1	412.6	411.6	410.6	409.6	409.9	406.9	405.5	404.2	403.0	402.9
30°	319.6	316.6	314.6	312.6	310.4	309.9	305.9	303.7	301.3	299.0	298.0
32.5°	202.0	198.5	196.6	194.6	192.3	191.6	187.7	185.2	182.8	180.2	178.8
35°	91.6	88.3	86.9	85.2	83.3	82.5	80.3	78.8	77.1	75.3	74.0
37.5°	29.1	28.4	28.0	27.6	27.0	26.6	26.2	25.8	25.3	24.6	24.0
40°	20.6	20.5	20.4	20.3	20.2	20.1	19.9	19.7	19.6	19.4	19.2
42.5°	16.2	16.1	16.0	15.9	15.8	15.7	15.6	15.5	15.3	15.2	15.1
45°	13.4	13.3	13.3	13.2	13.1	13.1	13.0	12.9	12.9	12.8	12.7
47.5°	11.4	11.3	11.3	11.2	11.2	11.1	11.1	11.0	10.9	10.9	10.8
50°	9.7	9.6	9.6	9.6	9.5	9.5	9.5	9.4	9.4	9.4	9.3
52.5°	8.4	8.3	8.3	8.3	8.2	8.2	8.2	8.1	8.1	8.1	8.0
55°	7.4	7.4	7.3	7.3	7.3	7.2	7.2	7.2	7.1	7.1	7.1
57.5°	6.6	6.5	6.4	6.4	6.4	6.4	6.4	6.4	6.3	6.3	6.3
60°	6.0	6.0	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
62.5°	5.4	5.3	5.3	5.2	5.2	5.2	5.2	5.1	5.1	5.1	5.1
65°	4.7	4.6	4.6	4.6	4.6	4.5	4.5	4.5	4.5	4.4	4.4
67.5°	4.0	3.9	3.9	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.6
70°	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3
72.5°	2.7	2.6	2.5	2.5	2.5	2.4	2.4	2.4	2.4	2.3	2.3
75°	2.0	1.9	1.9	1.9	1.8	1.8	1.8	1.8	1.7	1.7	1.7
77.5°	1.6	1.6	1.6	1.6	1.5	1.5	1.5	1.5	1.5	1.5	1.5
80°	1.4	1.4	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.2	1.2
82.5°	1.1	1.0	1.0	0.9	0.9	0.9	0.9	0.9	0.8	0.8	0.8
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.8	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.3
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.7	1.7
157.5°	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.4	2.4	2.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.9	2.9	2.9	2.9	2.9
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
177.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4616.8	4610.6	4605.3	4606.9	4595.2	4590.6	4586.6	4583.0	4579.9	4582.4	4569.0
5°	4035.1	4024.7	4014.6	4004.9	4017.9	3984.2	3973.5	3962.8	3953.2	3969.2	3939.1
7.5°	3277.4	3278.9	3256.3	3247.6	3238.2	3228.3	3244.6	3207.9	3197.9	3188.3	3181.0
10°	2513.2	2504.2	2507.8	2481.8	2471.6	2462.2	2453.0	2470.4	2433.9	2424.2	2414.5
12.5°	1820.9	1811.1	1800.6	1812.8	1780.2	1771.9	1764.8	1763.8	1750.6	1743.8	1736.8
15°	1281.4	1275.4	1268.4	1269.5	1253.5	1246.0	1240.8	1235.9	1247.3	1225.6	1219.9
17.5°	913.1	909.5	905.3	902.9	896.4	891.8	887.4	884.9	889.2	879.8	876.8
20°	686.2	683.9	681.4	678.8	676.8	674.4	671.6	669.5	670.4	666.2	664.4
22.5°	544.6	543.2	541.7	540.2	542.3	536.3	534.1	532.1	531.5	529.7	528.7
25°	460.5	459.5	458.3	457.1	457.7	454.6	453.2	451.9	451.3	450.7	450.1
27.5°	399.9	398.2	396.6	395.2	395.9	391.8	390.0	388.3	387.0	385.7	384.5
30°	294.3	291.8	289.4	287.1	287.3	282.9	280.8	278.7	277.4	280.8	275.6
32.5°	176.1	174.1	172.1	170.0	170.0	166.0	164.0	161.9	160.4	163.3	159.3
35°	73.1	72.2	71.0	69.6	69.2	66.6	65.0	63.3	62.2	64.4	61.9
37.5°	24.2	24.2	24.1	23.8	23.6	23.3	23.1	22.9	22.7	22.9	22.7
40°	19.1	19.0	18.9	18.8	18.7	18.6	18.5	18.3	18.2	18.2	18.0
42.5°	15.1	14.8	14.7	14.6	14.5	14.4	14.3	14.2	14.1	14.1	14.0
45°	12.7	12.6	12.5	12.4	12.4	12.3	12.2	12.2	12.1	12.1	12.0
47.5°	10.8	10.7	10.6	10.6	10.5	10.5	10.4	10.4	10.3	10.3	10.2
50°	9.3	9.2	9.2	9.1	9.1	9.0	9.0	8.9	8.9	8.8	8.8
52.5°	8.0	7.9	7.9	7.8	7.8	7.7	7.7	7.6	7.6	7.5	7.5
55°	7.1	7.0	7.0	7.0	7.0	6.9	6.9	6.9	6.9	6.9	6.8
57.5°	6.3	6.2	6.2	6.2	6.2	6.2	6.1	6.1	6.1	6.1	6.1
60°	5.9	5.8	5.8	5.8	5.8	5.8	5.7	5.7	5.7	5.7	5.6
62.5°	5.1	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
65°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.3	4.4
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
70°	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2	3.2
72.5°	2.3	2.2	2.2	2.2	2.2	2.2	2.2	2.1	2.1	2.1	2.1
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
77.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.5
80°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
82.5°	0.8	0.8	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.0	1.0	1.0	1.0
152.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.2	2.2	2.2	2.2
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.6	2.6	2.6
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
177.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.1
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4562.5	4556.7	4551.4	4546.6	4542.5	4544.3	4552.0	4529.3	4526.0	4523.3	4521.4
5°	3932.8	3926.9	3921.5	3930.5	3908.9	3902.9	3897.4	3892.5	3887.4	3892.1	3872.1
7.5°	3169.3	3160.6	3152.5	3145.1	3138.4	3158.7	3124.3	3117.6	3111.2	3105.1	3103.5
10°	2409.0	2395.7	2386.7	2378.8	2371.4	2367.6	2359.5	2354.6	2349.9	2345.6	2341.7
12.5°	1729.8	1737.1	1715.8	1709.0	1703.3	1697.6	1705.9	1688.8	1685.2	1681.9	1679.0
15°	1214.0	1211.6	1204.0	1199.5	1195.3	1191.3	1191.3	1184.7	1181.8	1178.8	1175.8
17.5°	873.6	870.1	877.6	864.3	861.0	858.1	855.2	863.1	850.9	848.6	846.3
20°	662.3	660.1	663.0	656.5	654.8	653.3	651.8	655.4	650.0	649.1	648.1
22.5°	527.8	526.8	528.2	524.5	523.1	521.6	520.6	522.6	520.1	519.9	519.7
25°	449.6	449.0	449.4	447.9	447.3	446.6	446.3	447.4	446.2	446.2	446.2
27.5°	383.6	382.8	383.5	381.0	380.1	379.2	378.4	379.6	377.5	377.2	377.1
30°	274.8	274.0	274.4	272.4	271.6	270.9	270.4	271.8	270.0	269.9	270.0
32.5°	158.6	157.9	157.8	156.3	155.6	155.1	154.8	155.9	154.5	154.3	154.2
35°	61.5	61.0	60.5	60.0	59.5	58.8	58.1	58.8	58.7	59.0	59.2
37.5°	22.6	22.4	22.1	22.0	22.0	21.9	21.8	21.9	21.8	21.8	21.7
40°	17.9	17.8	17.7	17.7	17.6	17.5	17.4	17.3	17.2	17.2	17.1
42.5°	13.9	13.8	13.7	13.8	13.6	13.5	13.4	13.4	13.3	13.3	13.2
45°	11.9	11.8	11.8	11.8	11.6	11.6	11.5	11.5	11.4	11.3	11.3
47.5°	10.1	10.1	10.0	10.0	9.9	9.8	9.8	9.7	9.7	9.6	9.6
50°	8.7	8.7	8.6	8.6	8.5	8.5	8.4	8.4	8.4	8.3	8.2
52.5°	7.5	7.5	7.4	7.4	7.4	7.4	7.3	7.3	7.3	7.2	7.2
55°	6.8	6.8	6.7	6.7	6.7	6.7	6.6	6.6	6.6	6.5	6.5
57.5°	6.1	6.1	6.1	6.1	6.0	6.0	6.0	6.0	6.0	5.9	5.9
60°	5.6	5.6	5.6	5.6	5.5	5.5	5.5	5.5	5.5	5.4	5.4
62.5°	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.9
65°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.5	4.5	4.5	4.5
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3
72.5°	2.1	2.1	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3
75°	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
77.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.6	1.6	1.6
80°	1.2	1.2	1.2	1.2	1.2	1.2	1.3	1.3	1.3	1.3	1.3
82.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.3	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
155°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	2.9	2.9	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
177.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4520.1	4519.4	4519.4	4525.5	4534.5	4514.3	4508.9	4504.1	4500.1	4496.9	4494.4
5°	3865.5	3860.0	3855.5	3852.0	3849.5	3848.0	3861.3	3876.1	3844.3	3844.0	3842.0
7.5°	3122.1	3089.7	3084.5	3080.0	3076.0	3072.7	3070.1	3083.8	3068.1	3068.4	3069.6
10°	2348.5	2336.0	2330.5	2325.5	2321.4	2318.1	2315.7	2320.2	2335.2	2309.4	2308.7
12.5°	1676.5	1693.4	1670.2	1664.5	1659.2	1654.5	1650.3	1647.5	1659.7	1645.1	1645.2
15°	1172.8	1179.6	1168.8	1166.2	1163.1	1160.2	1157.5	1155.1	1161.4	1153.8	1153.9
17.5°	844.0	846.3	841.3	840.1	838.5	837.0	835.7	834.6	838.0	843.5	835.0
20°	647.1	647.8	645.2	644.5	643.8	643.2	642.8	642.5	644.5	648.3	643.5
22.5°	519.4	519.8	522.8	519.3	519.3	519.3	519.5	519.7	521.1	523.8	520.9
25°	446.2	446.4	448.4	446.1	446.0	445.8	445.7	445.6	446.3	447.9	446.3
27.5°	377.2	377.5	380.9	377.9	378.1	378.3	378.7	379.4	381.0	384.2	382.3
30°	270.1	270.4	274.4	271.2	271.7	272.0	272.5	273.1	274.6	278.4	275.7
32.5°	154.0	154.0	157.4	154.7	155.3	155.9	156.6	157.4	159.0	162.7	161.0
35°	59.4	59.4	61.5	59.7	59.7	60.1	60.6	61.0	61.8	64.4	62.9
37.5°	21.5	21.4	21.4	21.2	21.2	21.3	21.3	21.2	21.2	21.3	21.1
40°	17.0	17.0	17.0	16.9	16.8	16.8	16.7	16.7	16.7	16.8	16.6
42.5°	13.1	13.1	13.0	12.9	12.9	12.9	12.8	12.8	12.7	12.8	12.7
45°	11.2	11.2	11.2	11.1	11.0	11.0	10.9	10.8	10.8	10.8	10.7
47.5°	9.5	9.5	9.5	9.4	9.4	9.3	9.3	9.2	9.2	9.1	9.1
50°	8.2	8.1	8.1	8.1	8.0	8.0	7.9	7.9	7.9	7.9	7.8
52.5°	7.1	7.1	7.1	7.0	7.0	7.0	6.9	6.9	6.8	6.8	6.8
55°	6.5	6.5	6.4	6.4	6.4	6.3	6.3	6.2	6.2	6.2	6.1
57.5°	5.9	5.9	5.8	5.8	5.8	5.8	5.8	5.7	5.7	5.7	5.7
60°	5.4	5.4	5.3	5.3	5.3	5.3	5.3	5.3	5.2	5.2	5.2
62.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8
65°	4.5	4.5	4.5	4.5	4.6	4.6	4.6	4.6	4.6	4.6	4.6
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.7	3.7	3.7	3.7	3.7
70°	3.3	3.3	3.3	3.3	3.3	3.4	3.4	3.4	3.4	3.4	3.4
72.5°	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.4	2.4	2.5	2.5
75°	1.9	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.1	2.1	2.1
77.5°	1.6	1.6	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.9	1.9
80°	1.3	1.4	1.4	1.4	1.4	1.5	1.5	1.5	1.5	1.6	1.6
82.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.7	0.7	0.7
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.8	0.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.5	1.4	1.4
155°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3	2.2
160°	2.6	2.6	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.4	3.4
170°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
177.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0	4857.0
2.5°	4492.7	4491.6	4491.3	4491.6	4492.5	4494.0	4496.2	4498.9	4502.2	4506.0	4510.4
5°	3837.5	3834.1	3831.9	3830.8	3830.8	3831.9	3834.1	3837.3	3841.6	3846.8	3853.1
7.5°	3071.6	3068.3	3065.2	3063.1	3061.9	3061.7	3062.5	3064.2	3067.1	3070.9	3075.9
10°	2308.9	2309.0	2304.4	2300.9	2298.7	2297.5	2297.5	2298.7	2301.1	2304.6	2309.4
12.5°	1645.9	1647.2	1645.9	1644.1	1643.1	1642.8	1643.4	1644.9	1647.3	1650.5	1654.7
15°	1154.3	1155.2	1155.3	1154.4	1153.9	1154.0	1154.7	1155.9	1157.8	1160.2	1163.3
17.5°	835.6	836.4	837.1	836.5	836.2	836.3	836.7	837.4	838.5	840.1	842.0
20°	644.3	645.2	646.2	646.1	646.1	646.4	646.8	647.5	648.4	649.6	651.0
22.5°	521.6	522.4	523.3	523.4	523.6	523.9	524.4	525.0	525.8	526.8	528.0
25°	446.6	447.0	447.5	447.6	447.6	447.7	447.9	448.2	448.5	449.0	449.6
27.5°	383.6	385.2	386.9	387.7	388.4	389.3	390.4	391.7	393.2	394.8	396.6
30°	277.0	278.5	280.3	281.7	283.1	284.6	286.4	288.3	290.5	292.8	295.4
32.5°	162.4	164.1	165.8	167.5	169.1	170.8	172.7	174.7	176.9	179.3	181.9
35°	63.6	64.4	65.2	66.1	67.1	68.2	69.4	70.7	72.2	73.8	75.6
37.5°	21.1	21.1	21.1	21.2	21.3	21.4	21.5	21.5	21.6	21.7	21.7
40°	16.6	16.6	16.6	16.6	16.5	16.5	16.5	16.6	16.6	16.6	16.7
42.5°	12.6	12.6	12.6	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5
45°	10.7	10.6	10.6	10.5	10.5	10.5	10.4	10.4	10.4	10.4	10.3
47.5°	9.0	9.0	8.9	8.9	8.9	8.8	8.8	8.8	8.8	8.7	8.7
50°	7.8	7.7	7.7	7.7	7.6	7.6	7.6	7.5	7.5	7.5	7.5
52.5°	6.7	6.7	6.7	6.6	6.6	6.6	6.6	6.5	6.5	6.5	6.5
55°	6.1	6.1	6.0	6.0	6.0	6.0	5.9	5.9	5.9	5.9	5.9
57.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.6	5.6	5.6	5.6	5.6
60°	5.2	5.2	5.2	5.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1
62.5°	4.8	4.8	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
65°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
67.5°	3.7	3.8	3.8	3.8	3.8	3.9	3.9	3.9	4.0	4.0	4.0
70°	3.4	3.5	3.5	3.5	3.5	3.6	3.6	3.7	3.7	3.7	3.8
72.5°	2.5	2.6	2.6	2.6	2.7	2.7	2.7	2.8	2.8	2.9	2.9
75°	2.2	2.2	2.2	2.3	2.3	2.3	2.4	2.4	2.4	2.5	2.5
77.5°	1.9	2.0	2.0	2.0	2.1	2.1	2.1	2.2	2.2	2.3	2.3
80°	1.6	1.7	1.7	1.7	1.8	1.8	1.9	1.9	1.9	2.0	2.0
82.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.9	0.9
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
155°	1.9	1.9	1.9	1.9	1.8	1.8	1.9	1.8	1.8	1.8	1.8
157.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
160°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.3	3.3	3.3	3.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3
177.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.0	3.0	3.1	3.1
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979206
 CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	4857.0	4857.0
2.5°	4515.2	4516.8
5°	3860.3	3864.0
7.5°	3082.0	3084.9
10°	2315.3	2320.2
12.5°	1659.8	1671.0
15°	1167.0	1167.7
17.5°	844.3	847.8
20°	652.7	655.4
22.5°	529.3	532.1
25°	450.2	453.1
27.5°	398.6	401.4
30°	298.1	303.4
32.5°	184.7	187.9
35°	77.5	80.9
37.5°	21.8	22.2
40°	16.7	16.8
42.5°	12.5	12.6
45°	10.3	10.4
47.5°	8.7	8.7
50°	7.4	7.5
52.5°	6.4	6.4
55°	5.8	5.9
57.5°	5.6	5.6
60°	5.1	5.1
62.5°	4.7	4.7
65°	4.6	4.6
67.5°	4.1	4.1
70°	3.8	3.9
72.5°	3.0	3.0
75°	2.6	2.6
77.5°	2.3	2.4
80°	2.1	2.1
82.5°	1.0	1.0
85°	0.2	0.2
87.5°	0.1	0.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



TEST NUMBER: P979206
CATALOG NUMBER: L820S10NF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.1	0.1
135°	0.1	0.1
137.5°	0.1	0.1
140°	0.2	0.2
142.5°	0.4	0.4
145°	0.5	0.5
147.5°	0.8	0.8
150°	1.1	1.1
152.5°	1.4	1.5
155°	1.8	1.8
157.5°	2.3	2.2
160°	2.7	2.7
162.5°	3.0	3.0
165°	3.2	3.2
167.5°	3.4	3.4
170°	3.4	3.4
172.5°	3.4	3.4
175°	3.3	3.3
177.5°	3.1	3.2
180°	2.9	2.9

(END OF REPORT)