

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P644067

Luminaire Tested: ML5615LSWFL559FS1E - 696WB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P644067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-69)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 696WB - 1200LM - 3000K
Description: ML56 RR, 55D TIR OPTIC, 6" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1476.5 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P644067

CATALOG NUMBER: ML5615LSWFL559FS1E - 696WB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P644067

CATALOG NUMBER: ML5615LSWFL559FS1E - 696WB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 94 | 93 | | | 93 | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 93 | 97 | 93 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 85 | | | 85 | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 89 | 84 | 99 | 93 | 88 | 84 | 90 | 86 | 82 | 88 | 84 | 81 | 85 | 82 | 80 | 78 | | | 78 | | | | | | | | | | | | | | | | |
| 4 | 95 | 87 | 81 | 77 | 93 | 86 | 81 | 76 | 84 | 79 | 75 | 82 | 78 | 74 | 80 | 76 | 74 | 72 | | | 72 | | | | | | | | | | | | | | | | |
| 5 | 90 | 81 | 75 | 70 | 88 | 80 | 74 | 70 | 78 | 73 | 69 | 77 | 72 | 69 | 75 | 71 | 68 | 66 | | | 66 | | | | | | | | | | | | | | | | |
| 6 | 85 | 76 | 69 | 65 | 84 | 75 | 69 | 64 | 73 | 68 | 64 | 72 | 67 | 63 | 70 | 66 | 63 | 61 | | | 61 | | | | | | | | | | | | | | | | |
| 7 | 80 | 71 | 64 | 60 | 79 | 70 | 64 | 59 | 69 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 58 | 57 | | | 57 | | | | | | | | | | | | | | | | |
| 8 | 76 | 66 | 60 | 55 | 75 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 62 | 58 | 54 | 53 | | | 53 | | | | | | | | | | | | | | | | |
| 9 | 72 | 62 | 56 | 52 | 71 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 49 | | | 49 | | | | | | | | | | | | | | | | |
| 10 | 69 | 58 | 52 | 48 | 68 | 58 | 52 | 48 | 57 | 52 | 48 | 56 | 51 | 48 | 56 | 51 | 48 | 46 | | | 46 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 84752 |
| 5° | 80921 |
| 10° | 76713 |
| 15° | 72452 |
| 20° | 65596 |
| 25° | 55497 |
| 30° | 45058 |
| 35° | 35275 |
| 40° | 26450 |
| 45° | 17653 |
| 50° | 8546 |
| 55° | 4473 |
| 60° | 2281 |
| 65° | 1518 |
| 70° | 625 |
| 75° | 551 |
| 80° | 410 |
| 85° | 818 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17653 cd/sqm



TEST NUMBER: P644067

CATALOG NUMBER: ML5615LSWFL559FS1E - 696WB - 1200LM - 3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 137.6 | 9.3 |
| 10°-20° | 355.4 | 24.1 |
| 20°-30° | 419.2 | 28.4 |
| 30°-40° | 330.7 | 22.4 |
| 40°-50° | 173.3 | 11.7 |
| 50°-60° | 45.3 | 3.1 |
| 60°-70° | 11.3 | 0.8 |
| 70°-80° | 2.7 | 0.2 |
| 80°-90° | 0.9 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 912.2 | 61.8 |
| 0°-40° | 1242.9 | 84.2 |
| 0°-60° | 1461.5 | 99.0 |
| 0°-90° | 1476.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1476.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1546 | |
| 5° | 1470 | 138 |
| 15° | 1277 | 355 |
| 25° | 918 | 419 |
| 35° | 527 | 331 |
| 45° | 228 | 173 |
| 55° | 47 | 45 |
| 65° | 12 | 11 |
| 75° | 3 | 3 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P644067

CATALOG NUMBER: ML5615LSWFL559FS1E - 696WB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1546.0 |
| 2.5° | 1526.5 |
| 5° | 1470.5 |
| 7.5° | 1422.4 |
| 10° | 1378.1 |
| 12.5° | 1332.6 |
| 15° | 1276.6 |
| 17.5° | 1206.4 |
| 20° | 1124.4 |
| 22.5° | 1025.5 |
| 25° | 917.5 |
| 27.5° | 810.7 |
| 30° | 711.8 |
| 32.5° | 618.1 |
| 35° | 527.1 |
| 37.5° | 446.4 |
| 40° | 369.6 |
| 42.5° | 296.7 |
| 45° | 227.7 |
| 47.5° | 151.0 |
| 50° | 100.2 |
| 52.5° | 67.7 |
| 55° | 46.8 |
| 57.5° | 29.9 |
| 60° | 20.8 |
| 62.5° | 15.6 |
| 65° | 11.7 |
| 67.5° | 6.5 |
| 70° | 3.9 |
| 72.5° | 2.6 |
| 75° | 2.6 |
| 77.5° | 2.6 |
| 80° | 1.3 |
| 82.5° | 1.3 |
| 85° | 1.3 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)