

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: HALO

Report Number: P979210

Luminaire Tested: L820S10SP935XXXXBLSHBXXXX

Issue Date: 4/1/2025

Test Information

Test Method: LM-79-2019
Report Number: P979210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (3DTHCNLSLWHSTLFWHST15LRS30KWH)
Test Lab: INNOVATION CENTER
Issue Date: 4/1/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: L820S10SP935XXXXBLSHBXXXX
Description: 2IN Sustainable LED Track Luminaire with spot optic
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1033.9 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.22' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9
Total Harmonic Distortion (THDi): 20
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979210
CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	101	103	100	99	100	98	97	97	96	95	93
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90
4	104	99	95	92	103	98	94	91	96	93	90	94	91	89	92	90	88	87
5	101	95	91	88	100	94	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	88	84	82	87	83	81	86	83	81	80
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	83	81	79	78
9	91	84	80	78	90	84	80	77	83	80	77	82	79	77	82	79	77	76
10	89	82	78	75	88	82	78	75	81	78	75	80	77	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	1865212	1865212	1865212	1865212
5°	1552513	1702520	1663062	1519006
10°	632804	833503	768629	604820
15°	257173	312946	297503	248681
20°	153725	170463	168706	149836
25°	119063	125306	125306	117988
30°	86214	101000	96905	82557
35°	23729	39063	33181	19532
40°	3145	3640	3499	3075
45°	1953	2221	2297	1991
50°	1685	1853	1937	1769
55°	1558	1699	1794	1652
60°	1895	1895	1949	1895
65°	2306	2178	2370	2370
70°	2533	2770	2691	2454
75°	2301	2301	2197	2092
80°	2962	2806	2650	2650
85°	311	932	621	311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 52.5°
 Vertical Angle: 82.5°
 Luminance: 3111 cd/sqm



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	447.3	43.3
10°-20°	314.0	30.4
20°-30°	189.6	18.3
30°-40°	66.2	6.4
40°-50°	4.6	0.4
50°-60°	3.3	0.3
60°-70°	3.5	0.3
70°-80°	2.3	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.1	0.0
140°-150°	0.3	0.0
150°-160°	0.8	0.1
160°-170°	1.0	0.1
170°-180°	0.3	0.0
0°-30°	950.9	92.0
0°-40°	1017.0	98.4
0°-60°	1024.9	99.1
0°-90°	1031.4	99.8
90°-120°	0.0	0.0
90°-150°	0.3	0.0
90°-180°	2.0	0.2
0°-180°	1033.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	6890	6890	6890	6890	6890	
5°	5713	6265	6120	5590	5713	426
15°	918	1117	1062	887	918	287
25°	399	420	420	395	399	184
35°	72	118	100	59	72	59
45°	5	6	6	5	5	4
55°	3	4	4	4	3	3
65°	4	3	4	4	4	4
75°	2	2	2	2	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	2	2	2	2	2	1
165°	4	4	4	4	4	1
175°	3	4	3	3	3	0
180°	3	3	3	3	3	



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6620.8	6620.9	6621.3	6622.1	6623.2	6624.7	6626.7	6629.1	6631.9	6635.1	6638.8
5°	5713.0	5720.6	5729.9	5740.9	5753.5	5767.8	5783.6	5800.9	5819.6	5839.8	5861.3
7.5°	3961.7	3972.6	3986.1	4002.3	4021.0	4042.4	4066.5	4093.1	4122.4	4154.2	4188.7
10°	2302.0	2310.7	2321.6	2334.7	2350.0	2367.6	2387.4	2409.4	2433.7	2460.1	2488.9
12.5°	1371.1	1375.3	1380.5	1386.9	1394.4	1403.0	1412.8	1423.6	1435.7	1448.8	1463.1
15°	917.6	919.7	922.3	925.5	929.3	933.6	938.4	943.7	949.5	955.9	962.7
17.5°	673.5	674.9	676.5	678.5	680.8	683.4	686.3	689.5	693.1	697.0	701.2
20°	533.6	534.5	535.6	537.0	538.5	540.2	542.0	544.0	546.2	548.5	551.0
22.5°	453.4	453.6	454.0	454.4	455.0	455.8	456.6	457.6	458.8	460.1	461.4
25°	398.6	398.7	398.9	399.2	399.6	400.0	400.5	401.1	401.8	402.6	403.3
27.5°	361.4	361.6	361.9	362.3	362.7	363.1	363.7	364.2	364.8	365.5	366.0
30°	275.8	276.4	277.3	278.3	279.5	280.9	282.5	284.2	286.1	288.1	289.9
32.5°	171.8	172.4	173.2	174.1	175.3	176.6	178.2	180.0	182.0	184.3	186.1
35°	71.8	72.4	73.1	73.9	74.9	76.1	77.5	79.0	80.6	82.4	83.7
37.5°	13.6	13.7	13.9	14.2	14.5	14.9	15.3	15.9	16.4	17.1	17.5
40°	8.9	8.9	8.9	9.0	9.0	9.0	9.0	9.1	9.1	9.2	9.2
42.5°	6.2	6.2	6.2	6.3	6.3	6.3	6.3	6.4	6.4	6.5	6.5
45°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
47.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
50°	4.0	4.0	4.0	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
52.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5
55°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
57.5°	3.3	3.3	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.1
60°	3.5	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4
62.5°	3.6	3.5	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4
65°	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5
67.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3	3.3
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.6	2.6	2.6	2.6	2.6
75°	2.2	2.2	2.2	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
77.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
80°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
82.5°	1.2	1.2	1.2	1.2	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	1.0	1.0	1.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.3	1.3	1.3
155°	1.9	1.9	1.9	1.9	1.9	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.3	2.3	2.3
160°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
162.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
165°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
167.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
170°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
172.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.8
175°	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.0	3.0	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6643.0	6647.6	6652.8	6658.4	6664.6	6671.3	6678.6	6686.3	6704.2	6701.0	6700.4
5°	5884.1	5908.1	5933.4	5948.1	5957.1	6018.6	6005.7	5995.1	6004.9	6016.3	6029.5
7.5°	4225.8	4262.9	4278.0	4295.7	4315.7	4375.4	4362.5	4387.0	4413.3	4441.4	4471.1
10°	2519.8	2536.0	2550.6	2567.1	2630.6	2617.6	2628.9	2655.6	2683.9	2713.5	2744.4
12.5°	1475.9	1483.2	1491.2	1500.1	1526.7	1520.7	1533.1	1547.3	1562.2	1577.9	1594.3
15°	967.2	970.2	973.6	977.5	988.2	986.6	993.0	999.8	1006.8	1014.2	1020.6
17.5°	703.2	704.7	706.5	715.9	713.7	713.3	716.5	719.9	723.5	727.2	729.7
20°	551.5	552.2	553.0	557.9	556.5	556.6	558.6	560.8	563.0	565.4	566.8
22.5°	461.9	462.5	463.2	466.6	465.7	465.8	466.8	467.8	468.8	469.7	472.9
25°	403.5	403.7	404.0	405.8	405.1	405.2	405.8	406.4	407.1	407.8	410.1
27.5°	366.1	366.4	366.8	368.6	368.3	368.4	368.9	369.4	369.9	370.1	371.3
30°	291.0	292.3	293.6	298.1	297.4	298.5	300.3	302.3	304.4	305.6	309.6
32.5°	187.2	188.5	190.0	194.9	193.9	195.1	197.1	199.2	201.6	202.7	206.9
35°	84.4	85.2	86.1	89.8	88.7	89.8	91.5	93.2	95.1	96.0	99.7
37.5°	17.8	18.1	18.4	19.6	19.2	19.8	20.6	21.4	22.2	22.6	23.9
40°	9.2	9.3	9.3	9.4	9.4	9.4	9.5	9.6	9.6	9.6	9.7
42.5°	6.5	6.5	6.6	6.7	6.7	6.7	6.7	6.8	6.9	6.9	7.0
45°	5.1	5.1	5.1	5.1	5.1	5.1	5.2	5.2	5.2	5.2	5.2
47.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.6
50°	3.9	3.9	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.1
52.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.6	3.6
55°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
57.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
60°	3.4	3.4	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.4	3.4
62.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
65°	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2	3.2	3.2
72.5°	2.6	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
75°	2.1	2.1	2.1	2.1	2.0	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	2.0	2.0	2.0	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.8	1.8	1.8	1.9	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.3	1.3	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.5
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.7	1.7
157.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
160°	2.9	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
162.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2
165°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
167.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
170°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.8	3.8	3.8	3.8
172.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
175°	3.5	3.5	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3	3.3	3.3
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6705.1	6710.1	6715.4	6721.0	6726.8	6732.8	6754.2	6750.6	6750.8	6754.9	6759.5
5°	6044.4	6061.0	6079.4	6117.2	6120.1	6127.3	6132.5	6140.4	6151.0	6188.6	6176.9
7.5°	4502.4	4597.1	4564.4	4569.2	4584.2	4600.9	4619.1	4700.2	4659.8	4681.2	4703.6
10°	2776.4	2814.4	2810.7	2830.0	2849.1	2867.7	2885.9	2909.4	2924.7	2946.8	2968.7
12.5°	1628.9	1613.2	1626.0	1638.5	1650.7	1662.3	1691.2	1685.3	1699.1	1712.1	1722.6
15°	1033.7	1030.8	1037.6	1044.5	1051.2	1057.9	1068.0	1072.5	1080.9	1087.5	1092.8
17.5°	735.0	734.6	738.1	741.6	745.2	757.4	752.2	756.6	760.8	763.5	775.2
20°	569.6	570.1	572.1	574.2	576.2	582.4	580.3	582.4	584.1	585.3	590.3
22.5°	471.2	471.7	472.7	473.8	474.9	477.9	477.2	478.7	479.7	480.4	482.9
25°	409.1	409.8	410.6	411.4	412.1	413.7	413.4	414.4	415.0	415.6	417.3
27.5°	370.5	370.8	371.2	371.7	372.2	373.4	373.5	374.0	374.4	374.8	375.8
30°	307.7	308.6	309.7	310.8	312.1	314.8	314.9	315.8	315.9	316.3	317.8
32.5°	204.7	205.9	207.2	208.6	210.0	212.8	213.3	214.6	215.4	216.3	217.8
35°	98.1	99.4	100.7	102.1	103.5	105.9	106.7	108.0	109.1	110.2	111.6
37.5°	23.4	24.2	24.8	25.4	25.9	26.4	26.8	27.7	28.4	28.9	29.2
40°	9.7	9.8	9.8	9.8	9.9	9.9	10.0	10.0	10.0	10.1	10.1
42.5°	7.0	7.1	7.1	7.2	7.2	7.3	7.3	7.4	7.4	7.5	7.5
45°	5.3	5.3	5.3	5.4	5.4	5.4	5.5	5.5	5.5	5.6	5.6
47.5°	4.6	4.6	4.6	4.7	4.7	4.7	4.8	4.8	4.8	4.9	5.0
50°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.2	4.2	4.3	4.3
52.5°	3.6	3.6	3.7	3.7	3.8	3.8	3.8	3.8	3.9	3.9	3.9
55°	3.3	3.3	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5
57.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3	3.3
60°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
62.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5
65°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.2	3.2	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.4	3.4
72.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
75°	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.4	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.5	0.6	0.5
150°	0.9	0.9	0.9	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.3	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7
162.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
165°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5
167.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
170°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
172.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6764.5	6769.9	6775.8	6786.5	6782.6	6781.7	6781.2	6781.0	6781.2	6785.2	6783.0
5°	6186.4	6198.3	6212.5	6265.0	6247.0	6255.2	6248.0	6243.4	6265.9	6239.3	6241.4
7.5°	4726.9	4751.0	4769.8	4775.3	4784.1	4791.9	4854.8	4805.2	4817.8	4831.7	4846.6
10°	2985.6	3007.5	3015.7	3032.1	3047.1	3118.5	3072.9	3084.0	3092.3	3098.5	3131.3
12.5°	1752.0	1742.9	1754.3	1763.4	1770.1	1783.3	1783.4	1792.8	1802.2	1847.2	1820.7
15°	1101.5	1104.8	1111.2	1116.6	1137.2	1124.3	1129.5	1134.0	1138.9	1152.5	1147.5
17.5°	768.6	771.4	773.7	775.5	782.5	778.5	781.2	784.1	786.7	790.9	790.8
20°	587.7	589.3	590.6	591.7	594.5	593.3	594.6	596.1	597.4	598.4	599.1
22.5°	481.7	482.6	483.4	484.2	485.7	485.6	486.2	486.6	489.5	486.9	487.4
25°	417.1	418.0	418.8	419.5	420.3	420.4	420.5	420.4	421.7	420.3	420.6
27.5°	375.6	376.0	376.3	376.6	376.9	377.1	377.1	377.2	378.2	377.6	377.9
30°	317.4	318.0	318.8	323.1	320.9	321.3	321.0	320.8	322.4	320.6	320.6
32.5°	217.9	218.7	219.4	223.6	220.7	221.4	221.9	222.3	224.6	223.1	223.2
35°	112.4	113.5	114.4	118.2	116.0	116.7	117.2	117.7	119.4	118.7	119.2
37.5°	29.9	30.5	30.8	32.3	31.1	32.1	33.1	33.7	34.6	34.5	34.9
40°	10.2	10.2	10.3	10.3	10.3	10.4	10.4	10.4	10.5	10.5	10.6
42.5°	7.5	7.5	7.6	7.7	7.7	7.7	7.8	7.8	7.8	7.8	7.9
45°	5.6	5.7	5.7	5.8	5.8	5.9	5.9	5.9	6.0	6.0	6.0
47.5°	5.0	5.1	5.1	5.2	5.2	5.2	5.3	5.3	5.3	5.3	5.4
50°	4.3	4.4	4.4	4.4	4.5	4.5	4.5	4.6	4.6	4.7	4.7
52.5°	4.0	4.0	4.0	4.1	4.1	4.1	4.1	4.1	4.1	4.2	4.2
55°	3.5	3.5	3.5	3.6	3.6	3.6	3.7	3.7	3.7	3.7	3.8
57.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.4	3.4	3.4	3.4
60°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.6	3.6	3.6
62.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.6	3.6
65°	3.5	3.5	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.6
67.5°	3.8	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.8	3.8	3.8
70°	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
72.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.6	2.6	2.6	2.6	2.6
75°	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
85°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.4
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.6	1.7	1.6	1.6	1.6
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
165°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
167.5°	3.8	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.7	3.7	3.7
170°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
172.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6784.8	6787.0	6789.7	6801.4	6796.1	6792.3	6788.6	6785.0	6781.6	6778.7	6777.4
5°	6246.6	6255.0	6285.0	6275.2	6282.5	6279.0	6280.3	6286.7	6279.2	6275.3	6274.4
7.5°	4894.9	4862.2	4856.0	4850.5	4845.6	4844.5	4838.5	4833.1	4824.3	4879.7	4814.3
10°	3110.3	3120.8	3129.9	3137.5	3151.1	3134.6	3119.8	3109.8	3100.8	3094.6	3090.7
12.5°	1826.0	1827.7	1825.8	1837.9	1816.4	1815.9	1821.4	1826.3	1850.1	1826.4	1819.9
15°	1150.7	1151.7	1150.6	1150.2	1146.0	1147.5	1150.2	1151.3	1155.5	1149.6	1147.2
17.5°	791.7	791.7	799.2	788.9	789.1	792.1	794.2	805.2	796.0	796.5	796.7
20°	599.4	599.2	602.1	597.9	598.9	600.7	602.0	607.4	603.2	603.3	603.0
22.5°	487.6	487.7	489.6	487.8	488.9	490.0	490.9	493.8	491.7	491.7	491.5
25°	420.7	420.8	421.8	420.7	421.3	421.7	422.1	423.6	422.6	422.7	422.7
27.5°	378.1	378.2	378.7	378.4	378.6	378.8	379.0	379.8	379.2	379.2	379.2
30°	320.6	320.7	321.7	321.1	321.2	321.3	321.2	322.6	320.8	320.3	319.7
32.5°	223.3	223.3	223.9	223.2	223.1	223.0	222.7	223.6	221.8	221.4	220.9
35°	119.6	119.8	120.3	120.0	120.1	120.1	119.9	120.8	119.1	118.4	117.4
37.5°	35.0	34.8	34.5	35.2	35.8	36.1	36.2	36.5	35.8	35.6	35.1
40°	10.6	10.6	10.6	10.6	10.6	10.7	10.7	10.7	10.8	10.8	10.7
42.5°	7.9	8.0	7.9	8.0	8.0	8.1	8.1	8.2	8.2	8.2	8.2
45°	6.0	6.1	6.1	6.1	6.2	6.2	6.2	6.3	6.3	6.3	6.3
47.5°	5.4	5.4	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.6	5.6
50°	4.7	4.8	4.8	4.8	4.9	4.9	4.9	4.9	5.0	5.0	5.0
52.5°	4.2	4.2	4.2	4.3	4.3	4.3	4.4	4.4	4.4	4.4	4.4
55°	3.8	3.8	3.8	3.8	3.9	3.9	3.9	3.9	3.9	3.9	4.0
57.5°	3.4	3.5	3.5	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6
60°	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.5
62.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
65°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.7	3.7
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.5	3.5	3.5	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6
72.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
75°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
85°	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.7	0.8	0.8	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
152.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.2	2.2	2.2	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.2	3.2	3.2	3.2	3.2	3.1	3.2	3.1	3.1	3.1	3.1
165°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
167.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
170°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
172.5°	3.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5
177.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6776.4	6776.1	6776.4	6777.3	6770.8	6764.5	6758.6	6751.4	6747.0	6739.6	6732.8
5°	6302.9	6279.2	6265.1	6254.8	6247.7	6279.7	6247.0	6234.3	6224.9	6214.0	6201.3
7.5°	4818.9	4820.3	4818.2	4812.5	4846.3	4794.7	4780.8	4764.0	4743.9	4720.5	4693.3
10°	3089.8	3083.7	3072.5	3108.7	3057.5	3046.9	3034.2	3017.2	2995.8	2970.0	2939.8
12.5°	1810.2	1797.3	1781.2	1788.1	1770.1	1770.0	1766.4	1759.4	1749.1	1735.6	1722.8
15°	1143.0	1137.0	1132.0	1135.6	1128.9	1126.2	1122.1	1116.7	1109.9	1101.9	1097.2
17.5°	796.0	794.4	803.7	796.1	793.5	791.8	789.6	786.8	783.4	779.4	777.9
20°	602.4	601.5	606.1	602.5	602.2	602.0	601.4	600.4	599.0	597.3	596.8
22.5°	491.1	490.8	493.3	491.1	491.3	491.2	490.9	490.3	489.5	488.6	488.7
25°	422.6	422.5	423.9	422.6	422.7	422.7	422.6	422.4	422.0	421.6	421.9
27.5°	379.0	379.1	380.1	379.5	379.8	379.9	379.8	379.7	379.5	379.3	379.5
30°	319.2	319.0	320.8	318.7	318.3	317.9	317.3	316.6	315.7	315.1	315.1
32.5°	220.4	220.3	222.3	219.7	219.0	218.1	217.0	215.8	214.4	213.4	213.1
35°	116.3	115.9	117.2	115.0	114.5	113.8	112.9	111.7	110.4	109.4	109.0
37.5°	34.5	34.6	35.4	34.1	33.8	33.3	32.6	31.8	30.7	30.0	29.7
40°	10.7	10.7	10.7	10.6	10.6	10.6	10.5	10.5	10.4	10.4	10.4
42.5°	8.2	8.2	8.2	8.2	8.1	8.1	8.0	8.0	7.9	7.9	7.8
45°	6.3	6.3	6.4	6.3	6.4	6.4	6.4	6.3	6.3	6.3	6.3
47.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.5
50°	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8
52.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.3	4.3	4.3	4.3
55°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	3.9
57.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.5	3.5
60°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
62.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
65°	3.7	3.7	3.7	3.7	3.7	3.7	3.6	3.6	3.6	3.6	3.6
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.5
72.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5	2.5
75°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.1	2.1
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.4	1.4	1.4	1.4
85°	0.3	0.4	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
152.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.2	2.2	2.2	2.2	2.2
160°	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
165°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
167.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
170°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
172.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
175°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.3	3.3	3.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6726.7	6720.1	6717.6	6715.3	6713.8	6713.0	6713.1	6714.6	6716.4	6718.4	6720.7
5°	6186.5	6169.2	6187.6	6171.0	6154.1	6137.0	6119.8	6115.0	6110.2	6105.5	6100.8
7.5°	4664.0	4708.8	4671.5	4633.9	4596.1	4558.1	4520.1	4510.6	4501.1	4491.6	4482.2
10°	2925.7	2957.0	2925.0	2892.9	2860.7	2828.4	2796.1	2785.3	2774.6	2763.9	2753.2
12.5°	1718.1	1736.7	1717.2	1697.7	1678.1	1658.4	1638.8	1632.2	1625.6	1619.1	1612.5
15°	1095.0	1102.8	1094.6	1086.3	1078.1	1069.8	1061.5	1058.4	1055.2	1052.1	1048.9
17.5°	785.4	781.0	776.6	772.2	767.8	763.4	758.9	757.5	756.1	754.6	753.2
20°	600.9	598.4	595.8	593.3	590.7	588.1	585.6	585.0	584.4	583.8	583.2
22.5°	491.7	490.5	489.4	488.2	487.1	485.9	484.8	484.4	484.0	483.6	483.2
25°	424.1	423.3	422.6	421.8	421.0	420.3	419.5	419.3	419.1	418.9	418.8
27.5°	381.0	380.8	380.6	380.3	380.1	379.9	379.7	379.7	379.6	379.6	379.6
30°	318.4	317.0	315.6	314.2	312.8	311.4	310.0	309.8	309.6	309.3	309.1
32.5°	216.4	214.5	212.6	210.8	208.9	207.0	205.1	204.6	204.1	203.7	203.2
35°	111.8	109.9	108.0	106.1	104.2	102.3	100.4	99.7	99.1	98.5	97.9
37.5°	31.0	29.9	28.7	27.6	26.4	25.3	24.1	23.8	23.4	23.1	22.8
40°	10.4	10.3	10.2	10.2	10.1	10.0	9.9	9.9	9.9	9.8	9.8
42.5°	7.9	7.8	7.7	7.6	7.6	7.5	7.4	7.3	7.3	7.3	7.2
45°	6.3	6.2	6.2	6.1	6.1	6.0	6.0	5.9	5.9	5.9	5.8
47.5°	5.5	5.5	5.4	5.4	5.3	5.2	5.2	5.2	5.1	5.1	5.1
50°	4.8	4.8	4.8	4.7	4.7	4.7	4.6	4.6	4.6	4.6	4.6
52.5°	4.3	4.3	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.1	4.1
55°	3.9	3.9	3.9	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.6
57.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4
60°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
62.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
65°	3.6	3.6	3.6	3.6	3.6	3.6	3.7	3.6	3.6	3.6	3.6
67.5°	3.8	3.8	3.8	3.8	3.8	3.9	3.9	3.9	3.9	3.9	3.9
70°	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4
72.5°	2.6	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.0
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.8	1.8	1.8	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
85°	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.8
152.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.1	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.1	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2
165°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
167.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
170°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
172.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
175°	3.5	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4
177.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6722.5	6713.0	6707.2	6702.0	6697.4	6697.9	6684.4	6679.1	6674.9	6671.9	6664.5
5°	6044.9	6033.3	6018.5	6000.8	5980.7	5962.0	5956.5	5981.9	5908.4	5886.6	5864.5
7.5°	4472.8	4377.5	4364.6	4349.0	4328.6	4303.3	4273.3	4238.9	4251.6	4192.2	4170.7
10°	2742.6	2666.5	2637.4	2626.2	2611.2	2592.6	2570.4	2544.6	2517.7	2532.1	2478.4
12.5°	1606.0	1568.0	1550.7	1541.2	1533.4	1523.7	1512.2	1498.8	1483.8	1482.1	1457.3
15°	1045.8	1028.0	1019.7	1013.2	1009.2	1004.4	999.0	992.8	985.9	982.6	971.2
17.5°	751.7	750.3	737.3	733.0	730.6	727.7	724.5	720.8	716.8	713.8	715.2
20°	582.6	582.0	575.1	572.6	571.2	569.5	567.5	565.3	562.8	560.4	561.0
22.5°	482.8	482.4	478.2	476.7	475.6	474.5	473.2	471.8	470.2	468.5	468.8
25°	418.6	418.4	415.8	414.9	414.3	413.7	412.9	412.1	411.1	410.1	410.2
27.5°	379.6	379.6	377.6	377.0	376.4	375.8	375.1	374.4	373.6	372.8	372.9
30°	308.9	308.6	303.2	301.4	300.3	299.4	298.4	297.2	296.0	294.5	295.1
32.5°	202.7	202.2	196.3	194.1	192.7	191.8	190.7	189.3	187.8	186.0	186.4
35°	97.3	96.7	91.3	89.2	87.7	86.7	85.5	84.1	82.5	80.7	80.6
37.5°	22.4	22.1	20.1	19.3	18.8	18.5	18.2	17.8	17.2	16.6	16.6
40°	9.8	9.8	9.7	9.6	9.6	9.5	9.5	9.4	9.4	9.3	9.3
42.5°	7.2	7.1	7.0	6.9	6.8	6.8	6.8	6.7	6.7	6.6	6.6
45°	5.8	5.8	5.7	5.6	5.6	5.6	5.5	5.5	5.5	5.5	5.4
47.5°	5.1	5.1	5.0	5.0	5.0	4.9	4.9	4.9	4.8	4.8	4.8
50°	4.5	4.5	4.5	4.5	4.4	4.4	4.4	4.4	4.3	4.3	4.3
52.5°	4.1	4.1	4.0	4.0	4.0	4.0	4.0	3.9	3.9	3.9	3.8
55°	3.6	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.5
57.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
60°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
62.5°	3.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
65°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
67.5°	3.9	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.3	1.3	1.3	1.3	1.3	1.2	1.2	1.2	1.2	1.2	1.2
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.1	1.1	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.6	1.6	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.3
160°	2.7	2.7	2.7	2.7	2.7	2.8	2.8	2.8	2.8	2.8	2.8
162.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
165°	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
167.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
170°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
172.5°	3.7	3.7	3.7	3.7	3.7	3.6	3.6	3.6	3.6	3.6	3.6
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.1
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6658.3	6652.9	6648.3	6644.8	6635.5	6628.8	6623.0	6618.0	6613.8	6620.7	6598.6
5°	5842.5	5868.3	5808.1	5791.5	5775.9	5762.8	5737.3	5715.6	5696.1	5681.7	5693.6
7.5°	4145.9	4117.9	4087.2	4124.3	4022.1	4004.5	3984.5	3966.5	3946.9	3929.9	3911.7
10°	2465.8	2449.5	2429.8	2413.3	2389.5	2368.1	2349.5	2341.6	2336.9	2323.6	2312.7
12.5°	1452.6	1446.1	1437.8	1427.8	1432.4	1408.7	1397.5	1387.0	1384.1	1394.8	1378.0
15°	966.4	962.4	957.6	952.0	949.3	941.4	936.1	930.2	926.6	927.7	924.2
17.5°	703.9	701.7	699.0	695.8	692.6	696.6	686.5	683.0	679.0	676.5	681.0
20°	554.4	552.9	551.4	549.6	547.5	549.2	543.7	541.4	538.9	536.6	538.0
22.5°	465.3	464.1	463.2	462.1	461.0	461.5	458.4	457.0	455.5	454.1	454.7
25°	408.0	407.1	406.4	405.6	404.7	404.7	402.9	401.9	400.8	399.6	400.0
27.5°	370.6	369.6	368.8	368.0	367.3	367.4	364.9	363.6	362.5	361.5	361.4
30°	291.4	289.8	288.7	287.4	286.0	286.1	282.5	280.5	278.6	276.5	275.9
32.5°	182.3	180.4	179.4	178.3	177.0	177.1	173.7	171.7	169.6	167.2	166.0
35°	77.5	75.8	75.2	74.4	73.4	73.3	71.1	69.8	68.3	66.6	65.5
37.5°	15.8	15.4	15.3	15.0	14.7	14.5	14.3	14.0	13.7	13.2	12.7
40°	9.2	9.1	9.1	9.1	9.1	9.1	9.1	9.0	9.0	9.0	8.9
42.5°	6.5	6.5	6.5	6.5	6.4	6.4	6.4	6.4	6.4	6.4	6.3
45°	5.4	5.4	5.4	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
47.5°	4.7	4.7	4.7	4.7	4.7	4.6	4.6	4.6	4.6	4.6	4.5
50°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
52.5°	3.8	3.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.6	3.6
55°	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4
57.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
60°	3.6	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5
62.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
65°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.7	3.7	3.7	3.7
67.5°	3.9	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.7	3.7
70°	3.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.2	1.1	1.1	1.1	1.1	1.1	1.1	1.0	1.0	1.0	1.0
85°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.9	0.9	0.9
152.5°	1.2	1.2	1.2	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
160°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.9
162.5°	3.2	3.2	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
165°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
167.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
170°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
172.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
175°	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3
177.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6592.8	6588.1	6584.4	6587.8	6574.3	6569.6	6565.8	6562.9	6560.9	6565.4	6555.4
5°	5642.5	5622.9	5605.9	5591.4	5624.8	5571.4	5564.2	5558.8	5551.2	5589.7	5515.1
7.5°	3892.6	3902.7	3857.1	3844.3	3829.6	3813.0	3857.5	3781.2	3764.9	3748.4	3736.2
10°	2298.8	2282.1	2288.3	2248.3	2240.4	2233.6	2224.0	2261.2	2210.1	2200.2	2188.0
12.5°	1372.8	1365.7	1356.6	1371.0	1340.0	1334.9	1332.6	1336.0	1329.0	1326.6	1322.8
15°	921.8	918.2	913.6	914.8	903.2	897.1	893.7	890.9	900.7	887.3	884.6
17.5°	672.6	670.1	667.3	665.5	661.2	657.8	654.5	652.7	655.4	649.7	647.9
20°	533.4	531.7	530.0	528.1	526.6	524.9	523.2	522.1	522.7	520.1	518.9
22.5°	452.1	451.1	450.1	449.0	450.3	447.2	446.3	445.5	445.5	444.2	443.4
25°	399.0	398.7	398.3	397.8	398.5	396.9	396.5	395.9	395.6	395.0	394.5
27.5°	359.5	358.5	357.8	357.2	358.1	355.6	354.9	354.4	353.8	352.8	352.0
30°	273.5	272.0	270.6	269.2	269.8	265.8	264.1	262.4	261.1	264.1	259.3
32.5°	164.1	162.8	161.4	159.9	160.3	156.9	155.4	153.9	152.7	155.6	151.4
35°	64.7	64.1	63.2	62.2	62.2	60.2	59.0	57.8	56.9	59.1	56.6
37.5°	12.9	13.0	12.8	12.5	12.2	12.0	11.8	11.5	11.3	11.8	11.9
40°	8.9	8.9	8.8	8.8	8.8	8.7	8.7	8.6	8.6	8.7	8.6
42.5°	6.4	6.3	6.2	6.2	6.2	6.2	6.1	6.1	6.1	6.1	6.1
45°	5.4	5.3	5.3	5.3	5.3	5.3	5.2	5.2	5.2	5.2	5.2
47.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
50°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
52.5°	3.6	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
55°	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5
57.5°	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5
60°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
62.5°	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
65°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.8
67.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.6	3.6	3.6
70°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
72.5°	2.5	2.4	2.4	2.4	2.4	2.5	2.4	2.4	2.4	2.4	2.4
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.0	0.9	0.9	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.7
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.3	1.3	1.3	1.3	1.3	1.4	1.3	1.4	1.4	1.4	1.4
155°	1.8	1.8	1.8	1.8	1.8	1.9	1.8	1.9	1.9	1.9	1.9
157.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
160°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
162.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
165°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
167.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.8	3.8	3.8	3.8	3.8
170°	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7
172.5°	3.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2
177.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6551.8	6548.7	6546.1	6544.0	6542.4	6546.4	6555.7	6535.8	6535.2	6535.6	6536.9
5°	5501.2	5490.5	5482.9	5509.5	5470.1	5466.0	5463.8	5463.6	5463.0	5481.3	5454.2
7.5°	3719.0	3712.2	3705.5	3699.0	3692.7	3746.9	3687.3	3684.9	3683.0	3681.5	3689.0
10°	2181.1	2167.9	2161.8	2161.2	2158.8	2159.8	2155.8	2154.8	2152.7	2149.5	2145.5
12.5°	1317.6	1326.4	1309.5	1305.8	1305.3	1303.9	1315.8	1303.1	1302.3	1300.9	1299.1
15°	881.3	880.1	874.4	870.8	868.3	867.2	868.8	866.8	867.1	867.1	867.0
17.5°	645.8	643.5	648.0	639.8	637.8	637.8	637.7	644.3	639.1	639.6	639.8
20°	517.6	516.2	518.0	514.1	512.9	512.5	512.7	516.0	514.0	514.5	514.9
22.5°	442.6	441.9	442.6	440.9	440.4	440.1	440.3	442.1	440.7	440.9	441.0
25°	394.0	393.6	393.8	393.0	392.8	392.6	392.7	393.5	393.1	393.3	393.4
27.5°	351.5	351.2	351.9	350.1	349.6	349.3	348.8	349.6	347.8	347.5	347.5
30°	258.4	257.5	257.7	256.1	255.4	254.9	254.6	255.9	254.2	254.1	254.1
32.5°	150.8	150.2	150.4	149.1	148.6	148.1	147.6	148.5	147.4	147.4	147.5
35°	56.3	56.0	55.7	55.2	54.8	54.2	53.7	54.3	53.9	54.1	54.3
37.5°	12.0	11.9	11.6	11.6	11.5	11.4	11.3	11.6	11.8	12.0	12.0
40°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.5	8.5	8.5
42.5°	6.1	6.1	6.1	6.1	6.1	6.0	6.0	6.0	6.1	6.1	6.1
45°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
47.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.8	4.7	4.8	4.7	4.7
50°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
52.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
55°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
57.5°	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
60°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
62.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
65°	3.8	3.8	3.8	3.7	3.8	3.8	3.8	3.8	3.8	3.8	3.8
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
70°	3.0	3.0	3.0	3.0	2.9	2.9	2.8	2.8	2.8	2.8	2.7
72.5°	2.3	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.2	2.2	2.2
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	1.9	1.9	1.8	1.8	1.8	1.7	1.7	1.7	1.6	1.5	1.4
80°	1.6	1.6	1.5	1.5	1.4	1.4	1.3	1.3	1.2	1.2	1.1
82.5°	0.7	0.6	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4	0.4
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.7
150°	0.9	0.9	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
160°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	3.0	2.9	3.0
162.5°	3.3	3.4	3.4	3.4	3.4	3.3	3.4	3.3	3.3	3.3	3.3
165°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
167.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
170°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1
177.5°	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.9	2.9
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6539.2	6542.4	6546.4	6556.0	6568.1	6554.6	6551.8	6549.6	6548.2	6547.5	6547.5
5°	5453.0	5454.0	5457.2	5462.4	5469.7	5479.1	5516.2	5556.2	5501.6	5513.8	5522.2
7.5°	3740.8	3677.6	3677.6	3679.1	3682.2	3686.9	3693.3	3737.0	3710.0	3720.7	3733.2
10°	2158.3	2140.1	2142.2	2143.2	2143.9	2144.6	2145.4	2157.8	2189.5	2159.4	2165.7
12.5°	1296.9	1314.8	1297.7	1298.6	1299.3	1299.9	1300.4	1301.6	1317.3	1306.3	1309.4
15°	866.7	873.5	867.5	868.5	869.7	870.8	871.9	873.1	880.8	877.4	879.9
17.5°	640.0	642.8	640.7	641.2	642.1	642.9	643.8	644.7	648.6	654.0	649.5
20°	515.2	516.6	516.2	516.8	517.4	517.9	518.4	518.9	520.8	523.8	520.8
22.5°	441.2	441.8	444.3	442.3	442.5	442.6	442.8	443.1	444.1	446.0	444.5
25°	393.5	393.8	395.1	393.8	393.9	393.9	394.0	394.0	394.5	395.6	394.6
27.5°	347.7	348.2	351.0	348.7	349.0	348.8	348.8	349.1	350.2	352.4	350.5
30°	254.2	254.4	258.0	255.1	255.5	255.6	255.9	256.2	257.5	260.8	258.4
32.5°	147.7	147.9	151.3	148.7	149.2	149.6	150.1	150.7	152.0	155.4	153.3
35°	54.4	54.5	56.9	55.0	55.1	55.3	55.6	56.0	56.7	59.4	57.9
37.5°	11.9	11.6	11.7	11.5	11.5	11.7	11.9	11.9	11.9	12.1	12.0
40°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.6	8.5
42.5°	6.1	6.1	6.1	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
45°	5.2	5.2	5.2	5.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1
47.5°	4.7	4.7	4.7	4.7	4.6	4.6	4.6	4.6	4.6	4.6	4.6
50°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.1	4.1	4.1
52.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
55°	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
57.5°	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.5	3.4	3.4
60°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
62.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
65°	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.7	3.8	3.8	3.7
67.5°	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.6	3.6	3.6
70°	2.7	2.7	2.7	2.7	2.7	2.7	2.8	2.8	2.8	2.9	2.9
72.5°	2.2	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
75°	2.0	2.0	2.0	2.0	2.1	2.1	2.1	2.0	2.0	2.0	2.0
77.5°	1.3	1.2	1.1	1.0	0.9	0.9	0.9	1.0	1.1	1.1	1.2
80°	1.1	1.1	1.0	1.0	1.0	1.0	1.1	1.1	1.2	1.2	1.3
82.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.4	2.5	2.5	2.4	2.5	2.4	2.4	2.4	2.4	2.4	2.4
160°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.9
162.5°	3.3	3.3	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3
165°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
167.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
170°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2
177.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9	6889.9
2.5°	6548.3	6549.7	6551.7	6554.3	6557.6	6561.3	6565.7	6570.5	6575.8	6581.6	6587.7
5°	5523.6	5527.4	5533.6	5542.2	5553.0	5566.0	5581.1	5598.3	5617.5	5638.7	5661.7
7.5°	3747.5	3752.7	3759.0	3767.7	3778.7	3792.2	3808.1	3826.6	3847.5	3871.1	3897.3
10°	2172.7	2179.6	2183.2	2188.0	2194.2	2201.8	2210.9	2221.6	2234.1	2248.4	2264.7
12.5°	1312.9	1316.7	1318.5	1319.9	1322.0	1324.7	1328.3	1332.6	1337.8	1343.9	1351.0
15°	882.6	885.5	887.6	888.6	890.0	891.9	894.2	897.0	900.2	904.0	908.2
17.5°	651.4	653.5	655.3	655.9	656.7	657.8	659.0	660.5	662.2	664.2	666.4
20°	521.5	522.3	523.1	523.4	523.7	524.2	524.8	525.6	526.6	527.8	529.1
22.5°	445.1	445.8	446.5	446.7	446.9	447.1	447.5	448.0	448.5	449.1	449.9
25°	394.9	395.2	395.5	395.7	395.8	396.0	396.3	396.6	397.0	397.4	397.9
27.5°	351.2	352.1	353.2	353.6	353.9	354.3	355.0	355.7	356.7	357.7	358.9
30°	259.5	260.7	262.1	262.9	263.5	264.3	265.3	266.4	267.7	269.2	270.9
32.5°	154.5	155.8	157.3	158.3	159.1	160.1	161.2	162.5	164.1	165.8	167.7
35°	58.7	59.6	60.5	61.3	61.8	62.5	63.3	64.2	65.3	66.5	67.9
37.5°	12.0	12.0	12.0	12.1	12.2	12.3	12.5	12.5	12.7	12.8	12.9
40°	8.5	8.5	8.5	8.5	8.6	8.6	8.6	8.6	8.7	8.7	8.8
42.5°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.1	6.1
45°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
47.5°	4.6	4.6	4.6	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
50°	4.1	4.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
52.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.6
55°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3
57.5°	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
60°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
62.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
65°	3.7	3.7	3.8	3.8	3.7	3.7	3.7	3.7	3.7	3.6	3.6
67.5°	3.6	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
70°	2.9	3.0	3.0	3.0	3.0	3.0	3.0	3.1	3.1	3.1	3.1
72.5°	2.3	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.4	2.4	2.4
75°	2.0	2.0	1.9	1.9	2.0	2.0	2.0	2.0	2.1	2.1	2.1
77.5°	1.3	1.4	1.5	1.6	1.6	1.7	1.7	1.8	1.8	1.9	1.9
80°	1.3	1.4	1.5	1.5	1.5	1.6	1.6	1.7	1.7	1.7	1.8
82.5°	0.6	0.6	0.6	0.6	0.7	0.7	0.8	0.9	0.9	1.0	1.0
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979210
 CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
160°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
162.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
165°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
167.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
170°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.8	3.8	3.8
172.5°	3.5	3.5	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3
177.5°	2.9	2.9	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.9	2.9
180°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8



TEST NUMBER: P979210
CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	6889.9	6889.9
2.5°	6594.3	6620.8
5°	5686.5	5713.0
7.5°	3926.1	3961.7
10°	2283.0	2302.0
12.5°	1359.1	1371.1
15°	913.0	917.6
17.5°	669.0	673.5
20°	530.7	533.6
22.5°	450.8	453.4
25°	398.5	398.6
27.5°	360.2	361.4
30°	272.8	275.8
32.5°	169.7	171.8
35°	69.4	71.8
37.5°	13.1	13.6
40°	8.8	8.9
42.5°	6.1	6.2
45°	5.1	5.1
47.5°	4.5	4.5
50°	4.0	4.0
52.5°	3.6	3.6
55°	3.3	3.3
57.5°	3.3	3.3
60°	3.4	3.5
62.5°	3.5	3.6
65°	3.6	3.6
67.5°	3.7	3.7
70°	3.2	3.2
72.5°	2.4	2.5
75°	2.1	2.2
77.5°	2.0	2.0
80°	1.8	1.9
82.5°	1.1	1.2
85°	0.1	0.1
87.5°	0.1	0.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



TEST NUMBER: P979210
CATALOG NUMBER: L820S10SP935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.1	0.1
135°	0.1	0.1
137.5°	0.1	0.1
140°	0.2	0.2
142.5°	0.3	0.3
145°	0.5	0.4
147.5°	0.7	0.6
150°	1.0	0.9
152.5°	1.4	1.4
155°	1.9	1.9
157.5°	2.4	2.4
160°	2.9	2.9
162.5°	3.3	3.3
165°	3.6	3.6
167.5°	3.8	3.8
170°	3.8	3.8
172.5°	3.6	3.7
175°	3.3	3.4
177.5°	3.0	3.0
180°	2.8	2.8

(END OF REPORT)