

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P644068

Luminaire Tested: ML5615LSWFL559FS1E - 696WB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P644068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-69)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSWFL559FS1E - 696WB - 1200LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 6" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1516.6 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P644068
CATALOG NUMBER: ML5615LSWFL559FS1E - 696WB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P644068

CATALOG NUMBER: ML5615LSWFL559FS1E - 696WB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93															
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85															
3	101	94	89	84	99	93	88	84	90	86	82	88	84	81	85	82	80	78				78															
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72				72															
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66															
6	85	76	69	65	84	75	69	64	73	68	64	72	67	63	70	66	63	61				61															
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57				57															
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53				53															
9	72	62	56	52	71	62	56	51	61	55	51	60	55	51	59	54	51	49				49															
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87060
5°	83128
10°	78806
15°	74427
20°	67381
25°	57003
30°	46286
35°	36232
40°	27165
45°	18134
50°	8776
55°	4597
60°	2346
65°	1557
70°	641
75°	572
80°	410
85°	818

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18134 cd/sqm



TEST NUMBER: P644068

CATALOG NUMBER: ML5615LSWFL559FS1E - 696WB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.4	9.3
10°-20°	365.1	24.1
20°-30°	430.6	28.4
30°-40°	339.7	22.4
40°-50°	178.0	11.7
50°-60°	46.5	3.1
60°-70°	11.6	0.8
70°-80°	2.8	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	937.1	61.8
0°-40°	1276.7	84.2
0°-60°	1501.3	99.0
0°-90°	1516.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1516.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1588	
5°	1511	141
15°	1311	365
25°	942	431
35°	541	340
45°	234	178
55°	48	47
65°	12	12
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P644068

CATALOG NUMBER: ML5615LSWFL559FS1E - 696WB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1588.1
2.5°	1568.0
5°	1510.6
7.5°	1461.1
10°	1415.7
12.5°	1368.9
15°	1311.4
17.5°	1239.2
20°	1155.0
22.5°	1053.4
25°	942.4
27.5°	832.8
30°	731.2
32.5°	635.0
35°	541.4
37.5°	458.5
40°	379.6
42.5°	304.8
45°	233.9
47.5°	155.1
50°	102.9
52.5°	69.5
55°	48.1
57.5°	30.7
60°	21.4
62.5°	16.0
65°	12.0
67.5°	6.7
70°	4.0
72.5°	2.7
75°	2.7
77.5°	2.7
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)