

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P837146

Luminaire Tested: **L830S10FL930**

Issue Date: 5/17/2024



Test Information

Test Method: LM-79-08
Report Number: P837146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (1529-C)
Test Lab: INNOVATION CENTER
Issue Date: 5/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L830S10FL930
Description: Sustainable LED Track Luminaire with Flood Optic and, 3000K, 90CRI LEDs
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 965.9 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.63
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P837146
CATALOG NUMBER: L830S10FL930

Luminous Intensity Polar Plot





TEST NUMBER: P837146
 CATALOG NUMBER: L830S10FL930

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	105	100	96	92	103	99	95	92	96	93	90	94	91	89	92	89	87	86		
4	101	95	90	87	100	94	89	86	92	88	85	90	87	84	88	85	83	82		
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78		
6	93	86	81	77	92	85	81	77	84	80	77	83	79	76	81	78	76	74		
7	90	82	77	74	89	82	77	73	80	76	73	79	75	73	78	75	72	71		
8	87	79	74	70	85	78	73	70	77	73	70	76	72	69	75	72	69	68		
9	83	75	70	67	82	75	70	67	74	70	67	73	69	66	72	69	66	65		
10	80	72	67	64	79	72	67	64	71	67	64	70	66	64	70	66	64	62		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	362082
5°	341212
10°	290486
15°	216957
20°	168598
25°	118583
30°	72848
35°	21929
40°	4837
45°	1937
50°	1253
55°	955
60°	709
65°	457
70°	330
75°	311
80°	186
85°	0



TEST NUMBER: P837146
 CATALOG NUMBER: L830S10FL930

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.9	19.8
10°-20°	367.0	38.0
20°-30°	305.8	31.7
30°-40°	89.3	9.2
40°-50°	8.1	0.8
50°-60°	3.1	0.3
60°-70°	1.3	0.1
70°-80°	0.5	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	863.6	89.4
0°-40°	952.9	98.7
0°-60°	964.1	99.8
0°-90°	965.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	965.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2248	
5°	2110	191
15°	1301	367
25°	667	306
35°	112	89
45°	8	8
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	



TEST NUMBER: P837146
CATALOG NUMBER: L830S10FL930

CANDELA DISTRIBUTION (FULL):

	0°
0°	2247.5
2.5°	2212.9
5°	2109.9
7.5°	1965.2
10°	1775.7
12.5°	1534.4
15°	1300.8
17.5°	1126.7
20°	983.4
22.5°	830.9
25°	667.1
27.5°	526.8
30°	391.6
32.5°	237.7
35°	111.5
37.5°	41.8
40°	23.0
42.5°	14.0
45°	8.5
47.5°	6.3
50°	5.0
52.5°	4.1
55°	3.4
57.5°	2.8
60°	2.2
62.5°	1.6
65°	1.2
67.5°	0.9
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.3
80°	0.2
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0



TEST NUMBER: P837146
CATALOG NUMBER: L830S10FL930

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







107.5°		0.0
110°		0.0



(END OF REPORT)