

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P272216

Luminaire Tested: **LA56069301EWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P272216
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A1805269A001)
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: LA56069301EWH
Description: HALO LA 5/6 INCH LED LUMINAIRE
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 636.8 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.27
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8.692
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P272216
CATALOG NUMBER: LA56069301EWH

Luminous Intensity Polar Plot





TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	94	96	94	92	92	91	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	76	71	91	82	75	70	79	74	69	77	72	68	74	70	66	64
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56
5	79	68	59	53	77	66	59	53	64	58	52	62	56	52	61	55	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	69	56	48	42	67	55	47	42	54	46	41	52	46	41	51	45	41	39
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	59	47	39	34	45	39	34	44	38	34	43	38	33	32
10	56	44	36	31	55	43	36	31	42	35	31	41	35	31	40	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15470	15470	15470	15470
5°	15480	15518	15425	15386
10°	15436	15520	15336	15258
15°	15346	15477	15193	15068
20°	15203	15390	14987	14795
25°	14959	15225	14668	14390
30°	14585	14939	14217	13850
35°	14061	14509	13605	13137
40°	13354	13905	12795	12244
45°	12443	13102	11784	11133
50°	11317	12076	10524	9816
55°	10026	10838	9185	8449
60°	8716	9528	7883	7149
65°	7498	8302	6667	5954
70°	6379	7197	5177	4776
75°	4639	6164	3156	3537
80°	2336	5114	1357	2084
85°	503	3900	252	440



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.7	4.2
10°-20°	75.9	11.9
20°-30°	112.6	17.7
30°-40°	128.9	20.2
40°-50°	120.2	18.9
50°-60°	90.2	14.2
60°-70°	54.6	8.6
70°-80°	23.4	3.7
80°-90°	3.6	0.6
90°-100°	0.1	0.0
100°-110°	0.1	0.0
110°-120°	0.1	0.0
120°-130°	0.1	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	215.1	33.8
0°-40°	344.0	54.0
0°-60°	554.4	87.1
0°-90°	636.0	99.9
90°-120°	0.3	0.0
90°-150°	0.6	0.1
90°-180°	1.0	0.2
0°-180°	636.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	282	282	282	282	282	
5°	281	282	280	280	281	27
15°	270	273	268	266	270	76
25°	247	252	242	238	247	114
35°	210	217	203	196	210	131
45°	160	169	152	144	160	123
55°	105	113	96	88	105	94
65°	58	64	51	46	58	58
75°	22	29	15	17	22	24
85°	1	6	0	1	1	2
90°	0	1	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	282.2	282.2	282.2	282.2	282.2	282.2	282.2	282.2	282.2	282.2	282.2
0.5°	282.2	282.4	282.3	282.4	282.4	282.3	282.3	282.2	282.1	282.2	282.1
1°	282.3	282.4	282.4	282.4	282.5	282.4	282.3	282.2	282.0	282.1	282.0
1.5°	282.2	282.4	282.4	282.5	282.4	282.3	282.3	282.1	281.9	281.9	281.8
2°	282.2	282.4	282.5	282.5	282.5	282.3	282.2	282.0	281.8	281.7	281.6
2.5°	282.1	282.4	282.4	282.5	282.4	282.2	282.2	281.8	281.6	281.5	281.3
3°	282.0	282.3	282.4	282.4	282.4	282.2	282.0	281.6	281.4	281.2	281.1
3.5°	281.8	282.2	282.3	282.4	282.3	282.1	281.9	281.5	281.1	280.9	280.7
4°	281.7	282.0	282.2	282.3	282.3	282.0	281.7	281.3	280.9	280.6	280.4
4.5°	281.4	281.8	282.1	282.1	282.1	281.8	281.5	281.0	280.6	280.4	280.0
5°	281.3	281.7	281.9	282.0	282.0	281.6	281.2	280.7	280.3	279.9	279.7
5.5°	280.9	281.5	281.6	281.8	281.8	281.4	281.0	280.5	279.9	279.6	279.3
6°	280.7	281.2	281.5	281.5	281.6	281.1	280.7	280.1	279.5	279.2	278.8
6.5°	280.3	280.9	281.1	281.3	281.3	280.9	280.4	279.8	279.1	278.7	278.4
7°	280.0	280.6	280.9	281.0	281.0	280.6	279.9	279.3	278.7	278.2	277.9
7.5°	279.6	280.2	280.5	280.7	280.7	280.2	279.6	278.9	278.2	277.7	277.3
8°	279.2	279.9	280.2	280.3	280.3	279.8	279.2	278.4	277.7	277.2	276.8
8.5°	278.8	279.5	279.8	279.9	280.0	279.4	278.8	277.9	277.2	276.6	276.2
9°	278.4	279.1	279.5	279.6	279.6	278.9	278.3	277.4	276.7	276.0	275.6
9.5°	277.8	278.6	279.0	279.2	279.2	278.5	277.8	276.9	276.1	275.4	274.9
10°	277.3	278.1	278.6	278.7	278.8	278.0	277.3	276.3	275.5	274.7	274.2
10.5°	276.7	277.6	278.0	278.3	278.2	277.5	276.7	275.7	274.9	274.1	273.5
11°	276.1	277.1	277.6	277.8	277.7	277.0	276.2	275.0	274.2	273.3	272.8
11.5°	275.6	276.5	276.9	277.2	277.2	276.4	275.5	274.4	273.5	272.6	272.0
12°	274.9	275.9	276.5	276.7	276.7	275.8	274.9	273.7	272.7	271.8	271.2
12.5°	274.2	275.2	275.8	276.0	276.0	275.3	274.3	273.0	272.0	271.1	270.4
13°	273.6	274.7	275.3	275.4	275.4	274.6	273.6	272.3	271.2	270.2	269.5
13.5°	272.7	273.9	274.6	274.7	274.8	273.9	272.8	271.6	270.4	269.4	268.6
14°	272.1	273.3	274.0	274.1	274.2	273.2	272.1	270.7	269.5	268.5	267.7
14.5°	271.2	272.5	273.2	273.4	273.4	272.5	271.3	270.0	268.7	267.5	266.7
15°	270.4	271.7	272.5	272.7	272.7	271.7	270.5	269.0	267.7	266.6	265.7
15.5°	269.5	270.9	271.7	271.9	272.0	270.9	269.6	268.2	266.8	265.7	264.7
16°	268.7	270.1	270.9	271.1	271.2	270.1	268.8	267.2	265.8	264.6	263.7
16.5°	267.8	269.2	270.0	270.3	270.3	269.2	267.8	266.3	264.8	263.5	262.6
17°	266.9	268.3	269.2	269.5	269.5	268.3	267.0	265.3	263.8	262.5	261.5
17.5°	265.9	267.3	268.3	268.6	268.7	267.4	266.0	264.3	262.7	261.3	260.3
18°	264.9	266.5	267.4	267.7	267.7	266.4	265.0	263.2	261.6	260.1	259.2
18.5°	263.8	265.5	266.4	266.7	266.8	265.5	263.9	262.2	260.5	259.0	257.9
19°	262.9	264.5	265.5	265.8	265.9	264.5	262.9	261.0	259.3	257.7	256.7
19.5°	261.7	263.4	264.4	264.8	264.9	263.5	261.8	260.0	258.1	256.5	255.3
20°	260.6	262.3	263.4	263.8	263.8	262.4	260.8	258.7	256.9	255.2	254.0
20.5°	259.4	261.1	262.3	262.7	262.7	261.3	259.6	257.5	255.6	253.9	252.6
21°	258.2	260.0	261.2	261.6	261.7	260.1	258.4	256.2	254.3	252.5	251.3
21.5°	256.9	258.8	260.0	260.5	260.6	259.0	257.1	255.0	253.0	251.0	249.8
22°	255.7	257.6	258.9	259.4	259.4	257.7	256.0	253.6	251.5	249.6	248.4



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	254.3	256.4	257.6	258.1	258.2	256.6	254.6	252.3	250.2	248.2	246.7
23°	253.0	255.1	256.4	257.0	257.0	255.2	253.3	250.9	248.7	246.7	245.2
23.5°	251.6	253.8	255.1	255.6	255.7	254.0	251.9	249.5	247.2	245.1	243.6
24°	250.2	252.3	253.8	254.4	254.4	252.6	250.6	248.0	245.6	243.5	242.1
24.5°	248.7	251.0	252.3	253.0	253.1	251.3	249.1	246.5	244.1	241.9	240.3
25°	247.3	249.5	251.0	251.7	251.7	249.8	247.7	244.9	242.5	240.2	238.7
25.5°	245.7	248.0	249.6	250.3	250.2	248.5	246.2	243.4	240.9	238.6	236.9
26°	244.2	246.4	248.1	248.8	248.8	246.9	244.7	241.8	239.2	236.9	235.2
26.5°	242.5	245.0	246.6	247.2	247.4	245.4	243.1	240.2	237.5	235.1	233.3
27°	241.0	243.4	245.1	245.8	245.9	243.9	241.4	238.5	235.8	233.2	231.6
27.5°	239.3	241.7	243.4	244.2	244.3	242.3	239.8	236.8	234.0	231.4	229.5
28°	237.5	240.1	241.9	242.7	242.7	240.6	238.1	235.0	232.2	229.5	227.8
28.5°	235.8	238.4	240.2	241.0	241.1	239.0	236.4	233.2	230.3	227.6	225.7
29°	234.1	236.7	238.5	239.3	239.4	237.2	234.6	231.4	228.4	225.7	223.8
29.5°	232.2	235.0	236.8	237.6	237.8	235.5	232.8	229.5	226.5	223.7	221.7
30°	230.4	233.1	235.0	235.9	236.0	233.8	231.0	227.7	224.6	221.7	219.7
30.5°	228.4	231.4	233.3	234.1	234.2	232.0	229.1	225.8	222.6	219.6	217.6
31°	226.6	229.4	231.5	232.3	232.5	230.1	227.3	223.8	220.6	217.6	215.5
31.5°	224.6	227.6	229.6	230.4	230.7	228.2	225.4	221.8	218.5	215.5	213.3
32°	222.7	225.6	227.8	228.6	228.7	226.3	223.4	219.8	216.5	213.3	211.2
32.5°	220.6	223.7	225.8	226.7	226.8	224.4	221.4	217.7	214.3	211.1	208.8
33°	218.6	221.7	223.9	224.8	224.9	222.4	219.4	215.7	212.2	209.0	206.7
33.5°	216.5	219.6	221.9	222.7	222.9	220.4	217.3	213.6	210.0	206.7	204.3
34°	214.4	217.6	219.9	220.8	220.8	218.3	215.3	211.4	207.8	204.5	202.1
34.5°	212.2	215.5	217.8	218.7	218.8	216.3	213.1	209.2	205.5	202.1	199.7
35°	210.1	213.3	215.8	216.7	216.8	214.1	211.0	207.0	203.3	199.8	197.4
35.5°	207.8	211.2	213.6	214.4	214.6	212.0	208.7	204.7	200.9	197.5	194.9
36°	205.6	209.0	211.5	212.4	212.5	209.9	206.6	202.5	198.6	195.1	192.6
36.5°	203.3	206.8	209.3	210.2	210.4	207.7	204.4	200.2	196.2	192.6	190.0
37°	201.0	204.5	207.2	208.0	208.2	205.4	202.1	197.8	193.8	190.1	187.6
37.5°	198.7	202.3	204.8	205.8	206.0	203.2	199.7	195.5	191.3	187.7	185.0
38°	196.3	200.0	202.6	203.5	203.6	200.9	197.4	193.0	188.9	185.2	182.6
38.5°	194.0	197.7	200.3	201.2	201.3	198.6	195.0	190.6	186.4	182.6	180.0
39°	191.5	195.2	198.0	198.9	199.1	196.2	192.6	188.2	183.9	180.1	177.5
39.5°	189.1	192.9	195.6	196.5	196.7	193.8	190.2	185.7	181.4	177.5	174.8
40°	186.6	190.4	193.2	194.2	194.3	191.4	187.7	183.2	178.8	174.9	172.2
40.5°	184.1	188.0	190.8	191.7	191.9	189.0	185.3	180.6	176.2	172.3	169.5
41°	181.5	185.5	188.3	189.3	189.4	186.5	182.7	178.1	173.6	169.6	166.9
41.5°	179.0	183.1	185.9	186.8	187.0	184.0	180.2	175.5	171.0	167.0	164.2
42°	176.4	180.6	183.4	184.4	184.6	181.5	177.6	172.9	168.3	164.3	161.5
42.5°	173.9	177.9	180.8	181.9	182.0	179.0	175.1	170.3	165.7	161.6	158.7
43°	171.2	175.4	178.3	179.3	179.4	176.4	172.5	167.6	163.0	158.9	156.0
43.5°	168.5	172.8	175.7	176.7	176.9	173.8	169.8	164.9	160.2	156.1	153.2
44°	165.9	170.2	173.1	174.2	174.4	171.3	167.2	162.3	157.5	153.3	150.4
44.5°	163.2	167.6	170.5	171.5	171.7	168.6	164.5	159.5	154.8	150.6	147.5



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	160.5	164.9	167.9	168.9	169.0	165.9	161.7	156.8	152.0	147.7	144.8
45.5°	157.8	162.2	165.2	166.2	166.4	163.2	159.1	154.0	149.2	145.0	142.0
46°	155.0	159.5	162.5	163.6	163.8	160.6	156.3	151.2	146.5	142.2	139.2
46.5°	152.3	156.8	159.8	160.8	161.0	157.8	153.6	148.5	143.7	139.4	136.4
47°	149.5	154.1	157.1	158.1	158.3	155.0	150.8	145.7	140.8	136.5	133.5
47.5°	146.8	151.3	154.3	155.4	155.5	152.3	147.9	142.9	137.9	133.7	130.6
48°	144.0	148.5	151.6	152.7	152.9	149.5	145.2	140.0	135.1	130.8	127.7
48.5°	141.2	145.7	148.8	149.9	150.0	146.7	142.4	137.2	132.3	128.0	124.8
49°	138.3	143.0	146.0	147.1	147.2	143.9	139.6	134.4	129.3	125.1	122.0
49.5°	135.6	140.1	143.2	144.3	144.5	141.2	136.8	131.6	126.4	122.2	119.1
50°	132.7	137.4	140.4	141.5	141.6	138.3	133.9	128.7	123.4	119.3	116.3
50.5°	129.9	134.5	137.6	138.6	138.8	135.5	131.0	125.9	120.5	116.5	113.5
51°	127.1	131.7	134.7	135.8	136.0	132.7	128.1	123.0	117.9	113.7	110.7
51.5°	124.3	128.8	131.9	132.9	133.2	129.8	125.3	120.1	115.1	110.9	107.9
52°	121.4	126.1	129.1	130.1	130.3	126.9	122.4	117.2	112.3	108.1	105.1
52.5°	118.6	123.2	126.3	127.3	127.5	124.1	119.6	114.4	109.5	105.4	102.5
53°	115.8	120.4	123.4	124.5	124.6	121.2	116.7	111.6	106.8	102.7	99.8
53.5°	113.0	117.6	120.6	121.6	121.8	118.4	113.9	108.9	104.0	100.0	97.1
54°	110.3	114.9	117.8	118.8	118.9	115.5	111.2	106.1	101.3	97.4	94.6
54.5°	107.6	112.0	115.0	116.0	116.1	112.8	108.3	103.4	98.7	94.7	91.9
55°	104.9	109.3	112.2	113.2	113.4	110.0	105.6	100.7	96.1	92.2	89.4
55.5°	102.2	106.6	109.5	110.4	110.6	107.3	102.9	98.1	93.5	89.6	86.9
56°	99.4	103.9	106.8	107.7	107.9	104.6	100.3	95.5	90.9	87.1	84.5
56.5°	96.9	101.1	104.1	104.9	105.1	101.9	97.7	92.9	88.4	84.6	82.1
57°	94.3	98.6	101.4	102.3	102.4	99.2	95.0	90.3	85.9	82.2	79.6
57.5°	91.8	96.0	98.7	99.6	99.7	96.6	92.4	87.8	83.5	79.8	77.3
58°	89.1	93.3	96.1	97.0	97.1	94.0	89.9	85.4	81.1	77.5	75.0
58.5°	86.7	90.8	93.5	94.3	94.5	91.4	87.4	82.9	78.7	75.2	72.7
59°	84.2	88.3	91.0	91.8	91.9	88.9	84.9	80.6	76.4	72.9	70.5
59.5°	81.9	85.9	88.5	89.2	89.4	86.4	82.5	78.2	74.1	70.7	68.3
60°	79.5	83.4	86.0	86.8	86.9	84.0	80.1	75.8	71.9	68.4	66.1
60.5°	77.1	81.0	83.6	84.3	84.4	81.5	77.8	73.5	69.6	66.3	64.0
61°	74.8	78.6	81.2	81.9	82.0	79.2	75.5	71.3	67.4	64.2	61.9
61.5°	72.6	76.3	78.8	79.4	79.6	76.8	73.2	69.0	65.3	62.1	59.9
62°	70.3	74.1	76.4	77.2	77.3	74.6	71.0	66.9	63.2	60.1	57.9
62.5°	68.2	71.8	74.1	74.9	75.0	72.3	68.8	64.7	61.2	58.1	55.9
63°	66.0	69.5	71.9	72.6	72.7	70.1	66.6	62.5	59.1	56.1	54.0
63.5°	63.9	67.5	69.7	70.4	70.5	67.9	64.5	60.5	57.1	54.2	52.1
64°	61.9	65.3	67.6	68.2	68.3	65.7	62.4	58.4	55.1	52.2	50.2
64.5°	59.8	63.2	65.4	66.0	66.2	63.6	60.4	56.4	53.2	50.4	48.3
65°	57.8	61.1	63.3	64.0	64.0	61.6	58.4	54.4	51.4	48.6	46.6
65.5°	55.7	59.1	61.2	61.8	62.0	59.6	56.4	52.4	49.5	46.8	44.8
66°	53.8	57.1	59.2	59.8	59.9	57.6	54.4	50.5	47.7	45.0	43.1
66.5°	52.0	55.3	57.2	57.8	57.9	55.6	52.5	48.6	45.9	43.3	41.4
67°	50.2	53.4	55.9	55.6	56.0	53.7	50.7	46.7	44.1	41.6	39.8



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	48.4	51.5	53.9	53.8	54.0	51.8	48.9	44.8	42.2	40.0	38.1
68°	46.6	49.6	51.9	52.0	52.1	50.0	47.0	42.9	40.2	38.3	36.5
68.5°	44.9	47.7	49.9	50.2	50.3	48.1	45.2	41.0	38.2	36.7	35.0
69°	43.2	46.0	47.9	48.4	48.5	46.4	43.5	39.2	36.2	35.1	33.4
69.5°	41.4	44.3	46.0	46.6	46.7	44.6	41.8	37.3	34.2	33.4	31.9
70°	39.8	42.5	44.3	44.8	44.9	43.0	40.1	35.4	32.3	31.7	30.5
70.5°	38.2	40.9	42.6	43.1	43.2	41.3	38.5	33.7	30.4	29.9	29.0
71°	36.5	39.2	40.9	41.5	41.5	39.6	36.9	31.9	28.5	28.1	27.6
71.5°	34.7	37.6	39.3	39.8	39.9	38.0	35.3	30.1	26.6	26.5	26.2
72°	32.9	36.0	37.6	38.1	38.2	36.4	33.8	28.4	24.8	24.8	24.9
72.5°	31.1	34.4	36.0	36.5	36.6	34.9	32.2	26.7	23.0	23.1	23.5
73°	29.2	32.9	34.5	35.0	35.0	33.3	30.8	25.1	21.2	21.5	22.2
73.5°	27.3	31.4	32.9	33.5	33.6	31.8	29.3	23.6	19.5	20.0	20.8
74°	25.5	29.8	31.4	31.9	32.0	30.4	27.8	22.0	17.9	18.5	19.6
74.5°	23.7	28.2	30.0	30.5	30.5	28.9	26.4	20.5	16.3	17.1	18.3
75°	21.9	26.5	28.3	29.0	29.1	27.5	25.0	19.0	14.9	15.7	17.1
75.5°	20.1	24.9	26.7	27.6	27.7	26.1	23.7	17.7	13.6	14.5	15.9
76°	18.4	23.2	25.2	26.2	26.3	24.7	22.3	16.3	12.4	13.3	14.7
76.5°	16.7	21.6	23.6	24.8	24.9	23.4	21.0	15.0	11.1	12.1	13.6
77°	15.1	20.1	22.1	23.5	23.6	22.1	19.7	13.9	9.9	10.9	12.5
77.5°	13.6	18.6	20.7	22.2	22.3	20.9	18.4	12.8	8.6	9.7	11.4
78°	12.2	17.1	19.3	20.9	21.0	19.6	17.2	11.6	7.6	8.7	10.3
78.5°	10.8	15.7	18.0	19.6	19.8	18.4	16.0	10.5	6.7	7.8	9.3
79°	9.6	14.4	16.7	18.4	18.5	17.2	14.8	9.4	5.9	6.9	8.3
79.5°	8.4	13.1	15.5	17.2	17.3	16.1	13.8	8.5	5.0	6.1	7.4
80°	7.4	11.9	14.3	16.1	16.2	14.9	12.7	7.6	4.3	5.3	6.5
80.5°	6.4	10.7	13.1	14.9	15.1	13.9	11.6	6.8	3.6	4.4	5.7
81°	5.6	9.6	12.1	13.8	14.0	12.9	10.5	5.9	2.9	3.7	5.0
81.5°	4.8	8.6	11.0	12.8	13.0	11.8	9.4	5.2	2.3	3.2	4.2
82°	4.1	7.6	10.1	11.7	11.9	10.8	8.4	4.4	1.7	2.7	3.6
82.5°	3.4	6.7	9.1	10.7	10.9	9.8	7.5	3.7	1.3	2.2	2.9
83°	2.6	5.8	8.3	9.7	9.8	8.8	6.7	3.1	1.0	1.8	2.3
83.5°	1.9	5.1	7.4	8.8	8.9	7.9	5.9	2.6	0.8	1.4	1.8
84°	1.4	4.3	6.6	7.9	8.0	7.0	5.1	2.2	0.6	1.1	1.4
84.5°	1.0	3.6	5.9	7.0	7.1	6.2	4.4	1.8	0.5	0.9	1.0
85°	0.8	2.8	5.2	6.2	6.2	5.4	3.7	1.4	0.4	0.7	0.8
85.5°	0.5	2.3	4.5	5.4	5.4	4.7	3.1	1.2	0.4	0.5	0.6
86°	0.4	1.8	3.8	4.7	4.7	3.9	2.5	0.9	0.3	0.4	0.4
86.5°	0.3	1.4	3.2	3.9	3.9	3.2	2.0	0.7	0.3	0.4	0.3
87°	0.3	1.1	2.6	3.2	3.2	2.6	1.5	0.6	0.2	0.3	0.1
87.5°	0.3	0.8	2.0	2.5	2.6	2.0	1.1	0.5	0.2	0.2	0.1
88°	0.2	0.6	1.5	1.9	2.0	1.5	0.9	0.4	0.1	0.1	0.1
88.5°	0.2	0.5	1.1	1.4	1.5	1.1	0.7	0.3	0.1	0.1	0.1
89°	0.1	0.4	0.8	1.1	1.1	0.9	0.5	0.2	0.1	0.1	0.1
89.5°	0.1	0.3	0.6	0.8	0.8	0.7	0.4	0.2	0.1	0.1	0.1



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.1	0.2	0.5	0.6	0.6	0.5	0.2	0.2	0.1	0.1	0.1
90.5°	0.1	0.1	0.3	0.4	0.4	0.3	0.1	0.2	0.1	0.1	0.1
91°	0.1	0.1	0.2	0.2	0.3	0.1	0.1	0.2	0.1	0.1	0.1
91.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
92.5°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
93°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
93.5°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
94°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.0
94.5°	0.0	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.0
95°	0.0	0.0	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.0
95.5°	0.0	0.0	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.1	0.0
96°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0
97.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.1	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.0
104°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1
104.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
105.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
106°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
106.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1
107°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
108°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1
108.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1
109°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
109.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
110.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
111°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
111.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
112°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
113°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
113.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
114°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
114.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
115.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2
139.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2
140°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2
140.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2
141°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2
141.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2
142°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2
142.5°	0.3	0.2	0.2	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2
143°	0.3	0.3	0.2	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2
143.5°	0.3	0.3	0.3	0.3	0.1	0.2	0.2	0.2	0.2	0.2	0.2
144°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
144.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
146°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
146.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
147°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
147.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
156°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
156.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
157°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
158°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
158.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
159°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
159.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
171°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
171.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.3	0.3
172.5°	0.3	0.3	0.3	0.3	0.3	0.2	0.3	0.3	0.3	0.3	0.3
173°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
173.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
174°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
174.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
176°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
176.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
177°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
178°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
178.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
179°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
179.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272216
CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	282.2	282.2	282.2	282.2	282.2	282.2
0.5°	282.1	282.1	282.1	282.2	282.3	282.2
1°	282.0	282.0	282.0	282.1	282.1	282.3
1.5°	281.8	281.8	281.8	282.0	282.1	282.2
2°	281.6	281.6	281.6	281.7	282.0	282.2
2.5°	281.3	281.3	281.4	281.6	281.9	282.1
3°	281.0	281.0	281.2	281.4	281.7	282.0
3.5°	280.7	280.7	280.9	281.2	281.5	281.8
4°	280.4	280.4	280.6	280.9	281.3	281.7
4.5°	280.0	280.0	280.2	280.6	281.1	281.4
5°	279.6	279.6	279.9	280.3	280.7	281.3
5.5°	279.2	279.2	279.4	279.9	280.4	280.9
6°	278.7	278.7	279.1	279.6	280.1	280.7
6.5°	278.3	278.3	278.6	279.2	279.7	280.3
7°	277.7	277.8	278.1	278.6	279.4	280.0
7.5°	277.2	277.2	277.6	278.2	279.0	279.6
8°	276.6	276.7	277.0	277.7	278.5	279.2
8.5°	276.1	276.1	276.4	277.2	278.1	278.8
9°	275.5	275.4	275.9	276.6	277.6	278.4
9.5°	274.8	274.8	275.2	276.1	277.0	277.8
10°	274.1	274.1	274.6	275.4	276.5	277.3
10.5°	273.4	273.4	273.9	274.8	275.8	276.7
11°	272.7	272.6	273.2	274.1	275.2	276.1
11.5°	271.9	271.8	272.5	273.4	274.5	275.6
12°	271.1	271.1	271.7	272.7	273.9	274.9
12.5°	270.2	270.2	270.8	271.9	273.2	274.2
13°	269.3	269.3	270.0	271.1	272.4	273.6
13.5°	268.4	268.4	269.1	270.3	271.6	272.7
14°	267.5	267.5	268.2	269.4	270.9	272.1
14.5°	266.6	266.5	267.3	268.5	270.0	271.2
15°	265.6	265.5	266.3	267.6	269.1	270.4
15.5°	264.6	264.4	265.3	266.6	268.2	269.5
16°	263.5	263.4	264.2	265.6	267.3	268.7
16.5°	262.4	262.3	263.2	264.6	266.3	267.8
17°	261.3	261.1	262.0	263.6	265.4	266.9
17.5°	260.1	260.0	260.9	262.5	264.3	265.9
18°	258.9	258.7	259.7	261.3	263.3	264.9
18.5°	257.7	257.5	258.5	260.2	262.2	263.8
19°	256.3	256.2	257.3	259.0	261.1	262.9
19.5°	255.0	254.9	256.1	257.7	259.9	261.7
20°	253.7	253.6	254.6	256.5	258.7	260.6
20.5°	252.3	252.2	253.3	255.1	257.5	259.4
21°	250.9	250.8	251.8	253.9	256.2	258.2
21.5°	249.5	249.3	250.5	252.5	254.9	256.9
22°	247.9	247.8	248.9	251.1	253.5	255.7



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	246.5	246.2	247.5	249.6	252.2	254.3
23°	244.8	244.7	245.9	248.1	250.7	253.0
23.5°	243.3	243.0	244.4	246.6	249.3	251.6
24°	241.5	241.4	242.8	245.1	247.8	250.2
24.5°	239.9	239.7	241.1	243.4	246.3	248.7
25°	238.2	237.9	239.4	241.9	244.7	247.3
25.5°	236.5	236.2	237.8	240.2	243.2	245.7
26°	234.6	234.4	235.8	238.5	241.5	244.2
26.5°	232.8	232.7	234.2	236.8	239.9	242.5
27°	230.9	230.8	232.3	235.0	238.1	241.0
27.5°	229.1	228.9	230.6	233.2	236.5	239.3
28°	227.1	226.9	228.5	231.4	234.6	237.5
28.5°	225.2	225.0	226.7	229.4	232.9	235.8
29°	223.1	223.0	224.7	227.6	230.9	234.1
29.5°	221.1	220.9	222.7	225.6	229.1	232.2
30°	219.0	218.8	220.6	223.6	227.1	230.4
30.5°	217.0	216.7	218.6	221.6	225.3	228.4
31°	214.8	214.6	216.4	219.6	223.2	226.6
31.5°	212.6	212.4	214.4	217.5	221.3	224.6
32°	210.4	210.1	212.2	215.4	219.1	222.7
32.5°	208.2	208.1	210.1	213.3	217.2	220.6
33°	206.0	205.7	207.7	211.1	214.9	218.6
33.5°	203.7	203.5	205.5	208.9	212.9	216.5
34°	201.3	201.1	203.2	206.7	210.6	214.4
34.5°	199.0	198.7	200.9	204.4	208.5	212.2
35°	196.6	196.3	198.6	202.1	206.1	210.1
35.5°	194.2	194.0	196.3	199.8	204.0	207.8
36°	191.7	191.5	193.8	197.4	201.6	205.6
36.5°	189.3	189.0	191.4	195.0	199.3	203.3
37°	186.8	186.5	188.9	192.6	196.8	201.0
37.5°	184.3	184.0	186.5	190.2	194.5	198.7
38°	181.7	181.5	183.9	187.7	192.0	196.3
38.5°	179.1	178.9	181.5	185.3	189.7	194.0
39°	176.5	176.3	178.7	182.6	187.1	191.5
39.5°	173.9	173.7	176.3	180.1	184.7	189.1
40°	171.3	171.1	173.6	177.5	182.1	186.6
40.5°	168.6	168.4	171.0	175.0	179.6	184.1
41°	166.0	165.7	168.3	172.4	176.9	181.5
41.5°	163.2	163.0	165.8	169.8	174.4	179.0
42°	160.5	160.3	163.0	167.1	171.5	176.4
42.5°	157.8	157.5	160.3	164.4	169.1	173.9
43°	155.0	154.8	157.5	161.7	166.4	171.2
43.5°	152.1	152.0	154.8	159.0	163.7	168.5
44°	149.4	149.1	152.1	156.2	160.9	165.9
44.5°	146.6	146.4	149.3	153.5	158.3	163.2



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	143.8	143.6	146.5	150.8	155.5	160.5
45.5°	140.9	140.7	143.7	148.0	152.7	157.8
46°	138.1	137.8	140.9	145.1	149.9	155.0
46.5°	135.2	135.0	138.0	142.4	147.2	152.3
47°	132.4	132.2	135.2	139.5	144.4	149.5
47.5°	129.5	129.3	132.4	136.7	141.5	146.8
48°	126.6	126.5	129.5	133.9	138.8	144.0
48.5°	123.7	123.6	126.7	131.1	135.9	141.2
49°	120.7	120.8	123.8	128.1	133.0	138.3
49.5°	118.0	117.9	121.0	125.4	130.2	135.6
50°	115.2	115.1	118.2	122.5	127.4	132.7
50.5°	112.3	112.3	115.4	119.7	124.5	129.9
51°	109.6	109.6	112.6	117.0	121.8	127.1
51.5°	106.8	106.9	109.8	114.1	118.9	124.3
52°	104.1	104.1	107.1	111.4	116.1	121.4
52.5°	101.4	101.4	104.4	108.6	113.3	118.6
53°	98.7	98.7	101.7	105.9	110.5	115.8
53.5°	96.1	96.1	99.0	103.2	107.8	113.0
54°	93.5	93.5	96.4	100.5	105.1	110.3
54.5°	91.0	90.9	93.8	97.9	102.4	107.6
55°	88.4	88.4	91.2	95.3	99.7	104.9
55.5°	85.9	85.9	88.6	92.7	97.1	102.2
56°	83.5	83.4	86.2	90.2	94.5	99.4
56.5°	81.1	81.0	83.7	87.6	91.9	96.9
57°	78.7	78.7	81.3	85.2	89.4	94.3
57.5°	76.4	76.4	79.0	82.8	86.9	91.8
58°	74.1	74.0	76.6	80.4	84.5	89.1
58.5°	71.8	71.7	74.3	78.0	82.1	86.7
59°	69.6	69.5	72.1	75.7	79.7	84.2
59.5°	67.4	67.4	69.8	73.4	77.3	81.9
60°	65.3	65.2	67.7	71.2	75.1	79.5
60.5°	63.2	63.1	65.5	69.0	72.8	77.1
61°	61.1	61.0	63.4	66.9	70.6	74.8
61.5°	59.1	58.9	61.3	64.7	68.4	72.6
62°	57.1	57.0	59.3	62.6	66.2	70.3
62.5°	55.1	55.1	57.3	60.5	64.1	68.2
63°	53.2	53.3	56.1	58.5	62.0	66.0
63.5°	51.3	51.4	54.1	56.6	60.0	63.9
64°	49.5	49.5	52.0	54.7	58.0	61.9
64.5°	47.7	47.6	50.0	52.8	55.9	59.8
65°	45.9	45.9	47.9	50.9	54.0	57.8
65.5°	44.1	44.0	46.1	49.1	52.2	55.7
66°	42.4	42.4	44.3	47.2	50.3	53.8
66.5°	40.8	40.7	42.6	45.4	48.5	52.0
67°	39.1	39.0	40.9	43.7	46.7	50.2



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	37.5	37.4	39.3	42.0	45.0	48.4
68°	35.9	35.8	37.7	40.3	43.2	46.6
68.5°	34.4	34.2	36.1	38.6	41.5	44.9
69°	32.8	32.7	34.5	37.1	39.9	43.2
69.5°	31.3	31.3	33.0	35.5	38.2	41.4
70°	29.8	29.8	31.5	33.9	36.6	39.8
70.5°	28.4	28.4	30.0	32.4	35.1	38.2
71°	27.0	26.9	28.6	30.9	33.5	36.5
71.5°	25.6	25.5	27.1	29.4	32.0	34.7
72°	24.3	24.2	25.7	28.0	30.3	32.9
72.5°	22.9	22.9	24.4	26.6	28.7	31.1
73°	21.7	21.6	23.0	25.2	27.1	29.2
73.5°	20.4	20.3	21.8	23.9	25.4	27.3
74°	19.1	19.0	20.5	22.5	23.8	25.5
74.5°	17.9	17.8	19.2	21.2	22.2	23.7
75°	16.8	16.7	18.0	19.9	20.6	21.9
75.5°	15.6	15.5	16.8	18.7	19.1	20.1
76°	14.5	14.4	15.7	17.4	17.6	18.4
76.5°	13.4	13.3	14.5	16.2	16.2	16.7
77°	12.4	12.2	13.4	15.0	14.8	15.1
77.5°	11.4	11.2	12.4	13.9	13.5	13.6
78°	10.3	10.2	11.3	12.7	12.3	12.2
78.5°	9.3	9.2	10.3	11.6	11.0	10.8
79°	8.4	8.3	9.4	10.6	9.9	9.6
79.5°	7.5	7.4	8.4	9.5	8.9	8.4
80°	6.6	6.6	7.5	8.6	7.9	7.4
80.5°	5.8	5.7	6.6	7.6	6.9	6.4
81°	5.0	5.0	5.8	6.8	6.1	5.6
81.5°	4.3	4.3	5.1	5.9	5.3	4.8
82°	3.6	3.6	4.4	5.2	4.6	4.1
82.5°	2.9	2.9	3.6	4.5	3.8	3.4
83°	2.3	2.3	2.9	3.8	3.1	2.6
83.5°	1.8	1.7	2.3	3.1	2.6	1.9
84°	1.3	1.3	1.8	2.5	2.1	1.4
84.5°	1.0	1.0	1.3	1.9	1.7	1.0
85°	0.7	0.7	1.0	1.4	1.3	0.8
85.5°	0.6	0.5	0.7	1.0	1.1	0.5
86°	0.4	0.4	0.6	0.8	0.8	0.4
86.5°	0.2	0.2	0.4	0.6	0.6	0.3
87°	0.1	0.1	0.2	0.4	0.5	0.3
87.5°	0.0	0.1	0.1	0.3	0.4	0.3
88°	0.0	0.1	0.1	0.1	0.3	0.2
88.5°	0.0	0.1	0.1	0.1	0.2	0.2
89°	0.0	0.1	0.1	0.1	0.1	0.1
89.5°	0.0	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.1	0.1	0.1	0.1	0.1
90.5°	0.0	0.1	0.1	0.1	0.1	0.1
91°	0.0	0.1	0.1	0.1	0.1	0.1
91.5°	0.0	0.1	0.1	0.1	0.1	0.1
92°	0.0	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.1	0.1	0.1	0.1	0.1
93°	0.0	0.1	0.1	0.1	0.1	0.0
93.5°	0.0	0.1	0.1	0.1	0.0	0.0
94°	0.0	0.1	0.1	0.1	0.0	0.0
94.5°	0.0	0.1	0.1	0.1	0.0	0.0
95°	0.0	0.1	0.1	0.1	0.0	0.0
95.5°	0.0	0.1	0.1	0.1	0.0	0.0
96°	0.0	0.1	0.1	0.1	0.0	0.0
96.5°	0.0	0.1	0.1	0.1	0.0	0.0
97°	0.0	0.1	0.1	0.1	0.1	0.0
97.5°	0.0	0.1	0.1	0.1	0.1	0.1
98°	0.0	0.1	0.1	0.1	0.1	0.1
98.5°	0.0	0.1	0.1	0.1	0.1	0.1
99°	0.0	0.1	0.1	0.1	0.1	0.1
99.5°	0.0	0.1	0.1	0.1	0.1	0.1
100°	0.0	0.1	0.1	0.1	0.1	0.1
100.5°	0.0	0.1	0.1	0.1	0.1	0.1
101°	0.0	0.1	0.1	0.1	0.1	0.1
101.5°	0.0	0.1	0.1	0.1	0.1	0.1
102°	0.0	0.1	0.1	0.1	0.1	0.1
102.5°	0.0	0.1	0.1	0.1	0.1	0.1
103°	0.0	0.1	0.1	0.1	0.1	0.1
103.5°	0.0	0.1	0.1	0.1	0.1	0.1
104°	0.0	0.1	0.1	0.1	0.1	0.1
104.5°	0.0	0.1	0.1	0.1	0.1	0.1
105°	0.1	0.1	0.1	0.1	0.1	0.1
105.5°	0.1	0.1	0.1	0.1	0.1	0.1
106°	0.1	0.1	0.1	0.1	0.1	0.1
106.5°	0.1	0.1	0.1	0.1	0.1	0.1
107°	0.1	0.1	0.1	0.1	0.1	0.1
107.5°	0.1	0.1	0.1	0.1	0.1	0.1
108°	0.1	0.1	0.1	0.1	0.1	0.1
108.5°	0.1	0.1	0.1	0.1	0.1	0.1
109°	0.1	0.1	0.1	0.1	0.1	0.1
109.5°	0.1	0.1	0.1	0.1	0.1	0.1
110°	0.1	0.1	0.1	0.1	0.1	0.1
110.5°	0.1	0.1	0.1	0.1	0.1	0.1
111°	0.1	0.1	0.1	0.1	0.1	0.1
111.5°	0.1	0.1	0.1	0.1	0.1	0.1
112°	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.1	0.1	0.1	0.1	0.1	0.1
113°	0.1	0.1	0.1	0.1	0.1	0.1
113.5°	0.1	0.1	0.1	0.1	0.1	0.1
114°	0.1	0.1	0.1	0.1	0.1	0.1
114.5°	0.1	0.1	0.1	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.1
115.5°	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.2	0.2	0.1	0.1	0.1
123°	0.1	0.2	0.2	0.2	0.1	0.1
123.5°	0.1	0.2	0.2	0.2	0.2	0.1
124°	0.1	0.2	0.2	0.2	0.2	0.2
124.5°	0.1	0.2	0.2	0.2	0.2	0.2
125°	0.1	0.2	0.2	0.2	0.2	0.2
125.5°	0.1	0.2	0.2	0.2	0.2	0.2
126°	0.1	0.2	0.2	0.2	0.2	0.2
126.5°	0.1	0.2	0.2	0.2	0.2	0.2
127°	0.1	0.2	0.2	0.2	0.2	0.2
127.5°	0.1	0.2	0.2	0.2	0.2	0.2
128°	0.1	0.2	0.2	0.2	0.2	0.2
128.5°	0.1	0.2	0.2	0.2	0.2	0.2
129°	0.1	0.2	0.2	0.2	0.2	0.2
129.5°	0.1	0.2	0.2	0.2	0.2	0.2
130°	0.1	0.2	0.2	0.2	0.2	0.2
130.5°	0.1	0.2	0.2	0.2	0.2	0.2
131°	0.1	0.2	0.2	0.2	0.2	0.2
131.5°	0.1	0.2	0.2	0.2	0.2	0.2
132°	0.1	0.2	0.2	0.2	0.2	0.2
132.5°	0.1	0.2	0.2	0.2	0.2	0.2
133°	0.1	0.2	0.2	0.2	0.2	0.2
133.5°	0.1	0.2	0.2	0.2	0.2	0.2
134°	0.1	0.2	0.2	0.2	0.2	0.2
134.5°	0.1	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.1	0.2	0.2	0.2	0.2	0.2
135.5°	0.1	0.2	0.2	0.2	0.2	0.2
136°	0.1	0.2	0.2	0.2	0.2	0.2
136.5°	0.1	0.2	0.2	0.2	0.2	0.2
137°	0.1	0.2	0.2	0.2	0.2	0.2
137.5°	0.1	0.2	0.2	0.2	0.2	0.2
138°	0.1	0.2	0.2	0.2	0.2	0.2
138.5°	0.1	0.2	0.2	0.2	0.2	0.2
139°	0.2	0.2	0.2	0.2	0.2	0.2
139.5°	0.2	0.2	0.2	0.2	0.2	0.2
140°	0.2	0.2	0.2	0.2	0.2	0.2
140.5°	0.2	0.2	0.2	0.2	0.2	0.2
141°	0.2	0.2	0.2	0.2	0.2	0.2
141.5°	0.2	0.3	0.3	0.2	0.2	0.2
142°	0.2	0.3	0.3	0.3	0.2	0.2
142.5°	0.2	0.3	0.3	0.3	0.3	0.3
143°	0.2	0.3	0.3	0.3	0.3	0.3
143.5°	0.2	0.3	0.3	0.3	0.3	0.3
144°	0.2	0.3	0.3	0.3	0.3	0.3
144.5°	0.2	0.3	0.3	0.3	0.3	0.3
145°	0.2	0.3	0.3	0.3	0.3	0.3
145.5°	0.2	0.3	0.3	0.3	0.3	0.3
146°	0.2	0.3	0.3	0.3	0.3	0.3
146.5°	0.2	0.3	0.3	0.3	0.3	0.3
147°	0.2	0.3	0.3	0.3	0.3	0.3
147.5°	0.2	0.3	0.3	0.3	0.3	0.3
148°	0.2	0.3	0.3	0.3	0.3	0.3
148.5°	0.2	0.3	0.3	0.3	0.3	0.3
149°	0.2	0.3	0.3	0.3	0.3	0.3
149.5°	0.2	0.3	0.3	0.3	0.3	0.3
150°	0.2	0.3	0.3	0.3	0.3	0.3
150.5°	0.2	0.3	0.3	0.3	0.3	0.3
151°	0.2	0.3	0.3	0.3	0.3	0.3
151.5°	0.2	0.3	0.3	0.3	0.3	0.3
152°	0.2	0.3	0.3	0.3	0.3	0.3
152.5°	0.2	0.3	0.3	0.3	0.3	0.3
153°	0.2	0.3	0.3	0.3	0.3	0.3
153.5°	0.2	0.3	0.3	0.3	0.3	0.3
154°	0.2	0.3	0.3	0.3	0.3	0.3
154.5°	0.2	0.3	0.3	0.3	0.3	0.3
155°	0.2	0.3	0.3	0.3	0.3	0.3
155.5°	0.2	0.3	0.3	0.3	0.3	0.3
156°	0.2	0.3	0.3	0.3	0.3	0.3
156.5°	0.2	0.3	0.3	0.3	0.3	0.3
157°	0.2	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272216
 CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.2	0.3	0.3	0.3	0.3	0.3
158°	0.2	0.3	0.3	0.3	0.3	0.3
158.5°	0.2	0.3	0.3	0.3	0.3	0.3
159°	0.2	0.3	0.3	0.3	0.3	0.3
159.5°	0.2	0.3	0.3	0.3	0.3	0.3
160°	0.2	0.3	0.3	0.3	0.3	0.3
160.5°	0.2	0.3	0.3	0.3	0.3	0.3
161°	0.2	0.3	0.3	0.3	0.3	0.3
161.5°	0.2	0.3	0.3	0.3	0.3	0.3
162°	0.2	0.3	0.3	0.3	0.3	0.3
162.5°	0.2	0.3	0.3	0.3	0.3	0.3
163°	0.2	0.3	0.3	0.3	0.3	0.3
163.5°	0.2	0.3	0.3	0.3	0.3	0.3
164°	0.2	0.3	0.3	0.3	0.3	0.3
164.5°	0.2	0.3	0.3	0.3	0.3	0.3
165°	0.2	0.3	0.3	0.3	0.3	0.3
165.5°	0.2	0.3	0.3	0.3	0.3	0.3
166°	0.2	0.3	0.3	0.3	0.3	0.3
166.5°	0.2	0.3	0.3	0.3	0.3	0.3
167°	0.2	0.3	0.3	0.3	0.3	0.3
167.5°	0.2	0.3	0.3	0.3	0.3	0.3
168°	0.2	0.3	0.3	0.3	0.3	0.3
168.5°	0.2	0.3	0.3	0.3	0.3	0.3
169°	0.2	0.3	0.3	0.3	0.3	0.3
169.5°	0.2	0.3	0.3	0.3	0.3	0.3
170°	0.2	0.3	0.3	0.3	0.3	0.3
170.5°	0.2	0.3	0.3	0.3	0.3	0.3
171°	0.2	0.3	0.3	0.3	0.3	0.3
171.5°	0.2	0.3	0.3	0.3	0.3	0.3
172°	0.3	0.3	0.3	0.3	0.3	0.3
172.5°	0.3	0.3	0.3	0.3	0.3	0.3
173°	0.3	0.3	0.3	0.3	0.3	0.3
173.5°	0.3	0.3	0.3	0.3	0.3	0.3
174°	0.3	0.3	0.3	0.3	0.3	0.3
174.5°	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.3	0.3	0.3	0.3	0.3	0.3
175.5°	0.3	0.3	0.3	0.3	0.3	0.3
176°	0.3	0.3	0.3	0.3	0.3	0.3
176.5°	0.3	0.3	0.3	0.3	0.3	0.3
177°	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.3	0.3	0.3	0.3	0.3	0.3
178°	0.3	0.3	0.3	0.3	0.3	0.3
178.5°	0.3	0.3	0.3	0.3	0.3	0.3
179°	0.3	0.3	0.3	0.3	0.3	0.3
179.5°	0.3	0.3	0.3	0.3	0.3	0.3



TEST NUMBER: P272216
CATALOG NUMBER: LA56069301EWH

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.3	0.3	0.3	0.3	0.3	0.3

(END OF REPORT)