

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P837174

Luminaire Tested: **L830S15WF930**

Issue Date: 5/17/2024



Test Information

Test Method: LM-79-08
Report Number: P837174
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (1529)
Test Lab: INNOVATION CENTER
Issue Date: 5/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L830S15WF930
Description: Sustainable LED Track Luminaire with Wide Flood Optic and, 3000K, 90CRI LEDs
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1498.0 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 0.91
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct

Input Watts (W): 15
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P837174
CATALOG NUMBER: L830S15WF930

Luminous Intensity Polar Plot





TEST NUMBER: P837174

CATALOG NUMBER: L830S15WF930

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88			
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	88	86	84	82			
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	78	77			
5	94	86	80	76	92	85	79	75	83	78	75	81	77	74	80	76	74	72			
6	89	81	75	71	88	80	74	70	78	74	70	77	73	69	76	72	69	68			
7	85	76	70	66	84	75	70	66	74	69	66	73	68	65	72	68	65	64			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60			
9	77	68	62	58	76	67	62	58	66	61	58	66	61	58	65	61	58	56			
10	74	64	59	55	73	64	58	55	63	58	55	62	58	54	62	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230621
5°	243000
10°	257359
15°	263474
20°	266989
25°	240330
30°	168373
35°	77685
40°	25384
45°	6152
50°	2732
55°	2359
60°	1837
65°	1105
70°	754
75°	436
80°	464
85°	185



TEST NUMBER: P837174

CATALOG NUMBER: L830S15WF930

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.1	9.7
10°-20°	447.0	29.8
20°-30°	597.1	39.9
30°-40°	265.5	17.7
40°-50°	31.6	2.1
50°-60°	7.6	0.5
60°-70°	3.1	0.2
70°-80°	0.8	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1189.2	79.4
0°-40°	1454.7	97.1
0°-60°	1493.9	99.7
0°-90°	1498.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1498.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1432	
5°	1503	145
15°	1580	447
25°	1352	597
35°	395	266
45°	27	32
55°	8	8
65°	3	3
75°	1	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	



TEST NUMBER: P837174

CATALOG NUMBER: L830S15WF930

CANDELA DISTRIBUTION (FULL):

	0°
0°	1431.5
2.5°	1464.5
5°	1502.6
7.5°	1527.1
10°	1573.2
12.5°	1598.7
15°	1579.7
17.5°	1570.9
20°	1557.3
22.5°	1484.6
25°	1352.0
27.5°	1167.3
30°	905.1
32.5°	630.5
35°	395.0
37.5°	214.9
40°	120.7
42.5°	62.4
45°	27.0
47.5°	13.6
50°	10.9
52.5°	9.5
55°	8.4
57.5°	7.9
60°	5.7
62.5°	3.6
65°	2.9
67.5°	2.4
70°	1.6
72.5°	0.8
75°	0.7
77.5°	0.6
80°	0.5
82.5°	0.3
85°	0.1
87.5°	0.1
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0



TEST NUMBER: P837174

CATALOG NUMBER: L830S15WF930

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







107.5°		0.0
110°		0.0



(END OF REPORT)