

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P534461

Luminaire Tested: **L808-13-FL-935-MB**

Issue Date: 6/9/2021

Test Information

Test Method: LM-79-08
Report Number: P534461
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-126-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L808-13-FL-935-MB
Description: 3" Track Fixture with Flood Optic
Light Source: (1) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1256.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.59
Luminous Opening: Circular (Dia: 0.02' x H: 0')
CIE Type: Direct

Input Watts (W): 12.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P534461
CATALOG NUMBER: L808-13-FL-935-MB

Luminous Intensity Polar Plot





TEST NUMBER: P534461

CATALOG NUMBER: L808-13-FL-935-MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95	93	92	90
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91	89	87	85
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87	84	82	81
5	96	89	84	81	95	88	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	79	76	83	79	75		81	78	75		80	77	74	73
7	89	81	76	72	88	80	76	72	79	75	72		78	74	71		77	74	71	70
8	86	77	72	69	84	77	72	69	76	71	68		75	71	68		74	70	68	67
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71	68	65	64
10	79	71	66	63	78	71	66	63	70	65	62		69	65	62		68	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66139438
5°	61419607
10°	50820702
15°	36392945
20°	26042264
25°	20981857
30°	13174179
35°	4716738
40°	1917879
45°	921026
50°	542413
55°	397596
60°	271908
65°	181602
70°	134638
75°	118613
80°	88395
85°	0



TEST NUMBER: P534461

CATALOG NUMBER: L808-13-FL-935-MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.2	19.9
10°-20°	445.2	35.4
20°-30°	383.4	30.5
30°-40°	136.9	10.9
40°-50°	25.8	2.1
50°-60°	9.2	0.7
60°-70°	3.8	0.3
70°-80°	1.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1078.9	85.9
0°-40°	1215.8	96.8
0°-60°	1250.9	99.6
0°-90°	1256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3016	
5°	2790	250
15°	1603	445
25°	867	383
35°	176	137
45°	30	26
55°	10	9
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P534461

CATALOG NUMBER: L808-13-FL-935-MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3016.2
1°	2996.9
2°	2962.3
3°	2918.1
4°	2860.1
5°	2790.3
6°	2712.2
7°	2620.3
8°	2516.6
9°	2405.4
10°	2282.4
11°	2148.3
12°	2011.5
13°	1871.9
14°	1734.4
15°	1603.1
16°	1476.0
17°	1364.0
18°	1265.2
19°	1185.1
20°	1116.0
21°	1056.5
22°	1000.6
23°	952.9
24°	908.7
25°	867.2
26°	819.5
27°	754.6
28°	679.3
29°	599.1
30°	520.3
32.5°	331.0
35°	176.2
37.5°	106.4
40°	67.0
42.5°	44.9
45°	29.7
47.5°	20.0
50°	15.9
52.5°	12.4
55°	10.4
57.5°	7.6
60°	6.2
62.5°	4.8
65°	3.5



TEST NUMBER: P534461

CATALOG NUMBER: L808-13-FL-935-MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2.8
70°	2.1
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)