

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P553810

Luminaire Tested: **L80916SP935MB**

Issue Date: 7/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P553810  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-226-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 7/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO  
Catalog Number: L80916SP935MB  
Description: SPOT OPTIC  
Light Source: 1600 LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1751.8 lumens  
Efficiency: N/A  
Efficacy: 125.1 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P553810  
CATALOG NUMBER: L80916SP935MB

### Luminous Intensity Polar Plot





TEST NUMBER: P553810

CATALOG NUMBER: L80916SP935MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98	98	98	98
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97	97	97	97
3	110	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95	95	95	95
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	95	94	94	94	94
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93	93	93	93
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91	91	91	91
7	103	98	95	93	102	97	94	92	96	94	92	95	93	91	94	93	91	90	90	90	90
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	91	90	89	89	89	89
9	100	95	92	90	99	94	92	90	94	91	89	93	91	89	92	90	89	88	88	88	88
10	98	93	91	89	98	93	90	89	93	90	88	92	90	88	92	90	88	87	87	87	87

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5791597
5°	3769064
10°	1084037
15°	263974
20°	85081
25°	36147
30°	18079
35°	10440
40°	6698
45°	4838
50°	3411
55°	2982
60°	2938
65°	2906
70°	2116
75°	0
80°	0
85°	0



TEST NUMBER: P553810  
 CATALOG NUMBER: L80916SP935MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1202.9	68.7
10°-20°	421.1	24.0
20°-30°	76.7	4.4
30°-40°	25.8	1.5
40°-50°	12.2	0.7
50°-60°	7.3	0.4
60°-70°	5.1	0.3
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1700.7	97.1
0°-40°	1726.5	98.6
0°-60°	1746.0	99.7
0°-90°	1751.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1751.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	26412	
5°	17123	###
15°	1163	421
25°	149	77
35°	39	26
45°	16	12
55°	8	7
65°	6	5
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	



TEST NUMBER: P553810

CATALOG NUMBER: L80916SP935MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	26411.8
1°	26097.4
2°	24691.6
3°	22519.9
4°	20049.4
5°	17122.9
6°	14070.5
7°	11218.7
8°	8613.3
9°	6579.8
10°	4868.5
12.5°	2361.2
15°	1162.8
17.5°	634.3
20°	364.6
22.5°	226.3
25°	149.4
27.5°	101.5
30°	71.4
32.5°	52.4
35°	39.0
37.5°	29.0
40°	23.4
42.5°	19.0
45°	15.6
47.5°	12.3
50°	10.0
52.5°	8.9
55°	7.8
57.5°	7.8
60°	6.7
62.5°	5.6
65°	5.6
67.5°	4.5
70°	3.3
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



TEST NUMBER: P553810

CATALOG NUMBER: L80916SP935MB

**CANDELA DISTRIBUTION (continued):**

	0°
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







92.5°		0.0
95°		0.0



(END OF REPORT)