

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P553824

Luminaire Tested: **L80925NF927MB**

Issue Date: 7/16/2021

Test Information

Test Method: LM-41-14
Report Number: P553824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-226-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L80925NF927MB
Description: NARROW FLOOD OPTIC
Light Source: 2500 LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2476.4 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 0.38 / 0.38 / 0.39
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P553824
CATALOG NUMBER: L80925NF927MB

Luminous Intensity Polar Plot





TEST NUMBER: P553824

CATALOG NUMBER: L80925NF927MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	104	100	97	106	102	99	96	100	97	95	97	95	94	95	94	92	91	91	91	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	88	88	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	86	86	86	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	83	83	83	83
7	97	90	86	84	96	90	86	83	89	85	83	88	85	83	87	84	82	81	81	81	81
8	94	88	84	81	93	87	84	81	86	83	81	86	83	80	85	82	80	79	79	79	79
9	92	85	82	79	91	85	81	79	84	81	79	84	81	78	83	80	78	77	77	77	77
10	90	83	80	77	89	83	79	77	82	79	77	82	79	77	81	78	76	75	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2948514
5°	2537964
10°	1715332
15°	907111
20°	360205
25°	122693
30°	50641
35°	26555
40°	15572
45°	9924
50°	7642
55°	6729
60°	5614
65°	4981
70°	3077
75°	0
80°	0
85°	0



TEST NUMBER: P553824

CATALOG NUMBER: L80925NF927MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	974.8	39.4
10°-20°	1101.6	44.5
20°-30°	280.7	11.3
30°-40°	67.0	2.7
40°-50°	26.3	1.1
50°-60°	15.7	0.6
60°-70°	9.3	0.4
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2357.1	95.2
0°-40°	2424.0	97.9
0°-60°	2466.1	99.6
0°-90°	2476.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2476.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13446	
5°	11530	975
15°	3996	1102
25°	507	281
35°	99	67
45°	32	26
55°	18	16
65°	10	9
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	



TEST NUMBER: P553824

CATALOG NUMBER: L80925NF927MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	13446.3
1°	13383.9
2°	13129.6
3°	12704.1
4°	12179.4
5°	11530.0
6°	10840.5
7°	10082.3
8°	9300.1
9°	8489.1
10°	7703.7
11°	6900.7
12°	6107.3
13°	5355.5
14°	4653.3
15°	3995.8
16°	3429.6
17°	2860.1
18°	2365.8
19°	1911.5
20°	1543.6
22.5°	884.6
25°	507.1
27.5°	310.3
30°	200.0
32.5°	139.2
35°	99.2
37.5°	72.0
40°	54.4
42.5°	41.6
45°	32.0
47.5°	25.6
50°	22.4
52.5°	19.2
55°	17.6
57.5°	16.0
60°	12.8
62.5°	11.2
65°	9.6
67.5°	8.0
70°	4.8
72.5°	1.6
75°	0.0



TEST NUMBER: P553824

CATALOG NUMBER: L80925NF927MB

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







77.5°		0.0
80°		0.0



(END OF REPORT)