

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P553826

Luminaire Tested: **L80925NF935MB**

Issue Date: 7/16/2021

Test Information

Test Method: LM-41-14
Report Number: P553826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-226-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L80925NF935MB
Description: NARROW FLOOD OPTIC
Light Source: 2500 LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2759.6 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 0.38 / 0.38 / 0.39
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P553826
CATALOG NUMBER: L80925NF935MB

Luminous Intensity Polar Plot





TEST NUMBER: P553826

CATALOG NUMBER: L80925NF935MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	104	100	97	106	102	99	96	100	97	95	97	95	94	95	94	92	91	91	91	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	88	88	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	86	86	86	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	83	83	83	83
7	97	90	86	84	96	90	86	83	89	85	83	88	85	83	87	84	82	81	81	81	81
8	94	88	84	81	93	87	84	81	86	83	81	86	83	80	85	82	80	79	79	79	79
9	92	85	82	79	91	85	81	79	84	81	79	84	81	78	83	80	78	77	77	77	77
10	90	83	80	77	89	83	79	77	82	79	77	82	79	77	81	78	76	75	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3285724
5°	2828212
10°	1911499
15°	1010857
20°	401415
25°	136726
30°	56414
35°	29580
40°	17347
45°	11071
50°	8529
55°	7493
60°	6271
65°	5552
70°	3398
75°	0
80°	0
85°	0



TEST NUMBER: P553826

CATALOG NUMBER: L80925NF935MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1086.3	39.4
10°-20°	1227.6	44.5
20°-30°	312.7	11.3
30°-40°	74.6	2.7
40°-50°	29.3	1.1
50°-60°	17.5	0.6
60°-70°	10.3	0.4
70°-80°	1.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2626.6	95.2
0°-40°	2701.2	97.9
0°-60°	2748.1	99.6
0°-90°	2759.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2759.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14984	
5°	12849	###
15°	4453	1228
25°	565	313
35°	110	75
45°	36	29
55°	20	18
65°	11	10
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	



TEST NUMBER: P553826

CATALOG NUMBER: L80925NF935MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	14984.1
1°	14914.6
2°	14631.2
3°	14157.0
4°	13572.3
5°	12848.6
6°	12080.3
7°	11235.4
8°	10363.7
9°	9460.0
10°	8584.7
11°	7689.9
12°	6805.8
13°	5968.0
14°	5185.4
15°	4452.8
16°	3821.8
17°	3187.2
18°	2636.4
19°	2130.1
20°	1720.2
22.5°	985.7
25°	565.1
27.5°	345.8
30°	222.8
32.5°	155.1
35°	110.5
37.5°	80.2
40°	60.6
42.5°	46.3
45°	35.7
47.5°	28.5
50°	25.0
52.5°	21.4
55°	19.6
57.5°	17.8
60°	14.3
62.5°	12.5
65°	10.7
67.5°	8.9
70°	5.3
72.5°	1.8
75°	0.0



TEST NUMBER: P553826

CATALOG NUMBER: L80925NF935MB

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







77.5°		0.0
80°		0.0



(END OF REPORT)