

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P553836

Luminaire Tested: **L80925WS927MB**

Issue Date: 7/16/2021

Test Information

Test Method: LM-41-14
Report Number: P553836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-226-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L80925WS927MB
Description: WIDE SPOT OPTIC
Light Source: 2500 LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2477.9 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.3
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P553836

CATALOG NUMBER: L80925WS927MB

Luminous Intensity Polar Plot





TEST NUMBER: P553836

CATALOG NUMBER: L80925WS927MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	98			
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	96			
3	110	106	103	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94			
4	107	102	99	97	106	101	98	96	100	97	95	98	96	94	96	94	93	92			
5	105	100	96	94	103	99	96	93	97	95	93	96	94	92	95	93	91	90			
6	102	97	94	91	101	97	93	91	95	93	91	94	92	90	93	91	89	89			
7	100	95	92	89	99	95	91	89	94	91	89	93	90	88	92	90	88	87			
8	99	93	90	88	98	93	90	87	92	89	87	91	89	87	90	88	86	86			
9	97	91	88	86	96	91	88	86	90	88	86	90	87	85	89	87	85	84			
10	95	90	87	84	94	89	86	84	89	86	84	88	86	84	88	85	84	83			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4901800
5°	3908597
10°	2014837
15°	607359
20°	158704
25°	59616
30°	30790
35°	17132
40°	10992
45°	7939
50°	6004
55°	4893
60°	4210
65°	4151
70°	3077
75°	0
80°	0
85°	0



TEST NUMBER: P553836

CATALOG NUMBER: L80925WS927MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1404.7	56.7
10°-20°	856.6	34.6
20°-30°	132.6	5.4
30°-40°	43.2	1.7
40°-50°	20.1	0.8
50°-60°	11.9	0.5
60°-70°	7.7	0.3
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2393.9	96.6
0°-40°	2437.2	98.4
0°-60°	2469.2	99.6
0°-90°	2477.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2477.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22354	
5°	17757	###
15°	2675	857
25°	246	133
35°	64	43
45°	26	20
55°	13	12
65°	8	8
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	



TEST NUMBER: P553836

CATALOG NUMBER: L80925WS927MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	22354.0
1°	22216.4
2°	21597.1
3°	20624.2
4°	19337.7
5°	17756.8
6°	16049.4
7°	14361.3
8°	12492.3
9°	10752.9
10°	9048.8
11°	7371.8
12°	5886.9
13°	4638.8
14°	3560.3
15°	2675.4
16°	2037.0
17°	1513.7
18°	1155.3
19°	873.7
20°	680.1
22.5°	387.2
25°	246.4
27.5°	171.2
30°	121.6
32.5°	88.0
35°	64.0
37.5°	49.6
40°	38.4
42.5°	30.4
45°	25.6
47.5°	20.8
50°	17.6
52.5°	16.0
55°	12.8
57.5°	11.2
60°	9.6
62.5°	8.0
65°	8.0
67.5°	8.0
70°	4.8
72.5°	1.6
75°	0.0



TEST NUMBER: P553836

CATALOG NUMBER: L80925WS927MB

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







77.5°		0.0
80°		0.0



(END OF REPORT)