

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P236661

Luminaire Tested: **L81211SP9040MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P236661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-557-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L81211SP9040MB
Description: HALO, TRACK-MINI, CYLINDER, 15D BEAM
Light Source: (1) 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1265.1 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.28
Luminous Opening: Circular (Dia: 0.19' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P236661
CATALOG NUMBER: L81211SP9040MB

Luminous Intensity Polar Plot





TEST NUMBER: P236661

CATALOG NUMBER: L81211SP9040MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	96	94	92	91
4	105	100	96	93	104	99	95	93	97	94	92	95	93	91	93	91	90	88
5	102	97	93	90	101	96	92	89	94	91	89	93	90	88	91	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	91	87	84	89	86	84	88	86	83	88	85	83	82
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	80
9	93	87	83	80	92	86	83	80	85	82	80	85	82	80	84	81	80	79
10	91	85	81	79	90	84	81	78	84	81	78	83	80	78	83	80	78	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4205589
5°	3266125
10°	1338593
15°	558116
20°	238332
25°	113039
30°	62524
35°	36930
40°	23562
45°	17256
50°	13646
55°	11078
60°	8810
65°	6918
70°	5699
75°	5724
80°	0
85°	0



TEST NUMBER: P236661

CATALOG NUMBER: L81211SP9040MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	617.9	48.8
10°-20°	414.0	32.7
20°-30°	131.6	10.4
30°-40°	51.4	4.1
40°-50°	24.8	2.0
50°-60°	14.4	1.1
60°-70°	7.6	0.6
70°-80°	3.3	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1163.6	92.0
0°-40°	1215.0	96.0
0°-60°	1254.2	99.1
0°-90°	1265.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1265.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10788	
5°	8346	618
15°	1383	414
25°	263	132
35°	78	51
45°	31	25
55°	16	14
65°	8	8
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P236661

CATALOG NUMBER: L81211SP9040MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	10788.2
1°	10719.3
2°	10494.1
3°	10038.5
4°	9316.4
5°	8346.4
6°	7271.4
7°	6140.0
8°	5053.7
9°	4097.5
10°	3381.6
12.5°	2147.6
15°	1382.9
17.5°	883.6
20°	574.5
22.5°	380.5
25°	262.8
27.5°	186.5
30°	138.9
32.5°	103.9
35°	77.6
37.5°	60.1
40°	46.3
42.5°	37.5
45°	31.3
47.5°	26.3
50°	22.5
52.5°	18.8
55°	16.3
57.5°	12.5
60°	11.3
62.5°	8.8
65°	7.5
67.5°	6.3
70°	5.0
72.5°	5.0
75°	3.8
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)