

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P21181

Luminaire Tested: **L805LRGSP830**

Issue Date: 3/3/2020



Test Information

Test Method: LM-79-08
Report Number: P21181
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L805LRGSP830
Description: HALO STASIS LED TRACK FIXTURE WITH SPECULAR SPOT
Light Source: (16) SMT WHITE LEDS 3000K
XPGWHT-LI-000-00DE7
Ballast/Driver: ROAL ELECTRONIC DRIVER
RSDL035-16


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2439.5 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.25
Luminous Opening: Rectangular (W 0.33' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 37.5
Input Voltage (V): NR
Input Current (Ain): 0.3144
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P21181
CATALOG NUMBER: L805LRGSP830

Luminous Intensity Polar Plot





TEST NUMBER: P21181
 CATALOG NUMBER: L805LRGSP830

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100			
1	116	114	112	110	113	111	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98			
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96	96	96	96			
3	110	106	103	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94	94	94	94			
4	107	103	99	97	106	102	98	96	100	97	95	98	96	94	96	94	93	92	92	92	92			
5	105	100	96	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	90	90			
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	89	89	89			
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	88	87	87	87	87			
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86	86	86	86			
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	85	85	85	85			
10	96	90	87	85	95	90	87	85	90	87	85	89	87	85	88	86	85	84	84	84	84			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1791612
5°	1312229
10°	469749
15°	157259
20°	51615
25°	12827
30°	4997
35°	5913
40°	6070
45°	4019
50°	1407
55°	788
60°	1292
65°	306
70°	944
75°	1996
80°	3347
85°	5187



TEST NUMBER: P21181
 CATALOG NUMBER: L805LRGSP830

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1466.6	60.1
10°-20°	754.0	30.9
20°-30°	115.1	4.7
30°-40°	46.9	1.9
40°-50°	30.2	1.2
50°-60°	8.5	0.3
60°-70°	4.8	0.2
70°-80°	6.9	0.3
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2335.7	95.7
0°-40°	2382.7	97.7
0°-60°	2421.4	99.3
0°-90°	2439.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2439.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27741	
5°	20241	###
15°	2352	754
25°	180	115
35°	75	47
45°	44	30
55°	7	9
65°	2	5
75°	8	7
85°	7	6
90°	0	



TEST NUMBER: P21181
CATALOG NUMBER: L805LRGSP830

CANDELA DISTRIBUTION (FULL):

	0°
0°	27741
2.5°	25927
5°	20241
7.5°	12324
10°	7163
12.5°	4283
15°	2352
17.5°	1316
20°	751
22.5°	395
25°	180
27.5°	88
30°	67
32.5°	67
35°	75
37.5°	86
40°	72
42.5°	47
45°	44
47.5°	25
50°	14
52.5°	9
55°	7
57.5°	10
60°	10
62.5°	4
65°	2
67.5°	6
70°	5
72.5°	6
75°	8
77.5°	5
80°	9
82.5°	6
85°	7
87.5°	6
90°	0

(END OF REPORT)