

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P22178-R2

Luminaire Tested: **L805SMLFL830**

Issue Date: 3/3/2020



Test Information

Test Method: LM-79-08
Report Number: P22178-R2
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L805SMLFL830
Description: ***THIS IS A REVISION OF P22178 TO UPDATE CATALOG
NUMBER***STASIS LED WITH (3) LEDS AND FLOOD OPTICS.
Light Source: (3) 3000K SMT LEDS
Ballast/Driver: -
ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 391.3 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): 0.06837
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P22178-R2
CATALOG NUMBER: L805SMLFL830

Luminous Intensity Polar Plot





TEST NUMBER: P22178-R2

CATALOG NUMBER: L805SMLFL830

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103		102	101	100		99	98	97	96
2	110	106	103	100	108	105	102	99	101	99	97		99	97	95		96	94	93	91
3	106	101	97	94	104	100	96	93	97	94	91		95	92	90		93	91	89	87
4	102	96	92	88	101	95	91	88	93	90	87		91	88	86		89	87	85	84
5	98	92	87	84	97	91	87	83	89	86	83		88	85	82		86	84	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	84	80	76	91	84	79	76	83	79	76		81	78	75		80	77	75	74
8	89	81	76	73	87	80	76	73	80	75	73		79	75	72		78	74	72	71
9	86	78	73	70	85	78	73	70	77	73	70		76	72	70		75	72	69	68
10	83	75	71	67	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228929
5°	213295
10°	179467
15°	144155
20°	104776
25°	52987
30°	16965
35°	6692
40°	3435
45°	2171
50°	1365
55°	765
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P22178-R2

CATALOG NUMBER: L805SMLFL830

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	22.3
10°-20°	174.1	44.5
20°-30°	103.0	26.3
30°-40°	18.5	4.7
40°-50°	5.5	1.4
50°-60°	2.1	0.5
60°-70°	0.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.4	93.1
0°-40°	382.8	97.8
0°-60°	390.5	99.8
0°-90°	391.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	391.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1044	
5°	969	87
15°	635	174
25°	219	103
35°	25	18
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P22178-R2

CATALOG NUMBER: L805SMLFL830

CANDELA DISTRIBUTION (FULL):

	0°
0°	1044
2.5°	1021
5°	969
7.5°	893
10°	806
12.5°	721
15°	635
17.5°	546
20°	449
22.5°	337
25°	219
27.5°	123
30°	67
32.5°	40
35°	25
37.5°	17
40°	12
42.5°	9
45°	7
47.5°	5
50°	4
52.5°	3
55°	2
57.5°	2
60°	1
62.5°	1
65°	1
67.5°	1
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)