

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO

Report Number: P328485

Luminaire Tested: **L815MED30NF940MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P328485  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1905-290-11)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO  
Catalog Number: L815MED30NF940MB  
Description: Medium, 3000lm, 25D, 4000K, black finish  
Light Source: (1) 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3028.0 lumens  
Efficiency: N/A  
Efficacy: 80.3 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.39  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 37.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P328485  
CATALOG NUMBER: L815MED30NF940MB

### Luminous Intensity Polar Plot





TEST NUMBER: P328485

CATALOG NUMBER: L815MED30NF940MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104		103	102	101		100	99	98	96
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97	96	94	93
3	107	103	99	96	106	101	98	95	99	96	94		96	94	92		94	92	91	90
4	104	98	94	91	102	97	94	91	95	92	90		94	91	89		92	90	88	87
5	101	95	91	88	99	94	90	87	92	89	86		91	88	86		89	87	85	84
6	98	92	87	84	97	91	87	84	90	86	84		88	85	83		87	85	83	81
7	95	89	85	82	94	88	84	81	87	84	81		86	83	81		85	82	80	79
8	93	86	82	79	92	86	82	79	85	81	79		84	81	78		83	80	78	77
9	90	84	80	77	90	83	79	77	83	79	77		82	79	76		81	78	76	75
10	88	82	78	75	87	81	77	75	81	77	75		80	77	74		79	76	74	73

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1783282
5°	1670920
10°	1238043
15°	565595
20°	197733
25°	85210
30°	40934
35°	24213
40°	17438
45°	15124
50°	11590
55°	12516
60°	10410
65°	8639
70°	5770
75°	524
80°	4049
85°	1557



TEST NUMBER: P328485

CATALOG NUMBER: L815MED30NF940MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1169.2	38.6
10°-20°	1285.1	42.4
20°-30°	318.6	10.5
30°-40°	106.8	3.5
40°-50°	66.8	2.2
50°-60°	46.0	1.5
60°-70°	31.4	1.0
70°-80°	3.1	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2772.8	91.6
0°-40°	2879.6	95.1
0°-60°	2992.4	98.8
0°-90°	3028.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3028.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	14458	
5°	13495	###
15°	4429	1285
25°	626	319
35°	161	107
45°	87	67
55°	58	46
65°	30	31
75°	1	3
85°	1	1
90°	0	



TEST NUMBER: P328485

CATALOG NUMBER: L815MED30NF940MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	14457.6
2.5°	14294.5
5°	13495.1
7.5°	11926.0
10°	9884.7
12.5°	7281.3
15°	4429.2
17.5°	2527.1
20°	1506.4
22.5°	952.2
25°	626.1
27.5°	414.0
30°	287.4
32.5°	212.1
35°	160.8
37.5°	123.2
40°	108.3
42.5°	90.1
45°	86.7
47.5°	85.5
50°	60.4
52.5°	63.9
55°	58.2
57.5°	33.1
60°	42.2
62.5°	39.9
65°	29.6
67.5°	28.5
70°	16.0
72.5°	0.0
75°	1.1
77.5°	0.0
80°	5.7
82.5°	0.0
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)