

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P328505

Luminaire Tested: **L815SML05FL940MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P328505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1905-290-5)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L815SML05FL940MB
Description: Small, 500lm, 45D, 4000K, black finish
Light Source: (1) 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 656.0 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 6.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P328505
CATALOG NUMBER: L815SML05FL940MB

Luminous Intensity Polar Plot





TEST NUMBER: P328505

CATALOG NUMBER: L815SML05FL940MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89		93	90	87		90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86	84	81	80
5	96	88	83	80	94	88	83	79	86	82	78		84	81	78		83	80	77	76
6	92	84	79	75	90	83	78	75	82	77	74		81	77	74		79	76	73	72
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76	72	70	68
8	85	76	71	67	83	76	71	67	75	70	67		74	70	67		73	69	66	65
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70	66	63	62
10	78	70	65	61	77	69	64	61	69	64	61		68	64	61		67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262260
5°	257803
10°	241055
15°	209717
20°	160687
25°	104183
30°	57857
35°	25511
40°	10820
45°	6977
50°	5254
55°	3747
60°	2412
65°	1453
70°	769
75°	339
80°	0
85°	0



TEST NUMBER: P328505

CATALOG NUMBER: L815SML05FL940MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	16.6
10°-20°	252.0	38.4
20°-30°	198.3	30.2
30°-40°	66.3	10.1
40°-50°	18.4	2.8
50°-60°	8.8	1.3
60°-70°	3.0	0.5
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.2	85.2
0°-40°	625.4	95.3
0°-60°	652.6	99.5
0°-90°	656.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	656.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1196	
5°	1171	109
15°	924	252
25°	431	198
35°	95	66
45°	22	18
55°	10	9
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P328505

CATALOG NUMBER: L815SML05FL940MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1196.0
2.5°	1192.5
5°	1171.2
7.5°	1133.0
10°	1082.6
12.5°	1014.0
15°	923.8
17.5°	813.1
20°	688.6
22.5°	559.0
25°	430.6
27.5°	319.9
30°	228.5
32.5°	151.3
35°	95.3
37.5°	57.1
40°	37.8
42.5°	28.4
45°	22.5
47.5°	18.5
50°	15.4
52.5°	12.2
55°	9.8
57.5°	7.1
60°	5.5
62.5°	3.9
65°	2.8
67.5°	2.0
70°	1.2
72.5°	0.8
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)