

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P328528

Luminaire Tested: **L815SML10NF935MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P328528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1905-290-4)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L815SML10NF935MB
Description: Small, 1000lm, 25D, 3500K, black finish
Light Source: (1) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1301.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.39
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 12.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P328528

CATALOG NUMBER: L815SML10NF935MB

Luminous Intensity Polar Plot





TEST NUMBER: P328528

CATALOG NUMBER: L815SML10NF935MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105		103	102	101		100	99	99	97
2	112	108	105	103	110	106	104	102	103	101	99		100	99	97		98	97	95	94
3	108	104	100	97	106	102	99	97	100	97	95		98	96	94		96	94	92	91
4	105	100	96	93	104	99	95	93	97	94	92		95	93	91		93	91	90	89
5	102	97	93	90	101	96	92	89	94	91	89		93	90	88		91	89	87	86
6	100	94	90	87	98	93	89	87	92	88	86		90	88	85		89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84		88	85	83		87	85	83	82
8	95	89	85	82	94	88	84	82	87	84	82		86	83	81		86	83	81	80
9	93	86	82	80	92	86	82	80	85	82	80		84	81	79		84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	78		83	80	78		82	79	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1498016
5°	1380406
10°	1015368
15°	487403
20°	123187
25°	34478
30°	18509
35°	14322
40°	12738
45°	10761
50°	8733
55°	6614
60°	2982
65°	1972
70°	962
75°	0
80°	0
85°	0



TEST NUMBER: P328528

CATALOG NUMBER: L815SML10NF935MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	544.5	41.9
10°-20°	590.2	45.4
20°-30°	85.8	6.6
30°-40°	34.5	2.7
40°-50°	26.9	2.1
50°-60°	14.8	1.1
60°-70°	4.0	0.3
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1220.4	93.8
0°-40°	1254.9	96.5
0°-60°	1296.6	99.7
0°-90°	1301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1301.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6832	
5°	6271	544
15°	2147	590
25°	142	86
35°	54	34
45°	35	27
55°	17	15
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P328528

CATALOG NUMBER: L815SML10NF935MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	6831.5
1°	6811.9
2°	6741.8
3°	6631.7
4°	6468.1
5°	6271.2
6°	6025.4
7°	5736.6
8°	5392.7
9°	4990.0
10°	4560.1
11°	4088.8
12°	3598.6
13°	3098.7
14°	2613.8
15°	2147.0
17.5°	1166.6
20°	527.9
22.5°	248.1
25°	142.5
27.5°	96.5
30°	73.1
32.5°	60.3
35°	53.5
37.5°	49.0
40°	44.5
42.5°	40.0
45°	34.7
47.5°	30.2
50°	25.6
52.5°	21.1
55°	17.3
57.5°	12.1
60°	6.8
62.5°	5.3
65°	3.8
67.5°	3.0
70°	1.5
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P328528

CATALOG NUMBER: L815SML10NF935MB

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)