

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: HALO

Report Number: P979202

Luminaire Tested: L820S10MF935XXXXBLSHBXXXX

Issue Date: 4/1/2025

Test Information

Test Method: LM-79-2019
Report Number: P979202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (LM79-2019)
Test Lab: INNOVATION CENTER
Issue Date: 4/1/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: L820S10MF935XXXXBLSHBXXXX
Description: 2IN Sustainable LED Track Luminaire with medium flood optic
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1043.9 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.22' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9
Total Harmonic Distortion (THDi): 20
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979202
CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	97	97	96
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	94	93	93	93	92
3	106	101	97	94	105	100	96	94	98	95	92	95	93	91	93	91	89	89	89	88
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	86	86	85
5	99	93	88	85	98	92	88	85	90	87	84	89	86	83	87	85	83	83	83	81
6	96	89	85	81	95	88	84	81	87	83	81	86	83	80	85	82	80	80	80	78
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	77	77	76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	80	76	74	74	74	73
9	87	80	76	73	86	80	75	72	79	75	72	78	74	72	77	74	72	72	72	71
10	85	77	73	70	84	77	73	70	76	72	70	76	72	70	75	72	69	69	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	1089121	1089121	1089121	1089121
5°	954770	1007979	995995	944009
10°	667193	746500	734569	659331
15°	388057	454312	442485	382816
20°	213735	249256	242112	209644
25°	137493	149262	146932	135850
30°	89809	107221	104470	87465
35°	22043	39063	35957	20589
40°	3605	4205	3887	3605
45°	2450	2603	2450	2527
50°	2106	2316	2148	2232
55°	2313	2313	2266	2407
60°	2274	2328	2274	2382
65°	2626	2690	2690	2819
70°	2612	2691	2770	2849
75°	2510	2615	2720	2720
80°	3118	3430	3430	3274
85°	311	621	621	311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 100°
 Vertical Angle: 82.5°
 Luminance: 3733 cd/sqm



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.7	29.6
10°-20°	417.2	40.0
20°-30°	229.0	21.9
30°-40°	69.2	6.6
40°-50°	5.4	0.5
50°-60°	4.3	0.4
60°-70°	4.0	0.4
70°-80°	2.8	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.1	0.0
140°-150°	0.3	0.0
150°-160°	0.8	0.1
160°-170°	0.9	0.1
170°-180°	0.3	0.0
0°-30°	955.0	91.5
0°-40°	1024.2	98.1
0°-60°	1033.9	99.0
0°-90°	1041.5	99.8
90°-120°	0.0	0.0
90°-150°	0.4	0.0
90°-180°	2.0	0.2
0°-180°	1043.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	4023	4023	4023	4023	4023	
5°	3513	3709	3665	3474	3513	300
15°	1385	1621	1579	1366	1385	390
25°	460	500	492	455	460	218
35°	67	118	109	62	67	60
45°	6	7	6	7	6	5
55°	5	5	5	5	5	4
65°	4	4	4	4	4	4
75°	2	2	3	3	2	3
85°	0	0	0	0	0	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	1	0	0	0	1	0
155°	2	2	2	2	2	1
165°	3	3	3	3	3	1
175°	4	4	3	3	4	0
180°	3	3	3	3	3	



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3870.7	3872.3	3874.1	3876.2	3878.4	3880.9	3883.5	3886.3	3889.3	3892.4	3895.7
5°	3513.4	3515.9	3519.0	3522.6	3526.7	3531.3	3536.4	3542.0	3548.1	3554.7	3561.8
7.5°	2995.8	2999.2	3003.4	3008.4	3014.2	3020.8	3028.2	3036.5	3045.5	3055.3	3065.9
10°	2427.1	2430.7	2435.3	2440.7	2447.0	2454.1	2462.0	2470.7	2480.2	2490.5	2501.5
12.5°	1875.7	1878.3	1881.8	1886.1	1891.3	1897.4	1904.4	1912.3	1921.1	1930.8	1941.5
15°	1384.6	1387.5	1391.1	1395.3	1400.4	1406.1	1412.6	1419.8	1427.8	1436.5	1445.9
17.5°	1010.8	1013.1	1015.9	1019.2	1023.2	1027.7	1032.8	1038.5	1044.8	1051.6	1059.1
20°	741.9	743.0	744.5	746.4	748.7	751.4	754.5	758.1	762.1	766.5	771.5
22.5°	565.3	566.3	567.6	569.1	570.8	572.8	575.1	577.6	580.3	583.3	586.3
25°	460.3	460.6	461.2	461.8	462.6	463.5	464.6	465.7	467.0	468.5	469.8
27.5°	393.2	393.7	394.4	395.2	396.0	397.0	398.1	399.3	400.6	402.0	403.1
30°	287.3	288.2	289.3	290.6	292.1	293.8	295.6	297.6	299.7	302.0	303.8
32.5°	172.5	173.1	173.9	174.9	176.1	177.4	178.9	180.6	182.4	184.4	185.9
35°	66.7	66.8	67.2	67.7	68.4	69.4	70.5	71.9	73.6	75.5	77.0
37.5°	14.0	14.1	14.2	14.4	14.6	14.9	15.2	15.6	16.1	16.6	17.0
40°	10.2	10.2	10.2	10.2	10.3	10.3	10.3	10.4	10.4	10.5	10.5
42.5°	7.2	7.2	7.2	7.3	7.3	7.3	7.3	7.4	7.4	7.5	7.5
45°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
47.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.7	5.7	5.7	5.7
50°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
52.5°	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9
55°	4.9	4.9	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
57.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.5	4.5	4.5	4.5
60°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
65°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.7	3.7
70°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
72.5°	2.6	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
75°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.2
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.3	1.3	1.3
85°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.2	1.2	1.2	1.2	1.2	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
160°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3899.1	3902.6	3906.2	3909.9	3913.6	3917.4	3921.3	3925.2	3931.9	3929.8	3929.1
5°	3569.3	3577.4	3585.9	3591.2	3594.7	3614.3	3610.5	3607.6	3613.4	3619.6	3626.3
7.5°	3077.3	3088.8	3094.0	3099.8	3106.4	3124.9	3121.4	3129.0	3137.4	3146.6	3156.7
10°	2513.2	2519.3	2524.9	2531.3	2556.0	2551.3	2555.5	2565.5	2576.0	2586.9	2598.2
12.5°	1951.2	1956.7	1962.9	1969.7	1990.5	1985.7	1994.1	2003.9	2014.3	2025.3	2036.9
15°	1452.4	1457.1	1462.4	1468.3	1483.8	1482.0	1490.1	1498.7	1507.9	1517.6	1525.6
17.5°	1063.1	1066.6	1070.5	1088.4	1085.3	1085.2	1091.6	1098.7	1106.3	1114.6	1119.7
20°	773.9	776.4	779.3	791.2	789.1	789.9	794.4	799.2	804.2	809.2	811.9
22.5°	587.5	588.8	590.4	597.1	595.6	596.4	599.1	601.9	605.0	607.6	615.0
25°	470.4	471.2	472.1	475.8	475.1	475.8	477.5	479.2	481.0	482.2	486.0
27.5°	403.4	403.9	404.5	407.4	406.7	407.0	408.0	409.1	410.3	411.1	413.8
30°	304.8	305.9	307.2	311.9	311.0	312.5	314.9	317.5	320.3	321.7	326.7
32.5°	186.7	187.7	189.0	193.5	192.5	194.5	197.3	200.4	203.6	205.5	211.4
35°	78.2	79.4	80.8	85.5	84.5	85.6	87.4	89.2	91.2	92.4	96.5
37.5°	17.3	17.6	17.9	18.8	18.5	18.8	19.2	19.6	20.0	20.2	21.0
40°	10.5	10.6	10.6	10.7	10.7	10.8	10.8	10.9	10.9	11.0	11.1
42.5°	7.6	7.6	7.6	7.8	7.7	7.8	7.9	7.9	8.0	8.1	8.2
45°	6.4	6.4	6.4	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.6
47.5°	5.7	5.7	5.7	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.9
50°	5.0	5.0	5.0	5.1	5.0	5.1	5.1	5.1	5.1	5.1	5.1
52.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
55°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
57.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.6	4.6	4.6
60°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
65°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
67.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
70°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
72.5°	2.7	2.7	2.7	2.8	2.8	2.8	2.8	2.8	2.8	2.9	2.9
75°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
77.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	1.3	1.3	1.3	1.4	1.4	1.4	1.4	1.5	1.5	1.5	1.5
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3
145°	0.6	0.6	0.5	0.6	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.4	1.4	1.4	1.4	1.4
155°	1.9	1.9	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.3	2.3	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.7	2.7	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	3.0	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.3	3.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3931.2	3933.5	3935.9	3938.4	3941.1	3943.9	3954.8	3952.6	3952.0	3953.1	3954.4
5°	3633.5	3641.1	3649.3	3664.8	3665.4	3668.1	3670.2	3672.9	3676.2	3687.4	3684.2
7.5°	3167.6	3198.7	3190.3	3191.7	3196.1	3200.9	3206.1	3228.8	3217.9	3225.8	3234.4
10°	2609.9	2624.5	2624.4	2633.5	2642.9	2652.5	2662.3	2674.6	2679.9	2687.8	2696.0
12.5°	2062.0	2050.5	2057.7	2065.5	2073.8	2082.6	2104.5	2101.4	2111.5	2122.1	2128.6
15°	1540.8	1535.6	1542.2	1548.8	1555.5	1562.3	1573.5	1576.7	1585.0	1591.9	1597.4
17.5°	1129.8	1127.8	1131.8	1136.3	1141.2	1160.0	1152.1	1157.9	1163.5	1166.6	1182.9
20°	817.5	818.7	823.1	827.4	831.7	844.3	840.2	844.5	848.2	851.1	861.6
22.5°	611.3	612.2	614.3	616.4	618.4	624.4	622.6	626.1	629.2	631.8	638.3
25°	483.8	484.6	485.8	486.9	487.9	490.8	490.1	491.5	492.4	493.4	496.1
27.5°	412.3	412.7	413.1	413.5	414.0	415.4	415.2	415.9	416.4	417.1	418.7
30°	324.3	325.4	326.7	328.2	329.9	333.3	333.5	334.7	335.2	335.9	337.7
32.5°	209.2	210.1	211.2	212.4	213.7	216.3	217.0	218.4	219.5	220.6	222.5
35°	95.1	96.2	97.4	98.7	100.0	102.2	103.6	105.5	107.2	108.8	110.6
37.5°	20.8	21.8	22.6	23.3	23.8	24.3	25.1	26.5	27.6	28.4	29.1
40°	11.0	11.1	11.2	11.3	11.3	11.4	11.5	11.5	11.5	11.6	11.6
42.5°	8.1	8.2	8.3	8.3	8.4	8.5	8.5	8.5	8.5	8.6	8.6
45°	6.6	6.6	6.6	6.6	6.6	6.6	6.7	6.7	6.7	6.7	6.7
47.5°	5.9	5.9	5.9	5.9	6.0	6.0	6.0	6.0	6.1	6.1	6.1
50°	5.1	5.2	5.2	5.2	5.2	5.2	5.3	5.3	5.3	5.3	5.3
52.5°	4.9	4.9	4.9	4.9	4.9	5.0	5.0	5.0	5.0	5.0	5.0
55°	4.8	4.8	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
57.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
60°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.3	4.3
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
65°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.2	4.2	4.2	4.2
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.9	3.9	3.9
70°	3.3	3.3	3.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
72.5°	2.9	2.9	2.9	3.0	3.0	3.0	3.0	3.0	3.1	3.1	3.1
75°	2.4	2.4	2.4	2.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.4
80°	2.0	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	1.5	1.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.7	1.7
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.1	1.1	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.3	1.3	1.3
155°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.7	1.7	1.7
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.1	2.1	2.1
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3956.0	3957.8	3959.9	3964.1	3963.0	3963.8	3964.6	3965.6	3966.6	3969.8	3967.5
5°	3688.0	3691.7	3695.1	3709.2	3701.3	3705.8	3708.3	3711.3	3725.6	3717.3	3719.6
7.5°	3243.6	3253.5	3261.0	3262.5	3265.8	3269.6	3291.2	3279.0	3283.6	3288.3	3292.9
10°	2701.1	2708.5	2710.4	2715.6	2720.8	2745.9	2731.6	2737.6	2743.1	2748.0	2762.3
12.5°	2147.5	2139.0	2143.5	2148.3	2153.2	2164.5	2164.1	2170.1	2175.4	2200.3	2183.7
15°	1606.8	1608.9	1615.1	1621.0	1645.5	1631.9	1635.5	1638.7	1641.2	1652.5	1646.7
17.5°	1172.6	1177.1	1181.5	1185.7	1199.0	1193.2	1196.4	1199.0	1201.5	1206.8	1207.1
20°	856.6	859.7	862.6	865.2	871.6	869.8	872.1	874.4	876.4	878.0	880.8
22.5°	635.8	637.4	639.0	640.5	643.6	644.0	645.8	647.3	654.7	649.6	651.3
25°	495.8	497.5	498.8	499.7	500.7	501.2	502.2	503.1	506.8	504.5	505.5
27.5°	418.6	419.3	419.8	420.3	420.7	421.1	421.5	421.8	423.6	422.5	422.8
30°	337.2	337.7	338.3	343.0	339.9	340.6	341.0	341.6	344.5	342.9	343.4
32.5°	223.1	224.4	225.6	230.6	227.5	228.2	228.8	229.5	231.9	230.9	231.8
35°	111.6	112.9	114.0	118.2	116.2	117.4	118.6	119.6	122.0	121.3	121.9
37.5°	29.5	29.9	30.2	31.6	30.8	31.9	32.9	33.7	34.8	35.0	35.7
40°	11.7	11.7	11.7	11.9	11.8	11.9	11.9	11.9	12.0	12.0	12.0
42.5°	8.6	8.6	8.7	8.8	8.7	8.8	8.9	8.9	9.0	8.9	8.9
45°	6.8	6.8	6.8	6.8	6.8	6.9	6.9	6.9	6.9	6.9	6.9
47.5°	6.1	6.2	6.2	6.2	6.2	6.3	6.3	6.3	6.3	6.3	6.3
50°	5.4	5.4	5.4	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
52.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.1	5.1	5.1
55°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
57.5°	4.6	4.6	4.7	4.7	4.7	4.7	4.7	4.8	4.7	4.7	4.7
60°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
65°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
67.5°	3.9	3.9	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
70°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.4	3.5	3.5
72.5°	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.8
85°	0.3	0.3	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.4	0.4
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6
150°	1.0	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9	0.9	0.9
152.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5
175°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
177.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3966.5	3965.9	3965.7	3968.8	3966.5	3964.9	3963.3	3961.6	3959.8	3958.0	3957.2
5°	3722.3	3725.6	3735.8	3731.3	3731.7	3729.3	3727.4	3725.8	3724.5	3723.7	3723.2
7.5°	3305.9	3298.7	3300.0	3301.3	3302.6	3305.0	3304.7	3305.2	3305.2	3323.8	3304.9
10°	2754.7	2757.2	2759.4	2761.3	2765.2	2764.4	2765.1	2766.5	2767.7	2770.6	2766.1
12.5°	2187.6	2190.9	2193.6	2208.0	2196.7	2197.9	2199.9	2201.2	2214.1	2200.8	2200.3
15°	1650.6	1653.7	1656.0	1661.0	1659.6	1662.7	1665.9	1667.9	1674.4	1667.7	1665.6
17.5°	1209.7	1211.5	1226.2	1212.7	1213.2	1215.4	1216.9	1232.4	1218.9	1219.0	1218.9
20°	883.1	884.7	893.9	886.5	887.6	888.9	889.5	898.1	888.8	888.0	886.5
22.5°	652.9	654.2	659.9	656.1	656.8	657.5	658.0	663.1	658.3	658.0	657.2
25°	506.0	506.1	507.6	505.4	506.4	507.1	507.6	510.0	507.8	507.8	507.3
27.5°	423.0	423.0	423.5	422.9	423.6	424.1	424.5	425.9	424.9	424.9	424.8
30°	343.9	344.3	345.7	344.7	344.6	344.5	344.4	345.8	344.1	344.1	343.9
32.5°	232.6	233.4	234.8	234.4	234.5	234.6	234.6	236.0	234.2	234.0	233.7
35°	122.2	122.4	122.7	122.7	123.1	123.3	123.3	124.3	123.1	123.0	122.7
37.5°	36.0	36.1	36.0	36.7	37.4	37.7	37.8	38.2	37.5	37.3	36.8
40°	12.0	12.0	12.0	12.0	12.0	12.0	11.9	12.0	11.9	11.9	11.8
42.5°	9.0	9.1	9.0	9.0	9.0	9.0	9.0	9.0	8.9	8.9	8.9
45°	6.9	7.0	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.8	6.8
47.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.2	6.2	6.2	6.2	6.2
50°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.4	5.4	5.4
52.5°	5.1	5.1	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9
55°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
57.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.8	4.7	4.7	4.7	4.7
60°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
65°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
67.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
70°	3.5	3.5	3.4	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4
72.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
75°	2.5	2.5	2.5	2.5	2.5	2.6	2.6	2.6	2.6	2.6	2.5
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.3	1.3	1.3	1.3	1.3	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.7	1.7	1.7	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.1	2.1	2.1	2.1	2.1	2.0	2.1	2.1	2.1	2.1	2.1
160°	2.5	2.5	2.5	2.5	2.5	2.4	2.5	2.4	2.4	2.4	2.4
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3	3.3
170°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3956.4	3955.8	3955.1	3954.6	3951.4	3948.7	3946.5	3945.0	3943.0	3939.2	3935.6
5°	3733.4	3722.2	3721.0	3719.1	3716.4	3723.5	3709.2	3702.1	3698.9	3696.8	3694.7
7.5°	3301.9	3299.0	3296.2	3293.3	3301.4	3286.8	3281.1	3275.3	3269.2	3262.7	3255.6
10°	2763.0	2759.0	2754.2	2764.5	2746.8	2745.0	2742.9	2739.4	2734.6	2728.4	2720.7
12.5°	2199.3	2197.8	2195.7	2207.6	2194.8	2191.1	2186.5	2180.8	2174.1	2166.4	2159.3
15°	1663.0	1659.9	1657.3	1661.9	1654.1	1651.2	1647.4	1642.6	1636.7	1629.9	1625.3
17.5°	1217.8	1215.7	1228.6	1217.0	1212.8	1210.3	1207.1	1203.1	1198.3	1192.6	1190.1
20°	884.5	882.0	890.2	882.0	880.5	879.2	877.1	874.4	871.0	866.9	865.5
22.5°	656.0	654.8	659.3	653.8	653.5	652.9	651.9	650.5	648.7	646.6	646.1
25°	506.3	505.6	507.8	505.2	505.4	505.2	504.6	503.6	502.3	501.0	500.7
27.5°	424.4	424.3	425.9	424.5	424.5	424.2	423.7	423.1	422.2	421.4	421.2
30°	343.6	343.7	346.2	343.9	343.5	343.1	342.5	341.8	340.9	340.3	340.2
32.5°	233.2	233.5	236.1	233.6	233.2	232.6	231.9	230.9	229.8	228.9	228.6
35°	122.2	122.5	124.7	122.4	121.9	121.3	120.4	119.4	118.1	117.2	116.8
37.5°	36.2	36.3	37.2	36.0	35.8	35.4	34.8	34.0	33.1	32.4	32.2
40°	11.8	11.7	11.8	11.7	11.6	11.6	11.5	11.4	11.4	11.3	11.3
42.5°	8.8	8.8	8.8	8.8	8.7	8.7	8.6	8.6	8.5	8.5	8.5
45°	6.8	6.8	6.7	6.7	6.7	6.7	6.6	6.6	6.6	6.6	6.5
47.5°	6.2	6.1	6.1	6.1	6.1	6.0	6.0	6.0	6.0	5.9	5.9
50°	5.4	5.4	5.4	5.3	5.3	5.3	5.3	5.3	5.2	5.2	5.2
52.5°	4.9	4.9	4.9	4.9	4.8	4.8	4.8	4.8	4.8	4.8	4.8
55°	4.9	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8	4.8	4.8
57.5°	4.7	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
60°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
65°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.1
67.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
70°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
72.5°	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2
75°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.5	2.5	2.5	2.5
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
177.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3932.2	3928.1	3927.4	3927.0	3927.1	3927.4	3928.2	3927.8	3928.0	3928.7	3930.0
5°	3692.3	3689.6	3699.0	3690.7	3682.2	3673.7	3665.1	3662.5	3660.0	3657.5	3655.0
7.5°	3248.4	3263.3	3252.6	3241.8	3231.0	3220.2	3209.3	3206.9	3204.5	3202.1	3199.8
10°	2717.2	2732.0	2720.1	2708.2	2696.2	2684.2	2672.2	2669.1	2665.9	2662.7	2659.5
12.5°	2156.0	2167.3	2156.1	2144.8	2133.5	2122.1	2110.8	2107.4	2104.0	2100.6	2097.2
15°	1622.2	1631.7	1621.1	1610.5	1600.0	1589.4	1578.8	1576.4	1574.0	1571.6	1569.2
17.5°	1202.2	1195.0	1187.8	1180.6	1173.4	1166.1	1158.9	1157.0	1155.0	1153.1	1151.1
20°	873.6	868.1	862.6	857.0	851.5	846.0	840.4	839.2	837.9	836.6	835.3
22.5°	652.5	648.8	645.0	641.3	637.6	633.9	630.1	629.4	628.7	627.9	627.2
25°	503.8	501.8	499.9	497.9	495.9	493.9	491.9	491.5	491.2	490.8	490.4
27.5°	422.8	421.8	420.9	419.9	419.0	418.0	417.0	416.9	416.8	416.7	416.6
30°	344.0	342.4	340.7	339.1	337.5	335.9	334.2	334.1	333.9	333.7	333.6
32.5°	232.2	230.2	228.2	226.3	224.3	222.3	220.4	220.2	220.1	220.0	219.9
35°	120.0	118.1	116.2	114.4	112.5	110.6	108.8	108.4	108.0	107.6	107.2
37.5°	33.7	32.6	31.5	30.4	29.3	28.2	27.1	26.9	26.7	26.5	26.3
40°	11.4	11.3	11.3	11.2	11.1	11.1	11.0	11.0	11.0	11.0	11.0
42.5°	8.5	8.5	8.4	8.3	8.3	8.2	8.1	8.1	8.1	8.1	8.1
45°	6.6	6.5	6.5	6.5	6.5	6.5	6.4	6.4	6.4	6.4	6.4
47.5°	5.9	5.9	5.9	5.9	5.8	5.8	5.8	5.8	5.8	5.8	5.8
50°	5.2	5.2	5.2	5.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1
52.5°	4.8	4.8	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
55°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.7	4.7
57.5°	4.8	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
60°	4.3	4.3	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
65°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
67.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
70°	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.4	3.4
72.5°	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2	3.2	3.2
75°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.7	1.7	1.7	1.7	1.7
85°	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.4	2.4	2.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.8	2.8	2.8	2.8	2.8	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3931.5	3928.1	3925.9	3923.7	3921.4	3921.7	3912.3	3908.0	3904.1	3900.8	3896.5
5°	3638.8	3636.0	3632.1	3627.4	3621.9	3616.8	3615.3	3622.7	3595.0	3586.0	3577.0
7.5°	3197.4	3169.2	3163.8	3157.8	3150.6	3142.5	3133.3	3123.3	3126.0	3105.0	3096.4
10°	2656.4	2627.1	2616.2	2609.9	2602.1	2593.0	2582.6	2570.8	2558.7	2562.8	2540.3
12.5°	2093.9	2067.2	2055.5	2048.4	2042.2	2034.9	2026.5	2017.0	2006.6	2005.9	1985.3
15°	1566.8	1545.0	1535.5	1528.1	1523.6	1518.2	1511.8	1504.5	1496.3	1493.0	1480.1
17.5°	1149.2	1147.2	1126.0	1119.6	1116.6	1112.8	1108.3	1103.0	1097.1	1092.8	1096.1
20°	834.1	832.8	819.1	814.3	812.4	810.0	807.0	803.6	799.6	795.9	798.0
22.5°	626.4	625.7	616.0	612.7	611.1	609.2	606.9	604.2	601.1	597.5	598.7
25°	490.1	489.7	484.7	482.8	482.0	481.2	480.3	479.3	478.1	476.9	477.7
27.5°	416.5	416.4	413.5	412.5	411.9	411.4	410.7	409.9	408.9	407.8	408.0
30°	333.4	333.2	327.4	325.5	324.3	323.3	322.2	320.9	319.6	318.1	318.7
32.5°	219.8	219.6	213.2	211.1	209.4	208.0	206.4	204.5	202.4	200.1	200.1
35°	106.9	106.5	100.9	99.0	97.6	96.4	95.1	93.5	91.6	89.5	89.3
37.5°	26.1	25.9	24.0	23.4	23.0	22.9	22.7	22.4	22.0	21.5	21.6
40°	11.0	11.0	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8
42.5°	8.1	8.1	8.0	7.9	7.9	7.9	7.9	7.9	7.8	7.8	7.8
45°	6.4	6.4	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.4	6.4
47.5°	5.8	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
50°	5.1	5.1	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
52.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.8
55°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
57.5°	4.7	4.7	4.7	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
60°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.3
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
65°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.3	4.3
67.5°	4.0	4.0	4.0	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
70°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
72.5°	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.0	3.0	3.0
75°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
82.5°	1.7	1.7	1.7	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.5
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.7	0.7
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.0	1.0
152.5°	1.2	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.6	1.6	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.2
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
172.5°	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.4	3.4
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3892.8	3889.6	3886.8	3885.0	3880.6	3877.6	3875.1	3873.1	3871.6	3875.6	3862.9
5°	3568.2	3576.1	3556.4	3550.2	3543.8	3537.8	3530.7	3524.0	3517.4	3513.1	3516.2
7.5°	3087.5	3078.3	3068.9	3079.3	3045.8	3038.6	3031.0	3024.5	3019.6	3015.2	3010.2
10°	2534.5	2527.9	2520.6	2515.0	2503.1	2492.4	2482.4	2476.1	2472.0	2463.7	2457.8
12.5°	1980.1	1973.9	1966.7	1958.5	1962.0	1940.5	1930.5	1921.1	1916.6	1923.8	1904.9
15°	1475.2	1471.4	1466.5	1460.6	1458.3	1445.9	1437.7	1429.0	1422.3	1421.1	1413.6
17.5°	1077.7	1074.1	1069.9	1065.0	1060.1	1067.1	1047.0	1039.8	1032.2	1028.1	1037.5
20°	785.8	783.2	780.3	777.0	773.4	777.0	765.9	761.6	757.0	753.7	758.1
22.5°	591.6	590.0	588.7	587.0	585.0	586.8	580.9	578.6	575.9	573.4	575.2
25°	474.1	472.9	472.1	471.1	469.9	470.7	467.6	466.2	464.7	463.0	463.6
27.5°	405.2	404.1	403.7	403.1	402.5	403.0	400.3	399.0	397.6	396.3	396.3
30°	314.4	312.4	310.8	309.2	307.5	307.4	303.3	300.9	298.5	295.9	295.0
32.5°	195.9	193.9	192.8	191.5	190.0	189.8	186.0	183.7	181.2	178.6	177.1
35°	85.4	83.2	82.1	80.7	79.2	78.7	76.9	75.9	74.6	73.2	72.3
37.5°	20.4	19.7	19.2	18.5	17.7	17.1	16.7	16.4	16.0	15.5	15.1
40°	10.7	10.7	10.7	10.7	10.6	10.6	10.5	10.5	10.4	10.4	10.3
42.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.7	7.6	7.6	7.5	7.4
45°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.5	6.5	6.5
47.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.8	5.8	5.8	5.8
50°	5.0	5.0	5.0	5.0	5.0	5.1	5.1	5.1	5.1	5.1	5.1
52.5°	4.8	4.8	4.8	4.8	4.8	4.9	4.9	4.9	4.9	4.9	5.0
55°	4.7	4.7	4.8	4.8	4.8	4.8	4.9	4.9	4.9	4.9	4.9
57.5°	4.7	4.6	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
60°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
62.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
65°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.4	4.4
67.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.8	3.8
70°	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
72.5°	3.0	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
75°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.1	2.1	2.1	2.1
82.5°	1.5	1.5	1.4	1.4	1.4	1.4	1.4	1.3	1.3	1.3	1.3
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
150°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
152.5°	1.3	1.3	1.3	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
155°	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.5	2.5	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	2.9	2.9	2.9	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3859.2	3856.0	3853.1	3854.3	3847.9	3845.6	3843.5	3841.7	3840.2	3841.8	3833.6
5°	3502.6	3497.0	3491.5	3486.1	3494.3	3474.4	3469.4	3465.0	3462.0	3473.8	3456.7
7.5°	3004.6	3007.2	2990.5	2984.9	2979.9	2975.3	2989.1	2963.4	2957.0	2950.3	2945.0
10°	2451.8	2445.8	2449.8	2429.9	2422.8	2416.4	2410.0	2424.7	2402.1	2398.5	2395.0
12.5°	1897.7	1889.6	1880.7	1892.4	1866.2	1860.9	1857.4	1859.5	1850.1	1845.8	1840.7
15°	1408.5	1402.7	1396.2	1398.3	1384.3	1378.3	1375.0	1372.4	1385.7	1365.9	1362.0
17.5°	1021.8	1017.7	1013.0	1010.4	1004.2	1000.0	996.1	994.3	1000.1	989.6	986.9
20°	749.5	746.9	743.8	740.4	737.8	734.8	731.5	729.8	732.2	727.7	726.2
22.5°	570.1	568.1	565.8	563.3	566.0	559.1	556.8	555.1	555.4	553.7	552.9
25°	461.8	461.2	460.5	459.7	461.1	458.1	457.1	456.1	455.6	454.8	454.1
27.5°	393.9	392.7	391.7	390.7	391.7	388.4	387.3	386.4	385.5	384.4	383.4
30°	292.1	290.2	288.2	286.3	286.6	282.3	280.2	278.1	276.6	279.8	274.6
32.5°	174.1	172.0	169.9	167.9	168.1	165.1	163.7	162.0	160.7	163.5	158.7
35°	70.4	68.8	67.1	65.4	65.1	63.3	62.3	61.2	60.3	62.3	59.4
37.5°	15.4	15.5	15.4	15.1	14.9	14.6	14.4	14.1	13.8	14.1	14.1
40°	10.3	10.3	10.4	10.4	10.4	10.3	10.3	10.2	10.2	10.2	10.1
42.5°	7.5	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
45°	6.5	6.5	6.5	6.5	6.6	6.6	6.6	6.6	6.6	6.6	6.6
47.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.9	5.9	5.9	5.9	5.9
50°	5.1	5.2	5.2	5.2	5.2	5.2	5.2	5.3	5.3	5.3	5.3
52.5°	5.0	5.0	5.1	5.1	5.1	5.1	5.1	5.2	5.2	5.2	5.2
55°	5.0	5.0	5.0	5.0	5.1	5.1	5.1	5.1	5.1	5.1	5.1
57.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
60°	4.3	4.3	4.3	4.3	4.3	4.4	4.4	4.4	4.4	4.4	4.4
62.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.4	4.4	4.4
65°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.5	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6
72.5°	2.9	2.9	2.9	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
75°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
77.5°	2.4	2.4	2.4	2.4	2.4	2.5	2.5	2.5	2.5	2.5	2.5
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	1.3	1.2	1.1	1.1	1.1	1.1	1.0	1.0	1.0	1.0	0.9
85°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
147.5°	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.0	1.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
152.5°	1.4	1.4	1.4	1.4	1.4	1.5	1.4	1.5	1.5	1.5	1.5
155°	1.8	1.8	1.8	1.8	1.8	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.2	2.2	2.2	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
160°	2.6	2.6	2.6	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3830.1	3827.2	3825.1	3823.6	3822.8	3825.5	3831.5	3821.3	3821.1	3821.1	3821.3
5°	3454.1	3451.6	3449.2	3455.8	3443.3	3441.0	3439.2	3438.1	3437.5	3444.1	3436.2
7.5°	2941.3	2940.3	2939.1	2937.8	2936.3	2951.9	2929.6	2927.2	2925.5	2924.6	2927.0
10°	2394.7	2385.2	2379.4	2375.1	2371.4	2370.6	2366.7	2364.9	2363.0	2361.1	2359.2
12.5°	1835.1	1842.0	1826.9	1824.2	1822.8	1821.4	1831.1	1815.3	1812.1	1809.1	1806.4
15°	1357.6	1356.7	1350.1	1346.6	1343.8	1342.0	1344.3	1338.7	1336.9	1334.9	1332.7
17.5°	984.0	980.9	990.5	977.4	975.5	974.5	973.3	983.9	970.7	969.6	968.4
20°	724.2	721.8	726.1	718.3	716.5	715.2	714.3	720.2	713.5	712.9	712.1
22.5°	551.9	550.5	552.3	548.5	547.4	546.4	545.9	548.8	545.9	545.8	545.6
25°	453.3	452.4	452.9	451.1	450.5	449.9	449.8	451.2	449.7	449.6	449.4
27.5°	382.6	382.1	382.8	380.4	379.4	378.6	377.7	378.5	376.0	375.5	375.3
30°	273.7	272.7	272.9	270.8	269.8	268.8	268.1	269.2	267.2	266.8	266.5
32.5°	157.7	156.8	156.7	155.0	154.0	153.0	152.2	152.9	151.6	151.6	151.6
35°	58.9	58.3	58.0	57.3	56.7	56.0	55.5	55.9	55.4	55.4	55.3
37.5°	14.1	13.9	13.7	13.6	13.5	13.4	13.4	13.6	13.7	13.8	13.7
40°	10.1	10.1	10.1	10.1	10.0	10.0	10.0	10.0	10.0	10.0	9.9
42.5°	7.4	7.4	7.4	7.4	7.3	7.3	7.3	7.3	7.3	7.3	7.3
45°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
47.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.8	5.8
50°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
52.5°	5.2	5.2	5.2	5.2	5.2	5.3	5.3	5.3	5.2	5.2	5.2
55°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.0	5.0
57.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.6
60°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
62.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
65°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.3	4.3	4.3	4.3
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.5
72.5°	2.9	2.9	2.9	2.9	2.9	2.8	2.8	2.8	2.8	2.8	2.8
75°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
77.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.4	2.4
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	0.9	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.8	0.8	0.8
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.4	0.3	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
150°	1.1	1.1	1.1	1.1	1.1	1.1	1.2	1.2	1.2	1.2	1.2
152.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
155°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.0	1.9	2.0
157.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
160°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3821.8	3822.5	3823.3	3827.7	3833.7	3827.7	3827.9	3828.4	3829.0	3829.8	3830.8
5°	3435.7	3435.5	3435.6	3435.9	3436.5	3437.5	3447.8	3459.0	3445.8	3449.8	3452.9
7.5°	2943.0	2923.7	2923.5	2923.6	2924.1	2925.1	2926.6	2939.3	2930.7	2933.9	2937.9
10°	2365.8	2357.9	2357.5	2357.1	2357.0	2357.3	2357.9	2364.0	2378.6	2363.8	2367.2
12.5°	1804.1	1820.2	1806.0	1806.1	1806.5	1807.2	1808.3	1810.3	1823.8	1813.6	1816.4
15°	1330.5	1339.0	1330.5	1330.8	1330.8	1330.9	1331.2	1331.7	1340.9	1334.0	1335.8
17.5°	967.4	971.9	967.0	966.9	966.6	966.4	966.4	966.6	972.3	980.7	971.0
20°	711.3	712.8	710.3	710.1	709.8	709.6	709.5	709.5	712.6	718.3	712.7
22.5°	545.3	545.8	549.8	544.4	544.4	544.7	545.1	545.6	547.9	551.9	548.5
25°	449.1	449.0	451.2	448.7	448.7	448.8	448.8	448.9	449.7	451.7	450.3
27.5°	375.4	375.9	379.3	375.8	375.7	375.4	375.3	375.5	376.8	379.7	377.5
30°	266.3	266.1	269.9	266.3	266.5	266.5	266.7	267.1	268.3	271.9	269.1
32.5°	151.6	151.7	155.1	152.4	152.9	153.1	153.4	153.8	155.0	158.3	155.6
35°	55.3	55.2	57.4	55.5	55.7	55.9	56.0	56.1	56.7	59.0	57.2
37.5°	13.6	13.4	13.4	13.3	13.3	13.5	13.5	13.5	13.5	13.7	13.6
40°	9.9	9.9	10.0	9.9	9.9	9.9	9.9	9.9	9.9	10.0	9.9
42.5°	7.3	7.2	7.2	7.2	7.2	7.2	7.2	7.1	7.1	7.2	7.1
45°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.4	6.4	6.4
47.5°	5.8	5.8	5.8	5.8	5.8	5.7	5.7	5.7	5.7	5.7	5.7
50°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.1	5.1	5.1
52.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.1	5.1	5.1	5.1	5.1
55°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	4.9	4.9	4.9	4.9
57.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.5	4.5	4.5	4.5	4.5
60°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
62.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.2
65°	4.3	4.3	4.3	4.3	4.3	4.2	4.2	4.2	4.2	4.2	4.2
67.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
70°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.4
72.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7
75°	2.6	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5	2.5	2.5
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.0	2.0	2.0	2.0	2.0
82.5°	0.8	0.8	0.9	0.9	0.8	0.8	0.8	0.8	0.8	0.9	0.9
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.8	0.8	0.8	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9
150°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
152.5°	1.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
155°	2.0	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.0	2.0	1.9
157.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
160°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.5
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
177.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1	4023.1
2.5°	3832.0	3833.4	3835.0	3836.9	3839.0	3841.3	3843.8	3846.6	3849.6	3852.9	3856.4
5°	3454.2	3455.9	3458.2	3460.9	3464.2	3467.9	3472.2	3476.9	3482.2	3487.9	3494.2
7.5°	2942.6	2943.4	2944.5	2946.2	2948.7	2951.8	2955.8	2960.4	2965.8	2972.0	2978.9
10°	2371.3	2375.4	2376.4	2378.2	2380.7	2384.0	2388.0	2392.9	2398.7	2405.2	2412.6
12.5°	1820.0	1824.2	1826.0	1827.4	1829.4	1832.2	1835.7	1840.0	1845.1	1851.0	1857.7
15°	1338.2	1341.0	1343.3	1344.7	1346.9	1349.7	1353.1	1357.3	1362.1	1367.6	1373.8
17.5°	973.2	975.7	978.1	979.5	981.3	983.5	986.1	989.3	992.8	996.9	1001.5
20°	714.2	715.9	717.7	718.7	719.8	721.2	722.9	724.9	727.2	729.8	732.8
22.5°	549.6	550.6	551.8	552.1	552.5	553.1	554.0	555.0	556.4	557.9	559.7
25°	450.9	451.6	452.4	452.8	453.1	453.4	453.8	454.3	454.8	455.5	456.3
27.5°	378.5	379.7	381.1	381.7	382.2	382.9	383.8	384.8	386.1	387.4	389.0
30°	270.2	271.4	272.8	273.6	274.1	274.8	275.7	276.9	278.2	279.7	281.5
32.5°	156.4	157.4	158.6	159.3	159.8	160.4	161.3	162.3	163.6	165.0	166.7
35°	57.7	58.2	58.9	59.3	59.6	60.0	60.5	61.1	61.9	62.8	63.8
37.5°	13.6	13.6	13.6	13.7	13.7	13.8	13.8	13.8	13.9	13.9	14.0
40°	9.9	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0
42.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
45°	6.4	6.4	6.4	6.4	6.3	6.3	6.3	6.3	6.3	6.3	6.3
47.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
50°	5.1	5.1	5.1	5.1	5.0	5.0	5.0	5.0	5.0	5.0	5.0
52.5°	5.1	5.1	5.1	5.1	5.0	5.0	5.0	5.0	5.0	5.0	5.0
55°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.8	4.8	4.8
57.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.4	4.4	4.4
60°	4.3	4.3	4.3	4.3	4.3	4.3	4.2	4.2	4.2	4.2	4.2
62.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
65°	4.2	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.1	4.1	4.1
67.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
70°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3
72.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.6	2.6
75°	2.5	2.5	2.5	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
77.5°	2.4	2.4	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
82.5°	0.9	0.9	0.9	1.0	1.0	1.0	1.0	1.0	1.0	1.1	1.1
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
145°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
147.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.8
150°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
152.5°	1.6	1.6	1.6	1.6	1.5	1.5	1.5	1.5	1.5	1.5	1.5
155°	2.0	2.0	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
157.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
160°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5
172.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
175°	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5
177.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
180°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9



TEST NUMBER: P979202
 CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	4023.1	4023.1
2.5°	3860.2	3870.7
5°	3501.0	3513.4
7.5°	2986.6	2995.8
10°	2420.9	2427.1
12.5°	1865.2	1875.7
15°	1380.7	1384.6
17.5°	1006.6	1010.8
20°	736.1	741.9
22.5°	561.8	565.3
25°	457.1	460.3
27.5°	390.7	393.2
30°	283.4	287.3
32.5°	168.5	172.5
35°	65.1	66.7
37.5°	14.0	14.0
40°	10.1	10.2
42.5°	7.2	7.2
45°	6.3	6.4
47.5°	5.6	5.6
50°	5.0	5.0
52.5°	5.0	5.0
55°	4.8	4.9
57.5°	4.4	4.4
60°	4.2	4.2
62.5°	4.1	4.1
65°	4.1	4.1
67.5°	3.6	3.6
70°	3.3	3.3
72.5°	2.6	2.6
75°	2.4	2.4
77.5°	2.3	2.3
80°	2.0	2.0
82.5°	1.1	1.2
85°	0.1	0.1
87.5°	0.1	0.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



TEST NUMBER: P979202
CATALOG NUMBER: L820S10MF935XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.1	0.1
135°	0.1	0.1
137.5°	0.1	0.1
140°	0.2	0.2
142.5°	0.4	0.4
145°	0.6	0.6
147.5°	0.8	0.8
150°	1.2	1.2
152.5°	1.5	1.5
155°	1.9	1.9
157.5°	2.3	2.3
160°	2.7	2.7
162.5°	3.0	3.0
165°	3.3	3.3
167.5°	3.4	3.4
170°	3.5	3.5
172.5°	3.5	3.6
175°	3.5	3.6
177.5°	3.5	3.5
180°	2.9	2.9

(END OF REPORT)