

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: HALO

Report Number: P979208

Luminaire Tested: L820S10SP927XXXXBLSHBXXXX

Issue Date: 4/1/2025

Test Information

Test Method: LM-79-2019
Report Number: P979208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (3DTHCNLSLWHSTLFWHST15LRS30KWH)
Test Lab: INNOVATION CENTER
Issue Date: 4/1/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: L820S10SP927XXXXBLSHBXXXX
Description: 2IN Sustainable LED Track Luminaire with spot optic
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 922.9 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.22' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9
Total Harmonic Distortion (THDi): 20
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979208
CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	101	103	100	99	100	98	97	97	96	95	93
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90
4	104	99	95	92	103	98	94	91	96	93	90	94	91	89	92	90	88	87
5	101	95	91	88	100	94	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	88	84	82	87	83	81	86	83	81	80
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	83	81	79	78
9	91	84	80	78	90	84	80	77	83	80	77	82	79	77	82	79	77	76
10	89	82	78	75	88	82	78	75	81	78	75	80	77	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	1664990	1664990	1664990	1664990
5°	1385848	1519767	1484521	1355956
10°	564878	744026	686106	539890
15°	229566	279342	265581	221999
20°	137218	152141	150585	133732
25°	106279	111834	111864	105323
30°	76961	90153	86496	73710
35°	21184	34866	29611	17450
40°	2827	3251	3110	2721
45°	1723	1991	2029	1799
50°	1474	1685	1727	1558
55°	1416	1510	1605	1463
60°	1678	1678	1733	1678
65°	2050	1986	2114	2114
70°	2295	2454	2375	2137
75°	1987	1987	1883	1883
80°	2650	2494	2494	2494
85°	311	621	621	311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 87.5°
 Vertical Angle: 82.5°
 Luminance: 2904 cd/sqm



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	399.3	43.3
10°-20°	280.3	30.4
20°-30°	169.2	18.3
30°-40°	59.1	6.4
40°-50°	4.1	0.4
50°-60°	2.9	0.3
60°-70°	3.2	0.3
70°-80°	2.1	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.1	0.0
140°-150°	0.2	0.0
150°-160°	0.7	0.1
160°-170°	0.9	0.1
170°-180°	0.3	0.0
0°-30°	848.8	92.0
0°-40°	907.8	98.4
0°-60°	914.9	99.1
0°-90°	920.7	99.8
90°-120°	0.0	0.0
90°-150°	0.3	0.0
90°-180°	2.0	0.2
0°-180°	922.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	6150	6150	6150	6150	6150	
5°	5100	5592	5463	4990	5100	380
15°	819	997	948	792	819	256
25°	356	374	374	353	356	164
35°	64	106	90	53	64	53
45°	4	5	5	5	4	4
55°	3	3	3	3	3	3
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	2	2	2	2	2	1
165°	3	3	3	3	3	1
175°	3	3	3	3	3	0
180°	2	2	2	2	2	



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	5910.1	5910.1	5910.5	5911.2	5912.2	5913.6	5915.3	5917.4	5919.9	5922.8	5926.1
5°	5099.7	5106.5	5114.8	5124.6	5135.9	5148.6	5162.7	5178.1	5194.9	5212.9	5232.1
7.5°	3536.4	3546.2	3558.2	3572.6	3589.4	3608.5	3629.9	3653.7	3679.8	3708.3	3739.1
10°	2054.9	2062.6	2072.4	2084.1	2097.7	2113.4	2131.1	2150.7	2172.4	2196.0	2221.7
12.5°	1223.9	1227.6	1232.3	1238.0	1244.7	1252.4	1261.1	1270.8	1281.5	1293.3	1306.0
15°	819.1	820.9	823.3	826.2	829.5	833.4	837.7	842.4	847.6	853.2	859.3
17.5°	601.2	602.4	603.9	605.6	607.7	610.0	612.6	615.5	618.7	622.2	625.9
20°	476.3	477.1	478.1	479.3	480.7	482.2	483.8	485.6	487.6	489.6	491.8
22.5°	404.7	404.9	405.2	405.7	406.2	406.8	407.6	408.5	409.5	410.7	411.9
25°	355.8	355.9	356.1	356.4	356.7	357.1	357.5	358.1	358.7	359.4	360.0
27.5°	322.6	322.8	323.1	323.4	323.7	324.2	324.6	325.1	325.7	326.2	326.7
30°	246.2	246.8	247.5	248.5	249.5	250.8	252.2	253.7	255.4	257.2	258.8
32.5°	153.4	153.9	154.6	155.4	156.4	157.7	159.1	160.7	162.5	164.5	166.1
35°	64.1	64.6	65.2	66.0	66.9	67.9	69.1	70.5	72.0	73.6	74.7
37.5°	12.1	12.3	12.4	12.7	13.0	13.3	13.7	14.2	14.7	15.2	15.7
40°	8.0	8.0	8.0	8.0	8.0	8.0	8.1	8.1	8.1	8.2	8.2
42.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.7	5.7	5.7	5.8	5.8
45°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
47.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
50°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
52.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.1
55°	3.0	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
57.5°	2.9	2.9	2.9	2.9	2.9	2.8	2.8	2.8	2.8	2.8	2.8
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
62.5°	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.0	3.0
65°	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.1
67.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
70°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
72.5°	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.3	2.3	2.3	2.3
75°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
77.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.2	1.2	1.2	1.2
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.6	1.6	1.6	1.6	1.6
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	3.0	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.0	3.0	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
177.5°	2.7	2.7	2.8	2.8	2.8	2.8	2.9	2.9	2.9	2.9	2.9
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208

CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	5929.8	5934.0	5938.6	5943.7	5949.2	5955.1	5961.6	5968.6	5984.5	5981.6	5981.1
5°	5252.4	5273.9	5296.4	5309.6	5317.6	5372.5	5361.0	5351.5	5360.2	5370.5	5382.2
7.5°	3772.1	3805.2	3818.8	3834.5	3852.4	3905.7	3894.2	3916.0	3939.5	3964.6	3991.1
10°	2249.3	2263.7	2276.8	2291.5	2348.2	2336.6	2346.6	2370.6	2395.8	2422.2	2449.8
12.5°	1317.5	1324.0	1331.2	1339.0	1362.8	1357.4	1368.5	1381.2	1394.5	1408.5	1423.2
15°	863.4	866.0	869.1	872.5	882.1	880.7	886.4	892.5	898.8	905.3	911.1
17.5°	627.7	629.1	630.6	639.0	637.1	636.7	639.6	642.6	645.8	649.2	651.4
20°	492.3	492.9	493.6	498.0	496.8	496.9	498.6	500.6	502.6	504.7	506.0
22.5°	412.3	412.9	413.5	416.5	415.7	415.8	416.7	417.6	418.5	419.3	422.1
25°	360.2	360.4	360.6	362.2	361.6	361.7	362.2	362.8	363.4	364.0	366.1
27.5°	326.8	327.1	327.4	329.1	328.7	328.9	329.3	329.7	330.2	330.3	331.5
30°	259.8	260.9	262.1	266.1	265.5	266.4	268.1	269.9	271.7	272.8	276.3
32.5°	167.1	168.3	169.6	174.0	173.1	174.1	175.9	177.8	180.0	180.9	184.7
35°	75.3	76.1	76.9	80.1	79.2	80.2	81.6	83.2	84.9	85.7	89.0
37.5°	15.9	16.2	16.5	17.5	17.1	17.7	18.4	19.1	19.8	20.2	21.4
40°	8.2	8.3	8.3	8.4	8.4	8.4	8.5	8.5	8.6	8.6	8.7
42.5°	5.8	5.8	5.9	6.0	5.9	6.0	6.0	6.1	6.1	6.2	6.3
45°	4.5	4.5	4.5	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.7
47.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.1
50°	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
52.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2
55°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	3.0
57.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
60°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
62.5°	3.0	3.1	3.1	3.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0
65°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
67.5°	3.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
70°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
72.5°	2.3	2.3	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
75°	1.9	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
77.5°	1.8	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.7	1.6	1.6	1.7	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.3	1.3	1.3	1.3	1.3
85°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.1	1.1	1.1	1.1	1.1
155°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.1	2.1	2.1	2.1	2.1	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
177.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	5985.3	5989.8	5994.5	5999.5	6004.7	6010.1	6029.1	6025.9	6026.1	6029.8	6033.8
5°	5395.5	5410.3	5426.8	5460.5	5463.1	5469.5	5474.2	5481.2	5490.7	5524.2	5513.8
7.5°	4019.1	4103.6	4074.4	4078.7	4092.1	4107.0	4123.2	4195.6	4159.6	4178.7	4198.7
10°	2478.3	2512.3	2509.0	2526.2	2543.2	2559.9	2576.1	2597.0	2610.8	2630.5	2650.0
12.5°	1454.1	1440.1	1451.4	1462.6	1473.5	1483.8	1509.7	1504.4	1516.7	1528.3	1537.7
15°	922.8	920.1	926.2	932.4	938.4	944.3	953.4	957.4	964.9	970.7	975.5
17.5°	656.1	655.7	658.9	662.0	665.2	676.1	671.5	675.4	679.1	681.5	692.0
20°	508.5	508.9	510.7	512.6	514.4	519.9	518.0	519.9	521.4	522.5	526.9
22.5°	420.6	421.1	422.0	422.9	423.9	426.6	426.0	427.3	428.2	428.9	431.0
25°	365.2	365.8	366.5	367.2	367.8	369.3	369.0	369.9	370.4	371.0	372.5
27.5°	330.8	331.0	331.4	331.8	332.3	333.3	333.4	333.9	334.2	334.5	335.4
30°	274.6	275.5	276.4	277.5	278.6	281.0	281.1	281.9	282.0	282.4	283.7
32.5°	182.8	183.8	184.9	186.2	187.5	190.0	190.4	191.5	192.3	193.1	194.4
35°	87.6	88.7	89.9	91.1	92.4	94.5	95.2	96.4	97.4	98.4	99.7
37.5°	20.9	21.6	22.2	22.7	23.1	23.6	23.9	24.7	25.3	25.8	26.1
40°	8.7	8.7	8.7	8.8	8.8	8.9	8.9	8.9	9.0	9.0	9.0
42.5°	6.3	6.3	6.4	6.4	6.5	6.5	6.5	6.6	6.6	6.7	6.7
45°	4.7	4.7	4.8	4.8	4.8	4.8	4.9	4.9	4.9	5.0	5.0
47.5°	4.1	4.1	4.1	4.2	4.2	4.2	4.2	4.3	4.3	4.4	4.4
50°	3.6	3.6	3.6	3.7	3.7	3.7	3.7	3.7	3.8	3.8	3.8
52.5°	3.2	3.3	3.3	3.3	3.4	3.4	3.4	3.4	3.5	3.5	3.5
55°	3.0	3.0	3.0	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1
57.5°	2.8	2.8	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
60°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.1	3.1
62.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
65°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
67.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
70°	2.9	2.9	2.9	2.9	2.9	2.9	3.0	3.0	3.0	3.0	3.0
72.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
75°	1.8	1.8	1.8	1.8	1.9	1.8	1.9	1.9	1.9	1.9	1.9
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.7	0.7
152.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
155°	1.6	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.4	2.4	2.4
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
177.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	6038.3	6043.2	6048.4	6057.9	6054.5	6053.7	6053.2	6053.1	6053.2	6056.8	6054.8
5°	5522.3	5532.9	5545.6	5592.5	5576.4	5583.7	5577.3	5573.2	5593.3	5569.5	5571.4
7.5°	4219.5	4241.0	4257.7	4262.7	4270.5	4277.5	4333.7	4289.3	4300.6	4313.0	4326.3
10°	2665.1	2684.6	2692.0	2706.6	2720.0	2783.7	2743.0	2753.0	2760.4	2765.9	2795.1
12.5°	1563.9	1555.8	1566.0	1574.1	1580.1	1591.9	1591.9	1600.3	1608.7	1648.9	1625.3
15°	983.3	986.2	991.9	996.7	1015.1	1003.6	1008.2	1012.2	1016.6	1028.8	1024.4
17.5°	686.1	688.5	690.6	692.2	698.5	694.9	697.3	699.9	702.3	706.0	705.9
20°	524.6	526.0	527.2	528.1	530.7	529.6	530.7	532.1	533.3	534.1	534.8
22.5°	430.0	430.8	431.5	432.2	433.6	433.5	434.0	434.4	436.9	434.7	435.0
25°	372.3	373.1	373.8	374.4	375.1	375.3	375.3	375.3	376.5	375.2	375.4
27.5°	335.3	335.6	335.9	336.1	336.4	336.6	336.6	336.7	337.6	337.1	337.3
30°	283.3	283.9	284.6	288.4	286.4	286.8	286.5	286.4	287.8	286.2	286.2
32.5°	194.5	195.2	195.8	199.6	197.0	197.6	198.1	198.5	200.5	199.1	199.2
35°	100.4	101.3	102.1	105.5	103.6	104.2	104.6	105.1	106.6	105.9	106.4
37.5°	26.7	27.2	27.5	28.9	27.8	28.7	29.5	30.1	30.9	30.8	31.1
40°	9.1	9.1	9.2	9.2	9.2	9.2	9.3	9.3	9.3	9.4	9.4
42.5°	6.7	6.7	6.8	6.9	6.9	6.9	6.9	7.0	7.0	7.0	7.0
45°	5.0	5.1	5.1	5.2	5.2	5.2	5.3	5.3	5.3	5.3	5.4
47.5°	4.5	4.5	4.6	4.6	4.7	4.7	4.7	4.7	4.7	4.8	4.8
50°	3.9	3.9	3.9	4.0	4.0	4.0	4.1	4.1	4.1	4.2	4.2
52.5°	3.5	3.6	3.6	3.6	3.6	3.7	3.7	3.7	3.7	3.7	3.7
55°	3.1	3.1	3.2	3.2	3.2	3.2	3.3	3.3	3.3	3.3	3.4
57.5°	2.9	2.9	2.9	2.9	2.9	3.0	3.0	3.0	3.0	3.0	3.1
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.2
62.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2	3.2
65°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2
67.5°	3.4	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.4	3.4	3.4
70°	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
72.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.3	2.3	2.3
75°	1.9	1.9	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.3	1.3	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
85°	0.3	0.3	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
152.5°	1.1	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
155°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
157.5°	2.0	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.9	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
177.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	6056.5	6058.5	6060.8	6071.3	6066.6	6063.1	6059.8	6056.6	6053.6	6051.0	6049.9
5°	5576.0	5583.5	5610.3	5601.6	5608.0	5604.9	5606.2	5611.8	5605.1	5601.7	5600.9
7.5°	4369.4	4340.2	4334.7	4329.8	4325.4	4324.5	4319.1	4314.3	4306.4	4355.9	4297.5
10°	2776.4	2785.8	2793.9	2800.7	2812.8	2798.1	2784.9	2775.9	2767.9	2762.4	2758.9
12.5°	1630.0	1631.5	1629.8	1640.6	1621.4	1621.0	1625.9	1630.2	1651.5	1630.3	1624.5
15°	1027.2	1028.1	1027.1	1026.7	1023.0	1024.3	1026.7	1027.7	1031.4	1026.2	1024.0
17.5°	706.7	706.7	713.4	704.2	704.4	707.0	708.9	718.8	710.6	711.0	711.2
20°	535.0	534.9	537.5	533.7	534.6	536.2	537.3	542.2	538.4	538.5	538.3
22.5°	435.3	435.4	437.0	435.4	436.4	437.4	438.2	440.8	438.9	438.9	438.7
25°	375.6	375.6	376.5	375.5	376.0	376.5	376.8	378.1	377.2	377.3	377.3
27.5°	337.5	337.6	338.1	337.8	338.0	338.1	338.3	339.0	338.5	338.5	338.5
30°	286.2	286.3	287.2	286.6	286.7	286.8	286.7	287.9	286.3	285.9	285.4
32.5°	199.3	199.3	199.9	199.2	199.2	199.0	198.8	199.6	198.0	197.6	197.2
35°	106.7	107.0	107.4	107.1	107.2	107.2	107.1	107.8	106.3	105.7	104.8
37.5°	31.2	31.1	30.8	31.4	31.9	32.2	32.3	32.6	32.0	31.8	31.4
40°	9.5	9.5	9.4	9.5	9.5	9.5	9.6	9.6	9.6	9.6	9.6
42.5°	7.1	7.2	7.1	7.1	7.2	7.2	7.3	7.3	7.3	7.3	7.3
45°	5.4	5.5	5.4	5.5	5.5	5.5	5.6	5.6	5.6	5.6	5.6
47.5°	4.8	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	5.0	5.0
50°	4.2	4.3	4.3	4.3	4.3	4.4	4.4	4.4	4.4	4.4	4.5
52.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.9	3.9	3.9	3.9	3.9
55°	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5
57.5°	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2
60°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
62.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
65°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3
67.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
70°	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2
72.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.4	1.4	1.4	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
150°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
152.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
155°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
157.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
177.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	6049.0	6048.7	6048.9	6049.8	6044.0	6038.3	6033.0	6026.6	6022.7	6016.1	6010.0
5°	5626.3	5605.1	5592.5	5583.3	5577.0	5605.6	5576.4	5565.0	5556.6	5546.9	5535.6
7.5°	4301.6	4302.8	4301.0	4295.9	4326.0	4280.0	4267.6	4252.6	4234.7	4213.7	4189.5
10°	2758.1	2752.7	2742.6	2775.0	2729.2	2719.8	2708.5	2693.3	2674.2	2651.1	2624.2
12.5°	1615.8	1604.3	1590.0	1596.1	1580.1	1580.0	1576.8	1570.6	1561.4	1549.3	1537.9
15°	1020.3	1015.0	1010.5	1013.7	1007.7	1005.3	1001.6	996.8	990.8	983.6	979.4
17.5°	710.6	709.1	717.4	710.7	708.3	706.8	704.8	702.3	699.3	695.7	694.4
20°	537.7	536.9	541.1	537.8	537.6	537.4	536.8	535.9	534.7	533.2	532.7
22.5°	438.4	438.1	440.3	438.4	438.5	438.5	438.2	437.7	436.9	436.1	436.2
25°	377.2	377.2	378.4	377.2	377.3	377.4	377.3	377.0	376.7	376.4	376.6
27.5°	338.3	338.4	339.3	338.8	339.0	339.1	339.1	338.9	338.7	338.6	338.8
30°	284.9	284.7	286.4	284.5	284.1	283.7	283.2	282.6	281.8	281.3	281.3
32.5°	196.7	196.6	198.5	196.1	195.5	194.7	193.7	192.6	191.4	190.5	190.2
35°	103.8	103.5	104.6	102.6	102.2	101.6	100.8	99.8	98.5	97.7	97.3
37.5°	30.8	30.9	31.6	30.5	30.2	29.8	29.1	28.3	27.4	26.8	26.5
40°	9.6	9.5	9.5	9.5	9.5	9.4	9.4	9.4	9.3	9.3	9.2
42.5°	7.3	7.3	7.3	7.3	7.3	7.2	7.2	7.1	7.1	7.0	7.0
45°	5.6	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.6	5.6
47.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
50°	4.5	4.4	4.4	4.4	4.4	4.4	4.4	4.3	4.3	4.3	4.3
52.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.8	3.8
55°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
57.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
60°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
62.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.2	3.2
65°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2
67.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
72.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
75°	2.0	2.0	2.0	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
150°	0.7	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
152.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
155°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
157.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
177.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	6004.6	5998.7	5996.5	5994.4	5993.0	5992.4	5992.4	5993.8	5995.4	5997.2	5999.2
5°	5522.4	5506.9	5523.4	5508.5	5493.4	5478.2	5462.8	5458.5	5454.2	5450.0	5445.9
7.5°	4163.4	4203.3	4170.0	4136.4	4102.7	4068.8	4034.9	4026.4	4017.9	4009.4	4001.0
10°	2611.7	2639.6	2611.0	2582.4	2553.6	2524.8	2495.9	2486.3	2476.7	2467.2	2457.7
12.5°	1533.6	1550.3	1532.9	1515.4	1497.9	1480.4	1462.9	1457.0	1451.1	1445.3	1439.4
15°	977.4	984.4	977.1	969.7	962.3	955.0	947.6	944.8	942.0	939.1	936.3
17.5°	701.1	697.2	693.2	689.3	685.4	681.4	677.5	676.2	674.9	673.6	672.3
20°	536.4	534.2	531.9	529.6	527.3	525.0	522.7	522.2	521.6	521.1	520.6
22.5°	438.9	437.9	436.8	435.8	434.8	433.8	432.7	432.4	432.0	431.7	431.3
25°	378.6	377.9	377.2	376.5	375.8	375.2	374.5	374.3	374.1	374.0	373.8
27.5°	340.1	339.9	339.7	339.5	339.3	339.1	338.9	338.9	338.9	338.9	338.9
30°	284.2	283.0	281.7	280.5	279.2	278.0	276.7	276.5	276.3	276.1	275.9
32.5°	193.2	191.5	189.8	188.1	186.5	184.8	183.1	182.7	182.2	181.8	181.4
35°	99.8	98.1	96.4	94.7	93.0	91.3	89.6	89.0	88.5	87.9	87.4
37.5°	27.7	26.7	25.6	24.6	23.6	22.6	21.5	21.2	20.9	20.6	20.3
40°	9.3	9.2	9.1	9.1	9.0	8.9	8.8	8.8	8.8	8.8	8.8
42.5°	7.0	7.0	6.9	6.8	6.7	6.7	6.6	6.6	6.5	6.5	6.4
45°	5.6	5.5	5.5	5.5	5.4	5.4	5.3	5.3	5.3	5.2	5.2
47.5°	4.9	4.9	4.8	4.8	4.7	4.7	4.6	4.6	4.6	4.6	4.6
50°	4.3	4.3	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.1	4.1
52.5°	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7
55°	3.5	3.5	3.4	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.2
57.5°	3.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.0	3.0
60°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
62.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
65°	3.2	3.2	3.2	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2
67.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.5	3.5	3.5	3.4	3.4
70°	3.2	3.1	3.1	3.1	3.1	3.0	3.0	3.0	3.0	3.0	3.0
72.5°	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
75°	1.9	1.9	1.9	1.9	1.9	1.9	1.8	1.8	1.8	1.8	1.8
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	1.3	1.3	1.3	1.3	1.2	1.2	1.2	1.2	1.2	1.2	1.2
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
150°	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
152.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
155°	1.4	1.4	1.4	1.4	1.4	1.4	1.5	1.5	1.5	1.5	1.5
157.5°	1.9	1.9	1.9	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.0
160°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
162.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
165°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
175°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
177.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.8	2.8	2.8	2.8	2.8
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	6000.8	5992.4	5987.2	5982.5	5978.4	5978.9	5966.9	5962.1	5958.3	5955.6	5949.1
5°	5396.0	5385.7	5372.4	5356.6	5338.6	5322.0	5317.0	5339.8	5274.1	5254.7	5235.0
7.5°	3992.6	3907.5	3896.0	3882.2	3863.9	3841.3	3814.6	3783.8	3795.2	3742.2	3723.0
10°	2448.2	2380.3	2354.3	2344.3	2330.9	2314.3	2294.4	2271.4	2247.4	2260.3	2212.4
12.5°	1433.6	1399.6	1384.2	1375.8	1368.8	1360.1	1349.8	1337.9	1324.5	1323.0	1300.8
15°	933.5	917.7	910.2	904.4	900.9	896.6	891.7	886.2	880.1	877.1	867.0
17.5°	671.0	669.8	658.2	654.3	652.2	649.6	646.7	643.4	639.8	637.1	638.4
20°	520.1	519.5	513.3	511.2	509.9	508.4	506.6	504.6	502.4	500.2	500.8
22.5°	431.0	430.7	426.9	425.5	424.6	423.6	422.4	421.1	419.7	418.2	418.5
25°	373.6	373.5	371.2	370.4	369.8	369.3	368.6	367.8	367.0	366.1	366.1
27.5°	338.8	338.8	337.1	336.5	336.0	335.4	334.8	334.2	333.5	332.8	332.8
30°	275.7	275.5	270.7	269.0	268.0	267.3	266.4	265.3	264.2	262.9	263.5
32.5°	180.9	180.5	175.2	173.3	172.0	171.2	170.2	169.0	167.6	166.1	166.4
35°	86.8	86.3	81.5	79.6	78.3	77.4	76.3	75.1	73.6	72.0	72.0
37.5°	20.0	19.7	17.9	17.2	16.8	16.5	16.2	15.9	15.4	14.8	14.8
40°	8.8	8.7	8.6	8.6	8.5	8.5	8.5	8.4	8.4	8.3	8.3
42.5°	6.4	6.4	6.2	6.1	6.1	6.1	6.0	6.0	6.0	5.9	5.9
45°	5.2	5.1	5.1	5.0	5.0	5.0	4.9	4.9	4.9	4.9	4.9
47.5°	4.5	4.5	4.5	4.5	4.4	4.4	4.4	4.3	4.3	4.3	4.3
50°	4.1	4.0	4.0	4.0	4.0	3.9	3.9	3.9	3.9	3.8	3.8
52.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.5	3.5	3.5	3.5	3.4
55°	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
57.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
60°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
62.5°	3.2	3.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
65°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
67.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
70°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.9	2.9	2.9
72.5°	2.3	2.3	2.2	2.3	2.3	2.3	2.3	2.2	2.2	2.2	2.2
75°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.6	1.6	1.6	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	1.2	1.2	1.2	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
85°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5
150°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
152.5°	1.0	1.0	1.0	1.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1
155°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
157.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
160°	2.4	2.4	2.4	2.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.8	2.8	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2	3.2	3.2
175°	3.1	3.1	3.1	3.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0
177.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	5943.6	5938.7	5934.6	5931.5	5923.2	5917.2	5912.0	5907.5	5903.8	5910.0	5890.3
5°	5215.3	5238.4	5184.6	5169.8	5155.9	5144.2	5121.4	5102.0	5084.6	5071.8	5082.4
7.5°	3700.8	3675.9	3648.4	3681.6	3590.3	3574.6	3556.7	3540.7	3523.2	3508.0	3491.8
10°	2201.1	2186.6	2169.0	2154.2	2133.0	2113.9	2097.2	2090.2	2086.0	2074.2	2064.4
12.5°	1296.7	1290.9	1283.5	1274.5	1278.6	1257.5	1247.4	1238.1	1235.6	1245.0	1230.1
15°	862.6	859.1	854.8	849.8	847.4	840.3	835.6	830.3	827.1	828.1	825.0
17.5°	628.4	626.3	623.9	621.1	618.2	621.8	612.8	609.7	606.1	603.9	607.9
20°	494.8	493.6	492.2	490.6	488.7	490.2	485.3	483.3	481.0	479.0	480.2
22.5°	415.3	414.3	413.5	412.5	411.5	412.0	409.2	407.9	406.6	405.4	405.8
25°	364.2	363.4	362.8	362.1	361.2	361.3	359.6	358.8	357.8	356.7	357.1
27.5°	330.8	329.9	329.2	328.5	327.9	328.0	325.7	324.6	323.6	322.7	322.6
30°	260.1	258.7	257.7	256.6	255.3	255.4	252.2	250.4	248.6	246.8	246.2
32.5°	162.8	161.0	160.2	159.2	158.0	158.1	155.1	153.3	151.4	149.3	148.2
35°	69.2	67.6	67.2	66.4	65.6	65.4	63.5	62.3	61.0	59.5	58.5
37.5°	14.1	13.7	13.6	13.4	13.1	12.9	12.7	12.5	12.2	11.8	11.4
40°	8.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.0	8.0	8.0
42.5°	5.8	5.8	5.8	5.8	5.7	5.7	5.7	5.7	5.7	5.7	5.6
45°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
47.5°	4.2	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.1	4.1	4.0
50°	3.8	3.8	3.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
52.5°	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2
55°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.0	3.0
57.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
60°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1
62.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2
65°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.3	3.3	3.3
67.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.3	3.3
70°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.8	2.8	2.8	2.8
72.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
75°	1.8	1.7	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.8
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
82.5°	1.1	1.0	1.0	1.0	1.0	0.9	1.0	0.9	0.9	0.9	0.9
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.7	0.7	0.7	0.7	0.7	0.8	0.8	0.7	0.8	0.8	0.8
152.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.2	1.2
155°	1.5	1.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
157.5°	2.0	2.0	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
160°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
170°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
172.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
175°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
177.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	5885.1	5880.8	5877.6	5880.6	5868.6	5864.4	5861.0	5858.4	5856.6	5860.6	5851.7
5°	5036.7	5019.3	5004.1	4991.2	5021.0	4973.3	4966.9	4962.1	4955.3	4989.7	4923.1
7.5°	3474.7	3483.7	3443.1	3431.7	3418.5	3403.7	3443.4	3375.3	3360.8	3346.0	3335.1
10°	2052.1	2037.1	2042.6	2007.0	1999.9	1993.8	1985.3	2018.5	1972.9	1964.0	1953.1
12.5°	1225.4	1219.0	1211.0	1223.8	1196.1	1191.6	1189.5	1192.6	1186.3	1184.2	1180.8
15°	822.8	819.6	815.5	816.6	806.2	800.8	797.8	795.2	804.0	792.1	789.7
17.5°	600.4	598.2	595.6	594.1	590.2	587.2	584.2	582.6	585.0	579.9	578.4
20°	476.1	474.7	473.1	471.4	470.0	468.6	467.0	466.0	466.6	464.2	463.2
22.5°	403.6	402.7	401.7	400.8	401.9	399.2	398.4	397.7	397.7	396.5	395.8
25°	356.2	355.9	355.5	355.1	355.7	354.3	353.9	353.4	353.1	352.6	352.1
27.5°	320.9	320.1	319.4	318.9	319.6	317.4	316.8	316.3	315.8	314.9	314.3
30°	244.1	242.8	241.6	240.3	240.8	237.3	235.7	234.2	233.1	235.8	231.4
32.5°	146.5	145.3	144.1	142.8	143.1	140.1	138.7	137.4	136.3	138.9	135.1
35°	57.8	57.2	56.5	55.6	55.5	53.7	52.7	51.6	50.8	52.8	50.5
37.5°	11.6	11.6	11.5	11.2	10.9	10.7	10.5	10.3	10.1	10.5	10.6
40°	7.9	7.9	7.9	7.8	7.8	7.8	7.7	7.7	7.7	7.7	7.7
42.5°	5.7	5.6	5.6	5.5	5.5	5.5	5.5	5.5	5.4	5.5	5.4
45°	4.8	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
47.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
50°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
52.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
55°	3.0	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
57.5°	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
62.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
65°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
67.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2
70°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7
72.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.1
75°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
77.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.5	1.5	1.5	1.5	1.5	1.6	1.5	1.6	1.6	1.6	1.5
82.5°	0.9	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.6
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4
147.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
150°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
155°	1.6	1.6	1.6	1.6	1.6	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.2
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.4	3.4	3.4
170°	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3
172.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.1
175°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
177.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	5848.4	5845.7	5843.4	5841.5	5840.1	5843.6	5852.0	5834.2	5833.6	5834.0	5835.2
5°	4910.7	4901.1	4894.3	4918.0	4882.9	4879.2	4877.3	4877.1	4876.5	4892.9	4868.7
7.5°	3319.8	3313.7	3307.7	3301.9	3296.3	3344.7	3291.5	3289.4	3287.6	3286.3	3293.0
10°	1947.0	1935.1	1929.8	1929.2	1927.0	1928.0	1924.4	1923.5	1921.6	1918.7	1915.1
12.5°	1176.1	1184.0	1168.9	1165.6	1165.2	1163.9	1174.6	1163.2	1162.5	1161.3	1159.6
15°	786.7	785.6	780.5	777.3	775.1	774.1	775.6	773.7	774.0	774.1	773.9
17.5°	576.5	574.4	578.4	571.1	569.3	569.3	569.2	575.1	570.5	570.9	571.2
20°	462.1	460.8	462.4	458.9	457.9	457.5	457.7	460.6	458.8	459.3	459.6
22.5°	395.1	394.4	395.1	393.6	393.1	392.8	393.1	394.7	393.4	393.5	393.7
25°	351.7	351.3	351.6	350.8	350.6	350.4	350.5	351.3	350.9	351.0	351.2
27.5°	313.8	313.5	314.1	312.5	312.0	311.8	311.3	312.1	310.4	310.2	310.2
30°	230.6	229.9	230.1	228.6	228.0	227.5	227.2	228.4	226.9	226.8	226.8
32.5°	134.6	134.1	134.2	133.1	132.6	132.2	131.8	132.6	131.6	131.6	131.7
35°	50.3	49.9	49.8	49.3	48.9	48.4	47.9	48.5	48.2	48.3	48.5
37.5°	10.7	10.6	10.4	10.4	10.3	10.2	10.1	10.4	10.6	10.7	10.7
40°	7.7	7.7	7.7	7.7	7.7	7.6	7.6	7.6	7.6	7.6	7.6
42.5°	5.4	5.4	5.4	5.5	5.4	5.4	5.4	5.4	5.4	5.4	5.4
45°	4.7	4.7	4.6	4.7	4.6	4.6	4.6	4.6	4.6	4.6	4.6
47.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
50°	3.7	3.7	3.7	3.8	3.7	3.7	3.7	3.7	3.8	3.8	3.8
52.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
55°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
57.5°	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
60°	3.1	3.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
62.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
65°	3.4	3.4	3.4	3.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4
67.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.2	3.2	3.2	3.2
70°	2.7	2.7	2.7	2.7	2.6	2.6	2.5	2.5	2.5	2.5	2.4
72.5°	2.1	2.1	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
75°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
77.5°	1.7	1.7	1.6	1.6	1.6	1.5	1.5	1.5	1.4	1.3	1.3
80°	1.5	1.4	1.4	1.3	1.3	1.2	1.2	1.1	1.1	1.0	1.0
82.5°	0.6	0.5	0.5	0.5	0.4	0.4	0.4	0.4	0.4	0.4	0.4
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.8	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.3
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
172.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
175°	2.9	2.9	2.9	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
177.5°	2.7	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	5837.2	5840.0	5843.7	5852.2	5863.0	5851.0	5848.4	5846.5	5845.2	5844.6	5844.7
5°	4867.7	4868.5	4871.3	4876.0	4882.5	4890.9	4924.0	4959.8	4911.0	4921.9	4929.4
7.5°	3339.2	3282.8	3282.8	3284.2	3286.9	3291.1	3296.8	3335.8	3311.7	3321.3	3332.4
10°	1926.6	1910.4	1912.3	1913.1	1913.8	1914.4	1915.1	1926.1	1954.5	1927.6	1933.2
12.5°	1157.7	1173.6	1158.4	1159.2	1159.8	1160.3	1160.8	1161.9	1175.8	1166.1	1168.9
15°	773.6	779.7	774.4	775.3	776.3	777.3	778.3	779.3	786.2	783.2	785.4
17.5°	571.3	573.8	572.0	572.4	573.1	573.9	574.7	575.5	579.0	583.8	579.8
20°	459.9	461.1	460.8	461.3	461.8	462.3	462.7	463.2	464.9	467.5	464.9
22.5°	393.8	394.4	396.6	394.8	395.0	395.1	395.3	395.5	396.4	398.1	396.8
25°	351.3	351.5	352.7	351.6	351.6	351.6	351.7	351.7	352.1	353.1	352.3
27.5°	310.4	310.8	313.3	311.3	311.5	311.3	311.4	311.7	312.6	314.5	312.8
30°	226.9	227.1	230.3	227.7	228.1	228.2	228.4	228.7	229.8	232.8	230.7
32.5°	131.8	132.0	135.0	132.7	133.2	133.5	133.9	134.5	135.6	138.7	136.9
35°	48.6	48.6	50.8	49.1	49.2	49.4	49.6	50.0	50.6	53.0	51.7
37.5°	10.6	10.4	10.4	10.3	10.3	10.5	10.6	10.6	10.6	10.8	10.7
40°	7.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.7	7.6
42.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.3
45°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
47.5°	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.1	4.1	4.1	4.1
50°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.7	3.7	3.7	3.7
52.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
55°	3.1	3.1	3.1	3.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0
57.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.1	3.0
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
62.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
65°	3.4	3.4	3.4	3.4	3.3	3.3	3.3	3.3	3.3	3.3	3.3
67.5°	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.2	3.2	3.2	3.2
70°	2.4	2.4	2.4	2.4	2.4	2.4	2.5	2.5	2.5	2.6	2.6
72.5°	2.0	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.0	2.0	2.0
75°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
77.5°	1.2	1.1	1.0	0.9	0.8	0.8	0.8	0.9	0.9	1.0	1.1
80°	1.0	0.9	0.9	0.9	0.9	0.9	0.9	1.0	1.1	1.1	1.2
82.5°	0.4	0.4	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.3	1.3	1.3	1.2	1.3	1.3	1.3	1.3	1.3	1.3	1.3
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
172.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
175°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
177.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3	6150.3
2.5°	5845.3	5846.5	5848.4	5850.7	5853.6	5857.0	5860.8	5865.2	5869.9	5875.0	5880.6
5°	4930.6	4934.0	4939.6	4947.2	4956.8	4968.4	4982.0	4997.3	5014.5	5033.4	5053.9
7.5°	3345.2	3349.8	3355.5	3363.2	3373.1	3385.1	3399.3	3415.8	3434.5	3455.5	3478.9
10°	1939.5	1945.6	1948.8	1953.1	1958.6	1965.4	1973.5	1983.1	1994.3	2007.1	2021.6
12.5°	1171.9	1175.4	1177.0	1178.2	1180.1	1182.5	1185.7	1189.5	1194.2	1199.7	1206.0
15°	787.8	790.5	792.3	793.2	794.5	796.2	798.2	800.7	803.6	806.9	810.7
17.5°	581.5	583.3	585.0	585.5	586.2	587.1	588.2	589.6	591.1	592.9	594.9
20°	465.6	466.3	466.9	467.2	467.5	467.9	468.5	469.2	470.1	471.1	472.3
22.5°	397.3	397.9	398.5	398.7	398.9	399.1	399.5	399.9	400.3	400.9	401.6
25°	352.5	352.8	353.1	353.2	353.3	353.5	353.7	354.0	354.3	354.7	355.2
27.5°	313.5	314.3	315.3	315.6	315.9	316.3	316.8	317.6	318.4	319.3	320.4
30°	231.6	232.7	233.9	234.7	235.2	235.9	236.8	237.8	239.0	240.3	241.8
32.5°	137.9	139.1	140.4	141.3	142.0	142.9	143.9	145.1	146.5	148.0	149.7
35°	52.4	53.2	54.0	54.7	55.2	55.8	56.5	57.3	58.3	59.4	60.6
37.5°	10.7	10.8	10.7	10.8	10.9	11.0	11.1	11.2	11.3	11.4	11.5
40°	7.6	7.6	7.6	7.6	7.6	7.7	7.7	7.7	7.7	7.8	7.8
42.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.4	5.4	5.4	5.4	5.4
45°	4.6	4.6	4.6	4.6	4.5	4.5	4.5	4.5	4.5	4.5	4.5
47.5°	4.1	4.1	4.1	4.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0
50°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
52.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
55°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
57.5°	3.0	3.0	3.0	3.0	3.0	2.9	2.9	2.9	2.9	2.9	2.9
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
62.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
65°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2	3.2
67.5°	3.2	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
70°	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.8	2.8
72.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.2
75°	1.8	1.8	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.9	1.9
77.5°	1.2	1.2	1.3	1.4	1.5	1.5	1.5	1.6	1.6	1.7	1.7
80°	1.2	1.3	1.3	1.3	1.4	1.4	1.4	1.5	1.5	1.6	1.6
82.5°	0.5	0.6	0.6	0.6	0.6	0.7	0.7	0.8	0.8	0.9	0.9
85°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
87.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
142.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
145°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
147.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
152.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.2	1.2
155°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
157.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.1	2.1	2.1
160°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
162.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
165°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
167.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
170°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.4	3.4
172.5°	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
175°	2.8	2.8	2.8	2.8	2.9	2.9	2.9	2.9	2.9	2.9	2.9
177.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.6	2.6
180°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5



TEST NUMBER: P979208
 CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	6150.3	6150.3
2.5°	5886.4	5910.1
5°	5076.0	5099.7
7.5°	3504.6	3536.4
10°	2037.9	2054.9
12.5°	1213.2	1223.9
15°	815.0	819.1
17.5°	597.2	601.2
20°	473.7	476.3
22.5°	402.4	404.7
25°	355.7	355.8
27.5°	321.5	322.6
30°	243.5	246.2
32.5°	151.5	153.4
35°	61.9	64.1
37.5°	11.7	12.1
40°	7.9	8.0
42.5°	5.5	5.6
45°	4.5	4.5
47.5°	4.0	4.0
50°	3.6	3.5
52.5°	3.2	3.2
55°	3.0	3.0
57.5°	2.9	2.9
60°	3.1	3.1
62.5°	3.2	3.2
65°	3.2	3.2
67.5°	3.3	3.3
70°	2.8	2.9
72.5°	2.2	2.2
75°	1.9	1.9
77.5°	1.8	1.8
80°	1.6	1.7
82.5°	1.0	1.1
85°	0.1	0.1
87.5°	0.1	0.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



TEST NUMBER: P979208
CATALOG NUMBER: L820S10SP927XXXXBLSHBXXXX

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.1	0.1
135°	0.1	0.1
137.5°	0.1	0.1
140°	0.2	0.2
142.5°	0.3	0.3
145°	0.4	0.4
147.5°	0.6	0.6
150°	0.9	0.8
152.5°	1.2	1.2
155°	1.7	1.7
157.5°	2.1	2.1
160°	2.6	2.6
162.5°	3.0	3.0
165°	3.2	3.3
167.5°	3.4	3.4
170°	3.4	3.4
172.5°	3.2	3.3
175°	3.0	3.0
177.5°	2.6	2.7
180°	2.5	2.5

(END OF REPORT)