

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P286844

Luminaire Tested: **L81211FL9027MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P286844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1902-134-3)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L81211FL9027MB
Description: HALO, TRACK-MINI, BLACK, 38D BEAM
Light Source: (1) 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1094.7 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.62
Luminous Opening: Circular (Dia: 0.19' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P286844
CATALOG NUMBER: L81211FL9027MB

Luminous Intensity Polar Plot





TEST NUMBER: P286844

CATALOG NUMBER: L81211FL9027MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	105	99	94	91	103	97	93	90	95	92	89		93	90	87		90	88	86	85
4	100	93	89	85	98	92	88	84	90	86	83		88	85	82		87	84	81	80
5	96	89	83	80	94	88	83	79	86	82	79		84	81	78		83	80	77	76
6	92	84	79	75	91	84	79	75	82	78	75		81	77	74		80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71		77	73	70		76	73	70	69
8	85	77	71	68	84	76	71	68	75	71	68		74	70	67		73	70	67	66
9	82	73	68	65	81	73	68	65	72	68	64		71	67	64		70	67	64	63
10	79	70	65	62	78	70	65	62	69	65	62		68	64	62		68	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	932713
5°	892174
10°	777838
15°	618210
20°	448952
25°	279156
30°	136167
35°	67387
40°	41271
45°	29550
50°	21712
55°	14952
60°	9668
65°	6365
70°	4673
75°	2109
80°	0
85°	0



TEST NUMBER: P286844

CATALOG NUMBER: L81211FL9027MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.6	19.0
10°-20°	420.5	38.4
20°-30°	296.6	27.1
30°-40°	98.2	9.0
40°-50°	42.5	3.9
50°-60°	20.3	1.9
60°-70°	7.5	0.7
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	924.6	84.5
0°-40°	1022.8	93.4
0°-60°	1085.6	99.2
0°-90°	1094.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1094.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2393	
5°	2280	208
15°	1532	420
25°	649	297
35°	142	98
45°	54	43
55°	22	20
65°	7	7
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P286844

CATALOG NUMBER: L81211FL9027MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2392.6
2.5°	2365.1
5°	2279.9
7.5°	2145.1
10°	1965.0
12.5°	1756.0
15°	1531.8
17.5°	1303.6
20°	1082.2
22.5°	862.2
25°	649.0
27.5°	452.4
30°	302.5
32.5°	202.1
35°	141.6
37.5°	105.9
40°	81.1
42.5°	66.0
45°	53.6
47.5°	44.0
50°	35.8
52.5°	28.9
55°	22.0
57.5°	16.5
60°	12.4
62.5°	9.6
65°	6.9
67.5°	5.5
70°	4.1
72.5°	2.8
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)