

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P236660

Luminaire Tested: **L81211SP9035MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P236660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-557-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L81211SP9035MB
Description: HALO, TRACK-MINI, CYLINDER, 15D BEAM
Light Source: (1) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1206.4 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.28
Luminous Opening: Circular (Dia: 0.19' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P236660
CATALOG NUMBER: L81211SP9035MB

Luminous Intensity Polar Plot





TEST NUMBER: P236660

CATALOG NUMBER: L81211SP9035MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105		103	102	101		100	99	99	97
2	111	108	105	103	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	104	100	97	106	102	99	97	100	97	95		98	95	94		96	94	92	91
4	105	100	96	93	104	99	95	93	97	94	92		95	93	91		93	91	90	88
5	102	97	93	90	101	96	92	89	94	91	89		93	90	88		91	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86		91	88	86		89	87	85	84
7	97	91	87	84	96	91	87	84	89	86	84		88	86	83		88	85	83	82
8	95	89	85	82	94	88	85	82	87	84	82		87	84	82		86	83	81	80
9	93	87	83	80	92	86	83	80	85	82	80		85	82	80		84	81	80	79
10	91	85	81	79	90	84	81	78	84	81	78		83	80	78		83	80	78	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4010439
5°	3114566
10°	1276485
15°	532247
20°	227255
25°	107791
30°	59643
35°	35216
40°	22493
45°	16429
50°	13039
55°	10535
60°	8342
65°	6641
70°	5471
75°	5422
80°	0
85°	0



TEST NUMBER: P236660

CATALOG NUMBER: L81211SP9035MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	589.2	48.8
10°-20°	394.8	32.7
20°-30°	125.5	10.4
30°-40°	49.0	4.1
40°-50°	23.7	2.0
50°-60°	13.7	1.1
60°-70°	7.2	0.6
70°-80°	3.2	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1109.6	92.0
0°-40°	1158.6	96.0
0°-60°	1196.0	99.1
0°-90°	1206.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1206.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10288	
5°	7959	589
15°	1319	395
25°	251	126
35°	74	49
45°	30	24
55°	16	14
65°	7	7
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P236660

CATALOG NUMBER: L81211SP9035MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	10287.6
1°	10221.9
2°	10007.1
3°	9572.7
4°	8884.1
5°	7959.1
6°	6934.0
7°	5855.1
8°	4819.2
9°	3907.4
10°	3224.7
12.5°	2048.0
15°	1318.8
17.5°	842.6
20°	547.8
22.5°	362.8
25°	250.6
27.5°	177.8
30°	132.5
32.5°	99.1
35°	74.0
37.5°	57.3
40°	44.2
42.5°	35.8
45°	29.8
47.5°	25.1
50°	21.5
52.5°	17.9
55°	15.5
57.5°	11.9
60°	10.7
62.5°	8.4
65°	7.2
67.5°	6.0
70°	4.8
72.5°	4.8
75°	3.6
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)