

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P285918

Luminaire Tested: **L81208FL9035MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P285918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1902-134-3)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L81208FL9035MB
Description: HALO, TRACK-MINI, 38D BEAM
Light Source: (1) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 864.7 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.62
Luminous Opening: Circular (Dia: 0.19' x H: 0')
CIE Type: Direct

Input Watts (W): 10.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P285918
CATALOG NUMBER: L81208FL9035MB

Luminous Intensity Polar Plot





TEST NUMBER: P285918

CATALOG NUMBER: L81208FL9035MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	105	99	94	91	103	97	93	90	95	92	89		93	90	87		90	88	86	85
4	100	93	89	85	98	92	88	84	90	86	83		88	85	82		87	84	81	80
5	96	89	83	80	94	88	83	79	86	82	79		84	81	78		83	80	77	76
6	92	84	79	75	91	84	79	75	82	78	75		81	77	74		80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71		77	73	70		76	73	70	69
8	85	77	71	68	84	76	71	68	75	71	68		74	70	67		73	70	67	66
9	82	73	68	65	81	73	68	65	72	68	64		71	67	64		70	67	64	63
10	79	70	65	62	78	70	65	62	69	65	62		68	64	62		68	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	736744
5°	704731
10°	614393
15°	488337
20°	354615
25°	220529
30°	107583
35°	53253
40°	32620
45°	23375
50°	17102
55°	11826
60°	7641
65°	4981
70°	3761
75°	1657
80°	0
85°	0



TEST NUMBER: P285918

CATALOG NUMBER: L81208FL9035MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.0	19.0
10°-20°	332.1	38.4
20°-30°	234.2	27.1
30°-40°	77.5	9.0
40°-50°	33.6	3.9
50°-60°	16.0	1.9
60°-70°	5.9	0.7
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.4	84.5
0°-40°	807.9	93.4
0°-60°	857.5	99.2
0°-90°	864.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	864.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1890	
5°	1801	164
15°	1210	332
25°	513	234
35°	112	78
45°	42	34
55°	17	16
65°	5	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P285918

CATALOG NUMBER: L81208FL9035MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1889.9
2.5°	1868.2
5°	1800.9
7.5°	1694.4
10°	1552.1
12.5°	1387.0
15°	1210.0
17.5°	1029.7
20°	854.8
22.5°	681.0
25°	512.7
27.5°	357.3
30°	239.0
32.5°	159.7
35°	111.9
37.5°	83.6
40°	64.1
42.5°	52.1
45°	42.4
47.5°	34.8
50°	28.2
52.5°	22.8
55°	17.4
57.5°	13.0
60°	9.8
62.5°	7.6
65°	5.4
67.5°	4.3
70°	3.3
72.5°	2.2
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)