

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P21908-R2

Luminaire Tested: **L805MEDSP830**

Issue Date: 3/3/2020



Test Information

Test Method: LM-79-08
Report Number: P21908-R2
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L805MEDSP830
Description: ***THIS IS A REVISION OF P21908 TO UPDATE CATALOG
NUMBER***STASIS LED WITH (7) LEDS AND SPOT FLOOD OPTICS
.---ABSOLUTE PHOTOMETRY IS BASED ON CALIBRATION FACTORS
CREATED USING A 500 WATT, NIST TRACEABLE, AND
OMNI-DIRECTIONAL LAB LUMEN STANDARD IN THE GONIOPHOTOMETER
WITH TEST DISTANCE OF 28.75 FEET----
Light Source: (7) SMT LEDS
Ballast/Driver: -
ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 999.1 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.15 / 0.15 / 0.14
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 17.2
Input Voltage (V): NR
Input Current (Ain): 0.1466
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P21908-R2
CATALOG NUMBER: L805MEDSP830

Luminous Intensity Polar Plot





TEST NUMBER: P21908-R2

CATALOG NUMBER: L805MEDSP830

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	116	114	113	112	114	112	111	110	108	107	106	106	105	104	103	103	101	101	100	100	99	99	99	99
2	114	111	109	107	112	110	108	106	107	105	104	104	104	103	102	102	101	100	100	100	98	98	98	98
3	112	109	106	104	110	107	105	103	105	103	102	102	103	101	100	100	101	100	99	99	98	98	98	98
4	110	107	104	102	109	106	103	102	104	102	100	100	102	101	99	99	101	99	98	98	97	97	97	97
5	109	105	103	101	108	104	102	100	103	101	99	99	102	100	99	99	100	99	98	98	97	97	97	97
6	108	104	101	100	107	103	101	99	102	100	99	99	101	99	98	98	100	99	97	97	97	97	97	97
7	107	103	100	99	106	102	100	98	101	99	98	98	101	99	98	98	100	98	97	97	97	97	97	97
8	106	102	100	98	105	102	99	98	101	99	98	98	100	98	97	97	100	98	97	97	96	96	96	96
9	105	101	99	98	104	101	99	97	100	98	97	97	100	98	97	97	99	98	97	97	96	96	96	96
10	104	101	99	97	104	100	98	97	100	98	97	97	99	98	97	97	99	98	96	96	96	96	96	96

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4281710
5°	1610623
10°	66568
15°	7013
20°	3604
25°	2893
30°	2902
35°	1334
40°	713
45°	155
50°	680
55°	762
60°	1311
65°	517
70°	319
75°	2533
80°	3775
85°	3761



TEST NUMBER: P21908-R2

CATALOG NUMBER: L805MEDSP830

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	929.6	93.0
10°-20°	29.8	3.0
20°-30°	12.0	1.2
30°-40°	10.9	1.1
40°-50°	1.6	0.2
50°-60°	2.2	0.2
60°-70°	2.9	0.3
70°-80°	3.6	0.4
80°-90°	6.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	971.3	97.2
0°-40°	982.2	98.3
0°-60°	986.1	98.7
0°-90°	999.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	999.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	39188	
5°	14685	930
15°	62	30
25°	24	12
35°	10	11
45°	1	2
55°	4	2
65°	2	3
75°	6	4
85°	3	7
90°	0	



TEST NUMBER: P21908-R2

CATALOG NUMBER: L805MEDSP830

CANDELA DISTRIBUTION (FULL):

0°	
0°	39188
1°	38564
2°	35522
3°	29383
4°	21844
5°	14685
6°	8779
7°	4665
8°	2361
9°	1200
10°	600
11°	302
12°	177
13°	103
14°	82
15°	62
17.5°	50
20°	31
22.5°	27
25°	24
27.5°	26
30°	23
32.5°	28
35°	10
37.5°	19
40°	5
42.5°	2
45°	1
47.5°	1
50°	4
52.5°	1
55°	4
57.5°	0
60°	6
62.5°	1
65°	2
67.5°	5
70°	1
72.5°	2
75°	6
77.5°	2
80°	6
82.5°	7
85°	3
87.5°	11



TEST NUMBER: P21908-R2
CATALOG NUMBER: L805MEDSP830

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0}$

(END OF REPORT)