

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P22179-R2

Luminaire Tested: **L805MEDSP840**

Issue Date: 3/3/2020



Test Information

Test Method: LM-79-08
Report Number: P22179-R2
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L805MEDSP840
Description: ***THIS IS A REVISION OF P22179 TO UPDATE CATALOG
NUMBER***STASIS LED WITH (7) LEDS AND SPOT FLOOD OPTICS.
Light Source: (7) 4000K SMT LEDS
Ballast/Driver: -
ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1240.9 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.16 / 0.16 / 0.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (Ain): 0.14335
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P22179-R2
CATALOG NUMBER: L805MEDSP840

Luminous Intensity Polar Plot





TEST NUMBER: P22179-R2

CATALOG NUMBER: L805MEDSP840

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	116	115	113	112	114	113	111	110	109	108	107	107	105	104	104	104	102	101	101	101	99	99	99	99
2	114	111	109	108	112	110	108	106	107	105	104	104	104	103	102	102	102	101	100	100	99	99	99	99
3	112	109	107	105	111	108	106	104	105	104	102	102	103	102	101	101	101	100	99	99	98	98	98	98
4	111	107	104	103	109	106	104	102	104	102	101	101	103	101	100	100	101	100	99	99	98	98	98	98
5	109	105	103	101	108	105	102	101	103	101	100	100	102	100	99	99	101	99	98	98	97	97	97	97
6	108	104	102	100	107	104	101	100	102	100	99	99	101	100	98	98	100	99	98	98	97	97	97	97
7	107	103	101	99	106	103	100	99	102	100	98	98	101	99	98	98	100	99	98	98	97	97	97	97
8	106	102	100	98	105	102	100	98	101	99	98	98	100	99	98	98	100	98	97	97	96	96	96	96
9	105	102	99	98	105	101	99	98	101	99	98	98	100	98	97	97	100	98	97	97	96	96	96	96
10	105	101	99	97	104	101	99	97	100	98	97	97	100	98	97	97	99	98	97	97	96	96	96	96

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5577196
5°	2307821
10°	113350
15°	10727
20°	4200
25°	2994
30°	4985
35°	3915
40°	161
45°	2093
50°	384
55°	1935
60°	740
65°	3210
70°	1803
75°	477
80°	710
85°	4246



TEST NUMBER: P22179-R2

CATALOG NUMBER: L805MEDSP840

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1158.1	93.3
10°-20°	41.5	3.3
20°-30°	10.5	0.8
30°-40°	10.6	0.9
40°-50°	5.5	0.4
50°-60°	6.1	0.5
60°-70°	4.5	0.4
70°-80°	2.9	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1210.1	97.5
0°-40°	1220.8	98.4
0°-60°	1232.3	99.3
0°-90°	1240.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1240.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	45216	
5°	18639	###
15°	84	41
25°	22	11
35°	26	11
45°	12	5
55°	9	6
65°	11	4
75°	1	3
85°	3	1
90°	0	



TEST NUMBER: P22179-R2

CATALOG NUMBER: L805MEDSP840

CANDELA DISTRIBUTION (FULL):

0°	
0°	45216
1°	44419
2°	41379
3°	35266
4°	26891
5°	18639
6°	11482
7°	6372
8°	3399
9°	1754
10°	905
11°	473
12°	254
13°	161
14°	111
15°	84
17.5°	49
20°	32
22.5°	16
25°	22
27.5°	19
30°	35
32.5°	11
35°	26
37.5°	14
40°	1
42.5°	11
45°	12
47.5°	4
50°	2
52.5°	15
55°	9
57.5°	1
60°	3
62.5°	1
65°	11
67.5°	2
70°	5
72.5°	5
75°	1
77.5°	2
80°	1
82.5°	1
85°	3
87.5°	0



TEST NUMBER: P22179-R2
CATALOG NUMBER: L805MEDSP840

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0}$

(END OF REPORT)