

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P181281

Luminaire Tested: **ICS-E01-LED-E1-T2**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P181281
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33671)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: ICS-E01-LED-E1-T2
Description: ICON SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 2
Light Source: (21) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2757.5 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 1' x H: 0.1')
IES Classification: Type II - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G1


Input Watts (W): 24.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P181281
 CATALOG NUMBER: ICS-E01-LED-E1-T2

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 3.4 fc
 Type II - Short - Semi-Cutoff

REPORT NUMBER: P181281
CATALOG NUMBER: ICS-E01-LED-E1-T2

Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P181281

CATALOG NUMBER: ICS-E01-LED-E1-T2


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	965.6	0.0	965.6
	% Fixture	35.0	0.0	35.0
Street Side	Lumens	1791.9	0.0	1791.9
	% Fixture	65.0	0.0	65.0
Total	Lumens	2757.5	0.0	2757.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.6	1.0
10°-20°	94.8	3.4
20°-30°	186.3	6.8
30°-40°	309.5	11.2
40°-50°	454.8	16.5
50°-60°	629.8	22.8
60°-70°	751.7	27.3
70°-80°	265.8	9.6
80°-90°	37.1	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2757.5	100.0
0°-180°	2757.5	100.0

Coefficient of Utilization



REPORT NUMBER: P181281


CATALOG NUMBER: ICS-E01-LED-E1-T2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	159.6	5.8			
FM (30°-60°)	877.9	31.8			
FH (60°-80°)	729.1	26.4			G1/1800
FVH (80°-90°)	25.4	0.9			G1/100
BL (0°-30°)	149.2	5.4	B1/500		
BM (30°-60°)	516.2	18.7	B1/1000		
BH (60°-80°)	288.4	10.5	B1/500		G1/500
BVH (80°-90°)	11.8	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type II Short





REPORT NUMBER: P181281

CATALOG NUMBER: ICS-E01-LED-E1-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7
2.5°	287.7	288.0	287.4	287.1	286.2	284.7	283.5	282.3	282.3	282.3	281.4
5°	300.3	300.9	299.7	298.8	296.1	294.6	292.5	291.0	290.4	290.1	289.2
7.5°	316.2	315.3	313.5	312.9	310.8	307.5	303.6	300.6	300.6	300.3	300.6
10°	332.1	329.7	328.8	327.9	324.6	320.4	315.9	312.6	312.3	312.0	311.1
12.5°	348.0	347.1	346.2	342.9	339.6	333.0	327.9	324.6	324.3	324.6	323.4
15°	369.0	366.9	366.0	360.3	353.1	345.9	339.6	336.6	335.7	336.0	335.1
17.5°	385.2	385.2	383.1	376.8	367.5	357.6	351.0	349.2	348.9	348.9	349.2
20°	398.1	397.8	395.7	390.6	379.5	369.6	366.3	365.7	365.4	365.4	366.3
22.5°	405.3	404.7	403.8	398.1	389.4	382.8	383.1	384.9	385.5	386.1	387.3
25°	408.9	408.0	407.7	403.8	397.5	396.6	402.0	406.8	408.0	409.2	410.7
27.5°	414.9	413.4	414.0	412.5	411.0	413.7	424.8	429.9	430.8	432.3	433.2
30°	431.4	430.8	433.2	433.8	435.0	438.9	449.1	453.9	456.0	456.0	460.2
32.5°	462.9	463.2	463.8	470.1	472.2	474.9	480.3	484.2	484.5	484.8	488.7
35°	505.2	507.0	512.1	517.5	522.6	522.3	519.0	521.1	519.6	521.4	521.7
37.5°	558.6	556.2	563.7	576.0	583.8	581.7	567.0	557.4	560.1	558.9	558.0
40°	599.7	602.4	616.8	633.0	639.0	645.6	626.4	609.9	607.5	603.0	600.3
42.5°	656.4	656.7	668.4	680.4	697.8	712.2	699.9	676.2	669.0	663.6	651.9
45°	708.9	708.0	717.6	732.3	753.0	773.7	778.2	752.4	749.7	740.1	724.8
47.5°	744.0	742.8	749.4	768.6	802.2	836.1	854.7	846.9	841.8	837.9	813.9
50°	767.7	765.3	772.8	793.2	830.7	882.9	931.6	938.2	936.1	936.1	920.8
52.5°	785.4	785.4	790.8	807.3	845.4	910.5	997.6	1030.9	1033.6	1036.6	1035.7
55°	775.5	777.0	790.5	814.5	854.7	929.8	1052.2	1125.1	1140.1	1152.7	1167.1
57.5°	741.6	746.7	764.7	804.0	857.1	944.2	1112.8	1257.1	1299.4	1336.0	1393.0
60°	692.1	698.7	724.8	774.9	839.4	920.8	1134.1	1368.7	1435.9	1515.7	1664.5
62.5°	607.2	613.8	639.3	689.4	744.6	831.0	1045.9	1385.2	1492.6	1605.7	1830.7
65°	430.2	419.7	449.1	494.1	557.4	641.1	845.1	1274.5	1429.0	1582.3	1860.1
67.5°	239.7	238.8	256.8	290.4	351.0	441.0	582.3	977.5	1119.7	1293.4	1634.5
70°	165.3	167.1	178.5	214.8	264.9	342.6	414.9	613.8	716.1	834.0	1169.5
72.5°	116.1	120.0	126.3	147.9	199.2	288.6	423.9	366.9	417.9	498.3	703.2
75°	68.1	70.8	75.3	85.8	113.4	192.9	438.9	322.5	322.5	341.4	425.4
77.5°	42.0	42.0	44.7	48.9	60.3	94.5	312.6	362.4	352.2	341.4	342.3
80°	21.6	23.1	27.0	29.1	33.6	43.2	140.4	338.1	370.8	392.7	377.4
82.5°	9.9	11.1	16.5	17.7	19.5	22.8	48.3	192.3	257.7	339.3	423.9
85°	5.1	5.1	8.7	10.8	11.7	10.5	17.7	77.7	117.6	179.4	280.8
87.5°	0.9	0.9	1.5	1.8	2.7	2.4	3.0	4.5	7.5	8.1	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181281

CATALOG NUMBER: ICS-E01-LED-E1-T2

CANDELA DISTRIBUTION (continued):

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7
2.5°	281.1	281.4	281.1	280.8	280.2	280.2	280.2	279.9	279.9	279.9	279.6
5°	289.2	288.0	288.3	287.7	287.4	287.1	287.4	286.8	286.2	286.5	286.2
7.5°	299.4	298.8	297.6	297.6	297.3	296.7	296.7	295.8	295.5	294.9	294.6
10°	310.8	309.3	309.9	309.3	309.6	308.4	307.8	307.2	306.6	306.6	306.9
12.5°	322.5	322.2	321.3	320.7	320.7	319.8	320.1	319.8	318.9	318.6	317.7
15°	334.5	334.5	333.6	333.9	333.6	333.0	332.4	332.4	331.8	331.2	331.5
17.5°	348.6	348.6	348.6	348.6	348.9	348.0	348.3	347.7	347.1	348.3	348.3
20°	366.9	368.1	368.1	367.8	369.3	368.4	368.1	369.6	368.1	370.2	369.9
22.5°	387.9	389.1	389.1	390.3	390.6	391.5	392.1	391.5	392.7	393.9	393.9
25°	411.3	412.5	413.4	415.2	416.1	415.5	415.8	417.3	417.9	419.1	420.3
27.5°	435.9	436.2	437.4	439.5	441.0	441.6	441.9	444.3	444.6	445.2	446.4
30°	459.9	462.9	462.3	465.0	465.9	466.8	468.6	469.5	471.6	472.8	472.8
32.5°	488.1	487.5	489.9	492.0	493.5	495.0	496.5	497.7	498.9	499.5	502.5
35°	523.2	524.4	524.4	524.7	528.3	528.6	529.8	532.5	533.4	535.2	536.4
37.5°	558.0	555.9	555.6	555.6	554.4	555.3	555.6	555.9	557.1	557.4	558.6
40°	597.0	594.3	591.9	590.4	588.0	584.7	584.1	582.6	583.5	583.2	583.5
42.5°	650.4	642.9	637.2	633.0	628.2	624.6	621.9	618.0	615.3	612.0	611.4
45°	718.5	704.4	694.8	687.9	681.0	671.1	665.4	659.4	654.0	648.6	644.1
47.5°	807.9	792.9	777.6	765.0	754.2	738.3	722.1	713.1	702.6	693.3	686.7
50°	913.2	895.2	888.0	870.3	856.8	832.8	812.7	798.0	777.0	762.9	750.6
52.5°	1021.0	1016.5	1012.6	997.6	981.7	967.9	950.2	924.4	903.0	886.8	861.6
55°	1167.7	1169.8	1168.3	1160.2	1154.5	1141.3	1134.1	1111.6	1102.0	1078.6	1052.2
57.5°	1414.6	1431.4	1452.7	1461.1	1472.5	1461.7	1474.3	1489.6	1451.5	1464.7	1441.0
60°	1729.9	1807.0	1852.9	1909.3	1946.2	1997.8	2007.1	2020.6	2016.7	2024.2	2039.5
62.5°	1922.5	2014.0	2101.9	2165.8	2234.2	2272.0	2317.6	2349.4	2382.4	2404.6	2398.3
65°	1979.2	2073.4	2153.2	2223.1	2284.3	2330.5	2372.8	2412.7	2443.0	2464.3	2476.9
67.5°	1771.0	1894.0	1978.0	2059.9	2138.8	2187.4	2222.8	2261.5	2305.9	2342.8	2350.0
70°	1332.7	1517.2	1636.3	1734.4	1827.1	1892.5	1942.0	1978.0	2012.5	2038.9	2067.7
72.5°	833.4	994.9	1131.1	1258.3	1356.7	1446.7	1488.4	1568.2	1557.7	1577.8	1599.4
75°	499.5	578.1	653.1	742.8	794.4	869.4	882.9	896.1	889.2	866.7	883.5
77.5°	347.1	360.0	359.4	354.3	348.9	335.7	318.6	309.3	303.0	294.0	297.6
80°	349.2	321.3	278.7	234.3	193.5	166.5	155.7	155.7	166.8	182.7	198.6
82.5°	417.3	387.6	345.6	289.2	229.2	186.6	158.1	146.7	148.8	165.0	185.4
85°	281.4	288.0	252.6	231.0	183.0	142.5	119.4	96.9	85.8	88.5	100.2
87.5°	10.2	12.3	4.5	6.0	4.2	3.6	3.6	3.9	2.7	3.3	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181281

CATALOG NUMBER: ICS-E01-LED-E1-T2

CANDELA DISTRIBUTION (continued):

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7
2.5°	279.3	279.0	279.0	278.4	278.4	278.1	278.1	277.8	277.5	277.5	277.2
5°	285.9	285.6	285.0	284.7	284.1	284.1	283.8	283.2	283.2	282.6	282.3
7.5°	295.2	294.6	294.0	293.7	293.4	292.5	292.5	291.9	291.9	291.3	291.0
10°	306.3	305.7	305.1	305.4	304.5	304.2	303.6	303.6	302.7	302.4	302.4
12.5°	318.3	318.0	318.0	317.1	316.8	316.5	315.3	315.3	315.3	314.7	315.0
15°	331.2	331.5	330.6	331.5	331.2	330.3	330.3	330.3	329.1	330.6	329.4
17.5°	348.6	349.5	348.9	349.2	348.6	348.6	348.9	348.6	349.2	349.2	351.0
20°	370.2	370.5	372.0	371.4	371.4	371.1	371.7	372.0	373.2	372.6	373.8
22.5°	393.9	395.4	395.7	396.9	396.9	396.6	397.2	398.4	399.0	399.9	399.6
25°	420.9	421.8	423.0	421.5	423.9	423.9	424.5	426.0	426.3	426.3	428.4
27.5°	446.1	448.5	448.8	450.3	449.4	450.0	452.1	453.0	454.2	454.2	454.8
30°	474.6	475.5	476.1	477.9	477.6	477.9	478.2	479.7	479.7	481.2	482.7
32.5°	504.0	504.6	505.2	507.0	507.6	508.8	508.2	509.4	510.9	511.2	512.1
35°	539.1	539.7	540.3	543.0	543.3	545.4	546.0	545.4	547.8	546.3	547.8
37.5°	559.5	562.2	562.8	564.6	564.0	565.5	566.4	567.6	568.2	569.4	571.8
40°	584.4	585.3	587.1	588.0	589.2	589.5	590.7	591.6	592.5	595.2	597.9
42.5°	609.9	611.1	612.0	613.2	614.7	615.9	616.8	619.5	620.1	621.9	627.0
45°	640.8	640.2	640.5	640.8	641.4	642.9	645.6	648.3	650.1	654.3	658.5
47.5°	679.2	675.3	673.8	671.4	672.0	675.3	675.9	680.4	684.0	687.9	693.0
50°	737.4	726.9	720.6	714.3	713.7	715.5	717.9	722.7	726.9	732.0	739.2
52.5°	835.2	815.1	802.5	785.1	780.3	779.4	777.6	780.3	781.5	788.4	801.9
55°	1033.3	996.1	972.1	945.1	919.9	912.3	897.9	900.9	897.9	902.1	922.3
57.5°	1446.7	1417.0	1393.6	1359.1	1315.9	1270.0	1258.6	1211.5	1220.8	1247.8	1230.4
60°	2047.0	2036.2	2019.4	2002.9	1943.8	1910.5	1856.2	1850.2	1812.1	1812.4	1787.5
62.5°	2383.0	2396.8	2386.6	2381.8	2378.5	2368.0	2341.0	2308.6	2260.0	2224.9	2173.3
65°	2479.0	2467.3	2456.2	2454.7	2453.8	2470.9	2474.8	2452.0	2407.9	2353.3	2293.9
67.5°	2367.1	2360.5	2361.1	2348.5	2356.3	2386.0	2406.7	2400.4	2359.9	2293.9	2218.3
70°	2100.7	2087.8	2101.0	2117.5	2129.2	2146.3	2167.0	2172.1	2135.2	2067.4	1990.3
72.5°	1573.0	1575.1	1587.7	1592.2	1639.3	1634.5	1653.1	1592.5	1565.8	1501.3	1461.7
75°	827.7	814.2	849.3	774.9	744.3	765.6	705.9	648.6	660.6	670.5	599.1
77.5°	292.5	273.6	241.5	228.6	190.2	161.1	131.7	118.8	111.9	108.3	103.8
80°	210.0	216.0	209.4	193.8	164.7	132.0	104.1	82.2	70.5	64.2	60.0
82.5°	212.4	236.1	246.6	242.1	215.7	163.2	107.7	68.7	51.0	42.6	39.6
85°	114.0	124.8	120.0	101.1	90.9	54.3	37.2	24.9	21.0	19.2	17.7
87.5°	4.5	3.6	3.0	3.0	3.3	3.6	3.0	3.3	3.0	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181281

CATALOG NUMBER: ICS-E01-LED-E1-T2

CANDELA DISTRIBUTION (continued):

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7	275.7
2.5°	276.6	276.6	276.6	276.3	275.7	274.2	272.7	271.5	270.6	269.7	268.5
5°	282.0	281.4	281.4	281.4	279.0	276.6	274.5	272.4	270.6	269.1	267.9
7.5°	291.0	290.7	289.5	289.2	287.4	283.5	281.1	277.5	275.4	273.3	272.7
10°	301.8	301.5	301.2	300.9	298.5	294.6	291.6	288.3	285.3	282.3	279.3
12.5°	314.4	314.1	313.8	312.9	312.0	309.9	306.6	303.0	299.4	293.1	289.8
15°	330.0	330.6	330.0	329.7	329.1	329.4	327.3	322.2	316.5	308.4	301.5
17.5°	350.7	350.1	349.8	351.0	350.7	352.2	351.6	345.0	336.3	323.4	311.4
20°	373.5	373.5	374.7	375.6	378.3	382.2	380.4	372.3	356.4	338.4	322.8
22.5°	400.8	401.4	402.6	402.0	406.2	412.5	413.1	401.7	381.0	356.1	334.2
25°	429.3	429.9	428.7	430.5	437.4	446.4	448.2	432.0	404.7	372.3	343.8
27.5°	456.3	456.9	456.9	459.3	465.9	481.2	483.0	465.0	428.7	386.4	350.7
30°	482.7	485.1	485.7	486.3	496.2	517.5	521.4	495.3	449.7	396.9	355.5
32.5°	516.0	516.9	518.1	519.6	531.0	557.1	557.1	521.4	463.2	403.5	356.4
35°	551.7	552.0	554.7	555.0	571.2	597.3	592.2	543.0	472.8	402.0	349.8
37.5°	573.3	574.5	577.2	580.8	597.9	634.8	623.1	561.6	474.6	392.1	334.8
40°	600.0	602.4	605.1	608.7	634.2	672.9	649.2	573.3	467.1	372.6	312.3
42.5°	628.8	632.1	636.3	642.9	673.2	706.5	669.0	575.1	450.0	350.7	285.6
45°	661.2	667.2	672.0	679.8	714.0	735.6	681.0	564.6	428.4	321.9	257.1
47.5°	698.7	703.5	711.9	720.3	754.5	755.4	682.2	544.2	399.0	293.1	226.8
50°	744.9	747.9	760.5	765.6	797.7	776.1	673.5	516.6	368.1	260.7	193.2
52.5°	806.4	810.6	826.8	834.6	857.4	804.3	661.2	486.6	332.7	224.4	158.7
55°	928.0	946.3	957.7	971.2	985.9	868.2	655.8	454.5	292.8	182.4	125.7
57.5°	1269.1	1263.1	1288.3	1318.9	1318.6	1014.4	688.2	426.9	245.7	139.5	96.6
60°	1777.3	1783.0	1770.1	1788.4	1730.2	1195.6	732.6	397.8	192.6	103.8	73.8
62.5°	2155.0	2122.0	2103.7	2082.1	1954.0	1215.4	700.2	338.1	140.1	72.9	56.7
65°	2244.4	2205.7	2166.4	2125.3	1932.1	1095.7	574.5	248.1	90.6	50.1	45.0
67.5°	2156.2	2094.1	2044.0	2001.7	1770.4	908.1	420.0	152.4	51.9	40.5	38.4
70°	1927.6	1858.9	1777.9	1730.5	1490.8	669.3	269.1	82.2	39.9	36.0	35.1
72.5°	1411.0	1354.6	1266.1	1211.8	1070.5	406.8	150.3	46.2	37.2	34.5	33.3
75°	549.6	520.2	483.3	486.3	434.1	180.0	68.1	39.9	36.3	33.9	32.7
77.5°	94.5	92.1	85.2	85.2	96.9	65.7	45.3	40.2	36.0	33.3	31.2
80°	56.7	55.5	52.8	52.2	50.4	46.2	43.5	40.8	35.4	31.5	28.8
82.5°	37.2	35.7	34.8	34.5	37.5	40.5	40.8	40.5	33.6	27.3	23.4
85°	15.9	15.9	15.9	16.2	21.6	32.7	33.6	36.0	27.6	21.3	16.8
87.5°	2.7	3.3	3.3	3.6	3.9	7.2	9.0	11.7	9.3	9.0	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181281

CATALOG NUMBER: ICS-E01-LED-E1-T2

CANDELA DISTRIBUTION (continued):

	165°	175°	180°
0°	275.7	275.7	275.7
2.5°	268.2	267.6	267.6
5°	267.3	266.7	267.0
7.5°	270.9	269.7	270.0
10°	277.5	276.3	275.7
12.5°	285.9	284.4	284.4
15°	294.6	291.0	290.7
17.5°	301.8	297.3	296.7
20°	309.9	303.9	303.0
22.5°	317.4	309.3	308.1
25°	322.8	312.9	311.4
27.5°	325.2	313.5	312.3
30°	327.0	313.8	312.0
32.5°	325.2	311.1	309.6
35°	315.3	300.0	299.1
37.5°	298.2	281.1	279.9
40°	275.7	257.7	254.7
42.5°	246.9	230.1	226.8
45°	219.0	199.8	198.3
47.5°	189.0	170.7	171.6
50°	157.5	141.0	140.7
52.5°	127.5	113.1	112.2
55°	100.5	90.3	89.4
57.5°	79.5	74.1	73.2
60°	64.8	62.1	61.2
62.5°	52.2	51.3	51.0
65°	43.5	43.5	43.5
67.5°	37.8	38.1	38.1
70°	34.8	35.1	34.8
72.5°	33.6	34.5	34.5
75°	32.7	33.3	32.1
77.5°	32.1	32.4	30.3
80°	31.8	31.5	27.6
82.5°	27.6	26.7	23.4
85°	25.2	19.2	16.2
87.5°	12.9	9.0	6.9
90°	0.0	0.0	0.0

(END OF REPORT)