

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P152180

Luminaire Tested: **VXS-E05-LED-E1-SL4**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P152180
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-SL4
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (105) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14770.6 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P152180

CATALOG NUMBER: VXS-E05-LED-E1-SL4

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 7.9 fc
Type IV - Short - Full Cutoff

REPORT NUMBER: P152180

CATALOG NUMBER: VXS-E05-LED-E1-SL4

Luminous Intensity Polar Plot



REPORT NUMBER: P152180

CATALOG NUMBER: VXS-E05-LED-E1-SL4


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3066.2	0.0	3066.2
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	11704.4	0.0	11704.4
	% Fixture	79.2	0.0	79.2
Total	Lumens	14770.6	0.0	14770.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.4	2.0
10°-20°	806.0	5.5
20°-30°	1193.2	8.1
30°-40°	1507.9	10.2
40°-50°	1705.4	11.5
50°-60°	2426.8	16.4
60°-70°	4519.6	30.6
70°-80°	2071.4	14.0
80°-90°	245.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14770.6	100.0
0°-180°	14770.6	100.0

Coefficient of Utilization



REPORT NUMBER: P152180


CATALOG NUMBER: VXS-E05-LED-E1-SL4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1345.0	9.1			
FM	(30°-60°)	4327.3	29.3			
FH	(60°-80°)	5849.7	39.6			G3/7500
FVH	(80°-90°)	182.4	1.2			G2/225
BL	(0°-30°)	948.7	6.4	B2/1000		
BM	(30°-60°)	1312.8	8.9	B2/2500		
BH	(60°-80°)	741.3	5.0	B2/1000		G2/1000
BVH	(80°-90°)	63.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P152180

CATALOG NUMBER: VXS-E05-LED-E1-SL4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7
2.5°	3200.0	3208.3	3198.3	3196.7	3196.7	3195.0	3185.0	3183.3	3169.9	3171.7	3175.0
5°	3223.3	3226.6	3220.0	3218.3	3215.0	3208.3	3200.0	3190.1	3180.0	3169.9	3161.7
7.5°	3246.6	3243.3	3238.3	3238.3	3233.4	3223.3	3206.6	3193.4	3171.7	3160.0	3145.0
10°	3280.0	3275.0	3268.3	3265.0	3256.7	3241.7	3218.3	3200.0	3173.4	3150.1	3125.0
12.5°	3311.7	3310.1	3300.0	3295.0	3281.7	3266.6	3238.3	3209.9	3175.0	3138.3	3105.0
15°	3368.3	3361.7	3351.7	3341.7	3320.0	3300.0	3256.7	3223.3	3173.4	3125.0	3073.4
17.5°	3466.6	3455.0	3445.0	3423.3	3396.7	3361.7	3298.3	3241.7	3173.4	3103.3	3045.0
20°	3646.6	3621.7	3608.3	3580.0	3533.4	3470.1	3371.7	3280.0	3178.3	3088.3	3009.9
22.5°	3849.9	3833.4	3815.0	3796.7	3723.3	3631.7	3498.3	3361.7	3208.3	3081.7	2981.7
25°	4078.3	4056.7	4046.6	4015.0	3946.6	3841.7	3660.0	3470.1	3276.7	3108.3	2981.7
27.5°	4281.7	4275.0	4273.4	4236.7	4171.7	4048.3	3833.4	3605.0	3369.9	3163.3	3006.6
30°	4466.6	4460.0	4456.7	4436.7	4361.7	4215.0	3981.7	3725.0	3471.7	3240.0	3053.4
32.5°	4663.3	4641.7	4631.7	4593.4	4508.3	4336.7	4070.1	3803.3	3551.7	3315.0	3105.0
35°	4823.3	4805.0	4785.0	4729.9	4610.1	4406.6	4108.3	3830.1	3583.3	3356.7	3131.7
37.5°	4940.0	4921.7	4893.4	4823.3	4675.0	4430.1	4106.6	3821.7	3571.7	3350.1	3136.7
40°	4991.7	4973.4	4943.3	4855.0	4686.6	4416.7	4075.0	3783.3	3536.7	3315.0	3116.7
42.5°	4971.7	4958.3	4920.0	4835.0	4649.9	4356.7	4011.7	3711.7	3470.1	3258.3	3071.7
45°	4895.0	4885.0	4848.3	4758.3	4566.6	4260.0	3918.3	3621.7	3390.1	3188.3	3011.7
47.5°	4780.0	4776.7	4740.0	4651.7	4461.7	4163.3	3821.7	3533.4	3310.1	3120.0	2961.7
50°	4653.4	4636.7	4618.3	4536.7	4363.3	4080.0	3751.7	3478.3	3265.0	3095.0	2940.0
52.5°	4573.4	4568.3	4551.7	4478.3	4311.7	4031.7	3720.0	3458.3	3261.7	3089.9	2928.3
55°	5283.3	5295.0	5141.7	4823.3	4543.3	4165.0	3815.0	3560.0	3343.3	3169.9	3051.7
57.5°	7815.0	7763.3	7500.0	6868.3	6155.0	5213.4	4535.0	4123.3	3855.0	3885.0	3945.0
60°	9105.0	9095.0	9046.6	8801.7	8326.6	7609.9	6815.0	5903.3	5613.4	5645.0	5668.3
62.5°	9681.7	9696.7	9733.4	9641.7	9516.7	9308.3	8911.7	8545.0	8156.7	8011.7	7623.3
65°	9948.3	9975.0	10058.3	10110.1	10158.3	10195.0	10351.7	10781.7	11065.0	10535.0	9301.7
67.5°	9396.7	9525.0	9800.0	10068.3	10308.3	10649.9	11180.0	12178.3	12873.4	12221.7	10433.4
70°	6849.9	7025.0	7340.0	8169.9	9056.7	9831.7	10858.3	12378.3	13426.6	12923.3	10713.4
72.5°	4295.0	4343.3	4483.3	4788.3	5446.6	6441.7	8236.7	10516.7	11726.6	11325.0	9055.0
75°	2725.0	2741.7	2736.7	2806.6	2918.3	3135.0	3845.0	6211.7	8033.4	7406.6	5046.6
77.5°	1623.3	1648.3	1658.3	1680.0	1733.4	1809.9	1868.3	2113.4	3368.3	3270.1	1831.7
80°	1360.0	1380.0	1363.3	1358.3	1325.0	1301.7	1329.9	1301.7	1208.3	1163.3	1071.7
82.5°	720.0	718.3	713.4	761.7	860.0	936.7	995.0	981.7	888.3	756.7	641.7
85°	395.0	408.3	408.3	425.0	410.1	411.7	425.0	448.3	415.0	346.6	283.3
87.5°	33.4	51.7	41.7	51.7	70.1	49.9	48.3	48.3	41.7	30.1	26.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152180

CATALOG NUMBER: VXS-E05-LED-E1-SL4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7
2.5°	3166.6	3163.3	3156.7	3151.7	3151.7	3143.3	3138.3	3135.0	3133.4	3126.6	3126.6
5°	3156.7	3145.0	3133.4	3125.0	3120.0	3111.7	3098.3	3091.7	3083.3	3076.7	3073.4
7.5°	3135.0	3113.4	3095.0	3081.7	3065.0	3051.7	3035.0	3020.0	3005.0	2998.3	2995.0
10°	3101.7	3073.4	3045.0	3020.0	2996.7	2973.4	2951.7	2930.1	2911.7	2898.3	2885.0
12.5°	3070.1	3026.6	2990.1	2953.4	2916.7	2888.3	2858.3	2826.6	2800.0	2775.0	2768.3
15°	3026.6	2976.7	2930.1	2885.0	2840.0	2793.4	2756.7	2721.7	2678.3	2649.9	2628.3
17.5°	2986.6	2926.6	2870.1	2816.7	2761.7	2713.4	2658.3	2611.7	2568.3	2525.0	2493.4
20°	2943.3	2878.3	2818.3	2758.3	2698.3	2636.7	2573.4	2513.4	2460.0	2408.3	2356.7
22.5°	2905.0	2838.3	2780.0	2715.0	2648.3	2578.3	2505.0	2430.1	2368.3	2301.7	2241.7
25°	2881.7	2808.3	2748.3	2685.0	2611.7	2535.0	2451.7	2363.3	2288.3	2211.7	2140.0
27.5°	2881.7	2786.6	2725.0	2661.7	2586.6	2505.0	2413.4	2316.7	2231.7	2146.6	2058.3
30°	2906.6	2790.1	2706.6	2640.0	2563.3	2475.0	2373.4	2271.7	2178.3	2078.3	1993.4
32.5°	2930.1	2796.7	2693.4	2608.3	2520.0	2433.4	2330.1	2221.7	2118.3	2023.3	1933.4
35°	2945.0	2796.7	2668.3	2560.0	2460.0	2375.0	2273.4	2165.0	2060.0	1966.6	1883.3
37.5°	2946.6	2783.3	2628.3	2505.0	2400.0	2311.7	2215.0	2113.4	2013.4	1926.6	1856.7
40°	2930.1	2756.7	2588.3	2446.6	2336.7	2246.6	2158.3	2066.6	1976.7	1905.0	1845.0
42.5°	2900.0	2728.3	2550.1	2400.0	2285.0	2191.7	2110.1	2031.7	1953.4	1891.7	1841.7
45°	2855.0	2689.9	2515.0	2371.7	2258.3	2160.0	2080.0	2015.0	1948.3	1896.7	1846.6
47.5°	2815.0	2676.7	2526.6	2390.1	2271.7	2169.9	2088.3	2033.4	1981.7	1946.6	1878.3
50°	2806.6	2670.1	2531.7	2405.0	2285.0	2181.7	2110.1	2081.7	2066.6	2045.0	1940.0
52.5°	2783.3	2668.3	2568.3	2498.3	2421.7	2373.4	2298.3	2325.0	2308.3	2231.7	2041.7
55°	3028.3	3061.7	3155.0	3288.3	3411.7	3440.0	3431.7	3400.0	3231.7	2780.0	2286.6
57.5°	4163.3	4351.7	4528.3	4606.6	4596.7	4508.3	4445.0	4316.7	4073.4	3523.3	2769.9
60°	5740.0	5769.9	5676.7	5538.3	5305.0	5110.1	4901.7	4661.7	4308.3	3769.9	3066.6
62.5°	7191.7	6788.3	6373.4	5983.3	5628.3	5318.3	5028.3	4693.4	4233.4	3671.7	3028.3
65°	8216.7	7363.3	6708.3	6148.3	5646.6	5213.4	4851.7	4416.7	3898.3	3391.7	2806.6
67.5°	8745.0	7436.7	6431.7	5651.7	4940.0	4340.0	3858.3	3435.0	3049.9	2828.3	2456.7
70°	8155.0	6311.7	4911.7	4030.1	3178.3	2548.3	2013.4	1690.1	1578.3	1788.3	1860.0
72.5°	6076.7	4108.3	2921.7	2260.0	1731.7	1380.0	1058.3	831.7	676.7	710.1	921.7
75°	2873.4	1773.4	1253.4	953.4	758.3	628.3	513.4	470.1	393.4	326.6	306.6
77.5°	1118.3	815.0	673.4	493.4	350.1	281.7	240.0	231.7	236.7	230.1	226.6
80°	851.7	576.7	361.7	265.0	228.3	201.7	178.3	171.7	175.0	183.3	191.7
82.5°	475.0	296.7	220.0	191.7	171.7	146.6	133.4	123.3	125.0	135.0	153.4
85°	183.3	143.3	131.7	126.6	118.3	95.0	81.7	83.3	95.0	113.4	113.4
87.5°	20.0	20.0	26.6	20.0	20.0	20.0	18.3	21.7	23.3	30.1	35.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152180

CATALOG NUMBER: VXS-E05-LED-E1-SL4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7	3151.7
2.5°	3123.3	3123.3	3123.3	3120.0	3121.7	3115.0	3115.0	3110.1	3118.3	3113.4	3111.7
5°	3075.0	3073.4	3066.6	3066.6	3066.6	3066.6	3071.7	3058.3	3068.3	3068.3	3063.3
7.5°	2993.4	2993.4	2975.0	2985.0	2981.7	2986.6	2993.4	2986.6	2996.7	3003.3	2998.3
10°	2880.0	2880.0	2865.0	2876.7	2871.7	2883.3	2895.0	2888.3	2895.0	2905.0	2908.3
12.5°	2755.0	2748.3	2735.0	2740.0	2740.0	2746.6	2751.7	2760.0	2768.3	2781.7	2788.3
15°	2609.9	2600.0	2583.3	2583.3	2573.4	2576.7	2586.6	2590.1	2606.6	2625.0	2646.6
17.5°	2461.7	2436.7	2418.3	2396.7	2380.0	2393.4	2405.0	2413.4	2426.6	2455.0	2470.1
20°	2321.7	2271.7	2236.7	2208.3	2190.1	2198.3	2213.4	2223.3	2235.0	2241.7	2246.6
22.5°	2183.3	2126.6	2078.3	2043.3	2013.4	2021.7	2015.0	2009.9	2018.3	1996.7	1995.0
25°	2063.3	1996.7	1931.7	1889.9	1853.4	1841.7	1806.6	1798.3	1775.0	1756.7	1743.3
27.5°	1976.7	1889.9	1818.3	1769.9	1711.7	1668.3	1623.3	1578.3	1553.4	1523.3	1508.3
30°	1908.3	1816.7	1731.7	1649.9	1573.4	1506.6	1446.6	1388.3	1348.3	1305.0	1276.7
32.5°	1845.0	1760.0	1656.7	1545.0	1441.7	1366.6	1288.3	1221.7	1158.3	1101.7	1060.0
35°	1801.7	1706.6	1575.0	1438.3	1321.7	1233.4	1150.1	1055.0	978.3	905.0	860.0
37.5°	1778.3	1661.7	1500.0	1348.3	1218.3	1118.3	1015.0	905.0	811.7	743.3	675.0
40°	1760.0	1616.7	1433.4	1268.3	1131.7	1011.7	891.7	761.7	658.3	586.6	533.4
42.5°	1740.0	1566.6	1375.0	1205.0	1053.4	913.4	768.3	630.1	531.7	481.7	458.3
45°	1718.3	1523.3	1320.0	1145.0	976.7	806.6	640.0	511.7	453.4	436.7	436.7
47.5°	1713.4	1495.0	1280.0	1086.6	889.9	683.3	521.7	441.7	425.0	428.3	435.0
50°	1733.4	1486.6	1245.0	1018.3	775.0	553.4	441.7	415.0	418.3	428.3	438.3
52.5°	1781.7	1493.4	1208.3	923.3	638.3	456.7	408.3	406.6	416.7	431.7	441.7
55°	1863.3	1493.4	1138.3	781.7	510.1	410.1	396.7	403.3	416.7	430.1	438.3
57.5°	2038.3	1478.3	1015.0	625.0	426.6	393.4	393.4	401.7	413.4	426.6	433.4
60°	2246.6	1458.3	841.7	483.3	385.0	380.0	391.7	401.7	411.7	423.3	430.1
62.5°	2260.0	1406.6	666.6	400.0	363.3	371.7	390.1	403.3	406.6	415.0	423.3
65°	2076.7	1226.6	529.9	358.3	353.4	366.6	385.0	395.0	396.7	400.0	408.3
67.5°	1818.3	1000.0	428.3	338.3	343.3	358.3	368.3	376.7	381.7	390.1	391.7
70°	1493.4	803.3	366.6	318.3	323.3	340.0	348.3	356.7	366.6	376.7	371.7
72.5°	1058.3	625.0	321.7	296.7	303.3	318.3	328.3	335.0	343.3	353.4	346.6
75°	449.9	436.7	278.3	268.3	278.3	288.3	298.3	308.3	316.7	321.7	321.7
77.5°	230.1	256.7	240.0	240.0	246.6	256.7	265.0	275.0	280.0	285.0	291.7
80°	195.0	198.3	201.7	208.3	215.0	225.0	233.4	241.7	243.3	245.0	248.3
82.5°	161.7	168.3	171.7	181.7	186.6	190.1	195.0	195.0	198.3	198.3	193.4
85°	116.7	125.0	129.9	131.7	129.9	131.7	133.4	136.7	145.0	145.0	138.3
87.5°	33.4	31.7	40.0	41.7	45.0	51.7	58.3	70.1	73.4	76.7	76.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152180

CATALOG NUMBER: VXS-E05-LED-E1-SL4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3151.7	3151.7	3151.7	3151.7
2.5°	3110.1	3113.4	3106.6	3108.3
5°	3063.3	3070.1	3061.7	3071.7
7.5°	3003.3	3013.4	3011.7	3009.9
10°	2916.7	2930.1	2930.1	2935.0
12.5°	2806.6	2815.0	2821.7	2825.0
15°	2658.3	2673.4	2681.7	2681.7
17.5°	2480.0	2489.9	2495.0	2488.3
20°	2253.4	2249.9	2251.7	2235.0
22.5°	1991.7	1996.7	1981.7	1985.0
25°	1735.0	1726.6	1733.4	1723.3
27.5°	1486.6	1488.3	1470.1	1478.3
30°	1249.9	1241.7	1218.3	1230.1
32.5°	1021.7	1000.0	975.0	960.0
35°	806.6	773.4	761.7	756.7
37.5°	633.4	596.7	585.0	571.7
40°	503.3	489.9	485.0	488.3
42.5°	451.7	451.7	455.0	456.7
45°	438.3	443.3	448.3	449.9
47.5°	440.0	445.0	451.7	453.4
50°	443.3	448.3	453.4	455.0
52.5°	445.0	445.0	448.3	449.9
55°	441.7	440.0	441.7	443.3
57.5°	435.0	431.7	433.4	438.3
60°	431.7	426.6	430.1	433.4
62.5°	423.3	421.7	425.0	426.6
65°	405.0	406.6	411.7	411.7
67.5°	388.3	390.1	391.7	393.4
70°	368.3	369.9	373.4	375.0
72.5°	345.0	351.7	356.7	363.3
75°	326.6	333.4	343.3	350.1
77.5°	295.0	300.0	311.7	320.0
80°	249.9	248.3	249.9	255.0
82.5°	191.7	191.7	190.1	188.3
85°	135.0	133.4	128.3	128.3
87.5°	73.4	71.7	70.1	66.6
90°	0.0	0.0	0.0	0.0

(END OF REPORT)