

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P181195

Luminaire Tested: **ICM-E06-LED-E1-T2-HSS**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P181195  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33723)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ICM-E06-LED-E1-T2-HSS  
Description: ICON SITE MEDIUM LED LUMINAIRE  
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 2 W/ HOUSE SIDE SHIELD  
Light Source: (126) 4000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8937.5 lumens  
Efficiency: N/A  
Efficacy: 59.4 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 1' x H: 0.1')  
IES Classification: Type II - Short - Non-Cutoff  
BUG Rating: B0 - U0 - G2  
  
Input Watts (W): 150.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P181195  
 CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 17.4 fc  
 Type II - Short - Non-Cutoff

REPORT NUMBER: P181195  
CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 71-Deg Lateral    - - - Horizontal Cone Through 64-Deg Vertical

REPORT NUMBER: P181195

CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	171.1	0.0	171.1
	% Fixture	1.9	0.0	1.9
<b>Street Side</b>	Lumens	8766.4	0.0	8766.4
	% Fixture	98.1	0.0	98.1
<b>Total</b>	Lumens	8937.5	0.0	8937.5
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.4	0.3
10°-20°	161.6	1.8
20°-30°	412.8	4.6
30°-40°	834.9	9.3
40°-50°	1526.1	17.1
50°-60°	2377.6	26.6
60°-70°	2642.7	29.6
70°-80°	861.9	9.6
80°-90°	92.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8937.5	100.0
0°-180°	8937.5	100.0

**Coefficient of Utilization**



REPORT NUMBER: P181195


CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	554.1	6.2			
FM	(30°-60°)	4672.3	52.3			
FH	(60°-80°)	3451.8	38.6			G2/5000
FVH	(80°-90°)	88.3	1.0			G1/100
BL	(0°-30°)	47.6	0.5	B0/110		
BM	(30°-60°)	66.2	0.7	B0/220		
BH	(60°-80°)	52.8	0.6	B0/110		G0/110
BVH	(80°-90°)	4.5	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G2**

Type II Short





REPORT NUMBER: P181195

CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	56°	57°	58°	59°
0°	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1
2.5°	267.9	264.2	264.2	258.6	251.2	243.7	236.3	234.4	232.6	230.7	230.7
5°	420.5	405.6	400.0	379.5	353.5	321.9	294.0	286.5	286.5	280.9	277.2
7.5°	660.5	653.0	614.0	593.5	532.1	455.8	375.8	368.4	366.5	359.1	347.9
10°	967.4	952.6	924.7	865.1	753.5	621.4	507.9	489.3	476.3	461.4	446.5
12.5°	1274.4	1255.8	1214.9	1118.1	1006.5	837.2	654.9	638.1	617.7	597.2	573.0
15°	1581.4	1568.4	1505.1	1408.4	1263.3	1060.5	829.8	800.0	783.3	742.3	723.7
17.5°	1847.5	1830.7	1780.5	1670.7	1520.0	1296.8	1023.3	986.1	958.1	934.0	889.3
20°	2078.2	2061.4	2013.0	1921.9	1752.6	1533.0	1231.6	1213.0	1162.8	1125.6	1099.5
22.5°	2219.5	2214.0	2182.3	2094.9	1944.2	1748.8	1469.8	1440.0	1406.5	1356.3	1326.5
25°	2307.0	2301.4	2282.8	2221.4	2119.1	1975.8	1732.1	1694.9	1665.1	1620.5	1583.3
27.5°	2398.2	2394.4	2379.5	2325.6	2271.6	2182.3	1998.2	1977.7	1912.6	1886.5	1851.2
30°	2548.9	2532.1	2545.1	2519.1	2450.2	2394.4	2266.1	2236.3	2208.4	2163.7	2132.1
32.5°	2788.9	2760.9	2788.9	2760.9	2731.2	2664.2	2541.4	2532.1	2504.2	2476.3	2431.6
35°	3082.8	3071.6	3094.0	3118.2	3094.0	3004.7	2855.8	2827.9	2816.8	2772.1	2755.4
37.5°	3378.6	3399.1	3440.0	3494.0	3479.1	3414.0	3203.7	3177.7	3157.2	3118.2	3088.4
40°	3696.8	3698.6	3786.1	3864.2	3903.3	3864.2	3587.0	3566.5	3538.6	3482.8	3475.4
42.5°	4042.8	4027.9	4093.0	4180.5	4260.5	4314.4	4093.0	4054.0	4014.9	3951.7	3908.9
45°	4349.8	4349.8	4401.9	4483.7	4606.5	4742.4	4627.0	4586.1	4548.9	4496.8	4448.4
47.5°	4576.8	4578.6	4610.3	4729.3	4921.0	5123.8	5127.5	5134.9	5107.0	5045.6	5047.5
50°	4736.8	4716.3	4759.1	4874.4	5095.8	5414.0	5642.8	5655.8	5678.2	5627.9	5642.8
52.5°	4854.0	4844.7	4872.6	4969.3	5190.7	5579.6	6065.2	6121.0	6154.5	6161.9	6223.3
55°	4792.6	4798.2	4865.1	5004.7	5242.8	5689.3	6424.2	6515.4	6593.5	6660.5	6736.8
57.5°	4589.8	4606.5	4723.7	4941.4	5254.0	5778.6	6805.6	6945.2	7092.1	7270.7	7421.4
60°	4266.1	4305.1	4463.3	4768.4	5146.1	5661.4	6919.1	7133.1	7358.2	7629.8	7933.1
62.5°	3791.7	3799.1	3903.3	4199.1	4615.8	5038.2	6398.2	6671.7	6969.3	7361.9	7786.1
64°	3142.3	3209.3	3257.7	3583.3	3955.4	4481.9	5709.8	5899.6	6314.5	6796.3	7330.3
65°	2593.5	2673.5	2712.6	3038.2	3464.2	3966.5	5110.7	5313.5	5750.7	6240.0	6906.1
67.5°	1529.3	1475.4	1588.8	1780.5	2137.7	2733.0	3447.5	3601.9	3927.5	4509.8	5041.9
70°	986.1	986.1	1090.2	1285.6	1616.8	2072.6	2368.4	2303.3	2372.1	2597.2	2973.0
72.5°	632.6	666.1	729.3	894.9	1201.9	1737.7	2420.5	2113.5	1953.5	1879.1	1875.4
75°	288.4	307.0	375.8	474.4	641.9	1133.0	2440.9	2307.0	2160.0	2018.6	1908.8
77.5°	61.4	70.7	119.1	245.6	312.6	522.8	1732.1	1933.0	2093.0	2139.5	2139.5
80°	31.6	33.5	50.2	115.3	134.0	176.7	667.9	878.1	1082.8	1352.6	1635.4
82.5°	13.0	14.9	29.8	52.1	55.8	54.0	176.7	223.3	307.0	446.5	666.1
85°	3.7	3.7	13.0	20.5	29.8	24.2	39.1	44.7	57.7	83.7	160.0
87.5°	0.0	0.0	1.9	3.7	5.6	9.3	11.2	11.2	11.2	11.2	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181195

CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS

**CANDELA DISTRIBUTION (continued):**

	60°	61°	62°	64°	65°	66°	67°	68°	69°	70°	71°
0°	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1
2.5°	228.8	228.8	227.0	225.1	225.1	221.4	221.4	219.5	219.5	217.7	217.7
5°	275.4	271.6	267.9	262.3	260.5	256.7	253.0	249.3	245.6	243.7	240.0
7.5°	342.3	338.6	327.4	320.0	310.7	305.1	297.7	292.1	286.5	282.8	275.4
10°	431.6	418.6	413.0	387.0	381.4	368.4	357.2	349.8	334.9	325.6	316.3
12.5°	558.1	534.0	524.7	480.0	467.0	448.4	435.4	416.7	400.0	388.8	372.1
15°	701.4	682.8	647.4	602.8	578.6	558.1	526.5	511.6	489.3	465.1	440.9
17.5°	872.6	839.1	800.0	742.3	712.6	680.9	651.2	619.5	582.3	560.0	534.0
20°	1071.6	1036.3	987.9	915.4	880.0	848.4	796.3	774.0	729.3	684.7	651.2
22.5°	1289.3	1254.0	1207.4	1125.6	1079.1	1027.0	984.2	945.1	893.0	848.4	809.3
25°	1534.9	1494.0	1458.6	1363.7	1306.1	1252.1	1205.6	1136.8	1092.1	1040.0	986.1
27.5°	1814.0	1765.6	1719.1	1614.9	1560.9	1501.4	1445.6	1373.0	1330.2	1244.7	1194.4
30°	2100.5	2040.9	1992.6	1886.5	1838.2	1776.8	1700.5	1635.4	1562.8	1505.1	1423.3
32.5°	2401.9	2353.5	2314.4	2202.8	2141.4	2065.1	1996.3	1927.5	1864.2	1771.2	1696.8
35°	2723.7	2680.9	2638.2	2541.4	2487.5	2429.8	2351.6	2267.9	2180.5	2083.7	2016.8
37.5°	3062.3	3028.9	2995.4	2878.2	2814.9	2753.5	2664.2	2580.5	2502.3	2400.0	2286.5
40°	3417.7	3386.1	3332.1	3235.4	3168.4	3112.6	3030.7	2952.6	2846.5	2733.0	2632.6
42.5°	3864.2	3795.4	3748.9	3642.8	3572.1	3510.7	3438.2	3321.0	3231.6	3095.8	2999.1
45°	4387.0	4321.9	4245.6	4137.7	4050.3	3949.8	3847.5	3767.5	3655.8	3533.0	3408.4
47.5°	4974.9	4922.8	4833.5	4727.5	4640.0	4539.6	4418.6	4316.3	4180.5	4037.2	3867.9
50°	5622.4	5568.4	5508.9	5389.8	5302.4	5207.5	5112.6	4991.7	4868.9	4697.7	4522.8
52.5°	6223.3	6234.5	6199.1	6143.3	6100.5	6001.9	5914.5	5799.1	5691.2	5534.9	5399.1
55°	6816.8	6913.5	6950.7	7004.7	7023.3	6943.3	6941.4	6772.1	6707.0	6615.9	6537.7
57.5°	7600.0	7814.0	7983.3	8310.7	8448.4	8588.0	8614.0	8494.9	8617.7	8459.6	8513.5
60°	8266.1	8658.7	9079.1	9925.6	10349.8	10669.8	10926.6	11116.3	11239.1	11447.5	11458.7
62.5°	8325.6	8943.3	9583.3	10818.7	11399.1	11884.7	12348.0	12671.7	12928.5	13164.7	13222.4
64°	8041.0	8805.6	9583.3	11077.3	11670.8	12210.3	12632.6	12954.5	13216.8	13363.8	13460.5
65°	7523.8	8379.6	9274.5	10906.1	11518.2	12091.2	12495.0	12818.7	13066.1	13213.1	13313.6
67.5°	5574.0	6401.9	7300.5	9200.1	10163.8	10688.4	11205.6	11659.6	11858.7	12044.7	12080.1
70°	3397.2	3998.2	4617.7	6379.6	7274.5	8217.7	8800.1	9464.2	9929.4	10215.9	10310.8
72.5°	2050.2	2258.6	2628.9	3575.8	4433.5	5095.8	5901.4	6535.9	7056.8	7345.2	7490.3
75°	1825.1	1799.1	1847.5	2241.9	2547.0	2945.1	3237.2	3635.4	3957.2	4057.7	4245.6
77.5°	2109.8	2035.4	1959.1	1884.7	1869.8	1832.6	1773.0	1787.9	1646.5	1510.7	1514.4
80°	1879.1	2057.7	2163.7	2085.6	1908.8	1730.2	1510.7	1237.2	967.4	800.0	729.3
82.5°	943.3	1341.4	1724.7	2104.2	2078.2	1920.0	1678.1	1378.6	1067.9	820.5	654.9
85°	290.2	515.4	725.6	1008.4	1170.2	1147.9	1008.4	980.5	699.5	545.1	420.5
87.5°	13.0	13.0	13.0	11.2	13.0	13.0	13.0	14.9	14.9	16.7	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P181195

CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS

**CANDELA DISTRIBUTION (continued):**

	72°	73°	74°	75°	76°	77°	78°	79°	80°	81°	82°
0°	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1
2.5°	217.7	215.8	214.0	212.1	212.1	212.1	210.2	210.2	208.4	208.4	206.5
5°	240.0	236.3	234.4	230.7	230.7	227.0	225.1	223.3	219.5	217.7	215.8
7.5°	269.8	266.0	260.5	254.9	253.0	247.4	241.9	238.1	234.4	230.7	227.0
10°	308.8	301.4	290.2	282.8	277.2	269.8	262.3	256.7	249.3	241.9	238.1
12.5°	359.1	344.2	333.0	320.0	308.8	297.7	284.7	277.2	269.8	258.6	251.2
15°	416.7	401.9	388.8	366.5	347.9	333.0	321.9	305.1	292.1	277.2	266.0
17.5°	515.4	476.3	450.2	427.9	409.3	381.4	359.1	340.5	323.7	305.1	292.1
20°	612.1	578.6	543.3	517.2	476.3	452.1	422.3	396.3	366.5	344.2	321.9
22.5°	753.5	710.7	666.1	627.0	571.2	537.7	498.6	465.1	427.9	390.7	366.5
25°	932.1	868.8	809.3	753.5	701.4	651.2	600.9	547.0	507.9	463.3	422.3
27.5°	1120.0	1049.3	991.6	919.1	852.1	790.7	727.4	669.8	602.8	545.1	496.7
30°	1356.3	1259.5	1192.6	1105.1	1038.1	952.6	874.4	798.1	716.3	649.3	580.5
32.5°	1596.3	1531.2	1417.7	1343.3	1242.8	1140.5	1058.6	971.2	870.7	783.3	699.5
35°	1912.6	1800.9	1706.1	1601.9	1492.1	1386.1	1280.0	1155.4	1053.0	945.1	842.8
37.5°	2191.6	2078.2	1968.4	1832.6	1707.9	1596.3	1467.9	1337.7	1216.8	1088.4	965.6
40°	2515.4	2374.0	2243.7	2117.2	1962.8	1830.7	1696.8	1534.9	1395.4	1254.0	1108.8
42.5°	2868.9	2725.6	2571.2	2426.1	2256.8	2094.9	1929.3	1767.5	1611.2	1440.0	1270.7
45°	3255.8	3105.1	2932.1	2766.5	2582.3	2403.7	2206.5	2020.5	1836.3	1644.7	1449.3
47.5°	3735.8	3542.3	3382.3	3175.8	2947.0	2759.1	2517.2	2305.1	2094.9	1871.6	1652.1
50°	4357.2	4137.7	3907.0	3678.2	3425.1	3187.0	2919.1	2667.9	2387.0	2137.7	1886.5
52.5°	5181.4	5017.7	4749.8	4487.5	4178.6	3875.4	3507.0	3181.4	2820.5	2502.3	2195.4
55°	6351.7	6243.8	6011.2	5724.7	5454.9	5012.1	4587.9	4081.9	3613.0	3155.4	2723.7
57.5°	8470.7	8353.5	8094.9	8026.1	7611.2	7285.6	6788.9	6134.0	5339.6	4640.0	3942.3
60°	11521.9	11293.1	11040.1	10993.6	10506.1	10163.8	9670.8	8973.1	8225.2	7108.9	6158.2
62.5°	13226.1	13157.3	12952.6	12701.5	12279.1	11771.2	11216.8	10541.5	9782.4	8803.8	7672.6
64°	13455.0	13391.7	13215.0	12932.2	12508.0	12003.8	11389.8	10716.3	9955.4	9062.4	8029.8
65°	13311.7	13222.4	13071.7	12811.2	12416.8	11933.1	11315.4	10632.6	9860.5	9001.0	8041.0
67.5°	12156.4	12115.4	11977.7	11735.9	11488.4	11053.1	10509.8	9899.6	9268.9	8416.8	7629.8
70°	10321.9	10292.2	10117.3	10020.5	9611.2	9335.9	8896.8	8416.8	7858.7	7265.2	6595.4
72.5°	7652.1	7551.7	7410.3	7263.3	6986.1	6608.4	6266.1	5754.5	5466.1	4965.6	4587.9
75°	4057.7	3994.4	3774.9	3467.9	3125.6	2948.9	2593.5	2275.4	2022.3	1908.8	1635.4
77.5°	1402.8	1278.1	1155.4	1017.7	807.4	636.3	507.9	405.6	320.0	282.8	236.3
80°	699.5	664.2	625.1	547.0	459.5	370.2	290.2	228.8	187.9	160.0	143.3
82.5°	567.4	502.3	448.4	392.6	314.4	258.6	204.7	167.4	137.7	120.9	106.0
85°	334.9	256.7	195.4	176.7	137.7	119.1	102.3	87.4	74.4	70.7	65.1
87.5°	13.0	16.7	16.7	13.0	16.7	14.9	14.9	13.0	13.0	13.0	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181195

CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS

**CANDELA DISTRIBUTION (continued):**

	83°	84°	85°	86°	87°	88°	89°	90°	95°	105°	115°
0°	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1	199.1
2.5°	206.5	204.7	204.7	202.8	200.9	200.9	200.9	199.1	195.4	187.9	182.3
5°	214.0	212.1	210.2	206.5	204.7	202.8	200.9	200.9	191.6	178.6	169.3
7.5°	223.3	219.5	215.8	212.1	210.2	206.5	202.8	200.9	187.9	171.2	161.9
10°	232.6	227.0	221.4	219.5	214.0	210.2	204.7	200.9	186.0	165.6	152.6
12.5°	243.7	236.3	228.8	223.3	215.8	212.1	206.5	200.9	182.3	160.0	145.1
15°	256.7	245.6	236.3	230.7	223.3	214.0	206.5	200.9	178.6	154.4	137.7
17.5°	273.5	260.5	249.3	238.1	227.0	217.7	210.2	202.8	173.0	147.0	128.4
20°	299.5	282.8	264.2	251.2	236.3	225.1	212.1	202.8	169.3	139.5	120.9
22.5°	334.9	308.8	288.4	266.0	247.4	232.6	217.7	206.5	163.7	132.1	111.6
25°	385.1	351.6	318.1	290.2	266.0	245.6	227.0	212.1	160.0	126.5	106.0
27.5°	440.9	401.9	357.2	323.7	290.2	260.5	240.0	221.4	160.0	122.8	100.5
30°	519.1	463.3	409.3	366.5	321.9	288.4	258.6	234.4	160.0	120.9	94.9
32.5°	614.0	550.7	481.9	420.5	368.4	320.0	282.8	251.2	163.7	117.2	91.2
35°	746.1	653.0	571.2	494.9	426.0	370.2	321.9	279.1	169.3	115.3	85.6
37.5°	850.2	738.6	634.4	547.0	467.0	398.1	336.7	290.2	163.7	107.9	80.0
40°	974.9	848.4	721.9	612.1	520.9	431.6	360.9	305.1	160.0	98.6	72.6
42.5°	1125.6	967.4	820.5	695.8	582.3	476.3	392.6	323.7	160.0	93.0	67.0
45°	1267.0	1094.0	930.2	774.0	641.9	524.7	422.3	344.2	158.1	87.4	59.5
47.5°	1441.9	1237.2	1045.6	865.1	712.6	569.3	454.0	362.8	156.3	81.9	54.0
50°	1648.4	1399.1	1183.3	967.4	781.4	623.3	491.2	383.3	152.6	76.3	48.4
52.5°	1877.2	1609.3	1334.0	1084.7	867.0	680.9	526.5	401.9	147.0	70.7	42.8
55°	2282.8	1914.4	1588.8	1280.0	997.2	766.5	578.6	429.8	141.4	65.1	37.2
57.5°	3255.8	2645.6	2184.2	1719.1	1313.5	984.2	720.0	509.8	134.0	57.7	29.8
60°	5112.6	4106.1	3322.8	2606.5	1987.0	1510.7	1060.5	753.5	143.3	48.4	26.0
62.5°	6558.2	5401.0	4403.7	3505.1	2721.9	2068.8	1544.2	1125.6	206.5	42.8	20.5
64°	6935.9	5763.8	4699.6	3758.2	2943.3	2269.8	1722.8	1272.6	266.0	42.8	18.6
65°	6991.7	5875.4	4805.6	3851.2	3019.6	2323.7	1774.9	1320.9	290.2	44.7	16.7
67.5°	6761.0	5810.3	4837.2	3890.3	3077.2	2398.2	1845.6	1397.2	327.4	42.8	13.0
70°	5905.2	5205.6	4405.6	3639.1	2902.3	2279.1	1774.9	1354.4	342.3	40.9	11.2
72.5°	4018.6	3536.8	3064.2	2520.9	2020.5	1665.1	1294.9	954.4	240.0	33.5	9.3
75°	1339.5	1306.1	1168.4	885.6	744.2	604.7	483.7	372.1	91.2	20.5	9.3
77.5°	223.3	191.6	167.4	160.0	134.0	130.2	113.5	91.2	39.1	13.0	9.3
80°	130.2	119.1	104.2	93.0	81.9	72.6	61.4	52.1	24.2	9.3	11.2
82.5°	96.7	85.6	76.3	67.0	57.7	50.2	42.8	35.3	13.0	9.3	11.2
85°	55.8	48.4	42.8	37.2	29.8	26.0	22.3	18.6	9.3	9.3	9.3
87.5°	11.2	11.2	9.3	9.3	9.3	9.3	9.3	7.4	9.3	9.3	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181195

CATALOG NUMBER: ICM-E06-LED-E1-T2-HSS

**CANDELA DISTRIBUTION (continued):**

	125°	135°	145°	155°	165°	175°	180°
0°	199.1	199.1	199.1	199.1	199.1	199.1	199.1
2.5°	178.6	173.0	171.2	171.2	171.2	171.2	171.2
5°	163.7	158.1	154.4	152.6	152.6	152.6	152.6
7.5°	152.6	145.1	141.4	137.7	137.7	135.8	135.8
10°	141.4	134.0	128.4	124.7	122.8	122.8	122.8
12.5°	132.1	124.7	117.2	113.5	113.5	111.6	111.6
15°	124.7	113.5	107.9	104.2	104.2	102.3	102.3
17.5°	115.3	106.0	100.5	96.7	94.9	94.9	94.9
20°	106.0	96.7	91.2	89.3	87.4	87.4	85.6
22.5°	98.6	89.3	83.7	81.9	80.0	80.0	78.1
25°	91.2	81.9	76.3	74.4	72.6	70.7	70.7
27.5°	85.6	76.3	70.7	67.0	65.1	63.3	63.3
30°	80.0	68.8	63.3	59.5	57.7	55.8	55.8
32.5°	74.4	63.3	55.8	52.1	50.2	48.4	48.4
35°	67.0	55.8	48.4	46.5	44.7	42.8	40.9
37.5°	61.4	48.4	42.8	39.1	37.2	35.3	35.3
40°	54.0	42.8	37.2	33.5	29.8	27.9	27.9
42.5°	48.4	37.2	31.6	26.0	24.2	22.3	22.3
45°	42.8	33.5	26.0	20.5	18.6	16.7	16.7
47.5°	37.2	27.9	20.5	16.7	14.9	13.0	13.0
50°	31.6	22.3	14.9	11.2	13.0	11.2	11.2
52.5°	27.9	16.7	11.2	11.2	11.2	11.2	11.2
55°	22.3	13.0	9.3	9.3	11.2	11.2	11.2
57.5°	18.6	9.3	7.4	9.3	9.3	9.3	9.3
60°	13.0	7.4	7.4	9.3	9.3	9.3	9.3
62.5°	11.2	7.4	7.4	7.4	9.3	9.3	9.3
64°	9.3	7.4	7.4	7.4	9.3	9.3	9.3
65°	9.3	7.4	7.4	7.4	9.3	9.3	9.3
67.5°	9.3	7.4	7.4	7.4	9.3	9.3	9.3
70°	7.4	7.4	7.4	7.4	9.3	9.3	9.3
72.5°	7.4	7.4	7.4	7.4	9.3	9.3	9.3
75°	7.4	7.4	7.4	7.4	9.3	9.3	9.3
77.5°	7.4	7.4	7.4	9.3	9.3	9.3	9.3
80°	7.4	7.4	7.4	9.3	9.3	9.3	9.3
82.5°	7.4	7.4	7.4	9.3	9.3	9.3	9.3
85°	7.4	7.4	7.4	9.3	9.3	9.3	9.3
87.5°	7.4	7.4	7.4	9.3	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)