

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P181369

Luminaire Tested: **ICM-E06-LED-E1-T3-HSS**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P181369
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33724)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: ICM-E06-LED-E1-T3-HSS
Description: ICON SITE MEDIUM LED LUMINAIRE
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ HOUSE SIDE SHIELD
Light Source: (126) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9099.5 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 1' x H: 0.1')
IES Classification: Type III - Short - Non-Cutoff
BUG Rating: B0 - U0 - G2

Input Watts (W): 150.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P181369

CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 13.2 fc
 Type III - Short - Non-Cutoff

REPORT NUMBER: P181369

CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P181369

CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	182.7	0.0	182.7
	% Fixture	2.0	0.0	2.0
Street Side	Lumens	8916.8	0.0	8916.8
	% Fixture	98.0	0.0	98.0
Total	Lumens	9099.5	0.0	9099.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.0	0.3
10°-20°	148.0	1.6
20°-30°	338.0	3.7
30°-40°	643.0	7.1
40°-50°	1290.6	14.2
50°-60°	2283.7	25.1
60°-70°	2983.8	32.8
70°-80°	1226.8	13.5
80°-90°	154.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9099.5	100.0
0°-180°	9099.5	100.0



REPORT NUMBER: P181369


CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	459.8	5.1			
FM	(30°-60°)	4139.1	45.5			
FH	(60°-80°)	4170.2	45.8			G2/5000
FVH	(80°-90°)	147.6	1.6			G2/225
BL	(0°-30°)	57.1	0.6	B0/110		
BM	(30°-60°)	78.2	0.9	B0/220		
BH	(60°-80°)	40.4	0.4	B0/110		G0/110
BVH	(80°-90°)	6.9	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short





REPORT NUMBER: P181369

CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	56°	57°	58°	59°
0°	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0
2.5°	334.9	329.3	331.2	320.0	312.6	303.3	295.8	294.0	292.1	288.4	290.2
5°	481.9	476.3	463.3	440.9	420.5	388.8	357.2	355.4	349.8	344.2	340.5
7.5°	669.8	660.5	645.6	608.4	558.1	502.3	439.1	433.5	426.0	418.6	411.2
10°	887.4	881.9	854.0	811.2	734.9	643.7	537.7	532.1	515.4	506.0	498.6
12.5°	1116.3	1092.1	1080.9	1006.5	919.1	794.4	658.6	638.1	625.1	612.1	593.5
15°	1289.3	1293.0	1267.0	1207.4	1105.1	960.0	790.7	768.4	749.8	725.6	703.3
17.5°	1445.6	1438.1	1410.2	1373.0	1276.3	1129.3	932.1	902.3	872.6	859.5	827.9
20°	1572.1	1568.4	1546.1	1510.7	1436.3	1294.9	1080.9	1056.8	1023.3	1000.9	965.6
22.5°	1672.6	1672.6	1659.5	1639.1	1566.5	1453.0	1239.1	1213.0	1179.5	1151.6	1112.6
25°	1752.6	1750.7	1752.6	1743.3	1694.9	1590.7	1400.9	1371.2	1343.3	1309.8	1272.6
27.5°	1843.7	1847.5	1843.7	1838.2	1817.7	1734.0	1564.7	1544.2	1512.6	1477.2	1440.0
30°	1985.1	1974.0	1972.1	1968.4	1944.2	1892.1	1734.0	1709.8	1685.6	1661.4	1635.4
32.5°	2134.0	2115.4	2109.8	2109.8	2093.0	2046.5	1929.3	1916.3	1880.9	1862.3	1840.0
35°	2303.3	2295.8	2288.4	2290.2	2282.8	2234.4	2137.7	2141.4	2130.2	2093.0	2070.7
37.5°	2550.7	2552.6	2539.6	2515.4	2515.4	2472.6	2416.8	2409.3	2381.4	2372.1	2359.1
40°	2904.2	2894.9	2883.7	2848.4	2835.4	2762.8	2710.7	2692.1	2669.8	2667.9	2653.0
42.5°	3313.5	3302.3	3302.3	3276.3	3250.3	3162.8	3064.2	3051.2	3027.0	3034.4	3028.9
45°	3693.0	3702.3	3715.4	3734.0	3737.7	3700.5	3557.2	3540.5	3527.5	3520.0	3514.4
47.5°	4020.5	4037.2	4080.0	4160.0	4262.4	4275.4	4161.9	4117.2	4107.9	4094.9	4083.7
50°	4254.9	4279.1	4375.8	4532.1	4731.2	4854.0	4792.6	4755.4	4753.5	4718.2	4714.4
52.5°	4388.9	4414.9	4573.1	4809.3	5118.2	5358.2	5434.5	5432.6	5428.9	5397.2	5384.2
55°	4418.6	4446.5	4636.3	4958.2	5399.1	5814.0	6106.1	6113.5	6130.3	6121.0	6121.0
57.5°	4336.8	4372.1	4578.6	4976.8	5546.1	6174.9	6813.1	6855.9	6876.3	6948.9	7032.6
60°	4186.1	4212.1	4418.6	4863.3	5572.1	6504.2	7732.1	7868.0	7974.0	8117.3	8253.1
62.5°	3907.0	3959.1	4156.3	4640.0	5494.0	6883.8	8829.8	9081.0	9287.5	9505.2	9767.5
65°	3568.4	3590.7	3758.2	4180.5	5144.2	7028.9	9436.3	9681.9	9946.1	10178.7	10413.1
67.5°	3144.2	3162.8	3307.9	3488.4	4245.6	6349.8	8839.1	9110.8	9348.9	9540.5	9847.5
70°	2059.5	2100.5	2455.8	2634.4	2967.5	4694.0	7228.0	7490.3	7672.6	7802.8	8158.2
72.5°	1508.8	1534.9	1678.1	2046.5	2128.4	2774.0	5086.5	5371.2	5438.2	5683.8	5849.3
75°	920.9	986.1	1309.8	1752.6	2074.4	1899.5	3047.5	3185.1	3339.6	3518.2	3676.3
77.5°	186.0	212.1	427.9	1207.4	1825.1	2029.8	1819.5	1845.6	1921.9	1938.6	1998.2
80°	29.8	31.6	55.8	520.9	1056.8	1640.9	1819.5	1795.4	1752.6	1722.8	1693.0
82.5°	13.0	14.9	24.2	132.1	225.1	547.0	1574.0	1696.8	1838.2	1916.3	1936.8
85°	5.6	5.6	9.3	26.0	33.5	37.2	266.0	351.6	627.0	833.5	960.0
87.5°	3.7	3.7	5.6	5.6	7.4	9.3	13.0	13.0	14.9	16.7	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181369

CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS

CANDELA DISTRIBUTION (continued):

	60°	61°	62°	64°	65°	66°	67°	68°	69°	70°	71°
0°	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0
2.5°	290.2	288.4	288.4	282.8	282.8	280.9	280.9	279.1	279.1	275.4	277.2
5°	338.6	334.9	331.2	325.6	323.7	320.0	316.3	310.7	308.8	305.1	303.3
7.5°	403.7	400.0	392.6	381.4	374.0	366.5	359.1	351.6	346.0	340.5	336.7
10°	483.7	472.6	468.8	446.5	437.2	422.3	413.0	405.6	394.4	385.1	379.5
12.5°	580.5	571.2	552.6	522.8	507.9	494.9	478.1	463.3	452.1	435.4	424.2
15°	680.9	673.5	647.4	614.0	595.4	571.2	554.4	539.5	515.4	504.2	483.7
17.5°	807.4	785.1	759.1	710.7	686.5	666.1	636.3	614.0	599.1	565.6	547.0
20°	937.7	913.5	880.0	826.1	792.6	760.9	736.7	707.0	675.4	653.0	621.4
22.5°	1086.5	1047.4	1021.4	954.4	915.4	881.9	840.9	809.3	777.7	742.3	707.0
25°	1244.7	1205.6	1174.0	1097.7	1056.8	1023.3	974.9	930.2	891.2	852.1	811.2
27.5°	1410.2	1374.9	1339.5	1261.4	1226.1	1179.5	1134.9	1082.8	1032.6	997.2	941.4
30°	1601.9	1572.1	1533.0	1449.3	1410.2	1361.9	1315.4	1254.0	1205.6	1157.2	1103.3
32.5°	1808.4	1784.2	1743.3	1668.8	1622.3	1581.4	1531.2	1471.6	1402.8	1352.6	1289.3
35°	2059.5	2018.6	1994.4	1923.7	1888.4	1843.7	1791.6	1739.5	1667.0	1596.3	1542.3
37.5°	2346.1	2327.5	2295.8	2228.9	2202.8	2156.3	2122.8	2070.7	2014.9	1925.6	1867.9
40°	2640.0	2627.0	2599.1	2532.1	2506.1	2474.4	2435.4	2385.1	2318.2	2271.6	2186.1
42.5°	3014.0	2993.5	2971.2	2907.9	2857.7	2818.6	2801.9	2759.1	2688.4	2628.9	2561.9
45°	3488.4	3479.1	3449.3	3386.1	3335.8	3309.8	3283.7	3211.2	3164.7	3105.1	3058.6
47.5°	4061.4	4031.7	4016.8	3946.1	3929.3	3908.9	3841.9	3801.0	3734.0	3687.5	3629.8
50°	4681.0	4649.3	4651.2	4565.6	4569.3	4554.4	4504.2	4455.8	4398.2	4357.2	4321.9
52.5°	5347.0	5361.9	5324.7	5350.7	5321.0	5287.5	5278.2	5218.6	5168.4	5166.5	5118.2
55°	6165.6	6141.4	6150.7	6176.8	6135.9	6173.1	6154.5	6078.2	6080.0	6094.9	6039.1
57.5°	7045.6	7081.0	7157.3	7174.0	7244.7	7196.3	7322.8	7231.7	7287.5	7287.5	7250.3
60°	8336.8	8478.2	8662.4	8805.6	8937.7	8894.9	9060.5	8956.3	9030.8	8967.5	8935.9
62.5°	9892.2	10080.1	10297.7	10530.3	10664.3	10697.7	10673.6	10720.1	10647.5	10601.0	10480.1
65°	10640.1	10826.1	11015.9	11295.0	11332.2	11360.1	11348.9	11270.8	11181.5	11049.4	10891.2
67.5°	10018.7	10279.1	10385.2	10707.0	10814.9	10775.9	10788.9	10688.4	10548.9	10418.7	10186.1
70°	8307.0	8604.7	8660.5	9121.9	9250.3	9436.3	9369.4	9339.6	9187.0	9077.3	8820.5
72.5°	6048.4	6281.0	6262.4	6781.4	6759.1	6835.4	7015.9	7008.4	6848.4	6813.1	6597.2
75°	3722.8	3862.3	3854.9	4223.3	4068.9	4046.5	4096.8	4074.4	3923.7	3767.5	3633.5
77.5°	1972.1	2035.4	1968.4	1858.6	1847.5	1722.8	1687.5	1685.6	1570.2	1428.8	1324.7
80°	1661.4	1596.3	1518.1	1358.1	1265.1	1181.4	1103.3	1030.7	952.6	848.4	721.9
82.5°	1940.5	1908.8	1853.0	1652.1	1555.4	1387.9	1263.3	1146.1	1002.8	894.9	733.0
85°	945.1	943.3	987.9	967.4	932.1	924.7	801.9	775.8	718.1	658.6	550.7
87.5°	26.0	18.6	22.3	18.6	22.3	24.2	16.7	39.1	24.2	22.3	26.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181369

CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS

CANDELA DISTRIBUTION (continued):

	72°	73°	74°	75°	76°	77°	78°	79°	80°	81°	82°
0°	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0
2.5°	275.4	273.5	271.6	271.6	269.8	269.8	267.9	266.0	266.0	264.2	264.2
5°	299.5	295.8	294.0	292.1	288.4	286.5	282.8	280.9	277.2	275.4	271.6
7.5°	329.3	325.6	318.1	314.4	308.8	307.0	297.7	294.0	290.2	286.5	280.9
10°	366.5	357.2	349.8	342.3	333.0	325.6	318.1	312.6	305.1	295.8	292.1
12.5°	413.0	400.0	388.8	375.8	364.7	353.5	340.5	331.2	320.0	310.7	301.4
15°	465.1	446.5	431.6	413.0	394.4	381.4	368.4	355.4	340.5	327.4	316.3
17.5°	524.7	500.5	480.0	457.7	437.2	418.6	396.3	379.5	362.8	344.2	329.3
20°	587.9	563.7	535.8	511.6	481.9	461.4	433.5	411.2	387.0	368.4	347.9
22.5°	671.6	640.0	604.7	571.2	539.5	507.9	478.1	450.2	420.5	392.6	372.1
25°	770.2	731.2	686.5	653.0	608.4	573.0	535.8	500.5	468.8	433.5	400.0
27.5°	893.0	840.9	792.6	746.1	697.7	653.0	604.7	563.7	520.9	480.0	442.8
30°	1036.3	986.1	913.5	861.4	813.0	751.6	703.3	649.3	600.9	541.4	500.5
32.5°	1226.1	1160.9	1084.7	1015.8	952.6	883.7	816.7	747.9	684.7	630.7	569.3
35°	1473.5	1397.2	1306.1	1218.6	1147.9	1064.2	978.6	900.5	827.9	749.8	673.5
37.5°	1786.1	1715.4	1616.8	1510.7	1415.8	1315.4	1226.1	1116.3	1019.5	924.7	827.9
40°	2096.8	2031.6	1929.3	1815.8	1693.0	1577.7	1464.2	1339.5	1216.8	1097.7	997.2
42.5°	2480.0	2383.3	2273.5	2145.1	2026.1	1888.4	1747.0	1603.7	1456.8	1313.5	1170.2
45°	2961.9	2887.5	2733.0	2595.4	2454.0	2292.1	2117.2	1953.5	1765.6	1596.3	1406.5
47.5°	3547.9	3414.0	3300.5	3174.0	2997.2	2840.9	2617.7	2424.2	2189.8	1964.7	1737.7
50°	4240.0	4165.6	4014.9	3856.8	3665.1	3479.1	3261.4	2982.3	2701.4	2461.4	2150.7
52.5°	5049.3	4943.3	4848.4	4684.7	4489.3	4251.2	4003.7	3700.5	3356.3	3017.7	2686.5
55°	6009.3	5934.9	5843.8	5713.5	5464.2	5194.5	4896.8	4534.0	4126.5	3670.7	3285.6
57.5°	7248.4	7170.3	7082.8	6814.9	6645.6	6314.5	5882.8	5507.0	5067.9	4483.7	4005.6
60°	8939.6	8833.5	8710.8	8493.1	8139.6	7709.8	7246.6	6690.3	6152.6	5514.5	4887.5
62.5°	10385.2	10215.9	9953.5	9672.6	9248.4	8755.4	8173.1	7518.2	6906.1	6187.9	5490.3
65°	10682.9	10450.3	10141.5	9774.9	9337.7	8781.4	8173.1	7546.1	6826.1	6150.7	5449.3
67.5°	9908.9	9639.1	9322.8	8913.5	8496.8	7923.8	7399.1	6761.0	6083.8	5499.6	4872.6
70°	8636.3	8236.3	7912.6	7477.3	7054.9	6604.7	6052.1	5574.0	5023.3	4485.6	4005.6
72.5°	6485.6	6091.2	5797.2	5449.3	5198.2	4721.9	4316.3	3959.1	3633.5	3231.6	2876.3
75°	3495.8	3200.0	3002.8	2844.7	2619.6	2305.1	2111.6	1866.1	1728.4	1560.9	1399.1
77.5°	1140.5	1004.7	857.7	714.4	614.0	461.4	446.5	355.4	334.9	325.6	251.2
80°	584.2	450.2	325.6	234.4	178.6	158.1	150.7	143.3	135.8	130.2	120.9
82.5°	586.1	424.2	292.1	202.8	147.0	122.8	115.3	111.6	106.0	100.5	93.0
85°	427.9	316.3	217.7	148.8	102.3	81.9	78.1	72.6	68.8	67.0	59.5
87.5°	27.9	20.5	18.6	16.7	16.7	16.7	18.6	16.7	18.6	18.6	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181369

CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS

CANDELA DISTRIBUTION (continued):

	83°	84°	85°	86°	87°	88°	89°	90°	95°	105°	115°
0°	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0	253.0
2.5°	262.3	260.5	260.5	258.6	256.7	256.7	254.9	254.9	249.3	240.0	232.6
5°	269.8	266.0	264.2	262.3	260.5	256.7	254.9	253.0	243.7	225.1	210.2
7.5°	275.4	271.6	269.8	266.0	260.5	258.6	254.9	251.2	236.3	210.2	193.5
10°	284.7	279.1	273.5	267.9	262.3	258.6	253.0	249.3	227.0	197.2	180.5
12.5°	294.0	286.5	279.1	269.8	264.2	258.6	253.0	245.6	219.5	186.0	167.4
15°	305.1	294.0	284.7	275.4	266.0	258.6	249.3	243.7	212.1	176.7	160.0
17.5°	316.3	303.3	290.2	277.2	267.9	256.7	249.3	240.0	204.7	169.3	150.7
20°	329.3	310.7	297.7	282.8	269.8	256.7	245.6	236.3	197.2	160.0	141.4
22.5°	347.9	325.6	305.1	288.4	271.6	258.6	245.6	232.6	189.8	152.6	134.0
25°	372.1	344.2	320.0	299.5	279.1	262.3	247.4	234.4	184.2	147.0	124.7
27.5°	407.4	372.1	346.0	318.1	292.1	271.6	253.0	238.1	180.5	141.4	119.1
30°	450.2	414.9	374.0	340.5	312.6	284.7	264.2	241.9	176.7	135.8	111.6
32.5°	513.5	463.3	414.9	374.0	334.9	303.3	273.5	251.2	174.9	126.5	104.2
35°	604.7	535.8	478.1	424.2	370.2	331.2	295.8	266.0	173.0	119.1	96.7
37.5°	734.9	653.0	578.6	502.3	435.4	379.5	331.2	292.1	173.0	113.5	89.3
40°	874.4	768.4	673.5	578.6	493.0	422.3	357.2	308.8	169.3	106.0	81.9
42.5°	1032.6	902.3	772.1	654.9	548.8	457.7	381.4	321.9	160.0	98.6	74.4
45°	1244.7	1073.5	917.2	766.5	628.8	509.8	413.0	336.7	150.7	93.0	67.0
47.5°	1510.7	1311.6	1108.8	919.1	738.6	587.9	459.5	360.9	145.1	85.6	61.4
50°	1907.0	1624.2	1356.3	1114.4	885.6	688.4	528.4	396.3	139.5	80.0	55.8
52.5°	2342.3	1994.4	1680.0	1369.3	1084.7	824.2	608.4	442.8	134.0	74.4	50.2
55°	2872.6	2444.7	2061.4	1657.7	1293.0	982.3	707.0	494.9	126.5	68.8	46.5
57.5°	3527.5	2986.1	2532.1	2039.1	1581.4	1187.0	839.1	582.3	119.1	61.4	40.9
60°	4258.6	3646.5	3075.4	2496.8	1942.3	1458.6	1034.4	707.0	111.6	54.0	35.3
62.5°	4785.1	4113.5	3460.5	2811.2	2202.8	1661.4	1192.6	803.7	100.5	46.5	31.6
65°	4779.6	4098.6	3441.9	2801.9	2210.2	1668.8	1198.1	822.3	89.3	40.9	27.9
67.5°	4258.6	3685.6	3099.6	2524.7	2007.5	1518.1	1108.8	762.8	76.3	37.2	24.2
70°	3503.3	3047.5	2584.2	2128.4	1713.5	1300.5	958.1	664.2	65.1	33.5	20.5
72.5°	2558.2	2225.1	1942.3	1620.5	1337.7	1027.0	764.7	520.9	52.1	27.9	18.6
75°	1270.7	1136.8	974.9	874.4	746.1	610.2	474.4	303.3	42.8	22.3	16.7
77.5°	241.9	215.8	206.5	178.6	163.7	145.1	128.4	91.2	33.5	16.7	14.9
80°	111.6	102.3	93.0	83.7	74.4	63.3	55.8	48.4	26.0	13.0	16.7
82.5°	87.4	80.0	70.7	63.3	55.8	48.4	40.9	35.3	16.7	11.2	16.7
85°	57.7	50.2	44.7	39.1	33.5	29.8	26.0	22.3	11.2	11.2	11.2
87.5°	16.7	16.7	14.9	14.9	13.0	13.0	11.2	11.2	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P181369

CATALOG NUMBER: ICM-E06-LED-E1-T3-HSS

CANDELA DISTRIBUTION (continued):

	125°	135°	145°	155°	165°	175°	180°
0°	253.0	253.0	253.0	253.0	253.0	253.0	253.0
2.5°	225.1	215.8	212.1	210.2	210.2	212.1	210.2
5°	199.1	189.8	186.0	182.3	182.3	182.3	184.2
7.5°	182.3	173.0	167.4	165.6	163.7	165.6	165.6
10°	167.4	160.0	152.6	148.8	148.8	148.8	148.8
12.5°	156.3	147.0	139.5	137.7	135.8	135.8	135.8
15°	147.0	135.8	130.2	126.5	124.7	124.7	126.5
17.5°	135.8	126.5	119.1	117.2	117.2	117.2	117.2
20°	128.4	117.2	111.6	107.9	107.9	107.9	107.9
22.5°	119.1	109.8	102.3	98.6	98.6	98.6	98.6
25°	111.6	102.3	94.9	91.2	91.2	91.2	91.2
27.5°	104.2	94.9	87.4	83.7	83.7	83.7	83.7
30°	96.7	87.4	80.0	76.3	76.3	76.3	76.3
32.5°	91.2	80.0	72.6	68.8	68.8	70.7	68.8
35°	81.9	72.6	65.1	61.4	61.4	61.4	61.4
37.5°	74.4	65.1	57.7	54.0	54.0	54.0	52.1
40°	68.8	57.7	50.2	46.5	44.7	44.7	44.7
42.5°	59.5	48.4	42.8	39.1	37.2	37.2	37.2
45°	54.0	42.8	35.3	31.6	31.6	31.6	31.6
47.5°	48.4	37.2	29.8	26.0	26.0	27.9	27.9
50°	42.8	31.6	24.2	24.2	24.2	26.0	26.0
52.5°	37.2	27.9	22.3	22.3	24.2	26.0	26.0
55°	33.5	24.2	20.5	22.3	24.2	26.0	26.0
57.5°	29.8	20.5	20.5	22.3	24.2	26.0	26.0
60°	26.0	18.6	18.6	20.5	24.2	26.0	26.0
62.5°	22.3	18.6	18.6	20.5	24.2	26.0	26.0
65°	20.5	18.6	18.6	20.5	24.2	26.0	26.0
67.5°	18.6	16.7	18.6	20.5	22.3	24.2	24.2
70°	16.7	16.7	18.6	20.5	22.3	24.2	24.2
72.5°	16.7	16.7	16.7	18.6	20.5	22.3	22.3
75°	16.7	16.7	16.7	18.6	20.5	22.3	22.3
77.5°	16.7	14.9	14.9	16.7	20.5	22.3	22.3
80°	16.7	14.9	14.9	16.7	18.6	22.3	22.3
82.5°	13.0	13.0	14.9	16.7	18.6	20.5	20.5
85°	11.2	13.0	13.0	14.9	16.7	20.5	20.5
87.5°	9.3	9.3	11.2	13.0	14.9	16.7	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)