

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P180412

Luminaire Tested: **ICM-F06-LED-E1-SL2-HSS-7030**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P180412  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33726)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: ICM-F06-LED-E1-SL2-HSS-7030  
Description: ICON SITE MEDIUM LED LUMINAIRE  
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 2 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD  
Light Source: (42) 3000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7716.4 lumens  
Efficiency: N/A  
Efficacy: 49.3 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 1' x H: 0.1')  
IES Classification: Type II - Short - Non-Cutoff  
BUG Rating: B0 - U0 - G2  
  
Input Watts (W): 156.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P180412  
 CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 16.2 fc  
 Type II - Short - Non-Cutoff

REPORT NUMBER: P180412  
CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

### Luminous Intensity Polar Plot



— Vertical Plane Through 71-Deg Lateral    - - - Horizontal Cone Through 63-Deg Vertical

REPORT NUMBER: P180412

CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	163.8	0.0	163.8
	% Fixture	2.1	0.0	2.1
<b>Street Side</b>	Lumens	7552.5	0.0	7552.5
	% Fixture	97.9	0.0	97.9
<b>Total</b>	Lumens	7716.4	0.0	7716.4
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.7	0.4
10°-20°	126.9	1.6
20°-30°	257.7	3.3
30°-40°	629.6	8.2
40°-50°	1408.1	18.2
50°-60°	1979.9	25.7
60°-70°	2328.3	30.2
70°-80°	840.7	10.9
80°-90°	112.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7716.4	100.0
0°-180°	7716.4	100.0



REPORT NUMBER: P180412


CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	364.6	4.7			
FM	(30°-60°)	3951.7	51.2			
FH	(60°-80°)	3124.1	40.5			G2/5000
FVH	(80°-90°)	112.2	1.5			G2/225
BL	(0°-30°)	52.7	0.7	B0/110		
BM	(30°-60°)	66.0	0.9	B0/220		
BH	(60°-80°)	44.9	0.6	B0/110		G0/110
BVH	(80°-90°)	0.2	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G2**

Type II Short





REPORT NUMBER: P180412

CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	56°	57°	58°	59°
0°	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0
2.5°	387.2	391.4	388.6	381.6	373.1	362.0	352.1	352.1	350.7	346.5	347.9
5°	507.8	509.2	503.6	486.8	471.4	447.4	420.8	418.0	415.3	411.0	409.6
7.5°	625.7	631.3	625.7	607.4	576.6	540.1	498.0	493.8	485.4	485.4	479.7
10°	746.2	746.2	740.7	719.6	691.5	639.6	586.3	579.4	569.5	566.7	558.3
12.5°	831.8	831.8	829.0	817.9	795.4	749.1	684.6	677.6	664.9	660.7	650.9
15°	865.5	865.5	866.9	876.7	878.1	857.1	789.8	784.2	771.5	760.3	756.1
17.5°	886.5	885.1	885.1	899.2	924.5	938.4	895.0	889.4	875.4	869.8	855.7
20°	932.8	930.1	921.6	921.6	945.5	994.6	994.6	993.2	977.8	973.5	966.5
22.5°	1001.6	998.8	973.5	952.5	963.7	1025.4	1083.0	1080.1	1074.5	1068.9	1064.8
25°	1113.8	1104.0	1060.5	998.8	988.9	1054.9	1150.2	1157.3	1161.5	1161.5	1164.3
27.5°	1283.5	1270.9	1193.8	1078.7	1035.3	1102.6	1224.7	1238.7	1251.3	1254.1	1266.7
30°	1519.2	1496.8	1386.0	1217.6	1118.1	1172.8	1334.1	1349.5	1367.7	1373.3	1392.9
32.5°	1906.4	1893.8	1787.2	1534.6	1321.4	1310.2	1487.0	1506.6	1530.4	1540.3	1564.1
35°	2495.6	2498.3	2411.4	2184.1	1889.6	1735.3	1760.5	1777.3	1785.8	1815.2	1827.8
37.5°	2895.4	2902.3	2922.0	2832.2	2621.8	2464.7	2266.9	2285.1	2241.7	2245.9	2247.3
40°	3114.2	3136.7	3251.6	3338.6	3321.8	3230.6	3072.1	3081.9	3000.6	2982.3	2894.0
42.5°	3260.1	3289.5	3473.3	3742.6	3880.1	3962.9	3926.4	3922.2	3859.1	3835.2	3760.9
45°	3351.3	3377.9	3609.4	4006.4	4323.4	4564.7	4664.3	4675.5	4622.2	4598.4	4536.6
47.5°	3347.1	3377.9	3626.2	4104.6	4571.7	4957.4	5238.0	5252.0	5284.3	5263.3	5267.5
50°	3161.9	3191.4	3441.0	3937.6	4498.7	5137.0	5650.5	5695.3	5747.2	5782.3	5799.1
52.5°	2937.4	2958.4	3180.1	3651.5	4187.3	5062.6	5894.5	5971.7	6048.8	6114.7	6161.1
55°	2854.7	2878.5	3052.5	3443.8	3937.6	4751.3	6008.1	6121.8	6231.2	6339.2	6427.6
57.5°	2898.2	2920.6	3045.4	3345.6	3789.0	4423.0	6040.4	6217.2	6396.7	6572.0	6746.0
60°	3058.1	3081.9	3188.6	3436.9	3749.6	4233.6	5914.2	6207.3	6506.1	6811.9	7099.5
62.5°	2995.0	3004.8	3161.9	3596.8	4030.2	4072.3	5455.5	5865.1	6321.0	6792.3	7256.6
63°	2934.6	2945.9	3105.8	3553.2	4115.7	4048.5	5313.8	5745.8	6227.0	6734.7	7239.8
65°	2661.1	2662.5	2784.6	3138.1	4020.4	4090.5	4682.5	5094.9	5647.7	6256.4	6894.7
67.5°	1986.3	1976.6	2094.3	2363.7	3156.3	4091.9	4019.0	4250.4	4634.8	5174.9	5747.2
70°	704.2	688.7	879.5	1252.7	1966.7	3347.1	3453.7	3469.1	3575.7	3867.5	4226.6
72.5°	228.7	232.8	280.6	458.7	906.2	2252.9	3126.8	3079.1	3051.1	3049.7	3097.3
75°	91.2	92.6	112.2	203.4	406.8	1085.8	2738.2	2764.9	2774.7	2788.8	2804.2
77.5°	43.4	47.7	63.2	113.6	202.0	537.3	1959.7	2185.5	2314.6	2414.2	2474.5
80°	15.4	18.2	35.1	70.1	94.0	246.9	1032.5	1245.7	1435.1	1679.2	1889.6
82.5°	0.0	0.0	7.0	49.1	51.9	99.6	423.6	496.6	568.1	736.5	945.5
85°	0.0	0.0	0.0	14.0	15.4	16.8	143.1	172.6	193.6	225.9	260.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	1.4	4.2	8.4	21.0	32.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P180412

CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	60°	61°	62°	64°	65°	66°	67°	68°	69°	70°	71°
0°	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0
2.5°	345.1	343.7	343.7	340.8	339.4	336.7	335.3	331.1	329.7	329.7	329.7
5°	408.2	402.6	399.8	392.7	388.6	387.2	380.2	377.3	373.1	374.5	367.5
7.5°	478.3	468.6	464.3	454.5	451.7	441.9	439.1	432.1	427.8	419.4	416.7
10°	555.5	542.9	535.9	520.5	516.2	509.2	500.8	492.4	485.4	476.9	472.7
12.5°	643.9	632.7	627.1	606.1	596.2	586.3	575.2	563.9	552.7	545.7	535.9
15°	747.7	729.5	723.8	704.2	687.4	674.7	659.4	645.3	636.8	622.8	613.0
17.5°	850.1	831.8	827.6	798.1	779.9	771.5	754.7	736.5	721.0	707.0	691.5
20°	952.5	939.9	928.7	900.6	880.9	866.9	844.5	826.2	813.6	794.0	774.3
22.5°	1054.9	1042.2	1033.9	1004.4	986.1	966.5	946.9	927.3	909.0	885.1	862.7
25°	1160.1	1151.7	1147.4	1120.8	1104.0	1085.8	1066.1	1043.6	1021.2	994.6	970.7
27.5°	1269.5	1272.3	1263.9	1258.3	1240.1	1227.4	1196.6	1181.1	1164.3	1132.0	1102.6
30°	1408.4	1416.8	1414.1	1418.2	1407.0	1398.6	1374.7	1355.1	1335.5	1304.6	1270.9
32.5°	1583.7	1595.0	1600.6	1616.0	1610.4	1607.6	1600.6	1572.6	1558.5	1505.2	1491.2
35°	1854.5	1848.8	1872.8	1885.3	1879.7	1876.9	1868.5	1853.1	1836.3	1798.3	1763.3
37.5°	2206.6	2212.2	2220.6	2195.4	2178.5	2177.1	2151.9	2136.5	2112.6	2070.5	2028.4
40°	2851.8	2816.8	2777.5	2670.9	2624.6	2598.0	2523.6	2502.5	2461.9	2404.4	2360.9
42.5°	3690.7	3655.7	3537.8	3359.6	3264.3	3132.4	3072.1	2997.8	2940.2	2846.2	2795.7
45°	4524.0	4423.0	4409.0	4201.3	4083.5	3909.6	3801.5	3676.7	3546.3	3422.8	3333.0
47.5°	5226.8	5204.3	5135.6	5009.3	4899.9	4754.1	4615.2	4423.0	4288.3	4113.0	3951.7
50°	5789.3	5787.9	5762.6	5689.7	5598.5	5480.7	5358.6	5195.9	5043.0	4828.4	4655.8
52.5°	6210.2	6232.6	6241.0	6218.5	6183.5	6079.7	6018.0	5881.9	5752.9	5570.5	5383.9
55°	6518.7	6601.5	6643.6	6691.3	6681.4	6645.0	6642.2	6553.8	6494.9	6350.5	6218.5
57.5°	6900.3	7036.4	7166.8	7398.3	7406.7	7488.0	7530.2	7572.2	7583.5	7525.9	7482.5
60°	7385.7	7663.4	7910.3	8394.3	8520.5	8719.7	8848.8	8989.1	9108.3	9118.1	9115.3
62.5°	7728.0	8155.8	8554.2	9272.4	9517.9	9748.0	9920.5	10056.6	10139.3	10223.5	10262.8
63°	7737.8	8206.3	8629.9	9370.7	9628.7	9847.6	10011.7	10137.9	10224.9	10275.4	10300.6
65°	7500.7	8068.8	8573.8	9311.7	9554.4	9774.7	9860.2	9942.9	9985.1	10004.7	9930.3
67.5°	6357.4	6913.0	7502.1	8326.9	8534.6	8798.3	8868.4	8910.5	8930.1	8925.9	8862.8
70°	4754.1	5219.8	5874.8	6817.5	7092.5	7350.6	7510.6	7579.3	7601.7	7594.7	7500.7
72.5°	3319.0	3592.6	4132.6	5181.9	5556.4	5887.5	6085.2	6187.7	6208.8	6166.6	6079.7
75°	2787.4	2801.3	2923.4	3497.1	3847.8	4201.3	4424.4	4489.0	4446.8	4319.2	4097.5
77.5°	2488.6	2519.4	2519.4	2604.9	2673.7	2771.9	2792.9	2635.8	2453.5	2217.8	2027.0
80°	2087.4	2195.4	2271.1	2334.2	2341.2	2321.6	2269.7	2181.3	2041.0	1861.5	1662.3
82.5°	1268.1	1481.3	1568.3	1893.8	2053.7	2161.7	2153.3	2035.5	1928.8	1742.2	1572.6
85°	319.8	345.1	374.5	486.8	545.7	666.3	742.1	777.1	789.8	725.2	656.5
87.5°	30.9	21.0	35.1	26.7	37.9	28.1	37.9	35.1	43.4	46.3	50.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P180412

CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	72°	73°	74°	75°	76°	77°	78°	79°	80°	81°	82°
0°	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0
2.5°	326.9	325.5	324.0	322.6	321.2	319.8	317.0	317.0	314.2	312.8	311.4
5°	363.4	360.6	359.1	356.3	352.1	349.3	345.1	339.4	335.3	333.9	331.1
7.5°	409.6	402.6	399.8	395.6	390.0	381.6	375.9	371.7	364.7	360.6	352.1
10°	461.5	454.5	446.0	437.7	429.2	419.4	412.4	406.8	395.6	390.0	380.2
12.5°	527.4	514.8	505.0	493.8	482.5	471.4	462.9	446.0	436.3	423.6	415.3
15°	594.8	583.5	572.4	558.3	541.5	523.3	514.8	499.4	486.8	467.2	455.9
17.5°	676.1	655.1	638.2	621.4	606.1	589.2	572.4	548.5	530.2	513.4	491.0
20°	756.1	730.9	712.7	690.1	667.7	641.1	621.4	604.6	579.4	556.9	533.0
22.5°	841.7	816.4	787.0	764.6	733.7	712.7	686.0	657.9	632.7	603.2	573.8
25°	945.5	918.8	885.1	855.7	820.7	791.2	758.9	726.6	695.8	662.1	624.3
27.5°	1073.1	1045.1	1008.6	973.5	927.3	890.8	859.9	816.4	777.1	735.1	691.5
30°	1234.4	1203.6	1158.7	1108.2	1061.9	1021.2	977.8	920.2	876.7	826.2	770.1
32.5°	1444.8	1408.4	1348.1	1300.4	1242.9	1189.6	1129.2	1071.7	1010.1	944.1	879.5
35°	1710.0	1676.3	1606.1	1536.0	1472.9	1409.8	1334.1	1268.1	1181.1	1101.2	1018.4
37.5°	1984.9	1924.7	1860.1	1784.4	1705.8	1630.1	1537.5	1446.2	1346.7	1259.7	1155.9
40°	2299.2	2226.2	2172.9	2091.5	1980.8	1872.8	1787.2	1673.5	1548.7	1432.3	1310.2
42.5°	2729.8	2648.5	2553.0	2429.6	2349.7	2223.5	2112.6	1978.0	1813.8	1683.4	1536.0
45°	3227.8	3116.9	3024.4	2905.1	2808.4	2651.3	2522.2	2342.6	2178.5	2007.4	1827.8
47.5°	3795.9	3658.4	3523.8	3406.0	3251.6	3097.3	2933.2	2742.4	2532.0	2344.0	2130.8
50°	4448.2	4253.2	4066.7	3915.2	3703.4	3525.2	3347.1	3132.4	2899.6	2683.6	2440.9
52.5°	5173.5	4947.7	4700.8	4467.8	4222.4	3993.7	3779.1	3532.2	3272.7	3008.9	2738.2
55°	6048.8	5879.1	5588.7	5292.7	4964.5	4658.6	4382.4	4076.5	3760.9	3414.3	3129.6
57.5°	7419.3	7336.6	7093.9	6797.9	6370.1	5998.4	5529.8	5155.3	4697.9	4221.0	3853.4
60°	9276.6	9174.2	9038.2	8798.3	8458.8	7953.8	7437.5	6855.4	6159.7	5498.9	4871.8
62.5°	10267.0	10230.5	10119.7	9954.2	9637.2	9238.8	8718.3	8078.7	7293.1	6490.7	5691.1
63°	10296.4	10250.2	10154.8	9986.5	9707.3	9321.5	8810.9	8189.4	7420.8	6602.9	5786.5
65°	9898.1	9879.9	9783.0	9599.3	9408.5	9113.9	8718.3	8183.9	7538.6	6765.6	5953.4
67.5°	8778.7	8724.0	8575.2	8519.1	8385.8	8181.1	7879.5	7512.0	7050.4	6443.0	5741.6
70°	7425.0	7343.6	7157.0	7057.4	6894.7	6765.6	6581.9	6319.6	6034.8	5611.1	5087.9
72.5°	5989.9	5821.5	5650.5	5390.9	5163.7	4933.6	4730.2	4545.1	4232.2	4061.0	3664.1
75°	3889.9	3584.1	3290.9	2898.2	2544.7	2231.8	1927.5	1773.1	1451.9	1321.4	1134.9
77.5°	1846.1	1674.9	1444.8	1266.7	1039.4	848.7	692.9	520.5	408.2	319.8	244.1
80°	1489.8	1345.3	1206.4	1045.1	874.0	697.2	534.4	399.8	283.4	196.4	138.9
82.5°	1328.5	1171.4	1000.2	889.4	772.9	632.7	519.1	423.6	312.8	228.7	155.7
85°	516.2	434.9	335.3	273.6	213.2	175.3	158.5	109.4	85.6	67.3	51.9
87.5°	44.9	36.5	29.5	19.6	21.0	11.3	12.7	8.4	7.0	7.0	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P180412

CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	83°	84°	85°	86°	87°	88°	89°	90°	95°	105°	115°
0°	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0	296.0
2.5°	310.0	308.7	307.2	304.4	304.4	301.6	300.2	298.8	291.8	276.4	263.7
5°	325.5	322.6	319.8	315.6	312.8	308.7	305.8	301.6	286.1	256.7	231.4
7.5°	347.9	342.2	338.0	329.7	325.5	319.8	315.6	308.7	283.4	238.5	203.4
10°	374.5	364.7	357.7	347.9	339.4	332.5	325.5	315.6	280.6	218.8	178.1
12.5°	406.8	395.6	381.6	370.3	359.1	349.3	339.4	326.9	276.4	202.0	158.5
15°	439.1	422.2	412.4	397.0	381.6	367.5	353.5	342.2	277.8	183.7	141.7
17.5°	475.5	458.7	437.7	420.8	404.0	385.8	368.9	346.5	270.7	169.8	129.0
20°	510.6	486.8	467.2	446.0	422.2	399.8	378.8	359.1	265.1	155.7	117.9
22.5°	548.5	520.5	495.2	468.6	439.1	413.9	388.6	363.4	255.4	143.1	108.0
25°	594.8	562.5	526.0	493.8	462.9	432.1	399.8	368.9	245.5	131.9	101.0
27.5°	650.9	608.8	572.4	531.6	488.2	448.9	413.9	380.2	235.6	123.4	94.0
30°	722.4	673.3	621.4	569.5	523.3	478.3	429.2	387.2	225.9	115.1	87.0
32.5°	817.9	756.1	692.9	632.7	571.0	513.4	461.5	406.8	220.3	108.0	80.0
35°	944.1	864.1	787.0	711.2	636.8	566.7	499.4	437.7	220.3	99.6	71.5
37.5°	1063.4	970.7	872.6	778.5	690.1	608.8	528.8	454.5	209.0	92.6	64.6
40°	1192.4	1081.6	966.5	855.7	749.1	648.1	556.9	471.4	199.2	84.2	57.5
42.5°	1390.1	1249.9	1099.8	970.7	843.1	718.2	604.6	503.6	186.6	75.7	50.5
45°	1649.7	1471.5	1294.8	1137.7	975.0	822.1	687.4	562.5	183.7	68.7	43.4
47.5°	1927.5	1717.0	1509.4	1308.8	1118.1	939.9	778.5	628.5	183.7	61.8	37.9
50°	2203.7	1940.0	1718.4	1485.6	1270.9	1060.5	868.3	697.2	185.2	56.1	30.9
52.5°	2453.5	2171.5	1923.3	1653.9	1416.8	1172.8	963.7	764.6	182.3	49.1	25.2
55°	2799.9	2468.9	2181.3	1883.9	1606.1	1331.3	1094.1	865.5	183.7	43.4	21.0
57.5°	3438.3	3049.7	2703.2	2313.2	1993.3	1638.4	1350.9	1073.1	200.6	36.5	15.4
60°	4354.3	3849.2	3362.4	2886.9	2480.1	2057.9	1684.8	1357.9	235.6	29.5	11.3
62.5°	4970.1	4309.3	3728.6	3203.9	2731.3	2289.3	1882.5	1510.8	259.5	23.8	7.0
63°	5033.2	4350.1	3766.4	3225.0	2742.4	2300.6	1891.0	1522.1	260.9	22.4	7.0
65°	5152.4	4420.2	3787.6	3229.2	2731.3	2285.1	1885.3	1520.7	263.7	18.2	5.6
67.5°	5016.4	4312.2	3665.5	3108.6	2633.0	2194.0	1815.2	1464.5	262.3	12.7	4.2
70°	4486.1	3902.5	3334.4	2815.4	2383.4	1986.3	1652.5	1335.5	241.3	8.4	2.8
72.5°	3293.8	2896.8	2456.3	2081.8	1795.5	1491.2	1272.3	1003.0	186.6	5.6	1.4
75°	976.4	889.4	747.7	659.4	582.1	481.1	427.8	333.9	95.3	2.8	0.0
77.5°	195.0	176.7	158.5	144.5	136.1	116.5	110.8	91.2	39.3	1.4	0.0
80°	102.4	84.2	71.5	63.2	54.7	44.9	37.9	30.9	7.0	0.0	0.0
82.5°	98.2	66.0	47.7	39.3	33.7	26.7	21.0	15.4	4.2	0.0	0.0
85°	36.5	28.1	21.0	16.8	14.0	12.7	9.9	8.4	0.0	0.0	0.0
87.5°	5.6	4.2	4.2	2.8	2.8	1.4	1.4	1.4	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P180412

CATALOG NUMBER: ICM-F06-LED-E1-SL2-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	125°	135°	145°	155°	165°	175°	180°
0°	296.0	296.0	296.0	296.0	296.0	296.0	296.0
2.5°	251.1	239.9	234.2	227.3	227.3	225.9	228.7
5°	209.0	193.6	182.3	174.0	175.3	171.2	172.6
7.5°	176.7	161.3	151.5	145.9	144.5	143.1	143.1
10°	152.9	138.9	130.4	126.2	124.8	124.8	124.8
12.5°	136.1	122.0	115.1	112.2	112.2	110.8	110.8
15°	122.0	110.8	103.8	101.0	101.0	99.6	101.0
17.5°	110.8	99.6	94.0	91.2	91.2	89.8	89.8
20°	101.0	91.2	85.6	81.4	81.4	80.0	81.4
22.5°	92.6	82.8	75.7	72.9	71.5	70.1	71.5
25°	84.2	74.3	67.3	63.2	61.8	61.8	60.3
27.5°	77.1	67.3	58.9	54.7	53.3	53.3	51.9
30°	70.1	58.9	50.5	46.3	44.9	44.9	44.9
32.5°	63.2	50.5	43.4	39.3	37.9	37.9	37.9
35°	56.1	43.4	36.5	32.3	30.9	30.9	30.9
37.5°	47.7	36.5	28.1	25.2	23.8	22.4	22.4
40°	40.7	28.1	21.0	18.2	15.4	15.4	15.4
42.5°	33.7	22.4	15.4	11.3	9.9	8.4	9.9
45°	28.1	16.8	9.9	5.6	4.2	4.2	4.2
47.5°	22.4	11.3	4.2	1.4	1.4	1.4	1.4
50°	16.8	7.0	1.4	0.0	0.0	1.4	1.4
52.5°	12.7	4.2	0.0	0.0	0.0	0.0	0.0
55°	7.0	1.4	0.0	0.0	0.0	0.0	0.0
57.5°	4.2	0.0	0.0	0.0	0.0	0.0	0.0
60°	2.8	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	1.4	0.0	0.0	0.0	0.0	0.0	0.0
63°	1.4	0.0	0.0	0.0	0.0	0.0	0.0
65°	1.4	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)