

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P151595

Luminaire Tested: **VXS-F03-LED-E1-SL4-HSS**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P151595
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F03-LED-E1-SL4-HSS
Description: VISION SITE SMALL LED LUMINAIRE
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (21) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5039.4 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G2

Input Watts (W): 78.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P151595

CATALOG NUMBER: VXS-F03-LED-E1-SL4-HSS

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 11.3 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P151595

CATALOG NUMBER: VXS-F03-LED-E1-SL4-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P151595

CATALOG NUMBER: VXS-F03-LED-E1-SL4-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	150.1	0.0	150.1
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	4889.3	0.0	4889.3
	% Fixture	97.0	0.0	97.0
Total	Lumens	5039.4	0.0	5039.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.1	0.8
10°-20°	134.9	2.7
20°-30°	258.1	5.1
30°-40°	429.3	8.5
40°-50°	580.9	11.5
50°-60°	908.4	18.0
60°-70°	1867.7	37.1
70°-80°	751.5	14.9
80°-90°	69.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5039.4	100.0
0°-180°	5039.4	100.0



REPORT NUMBER: P151595


CATALOG NUMBER: VXS-F03-LED-E1-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	375.0	7.4			
FM	(30°-60°)	1850.0	36.7			
FH	(60°-80°)	2597.3	51.5			G2/5000
FVH	(80°-90°)	66.9	1.3			G1/100
BL	(0°-30°)	57.1	1.1	B0/110		
BM	(30°-60°)	68.5	1.4	B0/220		
BH	(60°-80°)	21.9	0.4	B0/110		G0/110
BVH	(80°-90°)	2.6	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type IV Short





REPORT NUMBER: P151595

CATALOG NUMBER: VXS-F03-LED-E1-SL4-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5
2.5°	507.7	502.0	495.3	495.3	487.0	487.0	482.1	468.9	467.3	459.8	452.4
5°	648.1	643.1	634.8	627.4	620.8	609.2	600.9	585.3	568.0	551.4	536.6
7.5°	785.1	782.6	767.8	765.3	754.5	735.5	719.1	696.0	666.2	643.1	615.9
10°	912.2	906.4	903.1	889.1	873.4	852.7	827.2	799.1	764.5	728.1	689.3
12.5°	1013.0	1009.6	994.7	989.0	972.4	951.8	919.6	883.3	848.6	801.6	756.2
15°	1088.1	1082.3	1072.3	1063.3	1043.4	1025.3	995.5	956.0	913.9	862.7	808.2
17.5°	1150.8	1140.0	1137.6	1123.5	1102.9	1081.5	1048.4	1012.1	962.6	911.4	851.9
20°	1235.0	1220.1	1215.1	1194.5	1170.6	1140.8	1102.9	1057.5	1005.5	949.3	888.3
22.5°	1334.1	1323.3	1312.5	1294.4	1263.8	1221.8	1166.4	1116.9	1050.9	989.0	922.9
25°	1474.4	1465.3	1448.0	1423.2	1385.2	1334.9	1268.0	1195.3	1117.7	1038.5	960.9
27.5°	1610.6	1602.4	1589.9	1571.0	1528.1	1472.7	1390.2	1297.7	1199.5	1103.7	1017.8
30°	1738.5	1731.1	1718.8	1699.8	1661.8	1607.3	1514.0	1414.9	1292.7	1181.3	1078.1
32.5°	1876.4	1874.0	1859.9	1832.6	1799.7	1726.2	1624.7	1518.1	1394.3	1265.5	1145.0
35°	2032.4	2013.5	2000.2	1973.0	1916.9	1838.4	1719.6	1603.2	1472.7	1340.6	1206.1
37.5°	2164.6	2146.3	2129.8	2095.2	2026.6	1926.7	1792.2	1664.2	1529.7	1395.1	1258.1
40°	2261.1	2252.0	2232.2	2186.8	2110.1	1991.2	1845.9	1706.3	1571.0	1435.5	1300.2
42.5°	2333.0	2318.9	2296.6	2249.5	2158.8	2023.3	1867.4	1723.7	1589.9	1460.3	1327.5
45°	2359.4	2347.8	2327.2	2276.0	2177.7	2032.4	1866.5	1718.8	1590.8	1467.8	1345.6
47.5°	2343.6	2332.1	2314.0	2266.1	2169.4	2021.8	1851.6	1704.7	1582.5	1470.3	1362.1
50°	2291.6	2285.1	2271.0	2230.6	2143.9	2001.0	1838.4	1697.3	1580.8	1482.7	1385.2
52.5°	2286.7	2282.6	2265.3	2224.8	2136.5	1994.5	1836.8	1701.5	1594.9	1498.3	1401.8
55°	2794.4	2735.8	2604.6	2493.1	2309.8	2091.9	1920.2	1768.3	1654.3	1560.2	1492.5
57.5°	3971.6	3884.1	3711.6	3499.4	3078.3	2664.8	2333.8	2094.4	1976.3	1933.4	1959.0
60°	4523.0	4507.4	4480.1	4379.4	4163.9	3808.2	3411.9	2983.4	2811.7	2796.9	2848.9
62.5°	4784.8	4774.8	4783.1	4770.7	4703.8	4599.8	4485.9	4301.0	4130.9	4021.1	3788.3
65°	4905.3	4911.9	4959.0	4996.1	5004.4	5031.6	5114.9	5345.3	5513.7	5230.6	4584.1
67.5°	4599.0	4637.8	4745.9	4881.3	5039.8	5193.4	5441.0	5926.4	6272.3	5939.7	5021.7
69°	3807.4	3826.3	4090.5	4345.6	4732.7	5003.5	5362.6	5999.1	6387.9	6012.3	4987.0
70°	2997.5	3014.8	3297.9	3644.7	4299.4	4647.7	5117.4	5876.1	6279.8	5915.8	4808.7
72.5°	1352.2	1327.5	1427.4	1613.1	2324.7	2877.8	3699.2	4760.8	5181.0	4739.4	3597.6
75°	944.4	933.7	944.4	945.2	1055.9	1362.1	1718.8	2580.6	3191.5	2754.0	1718.8
77.5°	731.4	723.9	716.6	708.3	721.6	808.2	842.9	915.5	1188.7	1124.4	655.4
80°	578.7	572.1	590.3	584.5	584.5	594.4	587.8	560.5	509.3	472.2	422.7
82.5°	269.1	270.8	270.8	293.9	354.2	413.6	432.5	405.3	359.9	306.3	246.8
85°	25.6	28.9	48.7	75.1	149.4	168.4	169.2	140.3	140.3	110.6	89.1
87.5°	0.0	0.8	0.8	0.8	7.5	20.6	17.3	5.0	2.5	2.5	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P151595

CATALOG NUMBER: VXS-F03-LED-E1-SL4-HSS

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5
2.5°	439.2	436.7	426.8	416.9	407.8	397.9	388.8	379.8	369.8	362.4	353.4
5°	513.5	495.3	474.7	454.8	435.0	414.4	393.0	374.0	354.2	336.0	318.7
7.5°	588.6	553.1	525.1	489.5	457.3	425.2	395.4	364.9	336.8	310.4	285.6
10°	652.1	609.2	565.5	520.1	473.9	430.9	389.6	353.4	316.2	283.9	253.5
12.5°	704.1	649.6	596.1	539.1	487.0	432.5	381.3	337.6	293.9	257.5	226.2
15°	751.2	688.5	624.1	558.0	492.0	430.1	373.2	318.7	274.1	232.8	197.3
17.5°	789.2	717.4	644.8	570.5	499.5	426.8	362.4	305.5	253.5	210.5	175.9
20°	822.2	747.2	668.7	585.3	504.4	426.0	353.4	288.9	235.2	189.8	156.1
22.5°	852.7	777.6	693.5	604.2	511.8	425.2	345.1	276.6	219.6	174.2	140.3
25°	887.5	808.2	719.9	624.1	525.1	428.5	340.1	266.6	205.6	159.3	128.0
27.5°	926.2	842.9	751.2	648.9	542.4	435.0	338.4	256.0	193.2	145.3	118.0
30°	980.7	884.1	782.6	673.7	558.0	442.5	336.8	249.3	180.8	134.6	108.2
32.5°	1028.6	924.6	817.3	699.2	575.4	449.9	336.0	240.2	169.2	123.8	100.7
35°	1079.0	961.8	846.9	723.9	590.3	458.1	335.1	233.6	158.5	113.1	93.3
37.5°	1122.7	993.1	870.1	745.5	606.7	465.6	336.0	227.9	148.6	104.0	86.6
40°	1159.9	1025.3	895.6	765.3	624.1	477.2	336.8	222.1	138.7	95.8	80.9
42.5°	1192.8	1055.9	922.9	787.6	643.9	490.4	341.8	217.1	130.5	88.3	75.1
45°	1218.4	1083.9	952.6	819.0	676.1	511.8	350.9	213.8	122.2	81.8	70.2
47.5°	1244.9	1125.2	1003.0	868.5	723.1	545.7	366.5	213.0	115.5	76.8	66.0
50°	1281.2	1166.4	1047.6	918.9	766.1	580.3	385.5	213.8	107.4	71.8	61.9
52.5°	1307.7	1208.6	1105.4	1006.3	868.5	686.0	459.0	228.7	103.2	67.7	57.0
55°	1463.6	1446.3	1448.8	1465.3	1358.9	1167.3	767.8	330.3	121.3	76.8	56.2
57.5°	2063.8	2124.9	2160.4	2159.6	1983.7	1645.3	1031.1	424.4	135.3	89.1	66.8
60°	2853.1	2806.7	2741.6	2580.6	2346.9	1878.0	1153.3	456.5	117.2	71.0	61.1
62.5°	3550.6	3279.8	3039.6	2778.8	2472.4	1959.0	1178.0	454.0	102.4	53.7	42.9
65°	3985.6	3498.5	3110.6	2783.6	2422.9	1891.3	1114.5	416.9	86.6	43.7	35.5
67.5°	4089.6	3380.5	2831.5	2414.6	2024.1	1471.9	818.1	313.7	67.7	36.4	31.4
69°	3862.6	3004.9	2346.1	1873.2	1472.7	976.6	506.0	198.1	52.0	33.1	28.9
70°	3553.1	2613.6	1911.1	1503.3	1090.6	686.0	354.2	139.5	42.1	30.6	26.4
72.5°	2285.9	1372.8	939.5	653.8	449.9	273.3	138.7	62.7	32.2	25.6	21.5
75°	886.6	507.7	368.2	279.9	218.8	151.9	84.2	40.4	27.3	21.5	16.5
77.5°	436.7	334.3	273.3	187.4	109.0	67.7	45.4	31.4	22.3	15.6	10.8
80°	345.1	229.5	137.0	85.1	64.4	48.7	34.7	25.6	16.5	9.9	7.5
82.5°	176.7	96.6	71.0	57.8	47.9	37.9	28.1	18.1	10.8	6.6	5.8
85°	55.3	40.4	36.4	35.5	33.1	27.3	19.8	11.6	6.6	4.1	4.1
87.5°	4.1	5.8	7.5	5.8	6.6	5.8	7.5	5.0	3.3	3.3	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P151595

CATALOG NUMBER: VXS-F03-LED-E1-SL4-HSS

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5	380.5
2.5°	346.7	336.8	327.8	322.0	311.2	307.0	303.0	301.3	293.9	295.5	288.9
5°	303.0	285.6	272.4	259.2	246.8	237.7	230.4	221.2	213.8	210.5	203.9
7.5°	263.3	241.0	223.7	209.6	194.8	183.3	173.4	166.7	160.1	153.6	150.3
10°	228.7	204.8	184.9	170.9	156.9	146.9	139.5	134.6	130.5	128.0	127.2
12.5°	196.5	173.4	155.2	142.8	132.1	127.2	123.8	121.3	120.5	119.7	119.7
15°	171.7	148.6	134.6	125.5	120.5	118.0	117.2	115.5	113.9	113.1	113.1
17.5°	148.6	131.3	121.3	116.4	113.9	112.2	110.6	109.0	107.4	106.5	106.5
20°	133.0	118.9	113.9	110.6	108.2	106.5	104.0	102.4	101.6	100.7	99.9
22.5°	120.5	111.4	108.2	105.7	102.4	99.9	98.2	96.6	94.9	94.1	93.3
25°	111.4	105.7	103.2	99.9	96.6	94.1	91.6	89.1	87.5	86.6	85.1
27.5°	104.9	100.7	97.4	93.3	89.9	87.5	85.1	82.6	80.9	79.3	78.4
30°	99.1	94.9	90.8	87.5	83.4	80.9	77.6	75.1	74.3	72.6	71.0
32.5°	93.3	89.1	85.1	80.9	76.8	73.5	71.8	68.5	66.8	66.0	64.4
35°	86.6	82.6	77.6	74.3	70.2	66.8	64.4	61.9	60.3	58.7	57.8
37.5°	80.9	76.0	71.0	66.8	63.5	60.3	57.8	55.3	53.7	52.0	51.2
40°	74.3	69.3	64.4	60.3	57.0	54.5	52.0	49.5	47.9	47.0	47.0
42.5°	68.5	62.7	57.8	54.5	52.0	48.7	46.2	43.7	42.9	42.1	42.9
45°	62.7	57.0	52.8	49.5	47.0	43.7	41.2	39.6	38.8	39.6	40.4
47.5°	57.8	52.0	47.9	45.4	42.9	40.4	37.9	36.4	36.4	37.9	39.6
50°	52.8	47.0	43.7	42.1	39.6	37.1	33.9	33.1	33.9	35.5	37.1
52.5°	47.9	41.2	38.8	37.9	35.5	33.1	30.6	29.7	30.6	32.2	31.4
55°	42.9	36.4	35.5	34.7	32.2	28.9	26.4	26.4	26.4	25.6	23.9
57.5°	41.2	32.2	31.4	30.6	28.1	24.8	23.1	21.5	20.6	18.1	17.3
60°	42.9	28.9	28.9	27.3	24.8	21.5	19.0	16.5	14.8	13.2	13.2
62.5°	34.7	26.4	25.6	23.9	20.6	17.3	14.8	12.3	11.6	10.8	10.8
65°	28.1	23.9	22.3	19.8	17.3	14.0	11.6	9.9	9.1	9.1	9.9
67.5°	25.6	21.5	19.0	16.5	14.0	10.8	9.1	8.3	8.3	9.1	9.1
69°	23.9	19.8	17.3	14.8	12.3	9.9	8.3	8.3	8.3	8.3	9.1
70°	22.3	19.0	16.5	14.0	10.8	8.3	7.5	7.5	8.3	8.3	9.1
72.5°	17.3	14.8	14.0	11.6	8.3	7.5	6.6	7.5	7.5	8.3	8.3
75°	13.2	10.8	10.8	9.1	6.6	5.8	5.8	6.6	6.6	7.5	7.5
77.5°	9.1	7.5	7.5	6.6	5.8	5.0	5.0	5.8	6.6	6.6	7.5
80°	6.6	5.8	5.0	5.8	5.0	4.1	5.0	5.8	5.8	6.6	6.6
82.5°	5.0	5.0	5.0	5.0	4.1	4.1	5.0	5.0	5.8	6.6	6.6
85°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.0	5.0	5.8	5.8
87.5°	2.5	2.5	2.5	3.3	3.3	4.1	4.1	4.1	4.1	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P151595

CATALOG NUMBER: VXS-F03-LED-E1-SL4-HSS

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	380.5	380.5	380.5	380.5
2.5°	287.3	286.4	283.1	283.9
5°	201.5	196.5	199.8	199.0
7.5°	147.8	146.9	146.1	147.8
10°	126.3	126.3	125.5	126.3
12.5°	118.9	118.9	118.9	118.9
15°	113.1	113.1	112.2	112.2
17.5°	106.5	106.5	106.5	105.7
20°	99.9	99.1	99.1	99.1
22.5°	92.4	91.6	91.6	91.6
25°	85.1	84.2	84.2	84.2
27.5°	77.6	76.8	76.0	76.0
30°	70.2	69.3	68.5	68.5
32.5°	62.7	61.9	61.1	61.1
35°	56.2	56.2	55.3	54.5
37.5°	50.4	50.4	50.4	50.4
40°	46.2	47.0	47.0	47.0
42.5°	43.7	44.6	45.4	46.2
45°	42.1	43.7	44.6	44.6
47.5°	41.2	42.1	42.9	42.9
50°	37.9	37.1	37.1	37.1
52.5°	30.6	28.9	28.1	27.3
55°	22.3	21.5	19.8	19.8
57.5°	15.6	15.6	14.8	14.8
60°	12.3	12.3	11.6	12.3
62.5°	10.8	10.8	10.8	10.8
65°	9.9	9.9	9.9	9.9
67.5°	9.9	9.9	9.9	9.9
69°	9.1	9.1	9.1	9.1
70°	9.1	9.1	9.1	9.1
72.5°	8.3	8.3	8.3	8.3
75°	7.5	8.3	8.3	8.3
77.5°	7.5	7.5	7.5	7.5
80°	6.6	6.6	7.5	7.5
82.5°	6.6	6.6	6.6	6.6
85°	5.8	5.8	6.6	6.6
87.5°	5.0	5.0	5.8	5.8
90°	0.0	0.0	0.0	0.0

(END OF REPORT)