

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P151615

Luminaire Tested: **VXS-F05-LED-E1-SL4-HSS**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P151615
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-SL4-HSS
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND
HOUSE SIDE SHIELD
Light Source: (35) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8398.9 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G2

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P151615

CATALOG NUMBER: VXS-F05-LED-E1-SL4-HSS

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 18.8 fc
Type IV - Short - Semi-Cutoff

REPORT NUMBER: P151615

CATALOG NUMBER: VXS-F05-LED-E1-SL4-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P151615

CATALOG NUMBER: VXS-F05-LED-E1-SL4-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	250.1	0.0	250.1
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	8148.8	0.0	8148.8
	% Fixture	97.0	0.0	97.0
Total	Lumens	8398.9	0.0	8398.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	0.8
10°-20°	224.8	2.7
20°-30°	430.2	5.1
30°-40°	715.4	8.5
40°-50°	968.1	11.5
50°-60°	1514.0	18.0
60°-70°	3112.8	37.1
70°-80°	1252.5	14.9
80°-90°	115.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8398.9	100.0
0°-180°	8398.9	100.0

Coefficient of Utilization



REPORT NUMBER: P151615


CATALOG NUMBER: VXS-F05-LED-E1-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	625.0	7.4			
FM	(30°-60°)	3083.4	36.7			
FH	(60°-80°)	4328.8	51.5			G2/5000
FVH	(80°-90°)	111.5	1.3			G2/225
BL	(0°-30°)	95.1	1.1	B0/110		
BM	(30°-60°)	114.2	1.4	B0/220		
BH	(60°-80°)	36.5	0.4	B0/110		G0/110
BVH	(80°-90°)	4.3	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type IV Short



REPORT NUMBER: P151615

CATALOG NUMBER: VXS-F05-LED-E1-SL4-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3
2.5°	846.1	836.6	825.5	825.5	811.8	811.8	803.5	781.5	778.8	766.3	754.0
5°	1080.1	1071.8	1058.0	1045.7	1034.6	1015.4	1001.7	975.5	946.6	919.1	894.3
7.5°	1308.5	1304.4	1279.6	1275.4	1257.5	1225.9	1198.3	1159.9	1110.4	1071.8	1026.4
10°	1520.3	1510.7	1505.2	1481.9	1455.6	1421.2	1378.7	1331.8	1274.1	1213.5	1148.8
12.5°	1688.2	1682.7	1657.9	1648.3	1620.8	1586.4	1532.7	1472.2	1414.4	1336.0	1260.3
15°	1813.4	1803.7	1787.3	1772.1	1739.1	1708.8	1659.3	1593.3	1523.1	1437.8	1346.9
17.5°	1917.9	1900.1	1896.0	1872.5	1838.1	1802.4	1747.4	1686.8	1604.2	1519.0	1419.9
20°	2058.3	2033.6	2025.3	1990.9	1951.0	1901.5	1838.1	1762.5	1675.9	1582.3	1480.4
22.5°	2223.4	2205.5	2187.7	2157.4	2106.4	2036.3	1944.1	1861.6	1751.5	1648.3	1538.2
25°	2457.3	2442.2	2413.3	2372.0	2308.7	2224.8	2113.4	1992.2	1862.9	1730.9	1601.6
27.5°	2684.4	2670.6	2649.9	2618.2	2546.7	2454.6	2317.0	2162.9	1999.2	1839.6	1696.5
30°	2897.6	2885.2	2864.6	2833.0	2769.6	2678.9	2523.3	2358.2	2154.6	1968.9	1796.9
32.5°	3127.4	3123.2	3099.9	3054.4	2999.4	2877.0	2707.8	2530.3	2323.8	2109.2	1908.3
35°	3387.4	3355.8	3333.8	3288.3	3194.8	3064.0	2865.9	2671.9	2454.6	2234.4	2010.2
37.5°	3607.6	3577.3	3549.7	3492.0	3377.8	3211.3	2987.0	2773.8	2549.5	2325.2	2096.8
40°	3768.5	3753.4	3720.4	3644.7	3516.8	3318.7	3076.5	2843.9	2618.2	2392.6	2167.0
42.5°	3888.2	3864.9	3827.7	3749.2	3597.9	3372.2	3112.2	2872.8	2649.9	2433.9	2212.4
45°	3932.2	3913.0	3878.5	3793.3	3629.5	3387.4	3110.9	2864.6	2651.3	2446.3	2242.7
47.5°	3906.1	3886.8	3856.6	3776.8	3615.8	3369.5	3086.1	2841.1	2637.5	2450.5	2270.2
50°	3819.4	3808.4	3785.1	3717.6	3573.2	3335.1	3064.0	2828.8	2634.8	2471.1	2308.7
52.5°	3811.2	3804.2	3775.4	3708.0	3560.7	3324.1	3061.3	2835.6	2658.2	2497.2	2336.3
55°	4657.3	4559.7	4340.9	4155.1	3849.7	3486.4	3200.3	2947.2	2757.2	2600.4	2487.6
57.5°	6619.4	6473.5	6185.9	5832.3	5130.7	4441.3	3889.6	3490.6	3293.9	3222.3	3265.0
60°	7538.4	7512.2	7466.8	7299.1	6939.9	6346.9	5686.5	4972.4	4686.2	4661.5	4748.2
62.5°	7974.6	7958.0	7971.8	7951.2	7839.7	7666.4	7476.5	7168.3	6884.9	6701.9	6313.9
65°	8175.4	8186.4	8264.9	8326.8	8340.5	8385.9	8524.9	8908.8	9189.4	8717.5	7640.2
67.5°	7665.0	7729.6	7909.9	8135.5	8399.7	8655.6	9068.4	9877.4	10453.9	9899.4	8369.4
69°	6345.5	6377.2	6817.4	7242.6	7887.9	8339.2	8937.7	9998.4	10646.5	10020.5	8311.7
70°	4995.8	5024.7	5496.6	6074.5	7165.6	7746.2	8529.0	9793.5	10466.3	9859.5	8014.5
72.5°	2253.7	2212.4	2378.9	2688.5	3874.5	4796.3	6165.3	7934.7	8635.0	7898.9	5996.1
75°	1574.0	1556.2	1574.0	1575.3	1759.8	2270.2	2864.6	4301.0	5319.2	4589.9	2864.6
77.5°	1219.1	1206.6	1194.3	1180.5	1202.5	1346.9	1404.8	1525.8	1981.2	1874.0	1092.4
80°	964.5	953.5	983.7	974.1	974.1	990.7	979.6	934.2	848.9	787.0	704.5
82.5°	448.5	451.3	451.3	489.8	590.3	689.3	720.9	675.5	599.9	510.5	411.4
85°	42.7	48.2	81.1	125.2	249.0	280.7	282.1	233.9	233.9	184.4	148.6
87.5°	0.0	1.3	1.3	1.3	12.3	34.4	28.9	8.3	4.1	4.1	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P151615

CATALOG NUMBER: VXS-F05-LED-E1-SL4-HSS

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3
2.5°	731.9	727.9	711.3	694.8	679.7	663.2	648.1	633.0	616.4	604.0	588.9
5°	855.8	825.5	791.1	758.1	725.1	690.7	654.9	623.3	590.3	560.0	531.1
7.5°	981.0	921.9	875.0	815.9	762.3	708.6	659.1	608.2	561.3	517.3	476.1
10°	1086.9	1015.4	942.5	866.8	789.7	718.2	649.4	588.9	526.9	473.3	422.4
12.5°	1173.6	1082.8	993.4	898.4	811.8	720.9	635.6	562.7	489.8	429.2	377.0
15°	1252.0	1147.5	1040.2	930.1	820.0	716.8	621.9	531.1	456.8	388.0	328.8
17.5°	1315.3	1195.6	1074.5	950.8	832.4	711.3	604.0	509.1	422.4	350.9	293.1
20°	1370.4	1245.2	1114.5	975.5	840.6	709.9	588.9	481.6	392.1	316.5	260.0
22.5°	1421.2	1296.1	1155.8	1007.2	853.1	708.6	575.1	460.9	366.0	290.3	233.9
25°	1479.1	1346.9	1199.8	1040.2	875.0	714.1	566.8	444.5	342.6	265.5	213.3
27.5°	1543.7	1404.8	1252.0	1081.5	903.9	725.1	564.1	426.5	322.0	242.2	196.8
30°	1634.5	1473.6	1304.4	1122.7	930.1	737.5	561.3	415.5	301.3	224.2	180.2
32.5°	1714.3	1540.9	1362.1	1165.4	959.0	749.8	560.0	400.4	282.1	206.4	167.9
35°	1798.2	1602.9	1411.6	1206.6	983.7	763.6	558.7	389.3	264.1	188.5	155.4
37.5°	1871.2	1655.1	1450.2	1242.4	1011.3	776.0	560.0	379.8	247.7	173.4	144.5
40°	1933.1	1708.8	1492.8	1275.4	1040.2	795.2	561.3	370.2	231.2	159.6	134.8
42.5°	1988.2	1759.8	1538.2	1312.5	1073.2	817.3	569.6	361.9	217.4	147.3	125.2
45°	2030.8	1806.5	1587.8	1364.9	1126.8	853.1	584.8	356.4	203.6	136.2	117.0
47.5°	2074.8	1875.3	1671.7	1447.5	1205.3	909.4	610.9	355.0	192.6	128.0	110.1
50°	2135.3	1944.1	1746.0	1531.4	1276.8	967.3	642.5	356.4	178.9	119.7	103.2
52.5°	2179.4	2014.3	1842.3	1677.2	1447.5	1143.3	765.0	381.1	172.0	112.8	94.9
55°	2439.4	2410.6	2414.6	2442.2	2264.7	1945.5	1279.6	550.4	202.3	128.0	93.6
57.5°	3439.7	3541.5	3600.6	3599.3	3306.2	2742.1	1718.4	707.2	225.6	148.6	111.4
60°	4755.0	4677.9	4569.3	4301.0	3911.6	3130.2	1922.1	760.8	195.3	118.3	101.9
62.5°	5917.6	5466.3	5066.0	4631.2	4120.7	3265.0	1963.4	756.7	170.6	89.4	71.5
65°	6642.7	5831.0	5184.2	4639.5	4038.2	3152.1	1857.4	694.8	144.5	73.0	59.2
67.5°	6816.1	5634.2	4719.3	4024.5	3373.7	2453.2	1363.5	522.8	112.8	60.5	52.3
69°	6437.7	5008.2	3910.3	3121.9	2454.6	1627.7	843.4	330.3	86.6	55.0	48.2
70°	5921.8	4356.1	3185.2	2505.5	1817.5	1143.3	590.3	232.5	70.2	50.9	44.0
72.5°	3809.8	2288.1	1565.7	1089.7	749.8	455.4	231.2	104.6	53.7	42.7	35.8
75°	1477.7	846.1	613.7	466.4	364.6	253.2	140.3	67.5	45.4	35.8	27.6
77.5°	727.9	557.2	455.4	312.3	181.7	112.8	75.6	52.3	37.1	26.1	17.9
80°	575.1	382.5	228.4	141.8	107.4	81.1	57.8	42.7	27.6	16.5	12.3
82.5°	294.4	160.9	118.3	96.3	79.8	63.3	46.7	30.3	17.9	11.0	9.6
85°	92.2	67.5	60.5	59.2	55.0	45.4	33.1	19.3	11.0	6.8	6.8
87.5°	6.8	9.6	12.3	9.6	11.0	9.6	12.3	8.3	5.5	5.5	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P151615

CATALOG NUMBER: VXS-F05-LED-E1-SL4-HSS

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3	634.3
2.5°	577.8	561.3	546.2	536.6	518.8	511.8	505.0	502.2	489.8	492.5	481.6
5°	505.0	476.1	454.0	432.0	411.4	396.3	383.8	368.7	356.4	350.9	339.8
7.5°	438.9	401.8	372.8	349.4	324.7	305.5	288.9	277.9	266.9	256.0	250.4
10°	381.1	341.2	308.2	284.8	261.5	244.9	232.5	224.2	217.4	213.3	211.9
12.5°	327.5	288.9	258.7	238.0	220.1	211.9	206.4	202.3	200.8	199.5	199.5
15°	286.2	247.7	224.2	209.1	200.8	196.8	195.3	192.6	189.8	188.5	188.5
17.5°	247.7	218.8	202.3	194.0	189.8	187.2	184.4	181.7	178.9	177.5	177.5
20°	221.6	198.1	189.8	184.4	180.2	177.5	173.4	170.6	169.2	167.9	166.5
22.5°	200.8	185.7	180.2	176.1	170.6	166.5	163.7	160.9	158.2	156.9	155.4
25°	185.7	176.1	172.0	166.5	160.9	156.9	152.7	148.6	145.8	144.5	141.8
27.5°	174.7	167.9	162.4	155.4	149.9	145.8	141.8	137.6	134.8	132.1	130.7
30°	165.1	158.2	151.3	145.8	139.0	134.8	129.3	125.2	123.8	121.0	118.3
32.5°	155.4	148.6	141.8	134.8	128.0	122.5	119.7	114.2	111.4	110.1	107.4
35°	144.5	137.6	129.3	123.8	117.0	111.4	107.4	103.2	100.4	97.7	96.3
37.5°	134.8	126.6	118.3	111.4	105.9	100.4	96.3	92.2	89.4	86.6	85.3
40°	123.8	115.5	107.4	100.4	94.9	90.8	86.6	82.6	79.8	78.4	78.4
42.5°	114.2	104.6	96.3	90.8	86.6	81.1	77.1	73.0	71.5	70.2	71.5
45°	104.6	94.9	88.1	82.6	78.4	73.0	68.8	66.0	64.7	66.0	67.5
47.5°	96.3	86.6	79.8	75.6	71.5	67.5	63.3	60.5	60.5	63.3	66.0
50°	88.1	78.4	73.0	70.2	66.0	61.9	56.4	55.0	56.4	59.2	61.9
52.5°	79.8	68.8	64.7	63.3	59.2	55.0	50.9	49.5	50.9	53.7	52.3
55°	71.5	60.5	59.2	57.8	53.7	48.2	44.0	44.0	44.0	42.7	39.9
57.5°	68.8	53.7	52.3	50.9	46.7	41.2	38.5	35.8	34.4	30.3	28.9
60°	71.5	48.2	48.2	45.4	41.2	35.8	31.6	27.6	24.8	22.0	22.0
62.5°	57.8	44.0	42.7	39.9	34.4	28.9	24.8	20.6	19.3	17.9	17.9
65°	46.7	39.9	37.1	33.1	28.9	23.4	19.3	16.5	15.1	15.1	16.5
67.5°	42.7	35.8	31.6	27.6	23.4	17.9	15.1	13.8	13.8	15.1	15.1
69°	39.9	33.1	28.9	24.8	20.6	16.5	13.8	13.8	13.8	13.8	15.1
70°	37.1	31.6	27.6	23.4	17.9	13.8	12.3	12.3	13.8	13.8	15.1
72.5°	28.9	24.8	23.4	19.3	13.8	12.3	11.0	12.3	12.3	13.8	13.8
75°	22.0	17.9	17.9	15.1	11.0	9.6	9.6	11.0	11.0	12.3	12.3
77.5°	15.1	12.3	12.3	11.0	9.6	8.3	8.3	9.6	11.0	11.0	12.3
80°	11.0	9.6	8.3	9.6	8.3	6.8	8.3	9.6	9.6	11.0	11.0
82.5°	8.3	8.3	8.3	8.3	6.8	6.8	8.3	8.3	9.6	11.0	11.0
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	8.3	8.3	9.6	9.6
87.5°	4.1	4.1	4.1	5.5	5.5	6.8	6.8	6.8	6.8	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P151615

CATALOG NUMBER: VXS-F05-LED-E1-SL4-HSS

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	634.3	634.3	634.3	634.3
2.5°	478.8	477.4	471.9	473.3
5°	335.8	327.5	333.0	331.6
7.5°	246.3	244.9	243.5	246.3
10°	210.5	210.5	209.1	210.5
12.5°	198.1	198.1	198.1	198.1
15°	188.5	188.5	187.2	187.2
17.5°	177.5	177.5	177.5	176.1
20°	166.5	165.1	165.1	165.1
22.5°	154.1	152.7	152.7	152.7
25°	141.8	140.3	140.3	140.3
27.5°	129.3	128.0	126.6	126.6
30°	117.0	115.5	114.2	114.2
32.5°	104.6	103.2	101.9	101.9
35°	93.6	93.6	92.2	90.8
37.5°	83.9	83.9	83.9	83.9
40°	77.1	78.4	78.4	78.4
42.5°	73.0	74.3	75.6	77.1
45°	70.2	73.0	74.3	74.3
47.5°	68.8	70.2	71.5	71.5
50°	63.3	61.9	61.9	61.9
52.5°	50.9	48.2	46.7	45.4
55°	37.1	35.8	33.1	33.1
57.5°	26.1	26.1	24.8	24.8
60°	20.6	20.6	19.3	20.6
62.5°	17.9	17.9	17.9	17.9
65°	16.5	16.5	16.5	16.5
67.5°	16.5	16.5	16.5	16.5
69°	15.1	15.1	15.1	15.1
70°	15.1	15.1	15.1	15.1
72.5°	13.8	13.8	13.8	13.8
75°	12.3	13.8	13.8	13.8
77.5°	12.3	12.3	12.3	12.3
80°	11.0	11.0	12.3	12.3
82.5°	11.0	11.0	11.0	11.0
85°	9.6	9.6	11.0	11.0
87.5°	8.3	8.3	9.6	9.6
90°	0.0	0.0	0.0	0.0

(END OF REPORT)