

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P148210

Luminaire Tested: **VXS-E02-LED-E1-5XQ**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P148210
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E02-LED-E1-5XQ
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (42) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6360.8 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B3 - U0 - G2

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P148210

CATALOG NUMBER: VXS-E02-LED-E1-5XQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 6 fc
Type V - Short - Non-Cutoff

REPORT NUMBER: P148210

CATALOG NUMBER: VXS-E02-LED-E1-5XQ

Luminous Intensity Polar Plot



REPORT NUMBER: P148210

CATALOG NUMBER: VXS-E02-LED-E1-5XQ


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3180.4	0.0	3180.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3180.4	0.0	3180.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	6360.8	0.0	6360.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.4	0.9
10°-20°	169.9	2.7
20°-30°	284.5	4.5
30°-40°	433.7	6.8
40°-50°	692.6	10.9
50°-60°	1064.9	16.7
60°-70°	1550.5	24.4
70°-80°	1746.6	27.5
80°-90°	360.6	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6360.8	100.0
0°-180°	6360.8	100.0

Coefficient of Utilization



REPORT NUMBER: P148210


CATALOG NUMBER: VXS-E02-LED-E1-5XQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	255.9	4.0			
FM	(30°-60°)	1095.6	17.2			
FH	(60°-80°)	1648.6	25.9			G1/1800
FVH	(80°-90°)	180.3	2.8			G2/225
BL	(0°-30°)	255.9	4.0	B1/500		
BM	(30°-60°)	1095.6	17.2	B2/2500		
BH	(60°-80°)	1648.6	25.9	B3/2500		G1/1800
BVH	(80°-90°)	180.3	2.8			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type V Short



REPORT NUMBER: P148210

CATALOG NUMBER: VXS-E02-LED-E1-5XQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7
2.5°	603.7	603.9	603.8	603.5	603.6	603.5	603.1	603.0	601.9	602.5	603.5
5°	603.6	603.3	603.2	603.0	603.0	603.5	603.0	602.5	602.3	602.7	602.2
7.5°	603.3	602.7	602.4	602.2	602.3	602.5	602.0	601.3	601.9	601.3	600.6
10°	602.3	601.9	602.0	601.3	601.5	601.3	600.6	600.2	600.5	600.0	599.2
12.5°	602.7	601.9	601.7	601.3	601.1	601.0	600.2	599.4	599.5	599.2	598.3
15°	602.7	602.2	602.0	601.3	601.1	600.8	599.8	599.5	599.5	599.1	598.0
17.5°	603.0	602.7	602.7	601.9	601.5	601.3	600.2	599.7	600.2	599.2	598.5
20°	604.0	603.7	603.8	603.3	602.7	602.7	601.9	601.5	601.7	601.5	599.7
22.5°	606.0	606.0	606.3	606.2	606.0	606.2	605.5	605.5	605.7	605.6	604.1
25°	611.6	611.5	611.8	611.8	612.0	613.2	612.6	612.4	613.3	613.4	611.8
27.5°	622.4	622.0	622.3	622.6	623.5	625.1	624.7	625.2	626.5	626.1	624.9
30°	634.6	634.4	635.2	636.2	636.9	639.2	638.1	640.6	641.9	642.8	641.9
32.5°	652.6	652.6	654.2	654.8	656.4	658.7	659.0	661.0	662.5	664.1	663.0
35°	676.7	676.4	677.5	678.7	680.5	682.7	683.5	686.2	688.5	689.6	687.5
37.5°	713.3	711.5	713.7	714.3	715.9	716.3	718.7	722.1	724.5	724.1	722.7
40°	763.0	762.7	761.9	760.8	763.1	763.9	763.9	768.5	772.5	771.8	771.7
42.5°	820.9	819.5	818.4	818.4	819.8	820.2	825.3	828.7	831.5	832.2	831.5
45°	883.3	881.9	882.2	881.5	882.0	884.1	887.2	893.3	898.7	898.9	896.0
47.5°	950.3	945.7	949.3	944.1	947.4	949.0	956.5	965.5	974.8	976.5	974.0
50°	1018.3	1017.8	1017.5	1016.5	1018.0	1021.7	1030.9	1045.0	1054.0	1060.0	1056.0
52.5°	1092.6	1090.2	1089.0	1087.4	1088.8	1096.0	1108.8	1121.1	1137.3	1144.1	1138.7
55°	1165.0	1164.1	1159.8	1159.7	1162.9	1174.0	1188.0	1203.2	1220.7	1228.3	1226.3
57.5°	1239.4	1234.5	1233.2	1231.1	1237.5	1248.0	1265.2	1292.5	1310.7	1319.4	1314.4
60°	1312.0	1308.4	1305.5	1304.9	1309.1	1323.8	1348.5	1381.3	1403.8	1415.1	1407.2
62.5°	1390.1	1387.7	1384.4	1380.5	1389.6	1408.5	1439.2	1475.4	1508.7	1522.7	1510.5
65°	1486.9	1482.2	1478.5	1473.7	1481.1	1504.9	1543.3	1594.5	1639.0	1655.3	1646.6
67.5°	1589.3	1584.9	1585.2	1582.2	1595.5	1628.4	1678.0	1747.6	1807.2	1835.0	1818.7
70°	1678.7	1681.1	1681.9	1694.0	1717.0	1767.0	1849.6	1958.5	2049.0	2091.5	2074.0
71°	1652.3	1657.8	1666.3	1679.0	1718.7	1777.8	1890.7	2022.5	2130.5	2202.5	2178.3
72.5°	1577.6	1580.9	1585.3	1604.7	1649.5	1727.9	1843.9	1994.6	2133.5	2226.6	2198.7
75°	1469.6	1472.8	1474.4	1487.9	1528.7	1597.0	1703.3	1837.0	1959.5	2038.9	2031.0
77.5°	1306.6	1307.2	1318.9	1339.7	1385.5	1463.6	1575.6	1714.4	1829.5	1891.2	1852.0
80°	938.3	932.0	944.0	970.8	1027.6	1117.2	1231.8	1390.2	1517.9	1575.6	1515.0
82.5°	357.0	376.4	406.8	451.2	470.4	570.1	677.0	770.1	877.7	997.9	967.9
85°	38.3	43.1	54.2	67.2	84.8	117.3	162.2	221.3	272.8	320.6	284.7
87.5°	14.3	14.7	16.4	18.9	19.2	20.0	21.3	24.9	23.2	20.0	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P148210

CATALOG NUMBER: VXS-E02-LED-E1-5XQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7
2.5°	602.7	602.8	602.7	602.8	602.8	602.2	602.3	602.0
5°	602.5	602.0	602.2	602.3	602.2	602.5	602.0	602.3
7.5°	601.7	600.7	601.0	601.0	600.7	601.1	600.8	600.7
10°	600.0	598.7	599.3	599.0	598.9	599.1	599.0	599.0
12.5°	598.5	597.7	597.8	597.7	597.5	598.0	597.8	598.0
15°	598.1	596.9	596.7	596.3	596.5	596.9	596.9	597.3
17.5°	597.8	596.2	596.0	595.6	595.9	596.5	596.7	596.3
20°	598.9	597.5	597.2	596.9	596.7	597.5	597.3	597.3
22.5°	603.5	601.9	601.7	600.3	599.8	600.3	600.0	600.0
25°	611.0	609.0	608.3	606.5	605.2	605.2	604.7	604.4
27.5°	624.5	621.6	620.8	619.3	617.5	617.8	616.8	616.7
30°	640.2	637.5	635.1	633.0	630.9	630.1	628.8	628.6
32.5°	660.7	657.6	654.8	652.1	649.1	648.0	646.0	645.0
35°	685.8	681.9	678.5	676.7	673.7	672.1	670.8	672.3
37.5°	721.0	716.2	714.5	712.3	710.3	708.0	708.5	708.0
40°	769.6	765.4	763.6	759.8	759.4	756.7	758.3	756.7
42.5°	829.8	821.8	820.7	817.6	816.7	815.2	815.9	814.7
45°	895.3	888.2	886.8	882.0	882.2	878.7	880.0	880.0
47.5°	969.0	961.6	955.3	951.8	950.5	948.4	949.5	949.3
50°	1045.0	1034.8	1028.0	1021.1	1018.1	1019.1	1016.7	1020.7
52.5°	1126.6	1111.5	1101.9	1095.3	1089.6	1090.8	1091.2	1092.3
55°	1211.2	1191.8	1177.8	1169.3	1164.1	1164.5	1166.0	1167.3
57.5°	1296.2	1272.0	1253.1	1240.3	1237.0	1238.5	1238.5	1238.3
60°	1384.4	1355.3	1330.8	1316.5	1313.5	1312.6	1319.2	1317.0
62.5°	1479.0	1444.1	1418.9	1400.5	1396.2	1399.2	1405.0	1403.7
65°	1604.6	1556.4	1523.7	1505.5	1498.1	1501.1	1509.0	1508.6
67.5°	1766.3	1699.1	1655.9	1632.5	1627.2	1630.9	1635.1	1639.4
70°	2008.3	1912.2	1850.6	1800.0	1778.3	1774.2	1778.4	1778.7
71°	2093.5	1983.0	1884.9	1823.2	1787.7	1772.6	1773.9	1766.3
72.5°	2089.9	1953.8	1839.0	1774.5	1725.2	1713.2	1707.4	1698.2
75°	1949.2	1826.5	1726.8	1656.5	1609.0	1594.8	1584.5	1584.0
77.5°	1767.7	1677.2	1567.4	1492.8	1435.0	1411.5	1400.9	1400.6
80°	1421.0	1285.5	1205.2	1160.3	1090.6	1070.3	1049.0	1041.0
82.5°	859.3	671.5	546.0	485.2	451.5	371.8	333.7	315.6
85°	200.2	142.2	98.0	64.4	46.3	36.9	28.4	25.1
87.5°	13.5	10.7	9.5	7.7	5.8	5.6	3.5	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)