

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P147689

Luminaire Tested: **VXS-E02-LED-E1-5WQ-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P147689
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E02-LED-E1-5WQ-7030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (42) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5815.9 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G1


Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P147689
 CATALOG NUMBER: VXS-E02-LED-E1-5WQ-7030

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 3.5 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P147689
CATALOG NUMBER: VXS-E02-LED-E1-5WQ-7030

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P147689

CATALOG NUMBER: VXS-E02-LED-E1-5WQ-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2907.9	0.0	2907.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2907.9	0.0	2907.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	5815.9	0.0	5815.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.3	0.5
10°-20°	107.1	1.8
20°-30°	216.8	3.7
30°-40°	363.6	6.3
40°-50°	641.3	11.0
50°-60°	1130.9	19.4
60°-70°	1726.5	29.7
70°-80°	1442.7	24.8
80°-90°	156.8	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5815.9	100.0
0°-180°	5815.9	100.0



REPORT NUMBER: P147689


CATALOG NUMBER: VXS-E02-LED-E1-5WQ-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	177.1	3.0			
FM (30°-60°)	1067.8	18.4			
FH (60°-80°)	1584.6	27.2			G1/1800
FVH (80°-90°)	78.4	1.3			G1/100
BL (0°-30°)	177.1	3.0	B1/500		
BM (30°-60°)	1067.8	18.4	B2/2500		
BH (60°-80°)	1584.6	27.2	B3/2500		G1/1800
BVH (80°-90°)	78.4	1.3			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1

Type V Short





REPORT NUMBER: P147689

CATALOG NUMBER: VXS-E02-LED-E1-5WQ-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0
2.5°	304.5	305.1	304.5	304.5	304.5	304.5	304.5	303.8	303.8	303.8	304.5
5°	310.6	311.2	310.6	311.2	311.2	311.2	311.2	310.6	310.6	310.6	310.6
7.5°	320.3	320.3	320.3	320.9	320.3	320.3	320.9	320.3	320.3	320.3	320.3
10°	334.3	333.7	333.7	333.7	333.7	333.7	334.3	334.3	334.3	333.7	333.7
12.5°	351.3	350.8	351.3	351.3	351.9	351.9	351.9	351.9	351.9	351.9	351.3
15°	372.0	372.0	372.0	372.6	373.9	373.9	373.3	373.9	373.9	373.9	373.9
17.5°	395.1	396.4	395.1	395.8	396.4	395.8	397.0	397.6	398.2	397.6	395.8
20°	419.0	419.5	419.5	419.5	419.5	420.7	421.3	421.3	423.2	422.6	422.0
22.5°	441.5	442.7	442.7	443.3	443.3	445.1	445.1	445.1	446.3	447.6	446.3
25°	465.2	464.6	464.6	465.8	466.4	468.8	468.8	470.1	471.9	472.5	471.3
27.5°	486.5	485.9	485.9	487.8	488.3	491.4	491.4	493.8	495.0	495.6	494.4
30°	509.0	509.0	508.4	510.3	512.1	514.5	515.8	518.1	520.0	520.6	519.4
32.5°	535.9	534.6	535.2	536.5	537.6	540.1	542.0	545.0	547.4	548.0	546.8
35°	566.3	564.5	565.1	566.3	568.1	571.7	574.8	576.6	580.3	581.5	579.1
37.5°	599.8	600.4	599.8	602.8	605.9	610.2	613.8	616.2	619.9	621.7	619.9
40°	647.3	645.4	647.3	650.3	655.1	660.6	668.0	669.7	673.5	677.1	672.8
42.5°	708.8	707.6	711.8	714.2	719.7	725.8	734.9	739.8	745.3	747.8	744.0
45°	789.1	789.1	794.0	794.6	803.1	811.1	823.8	829.9	840.3	840.3	840.3
47.5°	878.0	881.7	884.8	890.8	896.9	911.5	924.4	937.7	947.5	948.7	946.8
50°	969.9	973.7	982.8	991.3	1004.7	1022.9	1037.0	1054.6	1063.1	1070.5	1068.0
52.5°	1071.7	1072.2	1083.2	1094.2	1113.7	1133.8	1156.3	1174.6	1189.7	1196.5	1191.0
55°	1183.1	1184.4	1194.1	1205.6	1227.6	1250.7	1278.7	1297.6	1317.1	1329.2	1320.1
57.5°	1303.6	1304.2	1314.0	1328.0	1354.2	1377.3	1404.1	1430.9	1449.2	1460.1	1454.1
60°	1437.0	1440.0	1447.4	1465.0	1489.9	1514.3	1541.1	1564.9	1586.2	1597.7	1591.7
62.5°	1579.5	1582.5	1592.8	1606.8	1628.8	1655.6	1681.1	1711.6	1729.3	1742.1	1733.0
65°	1675.1	1680.5	1697.0	1715.9	1748.2	1782.9	1812.7	1854.1	1875.4	1890.7	1882.1
67.5°	1681.1	1684.2	1704.4	1733.0	1776.2	1828.5	1889.4	1954.0	1996.0	2016.1	2001.5
69°	1639.8	1644.0	1663.5	1695.8	1743.9	1804.8	1877.2	1957.6	2022.2	2052.0	2038.0
70°	1592.8	1602.0	1623.3	1658.7	1705.5	1769.4	1844.4	1930.3	2005.7	2046.5	2036.2
72.5°	1494.2	1496.7	1510.7	1538.7	1574.6	1627.6	1698.2	1779.2	1851.1	1909.5	1918.0
75°	1326.2	1334.1	1344.5	1363.3	1381.6	1420.0	1467.5	1522.9	1564.9	1609.9	1611.7
77.5°	1002.3	1026.0	1033.9	1038.1	1046.1	1076.6	1117.9	1166.0	1200.7	1208.1	1206.8
80°	449.9	481.7	488.9	523.6	545.0	595.5	658.9	732.5	781.9	787.4	773.9
82.5°	88.3	94.4	110.3	137.6	187.6	217.4	258.8	310.6	358.0	385.4	369.0
85°	29.2	31.1	36.0	39.6	45.7	51.7	62.7	77.9	96.8	107.2	95.6
87.5°	11.6	11.6	13.4	14.6	15.9	15.9	15.9	14.6	14.0	11.6	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147689

CATALOG NUMBER: VXS-E02-LED-E1-5WQ-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	302.0	302.0	302.0	302.0	302.0	302.0	302.0	302.0
2.5°	303.8	303.8	303.8	303.8	303.8	303.8	303.8	303.8
5°	310.6	309.9	309.9	309.3	309.3	309.3	309.3	309.3
7.5°	319.7	319.1	318.4	319.1	318.4	318.4	318.4	318.4
10°	333.7	332.4	331.8	331.2	331.2	331.2	330.7	330.7
12.5°	350.2	350.2	349.5	348.9	347.7	348.3	347.7	346.4
15°	372.6	371.4	370.8	370.3	369.0	369.0	369.0	368.4
17.5°	395.1	394.0	394.0	392.1	391.5	391.5	391.5	392.1
20°	420.1	418.3	417.1	415.9	414.6	415.2	414.1	415.2
22.5°	445.1	442.7	441.5	439.6	437.8	437.8	437.2	436.0
25°	469.4	466.4	465.2	463.4	460.9	460.9	459.7	458.5
27.5°	492.6	489.5	488.3	484.7	482.3	481.7	480.4	479.8
30°	518.1	514.5	512.6	509.0	505.4	504.8	502.9	502.9
32.5°	545.0	541.3	540.1	534.6	531.6	531.6	530.4	529.1
35°	578.4	573.0	571.7	566.3	562.0	562.0	560.8	561.5
37.5°	618.0	613.8	609.5	605.3	600.4	599.8	598.5	597.3
40°	671.0	666.1	661.2	655.1	650.9	649.7	647.9	647.3
42.5°	741.7	736.8	727.0	722.2	717.9	714.2	713.7	713.1
45°	831.7	825.7	819.0	809.8	804.4	796.5	795.2	792.2
47.5°	940.1	928.6	917.0	909.1	900.5	891.4	889.6	884.8
50°	1055.2	1046.1	1026.6	1013.8	1000.4	991.3	985.2	983.4
52.5°	1178.9	1161.8	1142.3	1125.3	1105.8	1093.6	1082.6	1079.6
55°	1307.9	1283.5	1259.2	1239.1	1219.6	1205.0	1194.6	1189.7
57.5°	1437.0	1410.3	1383.4	1361.5	1345.1	1326.2	1315.9	1313.4
60°	1571.6	1546.0	1518.5	1496.7	1476.6	1460.1	1454.1	1442.5
62.5°	1714.1	1687.3	1661.7	1640.4	1614.8	1603.2	1592.8	1586.2
65°	1854.1	1823.0	1790.8	1768.3	1742.7	1726.2	1713.5	1704.4
67.5°	1962.5	1915.6	1872.3	1834.6	1799.9	1774.3	1757.9	1749.3
69°	1993.0	1934.5	1879.1	1829.7	1788.9	1760.3	1742.1	1733.6
70°	1989.3	1924.8	1863.8	1809.6	1765.2	1734.7	1717.1	1701.2
72.5°	1876.6	1817.6	1749.9	1690.9	1650.8	1621.5	1603.8	1595.3
75°	1601.5	1561.9	1513.2	1467.5	1438.2	1421.1	1399.3	1399.9
77.5°	1166.0	1167.3	1134.4	1087.5	1054.6	1048.5	1038.8	1029.0
80°	723.4	665.5	627.8	577.2	540.1	507.8	493.8	463.4
82.5°	333.7	260.6	202.2	152.8	117.5	91.9	80.4	65.8
85°	74.3	56.6	46.8	37.7	32.2	29.8	24.4	22.5
87.5°	10.4	9.1	8.5	7.9	6.7	4.9	3.6	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)