

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P147204

Luminaire Tested: **VXS-F05-LED-E1-5MQ-7030**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P147204  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: VXS-F05-LED-E1-5MQ-7030  
Description: VISION SITE SMALL LED LUMINAIRE  
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM  
Light Source: (35) 3000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12153.5 lumens  
Efficiency: N/A  
Efficacy: 91.2 lumens/watt  
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')  
IES Classification: Type V - Short - Full Cutoff  
BUG Rating: B4 - U0 - G2

Input Watts (W): 133.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P147204

CATALOG NUMBER: VXS-F05-LED-E1-5MQ-7030

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 2.3 fc  
 Type V - Short - Full Cutoff

REPORT NUMBER: P147204  
CATALOG NUMBER: VXS-F05-LED-E1-5MQ-7030

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P147204

CATALOG NUMBER: VXS-F05-LED-E1-5MQ-7030

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	6076.8	0.0	6076.8
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	6076.8	0.0	6076.8
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	12153.5	0.0	12153.5
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.8	0.7
10°-20°	273.3	2.2
20°-30°	528.4	4.3
30°-40°	1023.1	8.4
40°-50°	1847.4	15.2
50°-60°	3212.3	26.4
60°-70°	3646.8	30.0
70°-80°	1413.8	11.6
80°-90°	127.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12153.5	100.0
0°-180°	12153.5	100.0

**Coefficient of Utilization**



REPORT NUMBER: P147204


CATALOG NUMBER: VXS-F05-LED-E1-5MQ-7030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	441.3	3.6			
FM	(30°-60°)	3041.4	25.0			
FH	(60°-80°)	2530.3	20.8			G2/5000
FVH	(80°-90°)	63.8	0.5			G1/100
BL	(0°-30°)	441.3	3.6	B1/500		
BM	(30°-60°)	3041.4	25.0	B3/5000		
BH	(60°-80°)	2530.3	20.8	B4/5000		G2/5000
BVH	(80°-90°)	63.8	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B4-U0-G2**

Type V Short





REPORT NUMBER: P147204

CATALOG NUMBER: VXS-F05-LED-E1-5MQ-7030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	806.7	806.7	806.7	806.7	806.7	806.7	806.7	806.7	806.7	806.7	806.7
2.5°	811.8	814.3	813.7	812.4	812.4	812.3	811.8	809.9	809.3	810.6	811.8
5°	830.7	830.7	830.7	830.7	829.4	829.3	828.2	826.8	827.6	826.3	825.6
7.5°	859.5	857.6	857.6	857.0	857.0	855.8	853.9	851.4	852.0	851.4	850.8
10°	893.5	894.1	892.2	894.1	891.0	890.4	887.9	886.6	885.9	884.0	884.1
12.5°	934.3	932.4	932.4	931.2	929.9	928.7	924.9	924.4	921.8	920.5	918.5
15°	972.6	972.0	969.5	967.0	966.4	965.1	960.6	958.1	957.5	954.4	951.9
17.5°	1011.0	1009.7	1006.6	1005.3	1002.8	1000.9	997.1	993.4	991.5	990.3	987.2
20°	1051.8	1050.6	1047.5	1044.9	1041.9	1039.3	1033.6	1030.5	1028.6	1026.7	1024.1
22.5°	1102.8	1100.2	1095.1	1090.8	1083.9	1081.3	1073.8	1069.4	1066.3	1063.7	1062.5
25°	1158.0	1158.7	1151.7	1146.1	1137.9	1131.0	1121.6	1116.5	1113.4	1110.9	1110.3
27.5°	1227.2	1227.8	1221.6	1213.3	1200.8	1193.2	1180.6	1174.3	1172.4	1169.9	1169.3
30°	1336.5	1330.8	1320.1	1306.9	1295.5	1279.3	1261.0	1254.7	1248.5	1246.5	1246.6
32.5°	1537.5	1534.4	1525.6	1493.0	1477.8	1443.9	1411.8	1393.6	1372.8	1362.9	1356.6
35°	1678.2	1677.0	1670.1	1658.9	1649.3	1642.5	1623.6	1620.5	1616.7	1616.8	1621.8
37.5°	1782.0	1774.4	1773.2	1775.0	1772.4	1773.7	1788.8	1809.5	1827.2	1836.0	1834.7
40°	1935.2	1924.6	1930.9	1926.4	1920.8	1919.6	1924.6	1932.7	1940.9	1940.9	1939.1
42.5°	2135.6	2140.7	2143.2	2125.0	2113.1	2109.8	2121.9	2119.4	2127.5	2124.4	2116.3
45°	2433.6	2430.4	2425.9	2403.9	2385.1	2370.1	2373.3	2368.8	2369.4	2364.4	2358.1
47.5°	2733.9	2744.6	2726.3	2715.6	2694.3	2683.5	2692.4	2684.9	2699.3	2673.0	2660.3
50°	3025.4	3033.0	3026.7	3011.6	3011.6	3026.6	3037.3	3051.2	3071.3	3041.0	2995.9
52.5°	3264.2	3270.5	3279.9	3292.4	3323.2	3355.3	3400.4	3448.9	3487.3	3481.6	3430.1
55°	3409.9	3417.4	3433.2	3476.6	3531.8	3616.1	3718.4	3830.9	3918.9	3961.7	3923.9
57.5°	3458.9	3464.7	3507.4	3559.5	3645.6	3770.6	3942.2	4136.3	4305.3	4412.7	4395.9
60°	3447.7	3447.7	3491.0	3562.6	3683.2	3849.1	4091.7	4360.6	4619.5	4780.3	4756.5
62.5°	3328.9	3335.1	3397.3	3483.5	3629.2	3827.8	4116.8	4460.5	4770.3	4970.2	4950.6
65°	3068.8	3073.2	3140.3	3242.8	3405.6	3640.6	3956.6	4337.3	4692.3	4884.6	4848.2
67.5°	2648.4	2652.8	2707.5	2823.1	2995.2	3240.8	3582.2	4001.2	4348.6	4500.7	4391.4
70°	2106.7	2119.4	2154.6	2277.1	2407.7	2648.4	2962.6	3381.7	3709.6	3853.5	3732.8
72.5°	1435.8	1467.8	1510.5	1619.3	1744.2	1944.0	2194.2	2547.3	2810.6	2977.0	2869.6
75°	808.7	853.9	867.2	949.4	1052.4	1210.2	1393.0	1646.2	1911.9	2047.0	1917.7
77.5°	349.3	386.4	402.8	441.0	521.5	587.5	698.7	869.6	1075.0	1169.9	1014.7
80°	172.2	180.9	187.9	199.8	222.5	243.7	296.6	371.4	455.5	476.9	379.5
82.5°	133.3	139.5	151.5	160.8	166.4	172.2	177.2	187.2	195.4	199.8	188.5
85°	93.7	101.8	115.0	125.6	132.0	136.4	140.7	143.9	136.4	124.4	130.7
87.5°	24.5	32.1	44.6	48.4	54.7	57.8	56.6	58.4	52.8	38.3	42.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147204

CATALOG NUMBER: VXS-F05-LED-E1-5MQ-7030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	806.7	806.7	806.7	806.7	806.7	806.7	806.7	806.7
2.5°	811.2	810.6	811.2	811.2	811.2	810.6	810.6	810.6
5°	825.6	825.7	826.2	825.1	825.1	825.6	825.1	824.4
7.5°	850.2	849.5	849.5	848.9	849.5	848.9	848.9	848.3
10°	882.8	881.6	882.2	880.2	880.3	879.6	879.6	879.7
12.5°	917.9	916.1	916.7	914.8	911.7	912.3	913.0	912.3
15°	951.9	950.1	948.2	946.9	945.1	945.7	945.7	945.0
17.5°	986.5	982.7	982.1	980.2	979.5	979.6	979.5	980.2
20°	1022.3	1019.7	1019.2	1017.2	1016.6	1018.5	1019.1	1017.9
22.5°	1060.6	1059.3	1060.6	1059.3	1061.2	1062.5	1063.2	1061.9
25°	1109.0	1107.8	1109.6	1114.1	1116.6	1117.8	1121.0	1119.7
27.5°	1171.2	1169.9	1174.3	1180.6	1184.5	1190.7	1193.9	1195.1
30°	1251.6	1257.2	1259.8	1272.3	1274.8	1284.9	1284.9	1289.3
32.5°	1368.5	1379.2	1398.0	1417.5	1444.6	1464.0	1464.0	1474.1
35°	1624.8	1629.2	1643.7	1646.8	1652.4	1658.8	1652.4	1657.5
37.5°	1821.6	1802.1	1788.2	1768.7	1756.8	1756.8	1758.0	1756.8
40°	1922.1	1914.5	1908.2	1891.9	1889.3	1888.7	1888.7	1891.3
42.5°	2101.8	2083.5	2073.5	2059.7	2055.3	2054.0	2053.4	2054.6
45°	2335.5	2306.0	2279.0	2265.2	2253.2	2241.9	2245.6	2245.6
47.5°	2607.6	2561.7	2517.7	2493.9	2473.1	2463.6	2457.4	2455.5
50°	2938.7	2874.6	2818.0	2773.5	2743.2	2742.6	2745.7	2725.7
52.5°	3344.6	3243.4	3173.1	3112.7	3084.5	3081.3	3071.3	3060.0
55°	3794.4	3674.5	3558.2	3493.5	3456.4	3436.3	3424.4	3405.5
57.5°	4258.1	4096.7	3929.5	3825.9	3760.5	3715.3	3691.4	3680.7
60°	4615.8	4395.1	4174.6	4008.1	3899.5	3832.1	3790.7	3773.8
62.5°	4756.5	4457.4	4174.6	3955.9	3799.0	3705.9	3649.9	3625.5
65°	4588.7	4234.3	3912.5	3671.3	3496.0	3392.3	3331.4	3305.0
67.5°	4120.0	3807.0	3457.0	3217.0	3036.7	2934.3	2868.4	2848.8
70°	3453.9	3134.1	2799.8	2585.5	2424.7	2341.1	2272.6	2264.5
72.5°	2595.6	2319.8	2033.3	1856.2	1726.6	1588.4	1553.2	1570.8
75°	1663.8	1405.6	1150.5	990.9	872.7	740.7	689.9	702.5
77.5°	788.0	610.2	440.4	340.5	285.8	244.4	233.8	227.5
80°	292.2	236.9	209.2	198.5	191.1	184.1	179.1	173.4
82.5°	189.1	184.7	179.1	177.2	171.6	162.7	146.4	139.5
85°	141.3	141.3	133.9	134.5	130.1	118.8	103.6	95.5
87.5°	41.5	37.1	34.0	31.4	30.9	27.7	20.1	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)