

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P147724

Luminaire Tested: **VXS-F05-LED-E1-5WQ-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P147724
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-5WQ-7030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (35) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12002.8 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P147724

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 1.8 fc
Type V - Short - Semi-Cutoff

REPORT NUMBER: P147724

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P147724

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6001.4	0.0	6001.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6001.4	0.0	6001.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	12002.8	0.0	12002.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	0.5
10°-20°	221.0	1.8
20°-30°	447.5	3.7
30°-40°	750.3	6.3
40°-50°	1323.4	11.0
50°-60°	2333.9	19.4
60°-70°	3563.2	29.7
70°-80°	2977.4	24.8
80°-90°	323.5	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12002.8	100.0
0°-180°	12002.8	100.0

Coefficient of Utilization



REPORT NUMBER: P147724


CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	365.6	3.0			
FM	(30°-60°)	2203.8	18.4			
FH	(60°-80°)	3270.3	27.2			G2/5000
FVH	(80°-90°)	161.8	1.3			G2/225
BL	(0°-30°)	365.6	3.0	B1/500		
BM	(30°-60°)	2203.8	18.4	B2/2500		
BH	(60°-80°)	3270.3	27.2	B4/5000		G2/5000
BVH	(80°-90°)	161.8	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short



REPORT NUMBER: P147724

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	623.3	623.3	623.3	623.3	623.3	623.3	623.3	623.3	623.3	623.3	623.3
2.5°	628.3	629.5	628.3	628.3	628.3	628.3	628.3	627.0	627.0	627.0	628.3
5°	640.9	642.2	640.9	642.2	642.2	642.2	642.2	640.9	640.9	640.9	640.9
7.5°	661.0	661.0	661.0	662.3	661.0	661.0	662.3	661.0	661.0	661.0	661.0
10°	689.9	688.6	688.6	688.6	688.6	688.6	689.9	689.9	689.9	688.6	688.6
12.5°	725.1	723.8	725.1	725.1	726.3	726.3	726.3	726.3	726.3	726.3	725.1
15°	767.8	767.8	767.8	769.1	771.6	771.6	770.4	771.6	771.6	771.6	771.6
17.5°	815.5	818.1	815.5	816.8	818.1	816.8	819.4	820.6	821.9	820.6	816.8
20°	864.6	865.8	865.8	865.8	865.8	868.4	869.6	869.6	873.4	872.1	870.9
22.5°	911.1	913.6	913.6	914.8	914.8	918.7	918.7	918.7	921.1	923.6	921.1
25°	960.1	958.9	958.9	961.3	962.6	967.7	967.7	970.2	973.9	975.1	972.6
27.5°	1004.0	1002.8	1002.8	1006.6	1007.9	1014.1	1014.1	1019.2	1021.7	1022.9	1020.4
30°	1050.6	1050.6	1049.3	1053.1	1056.9	1061.9	1064.4	1069.4	1073.2	1074.4	1071.9
32.5°	1105.9	1103.3	1104.6	1107.2	1109.6	1114.6	1118.4	1124.7	1129.7	1131.0	1128.5
35°	1168.7	1164.9	1166.2	1168.7	1172.4	1180.0	1186.3	1190.1	1197.6	1200.1	1195.1
37.5°	1237.8	1239.1	1237.8	1244.0	1250.4	1259.2	1266.7	1271.7	1279.3	1283.0	1279.3
40°	1335.9	1332.0	1335.9	1342.1	1352.1	1363.5	1378.5	1382.3	1389.8	1397.4	1388.6
42.5°	1462.8	1460.2	1469.0	1474.1	1485.4	1497.9	1516.8	1526.8	1538.1	1543.2	1535.6
45°	1628.6	1628.6	1638.7	1639.9	1657.5	1673.9	1700.2	1712.8	1734.2	1734.2	1734.2
47.5°	1812.1	1819.7	1825.9	1838.4	1851.1	1881.2	1907.6	1935.2	1955.3	1957.8	1954.1
50°	2001.9	2009.4	2028.3	2045.8	2073.5	2111.2	2140.1	2176.5	2194.1	2209.2	2204.1
52.5°	2211.7	2213.0	2235.5	2258.2	2298.4	2339.9	2386.4	2424.0	2455.5	2469.3	2458.0
55°	2441.7	2444.1	2464.4	2488.2	2533.4	2581.1	2639.0	2677.9	2718.1	2743.3	2724.5
57.5°	2690.5	2691.7	2711.8	2740.7	2794.8	2842.6	2897.8	2953.2	2990.9	3013.5	3000.9
60°	2965.7	2972.0	2987.0	3023.5	3075.0	3125.3	3180.6	3229.6	3273.6	3297.5	3284.9
62.5°	3259.8	3266.0	3287.5	3316.3	3361.6	3416.9	3469.6	3532.4	3568.9	3595.3	3576.5
65°	3457.1	3468.4	3502.3	3541.2	3607.9	3679.5	3741.0	3826.5	3870.5	3901.9	3884.4
67.5°	3469.6	3476.0	3517.4	3576.5	3665.7	3773.8	3899.4	4032.6	4119.3	4160.8	4130.7
69°	3384.1	3393.0	3433.2	3499.8	3599.1	3724.8	3874.3	4040.1	4173.4	4234.9	4206.0
70°	3287.5	3306.2	3350.3	3423.1	3519.9	3651.8	3806.4	3983.6	4139.4	4223.6	4202.3
72.5°	3083.8	3088.8	3117.7	3175.5	3249.7	3359.1	3504.8	3671.9	3820.2	3940.8	3958.4
75°	2737.0	2753.4	2774.7	2813.7	2851.4	2930.6	3028.5	3142.9	3229.6	3322.6	3326.3
77.5°	2068.5	2117.5	2133.8	2142.6	2159.0	2221.8	2307.3	2406.5	2478.1	2493.2	2490.7
80°	928.7	994.0	1009.1	1080.7	1124.7	1229.0	1359.7	1511.7	1613.6	1624.9	1597.2
82.5°	182.2	194.8	227.5	284.0	387.0	448.6	534.1	640.9	739.0	795.4	761.6
85°	60.3	64.0	74.1	81.7	94.3	106.8	129.4	160.8	199.8	221.1	197.3
87.5°	23.8	23.8	27.7	30.2	32.6	32.6	32.6	30.2	28.9	23.8	21.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P147724

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	623.3	623.3	623.3	623.3	623.3	623.3	623.3	623.3
2.5°	627.0	627.0	627.0	627.0	627.0	627.0	627.0	627.0
5°	640.9	639.7	639.7	638.3	638.3	638.3	638.3	638.3
7.5°	659.8	658.4	657.2	658.4	657.2	657.2	657.2	657.2
10°	688.6	686.1	684.9	683.6	683.6	683.6	682.4	682.4
12.5°	722.6	722.6	721.3	720.1	717.5	718.8	717.5	715.0
15°	769.1	766.5	765.3	764.0	761.6	761.6	761.6	760.3
17.5°	815.5	813.1	813.1	809.3	808.0	808.0	808.0	809.3
20°	867.0	863.3	860.8	858.3	855.8	857.0	854.5	857.0
22.5°	918.7	913.6	911.1	907.3	903.5	903.5	902.3	899.8
25°	968.9	962.6	960.1	956.3	951.3	951.3	948.8	946.2
27.5°	1016.7	1010.4	1007.9	1000.3	995.2	994.0	991.5	990.3
30°	1069.4	1061.9	1058.1	1050.6	1043.0	1041.8	1038.0	1038.0
32.5°	1124.7	1117.2	1114.6	1103.3	1097.1	1097.1	1094.5	1092.0
35°	1193.8	1182.5	1180.0	1168.7	1159.9	1159.9	1157.4	1158.7
37.5°	1275.5	1266.7	1257.9	1249.1	1239.1	1237.8	1235.3	1232.7
40°	1384.9	1374.8	1364.8	1352.1	1343.3	1340.8	1337.1	1335.9
42.5°	1530.6	1520.5	1500.4	1490.4	1481.6	1474.1	1472.8	1471.5
45°	1716.6	1704.0	1690.2	1671.4	1660.0	1643.7	1641.2	1634.9
47.5°	1940.3	1916.4	1892.5	1876.2	1858.5	1839.8	1836.0	1825.9
50°	2177.8	2159.0	2118.8	2092.3	2064.7	2045.8	2033.3	2029.5
52.5°	2432.8	2397.7	2357.5	2322.3	2282.1	2257.0	2234.3	2228.1
55°	2699.3	2649.0	2598.8	2557.3	2517.1	2486.9	2465.6	2455.5
57.5°	2965.7	2910.5	2855.1	2809.8	2776.0	2737.0	2715.6	2710.6
60°	3243.4	3190.7	3134.1	3088.8	3047.4	3013.5	3000.9	2977.0
62.5°	3537.5	3482.2	3429.4	3385.4	3332.6	3308.8	3287.5	3273.6
65°	3826.5	3762.4	3695.9	3649.3	3596.6	3562.6	3536.3	3517.4
67.5°	4050.2	3953.5	3864.2	3786.3	3714.7	3661.9	3628.0	3610.4
69°	4113.1	3992.4	3878.0	3776.3	3692.0	3633.0	3595.3	3577.7
70°	4105.5	3972.3	3846.6	3734.8	3643.0	3580.2	3543.7	3511.1
72.5°	3873.1	3751.1	3611.6	3489.7	3406.8	3346.4	3310.1	3292.4
75°	3305.0	3223.3	3122.8	3028.5	2968.2	2933.1	2887.8	2889.0
77.5°	2406.5	2409.0	2341.1	2244.4	2176.5	2163.9	2143.8	2123.7
80°	1493.0	1373.6	1295.6	1191.3	1114.6	1048.1	1019.2	956.3
82.5°	688.6	537.8	417.2	315.4	242.5	189.7	165.9	135.8
85°	153.3	116.9	96.8	77.9	66.6	61.6	50.3	46.5
87.5°	21.3	18.9	17.6	16.4	13.8	10.1	7.6	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)