

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P148244

Luminaire Tested: **VXS-F05-LED-E1-5XQ-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P148244
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-5XQ-7030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (35) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11989.9 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U0 - G3

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P148244

CATALOG NUMBER: VXS-F05-LED-E1-5XQ-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 2.8 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148244

CATALOG NUMBER: VXS-F05-LED-E1-5XQ-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P148244

CATALOG NUMBER: VXS-F05-LED-E1-5XQ-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5995.0	0.0	5995.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5995.0	0.0	5995.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	11989.9	0.0	11989.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.3	0.9
10°-20°	320.3	2.7
20°-30°	536.3	4.5
30°-40°	817.6	6.8
40°-50°	1305.5	10.9
50°-60°	2007.3	16.7
60°-70°	2922.7	24.4
70°-80°	3292.4	27.5
80°-90°	679.7	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11989.9	100.0
0°-180°	11989.9	100.0

Coefficient of Utilization



REPORT NUMBER: P148244


CATALOG NUMBER: VXS-F05-LED-E1-5XQ-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	482.4	4.0			
FM	(30°-60°)	2065.2	17.2			
FH	(60°-80°)	3107.5	25.9			G2/5000
FVH	(80°-90°)	339.8	2.8			G3/500
BL	(0°-30°)	482.4	4.0	B1/500		
BM	(30°-60°)	2065.2	17.2	B2/2500		
BH	(60°-80°)	3107.5	25.9	B4/5000		G2/5000
BVH	(80°-90°)	339.8	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3

Type V Short



REPORT NUMBER: P148244

CATALOG NUMBER: VXS-F05-LED-E1-5XQ-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1
2.5°	1137.9	1138.5	1138.2	1137.6	1137.9	1137.6	1137.0	1136.7	1134.4	1135.8	1137.6
5°	1137.8	1137.2	1137.0	1136.6	1136.7	1137.6	1136.6	1135.8	1135.3	1136.1	1135.1
7.5°	1137.3	1136.0	1135.3	1135.0	1135.3	1135.6	1134.7	1133.5	1134.4	1133.5	1132.2
10°	1135.3	1134.4	1134.7	1133.5	1133.8	1133.5	1132.2	1131.3	1131.9	1131.0	1129.4
12.5°	1136.1	1134.4	1134.1	1133.5	1133.2	1132.8	1131.3	1129.7	1130.1	1129.4	1127.9
15°	1136.1	1135.0	1134.7	1133.5	1133.2	1132.5	1130.7	1130.1	1130.1	1129.1	1127.3
17.5°	1136.7	1136.1	1136.1	1134.5	1133.8	1133.5	1131.3	1130.4	1131.3	1129.4	1128.2
20°	1138.5	1137.9	1138.2	1137.3	1136.1	1136.0	1134.5	1133.8	1134.1	1133.8	1130.4
22.5°	1142.3	1142.3	1142.9	1142.6	1142.3	1142.6	1141.3	1141.3	1141.7	1141.7	1138.9
25°	1153.0	1152.6	1153.3	1153.3	1153.6	1155.9	1154.8	1154.6	1156.1	1156.1	1153.3
27.5°	1173.1	1172.4	1173.1	1173.7	1175.3	1178.1	1177.4	1178.4	1180.9	1180.3	1177.8
30°	1196.3	1195.8	1197.3	1199.2	1200.4	1204.8	1202.9	1207.7	1209.8	1211.7	1209.8
32.5°	1230.3	1230.3	1233.1	1234.3	1237.2	1241.6	1242.2	1246.0	1248.8	1251.9	1249.7
35°	1275.4	1274.9	1277.1	1279.3	1282.7	1286.8	1288.4	1293.5	1297.8	1300.0	1296.0
37.5°	1344.7	1341.1	1345.3	1346.5	1349.3	1350.3	1354.7	1360.9	1365.7	1365.1	1362.3
40°	1438.2	1437.6	1436.1	1434.2	1438.5	1440.1	1440.1	1448.6	1456.2	1454.9	1454.6
42.5°	1547.6	1544.8	1542.9	1542.9	1545.4	1546.0	1555.8	1562.1	1567.4	1568.6	1567.4
45°	1665.1	1662.3	1662.8	1661.6	1662.6	1666.6	1672.2	1683.9	1694.0	1694.3	1688.9
47.5°	1791.4	1782.6	1789.4	1779.7	1785.7	1788.8	1803.0	1819.9	1837.5	1840.6	1836.0
50°	1919.6	1918.7	1917.9	1916.1	1919.0	1925.8	1943.1	1969.8	1986.7	1998.1	1990.6
52.5°	2059.7	2054.9	2052.7	2049.6	2052.4	2065.9	2090.2	2113.4	2143.8	2156.7	2146.3
55°	2196.0	2194.4	2186.3	2185.9	2191.9	2213.0	2239.4	2268.0	2300.9	2315.4	2311.6
57.5°	2336.2	2327.0	2324.5	2320.7	2332.6	2352.4	2384.8	2436.4	2470.6	2486.9	2477.5
60°	2473.2	2466.1	2460.8	2459.6	2467.8	2495.4	2541.9	2603.7	2646.2	2667.6	2652.4
62.5°	2620.1	2615.8	2609.4	2602.3	2619.5	2655.0	2712.7	2781.3	2843.8	2870.3	2847.3
65°	2803.0	2793.9	2786.9	2777.8	2791.9	2836.6	2909.2	3005.6	3089.5	3120.2	3103.9
67.5°	2995.9	2987.4	2988.0	2982.4	3007.5	3069.4	3163.0	3294.0	3406.4	3459.0	3428.2
70°	3164.2	3168.9	3170.2	3193.2	3236.5	3330.8	3486.6	3691.7	3862.4	3942.5	3909.4
71°	3114.6	3125.0	3141.0	3164.9	3239.7	3351.2	3563.9	3812.4	4016.0	4151.7	4106.1
72.5°	2973.9	2980.2	2988.3	3024.8	3109.3	3257.0	3476.0	3759.9	4021.6	4197.2	4144.5
75°	2770.4	2776.3	2779.1	2804.6	2881.6	3010.4	3210.8	3462.7	3693.7	3843.1	3828.4
77.5°	2463.0	2464.0	2486.0	2525.3	2611.6	2759.0	2970.2	3231.5	3448.5	3564.9	3491.0
80°	1768.7	1756.8	1779.5	1830.1	1936.8	2105.9	2322.1	2620.4	2861.3	2970.1	2855.8
82.5°	673.0	709.4	766.8	850.5	886.6	1074.4	1276.2	1451.4	1654.4	1881.2	1824.4
85°	72.3	81.3	102.1	126.6	159.9	221.1	305.7	417.2	514.2	604.5	536.6
87.5°	27.0	27.7	30.8	35.4	36.2	37.7	40.2	46.8	43.6	37.7	30.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P148244

CATALOG NUMBER: VXS-F05-LED-E1-5XQ-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1
2.5°	1136.1	1136.4	1136.1	1136.4	1136.4	1135.1	1135.3	1134.7
5°	1135.6	1134.7	1135.1	1135.3	1135.1	1135.8	1134.8	1135.3
7.5°	1134.1	1132.2	1132.8	1132.8	1132.2	1133.3	1132.5	1132.2
10°	1131.0	1128.5	1129.7	1129.1	1128.8	1129.1	1129.1	1129.1
12.5°	1128.2	1126.6	1126.8	1126.6	1126.2	1127.3	1126.8	1127.3
15°	1127.6	1125.0	1124.8	1124.1	1124.4	1125.0	1125.0	1126.0
17.5°	1126.9	1123.7	1123.5	1122.8	1123.1	1124.4	1124.8	1124.1
20°	1128.8	1126.2	1125.7	1125.0	1124.8	1126.3	1126.0	1126.0
22.5°	1137.6	1134.4	1134.1	1131.6	1130.7	1131.6	1131.0	1131.0
25°	1151.7	1148.0	1146.6	1143.2	1140.7	1140.7	1139.8	1139.2
27.5°	1177.2	1171.5	1170.3	1167.5	1163.9	1164.6	1162.7	1162.5
30°	1206.7	1201.7	1197.3	1193.2	1189.1	1187.6	1185.4	1185.1
32.5°	1245.3	1239.7	1234.4	1229.3	1223.6	1221.5	1217.7	1215.8
35°	1292.8	1285.2	1279.0	1275.5	1269.8	1267.0	1264.6	1267.4
37.5°	1359.1	1349.9	1346.8	1342.8	1339.0	1334.6	1335.5	1334.5
40°	1450.8	1442.6	1439.5	1432.3	1431.3	1426.3	1429.4	1426.3
42.5°	1564.1	1549.1	1546.9	1541.3	1539.4	1536.6	1537.8	1535.6
45°	1687.7	1674.2	1671.6	1662.6	1662.9	1656.3	1658.8	1658.9
47.5°	1826.5	1812.4	1800.8	1794.2	1791.7	1787.6	1789.8	1789.4
50°	1969.7	1950.7	1937.8	1924.9	1919.3	1920.8	1916.4	1923.9
52.5°	2123.7	2095.1	2077.0	2064.7	2054.0	2056.3	2056.8	2059.1
55°	2283.1	2246.6	2220.2	2204.1	2194.4	2195.0	2197.9	2200.4
57.5°	2443.3	2397.7	2361.9	2338.0	2331.7	2334.5	2334.6	2334.3
60°	2609.4	2554.8	2508.6	2481.7	2475.9	2474.4	2486.6	2482.5
62.5°	2787.9	2722.3	2674.5	2639.9	2631.7	2637.4	2648.4	2645.9
65°	3024.5	2933.7	2872.1	2837.8	2824.0	2829.6	2844.5	2843.8
67.5°	3329.5	3202.6	3121.2	3077.2	3067.3	3074.1	3082.3	3090.2
70°	3785.7	3604.5	3488.2	3393.0	3352.1	3344.2	3352.4	3352.7
71°	3946.2	3737.9	3553.0	3436.7	3369.7	3341.5	3343.6	3329.5
72.5°	3939.7	3682.9	3466.5	3344.9	3251.9	3229.3	3218.2	3201.2
75°	3674.2	3442.9	3255.0	3122.5	3033.0	3006.2	2986.7	2985.8
77.5°	3332.0	3161.5	2954.4	2814.0	2705.0	2660.7	2640.8	2640.2
80°	2678.5	2423.2	2271.7	2187.2	2055.5	2017.5	1977.4	1962.3
82.5°	1619.9	1265.7	1029.2	914.5	851.1	700.9	629.0	595.0
85°	377.3	268.0	184.8	121.2	87.4	69.4	53.4	47.2
87.5°	25.5	20.1	17.9	14.4	11.0	10.7	6.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)