

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P155454

Luminaire Tested: **VXS-F05-LED-E1-T3-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P155454
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-T3-7030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 3
Light Source: (35) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11626.3 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P155454

CATALOG NUMBER: VXS-F05-LED-E1-T3-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 3.1 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155454

CATALOG NUMBER: VXS-F05-LED-E1-T3-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P155454

CATALOG NUMBER: VXS-F05-LED-E1-T3-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4014.9	0.0	4014.9
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	7611.4	0.0	7611.4
	% Fixture	65.5	0.0	65.5
Total	Lumens	11626.3	0.0	11626.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.0	1.0
10°-20°	354.1	3.0
20°-30°	608.7	5.2
30°-40°	988.3	8.5
40°-50°	1650.0	14.2
50°-60°	2598.1	22.3
60°-70°	3542.8	30.5
70°-80°	1533.7	13.2
80°-90°	230.6	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11626.3	100.0
0°-180°	11626.3	100.0

Coefficient of Utilization



REPORT NUMBER: P155454


CATALOG NUMBER: VXS-F05-LED-E1-T3-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	543.9	4.7			
FM	(30°-60°)	3246.8	27.9			
FH	(60°-80°)	3631.3	31.2			G2/5000
FVH	(80°-90°)	189.4	1.6			G2/225
BL	(0°-30°)	538.9	4.6	B2/1000		
BM	(30°-60°)	1989.5	17.1	B2/2500		
BH	(60°-80°)	1445.2	12.4	B3/2500		G3/2500
BVH	(80°-90°)	41.3	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type III Short



REPORT NUMBER: P155454

CATALOG NUMBER: VXS-F05-LED-E1-T3-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8
2.5°	1257.9	1262.9	1257.9	1259.2	1260.4	1259.2	1257.9	1257.9	1254.1	1256.7	1259.2
5°	1252.8	1256.7	1255.4	1256.7	1257.9	1256.7	1255.4	1256.7	1254.1	1255.4	1259.2
7.5°	1246.6	1245.4	1246.6	1249.1	1251.6	1251.6	1251.6	1252.8	1251.6	1251.6	1255.4
10°	1227.8	1229.0	1231.5	1235.3	1236.6	1240.3	1240.3	1244.0	1245.4	1247.9	1252.8
12.5°	1203.8	1205.2	1207.7	1210.2	1216.5	1222.7	1222.7	1231.5	1235.3	1241.6	1250.4
15°	1186.3	1187.6	1190.1	1192.5	1197.6	1203.8	1207.7	1217.7	1223.9	1235.3	1247.9
17.5°	1196.4	1195.1	1197.6	1198.9	1198.9	1203.8	1203.8	1211.4	1219.0	1229.0	1245.4
20°	1225.3	1225.3	1227.8	1227.8	1226.5	1229.0	1223.9	1223.9	1225.3	1230.3	1241.6
22.5°	1254.1	1252.8	1257.9	1260.4	1261.7	1265.5	1260.4	1259.2	1252.8	1249.1	1252.8
25°	1281.8	1280.5	1286.8	1290.6	1296.9	1300.6	1300.6	1300.6	1295.6	1289.3	1285.6
27.5°	1324.6	1324.6	1330.8	1334.6	1339.6	1347.2	1350.9	1350.9	1352.1	1343.3	1337.1
30°	1396.2	1397.4	1398.7	1403.7	1408.7	1411.2	1416.3	1420.0	1423.8	1418.8	1408.7
32.5°	1481.6	1474.1	1474.1	1481.6	1487.9	1495.4	1497.9	1503.0	1510.5	1506.7	1505.5
35°	1583.4	1580.8	1578.3	1580.8	1588.4	1597.2	1607.3	1616.1	1611.0	1618.5	1614.8
37.5°	1734.2	1736.7	1737.9	1737.9	1736.7	1739.2	1744.2	1753.1	1750.6	1753.1	1758.0
40°	1983.0	1974.2	1965.4	1966.6	1954.1	1956.6	1936.5	1945.3	1946.5	1937.7	1941.6
42.5°	2231.8	2236.9	2240.6	2250.7	2241.9	2236.9	2218.0	2218.0	2208.0	2199.2	2196.7
45°	2500.7	2510.8	2512.0	2532.1	2524.7	2540.9	2554.8	2551.0	2534.7	2533.4	2515.9
47.5°	2715.6	2732.0	2749.5	2773.5	2792.3	2828.7	2871.5	2892.8	2905.4	2915.4	2895.3
50°	2876.5	2884.0	2929.2	2966.9	3008.4	3068.7	3127.8	3204.5	3266.0	3294.9	3322.6
52.5°	2963.2	2982.1	3031.1	3090.2	3163.0	3253.5	3349.0	3470.9	3576.5	3646.8	3709.6
55°	2982.1	3000.9	3056.2	3131.6	3230.9	3352.7	3489.7	3655.6	3814.0	3949.6	4081.7
57.5°	2929.2	2950.7	3009.7	3096.4	3213.3	3361.6	3533.7	3751.1	3969.7	4189.7	4384.5
60°	2832.5	2858.9	2913.0	2998.3	3127.8	3294.9	3501.0	3773.8	4080.3	4417.1	4790.4
62.5°	2673.0	2700.5	2750.8	2845.1	2978.2	3163.0	3401.8	3741.0	4174.6	4704.9	5367.2
65°	2416.6	2429.1	2490.7	2586.2	2704.4	2907.9	3170.6	3580.2	4144.5	4882.1	5794.4
66°	2300.9	2322.3	2360.0	2436.7	2549.7	2740.7	3004.7	3420.6	4030.1	4820.5	5783.1
67.5°	2120.0	2136.3	2161.5	2213.0	2282.1	2422.8	2673.0	3066.2	3680.7	4508.9	5543.1
70°	1714.1	1721.7	1755.5	1773.2	1797.0	1843.5	1934.0	2160.2	2639.0	3416.9	4473.7
72.5°	1168.7	1190.1	1226.5	1276.8	1342.1	1405.0	1447.7	1476.6	1579.6	2038.3	2980.8
75°	857.0	879.7	926.1	992.7	1107.2	1237.8	1373.6	1436.4	1393.7	1334.6	1660.0
77.5°	497.6	527.8	566.7	630.9	736.4	909.8	1142.3	1348.4	1487.9	1496.7	1421.2
80°	209.8	213.7	237.5	270.2	335.5	457.4	638.3	934.9	1244.0	1452.6	1501.7
82.5°	47.8	59.1	75.4	89.2	109.3	150.8	223.7	372.0	672.3	1054.3	1374.8
85°	17.6	17.6	23.8	35.2	40.2	45.3	59.1	94.3	160.8	296.6	618.2
87.5°	0.0	1.2	2.5	2.5	5.1	6.3	10.1	13.8	12.5	11.3	37.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P155454

CATALOG NUMBER: VXS-F05-LED-E1-T3-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8
2.5°	1256.7	1255.4	1252.8	1252.8	1252.8	1252.8	1250.4	1251.6	1249.1	1250.4	1250.4
5°	1255.4	1255.4	1254.1	1251.6	1252.8	1252.8	1254.1	1251.6	1251.6	1252.8	1251.6
7.5°	1255.4	1254.1	1254.1	1254.1	1255.4	1254.1	1255.4	1255.4	1255.4	1256.7	1256.7
10°	1255.4	1255.4	1257.9	1259.2	1259.2	1260.4	1264.1	1264.1	1265.5	1266.7	1269.2
12.5°	1256.7	1261.7	1265.5	1269.2	1270.5	1273.0	1279.3	1279.3	1281.8	1285.6	1286.8
15°	1257.9	1265.5	1273.0	1275.5	1278.0	1283.0	1289.3	1291.8	1295.6	1299.4	1301.9
17.5°	1256.7	1266.7	1275.5	1279.3	1283.0	1289.3	1296.9	1299.4	1304.5	1309.4	1314.5
20°	1255.4	1269.2	1283.0	1288.1	1293.1	1301.9	1311.9	1318.2	1323.2	1330.8	1335.9
22.5°	1262.9	1279.3	1298.1	1305.7	1314.5	1325.8	1339.6	1347.2	1353.4	1360.9	1364.8
25°	1286.8	1299.4	1322.0	1334.6	1345.9	1364.8	1383.6	1392.3	1399.9	1406.2	1407.5
27.5°	1327.0	1330.8	1358.4	1374.8	1391.1	1421.2	1443.9	1450.2	1464.0	1469.0	1467.8
30°	1392.3	1386.1	1408.7	1433.9	1457.7	1499.2	1526.8	1543.2	1555.8	1555.8	1545.7
32.5°	1486.6	1476.6	1482.9	1511.7	1539.4	1599.7	1632.4	1653.8	1662.6	1660.0	1638.7
35°	1609.7	1603.5	1599.7	1622.4	1666.3	1736.7	1779.4	1790.8	1804.6	1802.1	1774.4
37.5°	1755.5	1750.6	1750.6	1776.9	1819.7	1923.9	1970.5	1977.9	1976.7	1956.6	1905.1
40°	1927.7	1925.2	1913.9	1929.0	1965.4	2101.1	2163.9	2174.0	2160.2	2127.6	2067.2
42.5°	2175.2	2160.2	2125.0	2133.8	2161.5	2293.4	2375.1	2402.7	2388.9	2356.3	2258.2
45°	2498.2	2481.9	2422.8	2415.3	2430.4	2546.0	2651.5	2657.8	2655.3	2613.9	2498.2
47.5°	2877.7	2852.6	2789.7	2769.6	2764.7	2871.5	2973.3	2983.3	2977.0	2915.4	2760.8
50°	3288.7	3252.2	3210.8	3196.9	3176.8	3253.5	3356.5	3357.8	3332.6	3247.2	3102.7
52.5°	3727.3	3714.7	3707.2	3693.3	3684.6	3751.1	3814.0	3776.3	3738.5	3649.3	3523.6
55°	4169.5	4221.1	4273.9	4279.0	4294.0	4365.6	4364.4	4261.3	4233.7	4184.7	4060.2
57.5°	4639.6	4830.6	4996.5	5048.0	5098.2	5231.5	5218.9	5117.1	5081.9	5021.6	4918.5
60°	5279.2	5794.4	6273.3	6387.6	6466.7	6626.3	6611.3	6454.2	6527.0	6522.1	6388.8
62.5°	6175.2	7032.2	7749.8	7925.7	7981.0	7998.7	7903.1	7733.5	7805.1	7885.5	7475.9
65°	6782.2	7790.1	8526.4	8662.2	8669.6	8459.8	8247.5	8047.7	8030.1	7960.9	7375.3
66°	6796.0	7827.7	8566.6	8698.5	8652.1	8365.6	8096.7	7895.5	7808.8	7656.8	7049.8
67.5°	6552.2	7592.7	8388.2	8527.7	8425.9	8020.0	7649.2	7390.4	7220.7	6974.4	6439.1
70°	5502.9	6534.6	7514.8	7774.9	7807.6	7201.9	6687.9	6383.8	6155.1	5817.1	5355.9
72.5°	4091.7	5024.1	5888.7	6137.5	6264.5	5780.6	5347.0	5115.9	4802.9	4447.3	4119.3
75°	2564.9	3223.3	3802.6	3977.3	3857.9	3483.4	3223.3	3126.5	2818.7	2606.3	2456.8
77.5°	1466.5	1672.6	1719.1	1652.5	1511.7	1157.4	823.1	609.4	529.0	585.6	645.9
80°	1431.3	1311.9	1045.5	919.9	833.2	573.1	336.8	231.2	192.2	197.3	213.7
82.5°	1550.7	1663.8	1369.7	1117.2	937.5	633.4	349.3	186.0	125.7	148.3	167.2
85°	1007.9	1402.4	1262.9	1064.4	862.1	541.7	287.8	96.8	64.0	84.1	115.6
87.5°	101.8	111.8	95.5	129.4	96.8	45.3	22.6	13.8	12.5	15.1	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P155454

CATALOG NUMBER: VXS-F05-LED-E1-T3-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8	1252.8
2.5°	1251.6	1251.6	1252.8	1254.1	1255.4	1256.7	1256.7	1256.7	1256.7	1259.2	1257.9
5°	1254.1	1256.7	1259.2	1260.4	1262.9	1262.9	1266.7	1265.5	1265.5	1269.2	1270.5
7.5°	1259.2	1262.9	1268.0	1266.7	1271.7	1270.5	1273.0	1273.0	1269.2	1270.5	1268.0
10°	1270.5	1275.5	1278.0	1274.3	1275.5	1270.5	1269.2	1262.9	1255.4	1251.6	1246.6
12.5°	1289.3	1294.4	1294.4	1288.1	1280.5	1269.2	1260.4	1246.6	1235.3	1229.0	1222.7
15°	1305.7	1310.7	1309.4	1299.4	1288.1	1270.5	1257.9	1241.6	1225.3	1215.2	1208.9
17.5°	1318.2	1320.7	1317.0	1303.1	1290.6	1274.3	1261.7	1244.0	1225.3	1212.6	1201.3
20°	1337.1	1334.6	1325.8	1308.2	1294.4	1279.3	1269.2	1254.1	1232.7	1216.5	1200.1
22.5°	1364.8	1354.7	1338.3	1319.5	1305.7	1291.8	1281.8	1265.5	1244.0	1223.9	1205.2
25°	1401.1	1381.0	1358.4	1338.3	1325.8	1310.7	1299.4	1281.8	1259.2	1236.6	1213.9
27.5°	1454.0	1418.8	1389.8	1372.2	1358.4	1339.6	1325.8	1303.1	1279.3	1252.8	1227.8
30°	1513.1	1465.3	1437.6	1423.8	1408.7	1388.6	1367.3	1338.3	1310.7	1281.8	1251.6
32.5°	1589.6	1531.8	1505.5	1491.6	1471.5	1446.4	1421.2	1388.6	1349.6	1311.9	1275.5
35°	1690.2	1631.1	1603.5	1582.2	1554.5	1521.8	1485.4	1441.3	1388.6	1338.3	1291.8
37.5°	1798.2	1734.2	1707.8	1685.2	1643.7	1600.9	1549.4	1485.4	1413.8	1347.2	1289.3
40°	1935.2	1876.2	1842.3	1803.3	1754.3	1680.1	1599.7	1506.7	1415.0	1333.3	1265.5
42.5°	2108.7	2049.6	1999.4	1937.7	1852.3	1737.9	1623.6	1503.0	1392.3	1299.4	1226.5
45°	2338.7	2267.0	2180.3	2072.2	1934.0	1774.4	1624.9	1479.1	1349.6	1246.6	1168.7
47.5°	2620.1	2510.8	2368.8	2186.6	1988.0	1784.5	1604.8	1431.3	1283.0	1171.2	1084.5
50°	2954.4	2782.3	2548.5	2280.8	2015.6	1769.3	1554.5	1359.7	1188.8	1069.4	966.3
52.5°	3336.4	3054.9	2710.6	2348.7	2014.4	1719.1	1469.0	1251.6	1065.6	932.4	834.4
55°	3785.1	3366.6	2877.7	2399.0	1979.3	1626.1	1338.3	1099.6	913.6	790.5	700.0
57.5°	4442.3	3871.7	3169.3	2476.9	1908.9	1482.9	1161.1	917.4	754.0	637.1	560.5
60°	5643.6	4714.9	3694.6	2634.0	1800.8	1273.0	953.8	722.6	585.6	491.4	439.8
62.5°	6548.4	5367.2	3978.5	2598.8	1583.4	1014.1	707.5	526.5	431.0	366.9	334.3
65°	6419.0	5164.9	3675.8	2238.1	1241.6	715.0	469.9	358.1	296.6	266.4	247.6
66°	6126.2	4900.9	3413.1	2014.4	1073.2	594.4	387.0	300.3	255.1	233.8	221.1
67.5°	5570.8	4410.9	2943.1	1651.3	824.4	431.0	291.5	237.5	207.4	198.5	189.7
70°	4630.8	3517.4	2065.9	961.3	420.9	240.0	184.8	165.9	158.3	157.1	154.6
72.5°	3548.8	2489.4	1216.5	454.9	218.7	159.6	143.2	137.0	134.5	134.5	135.8
75°	2175.2	1398.7	537.8	222.4	153.3	134.5	126.9	124.5	123.1	124.5	123.1
77.5°	726.3	444.9	229.9	168.4	139.5	124.5	119.4	116.9	116.9	116.9	116.9
80°	222.4	193.6	176.0	155.9	131.9	118.1	110.6	109.3	110.6	111.8	108.1
82.5°	167.2	158.3	148.3	138.2	119.4	105.6	103.0	103.0	103.0	99.3	94.3
85°	123.1	121.9	100.5	94.3	88.0	88.0	88.0	88.0	84.1	77.9	72.8
87.5°	22.6	21.3	22.6	23.8	35.2	37.7	37.7	40.2	43.9	41.5	41.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P155454

CATALOG NUMBER: VXS-F05-LED-E1-T3-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1252.8	1252.8	1252.8	1252.8	1252.8
2.5°	1257.9	1256.7	1260.4	1257.9	1259.2
5°	1269.2	1268.0	1270.5	1268.0	1271.7
7.5°	1265.5	1262.9	1261.7	1262.9	1264.1
10°	1239.1	1236.6	1235.3	1234.0	1235.3
12.5°	1216.5	1211.4	1211.4	1208.9	1210.2
15°	1200.1	1196.4	1195.1	1192.5	1193.8
17.5°	1192.5	1186.3	1183.7	1181.2	1181.2
20°	1187.6	1180.0	1176.3	1173.7	1172.4
22.5°	1187.6	1176.3	1171.2	1168.7	1167.5
25°	1192.5	1178.8	1171.2	1167.5	1166.2
27.5°	1202.6	1185.1	1176.3	1171.2	1171.2
30°	1220.2	1197.6	1185.1	1178.8	1177.5
32.5°	1237.8	1207.7	1190.1	1182.5	1180.0
35°	1246.6	1207.7	1186.3	1173.7	1171.2
37.5°	1236.6	1191.3	1164.9	1146.1	1142.3
40°	1205.2	1157.4	1128.5	1110.9	1108.4
42.5°	1163.6	1117.2	1083.2	1070.7	1066.9
45°	1107.2	1051.8	1017.9	1000.3	1001.6
47.5°	1010.4	953.8	923.6	907.3	909.8
50°	896.0	840.7	814.3	796.7	800.5
52.5°	770.4	720.1	694.9	686.1	683.6
55°	638.3	599.4	581.9	571.8	568.0
57.5°	517.7	490.1	477.5	465.0	466.2
60°	408.4	394.6	390.8	377.0	375.8
62.5°	321.7	313.0	309.1	299.1	300.3
65°	243.8	241.2	243.8	237.5	240.0
66°	219.9	221.1	221.1	217.4	219.9
67.5°	189.7	192.2	196.1	192.2	194.8
70°	157.1	159.6	162.1	162.1	162.1
72.5°	137.0	139.5	140.7	140.7	140.7
75°	125.7	126.9	128.2	125.7	125.7
77.5°	118.1	118.1	115.6	114.4	113.1
80°	106.8	105.6	101.8	99.3	99.3
82.5°	89.2	86.7	84.1	80.4	80.4
85°	67.9	65.4	62.8	57.8	55.3
87.5°	35.2	36.5	35.2	28.9	25.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)