

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P156504

Luminaire Tested: **VXS-F06-LED-E1-T4-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P156504
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F06-LED-E1-T4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 4
Light Source: (42) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13671.6 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 156.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P156504

CATALOG NUMBER: VXS-F06-LED-E1-T4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 4.7 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156504

CATALOG NUMBER: VXS-F06-LED-E1-T4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P156504

CATALOG NUMBER: VXS-F06-LED-E1-T4-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2917.2	0.0	2917.2
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	10754.4	0.0	10754.4
	% Fixture	78.7	0.0	78.7
Total	Lumens	13671.6	0.0	13671.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.0	1.3
10°-20°	531.3	3.9
20°-30°	915.1	6.7
30°-40°	1384.5	10.1
40°-50°	1794.5	13.1
50°-60°	2474.1	18.1
60°-70°	3843.9	28.1
70°-80°	2235.3	16.3
80°-90°	317.9	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13671.6	100.0
0°-180°	13671.6	100.0

Coefficient of Utilization



REPORT NUMBER: P156504


CATALOG NUMBER: VXS-F06-LED-E1-T4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	840.5	6.1			
FM	(30°-60°)	4388.6	32.1			
FH	(60°-80°)	5281.3	38.6			G3/7500
FVH	(80°-90°)	243.9	1.8			G3/500
BL	(0°-30°)	780.9	5.7	B2/1000		
BM	(30°-60°)	1264.6	9.2	B2/2500		
BH	(60°-80°)	797.8	5.8	B2/1000		G2/1000
BVH	(80°-90°)	73.9	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P156504

CATALOG NUMBER: VXS-F06-LED-E1-T4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1
2.5°	1768.9	1774.9	1770.4	1771.9	1771.9	1773.4	1773.4	1774.9	1773.4	1777.9	1780.9
5°	1737.2	1740.2	1738.8	1741.8	1744.8	1750.8	1749.2	1756.8	1758.3	1762.8	1770.4
7.5°	1725.2	1722.1	1723.6	1728.2	1731.2	1734.2	1737.2	1743.2	1747.8	1758.3	1764.4
10°	1737.2	1735.6	1737.2	1740.2	1740.2	1741.8	1738.8	1744.8	1747.8	1756.8	1762.8
12.5°	1786.9	1786.9	1783.9	1783.9	1780.9	1777.9	1770.4	1765.8	1764.4	1765.8	1768.9
15°	1866.8	1863.8	1857.8	1853.3	1847.3	1836.7	1826.2	1817.1	1811.1	1802.1	1799.1
17.5°	1945.3	1940.8	1934.7	1928.7	1921.1	1910.6	1894.0	1883.5	1866.8	1856.4	1850.3
20°	2035.8	2026.7	2019.2	2011.6	1996.6	1993.6	1977.0	1958.9	1939.3	1915.1	1912.1
22.5°	2153.4	2138.3	2129.3	2124.8	2109.6	2105.2	2078.0	2052.3	2028.3	1996.6	1989.0
25°	2272.5	2257.4	2253.0	2246.9	2236.4	2230.4	2204.7	2176.1	2144.4	2100.6	2091.6
27.5°	2388.6	2390.2	2378.1	2382.6	2379.6	2369.0	2343.4	2314.7	2290.7	2239.4	2228.8
30°	2533.4	2524.4	2518.3	2527.4	2516.8	2518.3	2495.8	2480.6	2441.5	2411.3	2390.2
32.5°	2684.2	2682.7	2691.7	2697.8	2696.3	2693.3	2675.1	2660.1	2625.4	2581.7	2572.6
35°	2890.8	2899.9	2907.4	2934.5	2934.5	2954.2	2936.1	2917.9	2877.2	2824.5	2806.3
37.5°	3031.1	3034.1	3064.2	3100.4	3145.7	3187.9	3200.0	3204.5	3187.9	3148.7	3121.6
40°	3159.3	3165.3	3213.5	3269.3	3335.6	3418.7	3468.4	3491.0	3495.5	3477.4	3418.7
42.5°	3287.5	3296.5	3346.2	3427.7	3519.7	3625.2	3712.6	3768.5	3800.1	3800.1	3765.5
45°	3436.7	3448.8	3503.0	3592.0	3699.1	3831.8	3952.4	4059.5	4110.8	4113.8	4080.6
47.5°	3613.2	3623.7	3687.0	3777.5	3887.6	4021.8	4174.1	4296.3	4391.3	4397.3	4370.2
50°	3840.8	3856.0	3908.7	3990.2	4103.2	4239.0	4391.3	4561.7	4661.1	4685.3	4656.7
52.5°	4142.5	4145.5	4189.2	4264.6	4374.7	4504.4	4665.7	4851.2	4982.4	5002.0	4955.2
55°	4558.7	4554.1	4582.8	4664.2	4747.2	4848.2	5015.5	5223.6	5369.9	5400.1	5351.8
57.5°	5124.1	5119.6	5143.7	5163.3	5318.7	5416.7	5581.0	5780.1	5921.9	6009.3	5926.4
60°	6000.3	5995.8	6034.9	6149.5	6265.7	6408.9	6568.8	6807.0	7006.1	7031.7	6950.4
62.5°	6635.1	6657.7	6743.7	6877.9	7113.2	7393.7	7686.2	7999.9	8408.5	8538.2	8499.0
65°	6413.5	6458.8	6577.8	6781.5	7095.1	7482.6	7941.0	8509.5	9057.0	9363.1	9354.1
66°	6214.4	6264.1	6410.5	6606.5	6938.2	7362.0	7862.7	8482.4	9094.7	9432.4	9453.6
67.5°	5852.5	5908.3	6051.5	6283.7	6606.5	7057.4	7595.8	8269.8	8962.0	9355.5	9411.3
70°	5148.3	5211.6	5315.6	5507.2	5825.4	6228.0	6795.0	7398.1	8123.5	8574.4	8642.3
72.5°	4303.8	4359.6	4475.8	4632.5	4893.4	5146.7	5591.6	6036.5	6555.2	7069.4	7019.7
75°	3089.8	3114.0	3183.3	3353.8	3494.0	3721.8	4079.1	4444.0	4798.4	5033.7	5066.8
77.5°	1606.0	1669.3	1767.4	1955.9	2108.2	2313.3	2545.5	2819.9	3079.3	3294.9	3236.2
80°	1051.1	1078.2	1165.7	1262.2	1373.8	1505.0	1660.3	1762.8	1796.1	1782.5	1796.1
82.5°	606.2	656.0	772.1	846.0	928.9	974.2	1097.8	1215.4	1281.8	1198.9	1168.7
85°	76.9	99.5	313.7	395.1	452.4	520.2	557.9	628.8	586.6	524.8	639.4
87.5°	16.6	15.1	21.1	45.3	46.7	39.2	73.9	78.4	48.3	24.1	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156504

CATALOG NUMBER: VXS-F06-LED-E1-T4-7030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1
2.5°	1783.9	1785.5	1788.5	1793.0	1796.1	1799.1	1802.1	1806.5	1809.5	1812.6	1818.7
5°	1776.4	1782.5	1788.5	1794.5	1802.1	1814.1	1821.7	1827.7	1833.7	1845.8	1850.3
7.5°	1771.9	1782.5	1791.5	1802.1	1814.1	1824.7	1838.2	1845.8	1854.8	1862.4	1871.4
10°	1768.9	1783.9	1793.0	1808.1	1821.7	1832.2	1847.3	1856.4	1866.8	1876.0	1880.4
12.5°	1774.9	1782.5	1791.5	1806.5	1823.1	1838.2	1854.8	1862.4	1871.4	1879.0	1880.4
15°	1800.5	1800.5	1802.1	1814.1	1830.7	1842.8	1856.4	1863.8	1868.4	1873.0	1873.0
17.5°	1847.3	1836.7	1829.2	1830.7	1841.2	1848.8	1856.4	1856.4	1853.3	1851.8	1848.8
20°	1901.6	1888.0	1873.0	1862.4	1859.4	1853.3	1848.8	1833.7	1821.7	1811.1	1803.5
22.5°	1980.0	1958.9	1937.7	1918.1	1900.1	1877.4	1851.8	1821.7	1793.0	1773.4	1761.3
25°	2076.5	2059.9	2034.3	2004.1	1981.5	1939.3	1906.1	1862.4	1826.2	1800.5	1779.4
27.5°	2213.7	2194.1	2169.9	2142.8	2109.6	2062.9	2022.2	1971.0	1927.3	1889.5	1862.4
30°	2384.1	2358.4	2340.4	2307.3	2284.6	2231.8	2191.1	2127.8	2043.3	1983.0	1945.3
32.5°	2559.1	2530.4	2515.3	2489.6	2464.0	2432.3	2370.6	2272.5	2163.9	2065.9	2001.1
35°	2792.7	2762.6	2735.4	2712.8	2675.1	2616.4	2562.1	2444.5	2295.1	2157.9	2049.3
37.5°	3086.8	3037.1	2969.2	2911.9	2845.6	2761.1	2678.1	2557.5	2387.2	2209.2	2064.5
40°	3400.5	3313.1	3216.6	3109.4	2994.8	2872.7	2777.7	2655.5	2464.0	2253.0	2053.9
42.5°	3727.8	3589.0	3454.8	3304.0	3144.1	2999.4	2875.8	2741.6	2521.3	2265.0	2011.6
45°	4051.9	3896.7	3693.1	3495.5	3293.5	3114.0	2975.2	2824.5	2574.1	2269.5	1955.9
47.5°	4320.4	4160.5	3928.3	3681.0	3441.2	3237.6	3074.8	2911.9	2645.0	2301.1	1942.3
50°	4603.8	4409.3	4151.5	3859.0	3587.5	3359.8	3186.4	3017.5	2744.6	2382.6	1986.0
52.5°	4913.1	4689.8	4388.3	4061.0	3763.9	3509.1	3320.6	3147.2	2871.2	2497.2	2068.9
55°	5290.1	5017.1	4689.8	4320.4	4002.2	3720.2	3512.1	3307.0	3022.0	2633.0	2173.1
57.5°	5866.1	5531.3	5163.3	4742.6	4389.7	4056.5	3807.7	3570.9	3255.8	2835.0	2314.7
60°	6908.1	6550.7	6072.6	5563.0	5148.3	4759.2	4394.3	4100.2	3712.6	3233.2	2628.4
62.5°	8401.0	7926.0	7288.1	6574.8	6031.9	5471.0	5059.3	4622.0	4140.9	3623.7	2997.9
65°	9230.4	8654.3	7800.8	6973.0	6274.7	5665.5	5142.3	4635.5	4101.8	3607.2	3083.8
66°	9333.0	8732.7	7846.0	6974.4	6241.6	5615.8	5065.3	4540.5	3994.6	3522.7	3047.7
67.5°	9290.7	8677.0	7763.1	6843.2	6098.3	5425.7	4857.2	4312.8	3768.5	3328.1	2927.0
70°	8598.5	8016.5	7119.2	6228.0	5520.7	4857.2	4314.3	3779.0	3279.9	2902.9	2607.4
72.5°	7140.3	6642.7	5863.0	5163.3	4608.4	4061.0	3601.0	3089.8	2667.7	2388.6	2213.7
75°	5154.3	4852.7	4142.5	3741.3	3254.2	2890.8	2444.5	2141.3	1838.2	1702.5	1672.3
77.5°	3255.8	2850.1	2399.2	1975.4	1624.1	1346.6	1048.1	889.7	742.0	726.8	877.6
80°	1648.2	1483.8	1143.0	910.8	766.0	619.8	490.1	371.0	259.4	312.1	374.0
82.5°	1079.7	900.3	705.7	580.6	505.2	419.2	325.7	226.2	165.9	186.9	256.4
85°	583.6	497.6	401.1	316.7	256.4	229.2	153.8	108.6	107.0	114.6	146.3
87.5°	42.2	42.2	33.2	30.2	36.2	30.2	27.2	27.2	25.6	27.2	36.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156504

CATALOG NUMBER: VXS-F06-LED-E1-T4-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1	1802.1
2.5°	1821.7	1826.2	1827.7	1835.2	1839.8	1842.8	1845.8	1845.8	1847.3	1851.8	1853.3
5°	1856.4	1863.8	1873.0	1879.0	1882.0	1891.0	1894.0	1894.0	1897.1	1903.1	1907.6
7.5°	1877.4	1888.0	1897.1	1900.1	1906.1	1909.1	1913.7	1916.7	1916.7	1922.7	1925.7
10°	1885.0	1891.0	1900.1	1900.1	1906.1	1906.1	1910.6	1912.1	1912.1	1918.1	1922.7
12.5°	1885.0	1888.0	1895.5	1895.5	1900.1	1901.6	1907.6	1912.1	1913.7	1921.1	1927.3
15°	1876.0	1879.0	1885.0	1886.5	1897.1	1903.1	1916.7	1925.7	1925.7	1933.3	1936.3
17.5°	1850.3	1857.8	1869.9	1882.0	1901.6	1915.1	1931.7	1939.3	1933.3	1928.7	1924.1
20°	1808.1	1821.7	1850.3	1880.4	1915.1	1933.3	1942.3	1934.7	1913.7	1892.5	1879.0
22.5°	1765.8	1793.0	1841.2	1886.5	1925.7	1937.7	1933.3	1906.1	1871.4	1845.8	1827.7
25°	1785.5	1817.1	1863.8	1904.6	1930.3	1927.3	1909.1	1871.4	1833.7	1800.5	1770.4
27.5°	1866.8	1901.6	1927.3	1940.8	1937.7	1916.7	1888.0	1845.8	1800.5	1756.8	1714.6
30°	1943.8	1961.9	1967.9	1957.4	1933.3	1898.5	1862.4	1814.1	1753.8	1699.5	1651.3
32.5°	1978.4	1960.4	1931.7	1903.1	1863.8	1833.7	1783.9	1731.2	1655.8	1590.9	1542.7
35°	1978.4	1906.1	1833.7	1773.4	1714.6	1676.9	1619.6	1548.7	1479.4	1425.1	1387.4
37.5°	1934.7	1796.1	1676.9	1578.9	1505.0	1464.2	1378.3	1314.9	1256.2	1238.0	1213.9
40°	1854.8	1649.7	1477.8	1349.6	1256.2	1195.9	1109.8	1066.1	1043.5	1034.5	1029.9
42.5°	1747.8	1486.8	1257.6	1099.3	998.2	930.5	873.2	846.0	844.5	843.0	843.0
45°	1633.2	1311.9	1043.5	855.0	766.0	705.7	678.5	668.1	677.1	675.5	677.1
47.5°	1562.3	1179.3	847.5	646.9	579.1	539.9	526.3	530.8	538.3	535.3	535.3
50°	1553.3	1111.4	716.3	503.6	452.4	432.7	429.7	429.7	434.3	431.3	429.7
52.5°	1586.4	1100.8	648.4	432.7	392.1	375.4	372.4	371.0	369.4	360.4	352.8
55°	1643.7	1125.0	628.8	414.7	372.4	354.4	349.8	346.8	340.8	328.7	315.1
57.5°	1758.3	1200.3	646.9	423.7	378.5	363.4	358.9	358.9	346.8	327.3	307.7
60°	2034.3	1391.9	720.8	458.4	407.2	392.1	395.1	393.6	375.4	346.8	316.7
62.5°	2390.2	1642.2	817.3	506.6	443.3	440.3	455.4	452.4	422.3	378.5	334.8
65°	2554.5	1759.8	844.5	517.2	450.9	464.5	494.6	491.6	453.9	393.6	337.8
66°	2557.5	1759.8	832.4	508.2	440.3	456.9	487.0	485.6	447.9	387.6	331.7
67.5°	2495.8	1711.6	797.7	490.1	419.2	431.3	458.4	456.9	422.3	372.4	319.7
70°	2263.5	1532.1	708.7	458.4	390.6	384.6	393.6	387.6	365.0	330.3	294.1
72.5°	1939.3	1286.3	618.2	434.3	371.0	346.8	340.8	336.3	318.1	298.5	276.0
75°	1527.6	1017.9	542.9	416.2	352.8	321.2	310.7	304.7	292.5	279.0	260.9
77.5°	942.5	728.4	473.5	392.1	339.3	307.7	300.1	291.1	273.0	256.4	242.8
80°	420.7	450.9	389.0	342.3	303.1	274.4	262.4	248.8	230.7	220.2	212.6
82.5°	280.5	291.1	282.0	256.4	229.2	206.6	188.5	188.5	185.5	176.5	173.4
85°	179.5	180.9	174.9	158.3	147.8	134.2	126.6	128.2	134.2	132.7	131.2
87.5°	40.7	40.7	48.3	45.3	52.7	55.8	60.3	64.9	73.9	73.9	78.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156504

CATALOG NUMBER: VXS-F06-LED-E1-T4-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1802.1	1802.1	1802.1	1802.1	1802.1
2.5°	1854.8	1857.8	1860.8	1856.4	1857.8
5°	1907.6	1906.1	1913.7	1909.1	1912.1
7.5°	1924.1	1925.7	1931.7	1931.7	1933.3
10°	1925.7	1928.7	1936.3	1940.8	1943.8
12.5°	1933.3	1939.3	1951.3	1954.3	1954.3
15°	1939.3	1942.3	1949.8	1952.8	1955.9
17.5°	1918.1	1912.1	1915.1	1916.7	1915.1
20°	1865.4	1859.4	1857.8	1851.8	1854.8
22.5°	1808.1	1791.5	1780.9	1768.9	1768.9
25°	1738.8	1713.1	1691.9	1670.9	1675.3
27.5°	1673.9	1640.7	1619.6	1606.0	1603.0
30°	1610.6	1575.9	1556.3	1539.7	1539.7
32.5°	1505.0	1480.8	1455.2	1444.7	1443.1
35°	1358.7	1343.6	1322.5	1318.0	1310.5
37.5°	1194.3	1189.8	1171.7	1170.2	1162.7
40°	1022.4	1025.4	1019.4	1016.4	1011.8
42.5°	850.5	865.6	862.6	861.0	858.0
45°	686.1	696.7	698.2	702.7	710.3
47.5°	539.9	542.9	545.9	544.4	545.9
50°	422.3	414.7	413.2	408.7	413.2
52.5°	340.8	328.7	322.7	316.7	313.7
55°	300.1	288.0	282.0	279.0	276.0
57.5°	289.5	277.5	268.4	262.4	260.9
60°	292.5	274.4	262.4	254.8	253.4
62.5°	300.1	276.0	259.4	251.8	250.4
65°	298.5	273.0	257.8	248.8	247.4
66°	294.1	269.9	254.8	247.4	245.8
67.5°	286.5	265.4	251.8	245.8	242.8
70°	273.0	259.4	248.8	241.2	238.2
72.5°	260.9	250.4	241.2	233.8	232.2
75°	247.4	238.2	229.2	223.2	221.7
77.5°	230.7	221.7	215.6	211.1	209.6
80°	203.6	197.5	191.5	185.5	185.5
82.5°	168.9	164.4	158.3	153.8	152.3
85°	129.6	129.6	125.2	120.6	119.2
87.5°	76.9	75.4	75.4	70.9	70.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)