

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P147719

Luminaire Tested: **VXS-E05-LED-E1-5WQ-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P147719
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-5WQ-7030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (105) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14539.6 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2

Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P147719

CATALOG NUMBER: VXS-E05-LED-E1-5WQ-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 2.2 fc
Type V - Short - Semi-Cutoff

REPORT NUMBER: P147719

CATALOG NUMBER: VXS-E05-LED-E1-5WQ-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P147719

CATALOG NUMBER: VXS-E05-LED-E1-5WQ-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7269.8	0.0	7269.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	7269.8	0.0	7269.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	14539.6	0.0	14539.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	0.5
10°-20°	267.7	1.8
20°-30°	542.1	3.7
30°-40°	908.9	6.3
40°-50°	1603.2	11.0
50°-60°	2827.1	19.4
60°-70°	4316.2	29.7
70°-80°	3606.7	24.8
80°-90°	391.9	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14539.6	100.0
0°-180°	14539.6	100.0

Coefficient of Utilization



REPORT NUMBER: P147719


CATALOG NUMBER: VXS-E05-LED-E1-5WQ-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	442.8	3.0			
FM	(30°-60°)	2669.6	18.4			
FH	(60°-80°)	3961.4	27.2			G2/5000
FVH	(80°-90°)	196.0	1.3			G2/225
BL	(0°-30°)	442.8	3.0	B1/500		
BM	(30°-60°)	2669.6	18.4	B3/5000		
BH	(60°-80°)	3961.4	27.2	B4/5000		G2/5000
BVH	(80°-90°)	196.0	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short



REPORT NUMBER: P147719

CATALOG NUMBER: VXS-E05-LED-E1-5WQ-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	755.0	755.0	755.0	755.0	755.0	755.0	755.0	755.0	755.0	755.0	755.0
2.5°	761.1	762.7	761.1	761.1	761.1	761.1	761.1	759.6	759.6	759.6	761.1
5°	776.4	777.8	776.4	777.8	777.8	777.8	777.8	776.4	776.4	776.4	776.4
7.5°	800.7	800.7	800.7	802.2	800.7	800.7	802.2	800.7	800.7	800.7	800.7
10°	835.8	834.2	834.2	834.2	834.2	834.2	835.8	835.8	835.8	834.2	834.2
12.5°	878.3	876.8	878.3	878.3	879.9	879.9	879.9	879.9	879.9	879.9	878.3
15°	930.1	930.1	930.1	931.6	934.6	934.6	933.2	934.6	934.6	934.6	934.6
17.5°	988.0	991.0	988.0	989.4	991.0	989.4	992.5	994.0	995.5	994.0	989.4
20°	1047.4	1048.8	1048.8	1048.8	1048.8	1051.9	1053.4	1053.4	1057.9	1056.5	1054.9
22.5°	1103.6	1106.6	1106.6	1108.2	1108.2	1112.7	1112.7	1112.7	1115.9	1118.9	1115.9
25°	1163.0	1161.5	1161.5	1164.6	1166.0	1172.1	1172.1	1175.1	1179.8	1181.2	1178.2
27.5°	1216.3	1214.7	1214.7	1219.3	1220.8	1228.5	1228.5	1234.5	1237.6	1239.1	1236.1
30°	1272.6	1272.6	1271.1	1275.6	1280.2	1286.3	1289.3	1295.4	1300.0	1301.6	1298.4
32.5°	1339.6	1336.6	1338.0	1341.1	1344.1	1350.3	1354.8	1362.4	1368.5	1370.1	1366.9
35°	1415.6	1411.1	1412.6	1415.6	1420.3	1429.4	1437.0	1441.6	1450.7	1453.8	1447.7
37.5°	1499.4	1500.9	1499.4	1507.0	1514.6	1525.3	1534.4	1540.5	1549.6	1554.2	1549.6
40°	1618.1	1613.6	1618.1	1625.8	1637.9	1651.6	1669.9	1674.5	1683.6	1692.7	1682.1
42.5°	1771.9	1768.8	1779.5	1785.6	1799.3	1814.5	1837.3	1849.5	1863.2	1869.3	1860.2
45°	1972.8	1972.8	1985.0	1986.5	2007.9	2027.7	2059.6	2074.8	2100.7	2100.7	2100.7
47.5°	2195.1	2204.2	2211.8	2227.0	2242.3	2278.9	2310.8	2344.2	2368.6	2371.7	2367.2
50°	2425.0	2434.1	2456.9	2478.2	2511.7	2557.4	2592.4	2636.6	2657.8	2676.2	2670.1
52.5°	2679.2	2680.7	2708.1	2735.4	2784.1	2834.4	2890.8	2936.4	2974.5	2991.2	2977.5
55°	2957.7	2960.8	2985.2	3014.1	3068.8	3126.7	3196.7	3243.9	3292.6	3323.1	3300.2
57.5°	3259.2	3260.6	3285.0	3320.0	3385.5	3443.3	3510.3	3577.3	3623.0	3650.4	3635.1
60°	3592.5	3600.1	3618.3	3662.5	3725.0	3785.8	3852.8	3912.2	3965.5	3994.4	3979.2
62.5°	3948.7	3956.4	3982.2	4017.2	4072.0	4139.0	4202.9	4279.1	4323.2	4355.1	4332.3
65°	4187.7	4201.5	4242.5	4289.7	4370.4	4457.1	4531.7	4635.2	4688.5	4726.6	4705.3
67.5°	4202.9	4210.6	4260.8	4332.3	4440.4	4571.3	4723.5	4884.9	4989.9	5040.2	5003.6
69°	4099.4	4110.1	4158.8	4239.5	4359.7	4511.9	4693.1	4894.0	5055.4	5129.9	5094.9
70°	3982.2	4005.1	4058.3	4146.6	4263.8	4423.6	4610.9	4825.5	5014.3	5116.3	5090.4
72.5°	3735.6	3741.7	3776.7	3846.7	3936.6	4069.0	4245.6	4448.0	4627.7	4773.8	4795.1
75°	3315.4	3335.2	3361.1	3408.3	3454.0	3549.8	3668.6	3807.2	3912.2	4024.9	4029.4
77.5°	2505.6	2565.0	2584.8	2595.4	2615.2	2691.3	2794.8	2915.1	3001.9	3020.1	3017.1
80°	1125.0	1204.1	1222.4	1309.1	1362.4	1488.8	1647.0	1831.3	1954.6	1968.3	1934.8
82.5°	220.7	236.0	275.5	344.0	468.8	543.4	646.9	776.4	895.1	963.6	922.5
85°	73.1	77.6	89.8	99.0	114.2	129.4	156.8	194.8	242.1	267.9	239.0
87.5°	28.9	28.9	33.5	36.6	39.6	39.6	39.6	36.6	35.0	28.9	25.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P147719

CATALOG NUMBER: VXS-E05-LED-E1-5WQ-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	755.0	755.0	755.0	755.0	755.0	755.0	755.0	755.0
2.5°	759.6	759.6	759.6	759.6	759.6	759.6	759.6	759.6
5°	776.4	774.8	774.8	773.3	773.3	773.3	773.3	773.3
7.5°	799.2	797.6	796.2	797.6	796.2	796.2	796.2	796.2
10°	834.2	831.2	829.6	828.1	828.1	828.1	826.6	826.6
12.5°	875.3	875.3	873.8	872.2	869.2	870.8	869.2	866.1
15°	931.6	928.6	927.0	925.5	922.5	922.5	922.5	920.9
17.5°	988.0	984.9	984.9	980.3	978.8	978.8	978.8	980.3
20°	1050.4	1045.8	1042.7	1039.7	1036.7	1038.1	1035.1	1038.1
22.5°	1112.7	1106.6	1103.6	1099.1	1094.5	1094.5	1093.0	1089.9
25°	1173.7	1166.0	1163.0	1158.4	1152.3	1152.3	1149.3	1146.2
27.5°	1231.5	1223.9	1220.8	1211.7	1205.6	1204.1	1201.0	1199.5
30°	1295.4	1286.3	1281.8	1272.6	1263.4	1262.0	1257.4	1257.4
32.5°	1362.4	1353.3	1350.3	1336.6	1328.9	1328.9	1325.9	1322.8
35°	1446.1	1432.4	1429.4	1415.6	1405.1	1405.1	1402.0	1403.5
37.5°	1545.1	1534.4	1523.7	1513.2	1500.9	1499.4	1496.4	1493.4
40°	1677.5	1665.4	1653.2	1637.9	1627.3	1624.2	1619.7	1618.1
42.5°	1854.1	1842.0	1817.6	1805.4	1794.7	1785.6	1784.0	1782.6
45°	2079.4	2064.1	2047.5	2024.6	2010.9	1991.1	1988.1	1980.4
47.5°	2350.4	2321.5	2292.5	2272.7	2251.4	2228.6	2224.0	2211.8
50°	2638.0	2615.2	2566.5	2534.5	2501.0	2478.2	2463.0	2458.4
52.5°	2947.0	2904.5	2855.8	2813.2	2764.5	2734.0	2706.5	2699.0
55°	3269.8	3208.9	3148.0	3097.8	3049.1	3012.5	2986.6	2974.5
57.5°	3592.5	3525.5	3458.5	3403.7	3362.7	3315.4	3289.5	3283.5
60°	3928.9	3865.0	3796.5	3741.7	3691.5	3650.4	3635.1	3606.2
62.5°	4285.2	4218.1	4154.2	4100.9	4037.0	4008.1	3982.2	3965.5
65°	4635.2	4557.6	4476.9	4420.6	4356.7	4315.5	4283.6	4260.8
67.5°	4906.2	4789.0	4680.9	4586.5	4499.8	4435.9	4394.7	4373.5
69°	4982.3	4836.2	4697.6	4574.4	4472.3	4400.8	4355.1	4333.9
70°	4973.2	4811.8	4659.6	4524.1	4413.0	4336.9	4292.7	4253.2
72.5°	4691.6	4543.9	4374.9	4227.3	4126.8	4053.8	4009.6	3988.3
75°	4003.5	3904.6	3782.8	3668.6	3595.5	3553.0	3498.1	3499.7
77.5°	2915.1	2918.1	2836.0	2718.8	2636.6	2621.3	2597.0	2572.6
80°	1808.4	1663.8	1569.4	1443.1	1350.3	1269.5	1234.5	1158.4
82.5°	834.2	651.5	505.4	382.1	293.8	229.8	200.9	164.4
85°	185.7	141.6	117.2	94.4	80.7	74.6	60.9	56.4
87.5°	25.9	22.8	21.3	19.8	16.8	12.2	9.1	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)