

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P156489

Luminaire Tested: **VXS-E05-LED-E1-T4-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P156489
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-T4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4
Light Source: (105) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13800.9 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P156489

CATALOG NUMBER: VXS-E05-LED-E1-T4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 4.8 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156489

CATALOG NUMBER: VXS-E05-LED-E1-T4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P156489

CATALOG NUMBER: VXS-E05-LED-E1-T4-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2944.8	0.0	2944.8
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	10856.1	0.0	10856.1
	% Fixture	78.7	0.0	78.7
Total	Lumens	13800.9	0.0	13800.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.6	1.3
10°-20°	536.3	3.9
20°-30°	923.8	6.7
30°-40°	1397.6	10.1
40°-50°	1811.5	13.1
50°-60°	2497.5	18.1
60°-70°	3880.3	28.1
70°-80°	2256.4	16.3
80°-90°	320.9	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13800.9	100.0
0°-180°	13800.9	100.0

Coefficient of Utilization



REPORT NUMBER: P156489


CATALOG NUMBER: VXS-E05-LED-E1-T4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	848.5	6.1			
FM	(30°-60°)	4430.1	32.1			
FH	(60°-80°)	5331.3	38.6			G3/7500
FVH	(80°-90°)	246.3	1.8			G3/500
BL	(0°-30°)	788.2	5.7	B2/1000		
BM	(30°-60°)	1276.5	9.2	B2/2500		
BH	(60°-80°)	805.4	5.8	B2/1000		G2/1000
BVH	(80°-90°)	74.6	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P156489

CATALOG NUMBER: VXS-E05-LED-E1-T4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1
2.5°	1785.6	1791.7	1787.2	1788.6	1788.6	1790.2	1790.2	1791.7	1790.2	1794.7	1797.8
5°	1753.7	1756.7	1755.1	1758.2	1761.2	1767.4	1765.8	1773.5	1774.9	1779.5	1787.2
7.5°	1741.5	1738.4	1739.9	1744.5	1747.6	1750.6	1753.7	1759.7	1764.2	1774.9	1781.0
10°	1753.7	1752.1	1753.7	1756.7	1756.7	1758.2	1755.1	1761.2	1764.2	1773.5	1779.5
12.5°	1803.8	1803.8	1800.8	1800.8	1797.8	1794.7	1787.2	1782.6	1781.0	1782.6	1785.6
15°	1884.6	1881.5	1875.4	1870.9	1864.8	1854.1	1843.4	1834.3	1828.2	1819.1	1816.1
17.5°	1963.7	1959.2	1953.1	1946.9	1939.4	1928.7	1911.9	1901.2	1884.6	1873.9	1867.8
20°	2055.0	2045.9	2038.3	2030.7	2015.4	2012.4	1995.6	1977.4	1957.6	1933.3	1930.3
22.5°	2173.8	2158.5	2149.4	2144.9	2129.6	2125.1	2097.6	2071.8	2047.5	2015.4	2007.9
25°	2294.0	2278.9	2274.2	2268.2	2257.5	2251.4	2225.5	2196.6	2164.7	2120.5	2111.4
27.5°	2411.3	2412.7	2400.6	2405.2	2402.1	2391.5	2365.6	2336.7	2312.3	2260.5	2249.8
30°	2557.4	2548.3	2542.2	2551.3	2540.6	2542.2	2519.3	2504.1	2464.6	2434.1	2412.7
32.5°	2709.6	2708.1	2717.2	2723.3	2721.8	2718.8	2700.5	2685.3	2650.3	2606.1	2597.0
35°	2918.1	2927.3	2934.9	2962.3	2962.3	2982.1	2963.8	2945.6	2904.5	2851.2	2833.0
37.5°	3059.7	3062.8	3093.3	3129.7	3175.4	3218.0	3230.3	3234.8	3218.0	3178.4	3151.1
40°	3189.1	3195.2	3243.9	3300.2	3367.3	3451.0	3501.1	3524.0	3528.6	3510.3	3451.0
42.5°	3318.5	3327.7	3377.8	3460.1	3553.0	3659.5	3747.8	3804.1	3836.1	3836.1	3801.0
45°	3469.2	3481.3	3536.2	3626.0	3734.1	3868.1	3989.8	4097.9	4149.6	4152.7	4119.2
47.5°	3647.4	3657.9	3721.9	3813.3	3924.4	4059.8	4213.6	4336.9	4432.7	4438.9	4411.5
50°	3877.2	3892.4	3945.7	4027.9	4142.1	4279.1	4432.7	4604.8	4705.3	4729.6	4700.7
52.5°	4181.7	4184.7	4228.8	4305.0	4416.1	4546.9	4709.8	4897.1	5029.5	5049.3	5002.1
55°	4601.8	4597.2	4626.1	4708.3	4792.0	4894.0	5063.0	5273.1	5420.7	5451.2	5402.5
57.5°	5172.6	5168.1	5192.4	5212.2	5369.0	5467.9	5633.9	5834.8	5977.9	6066.2	5982.5
60°	6057.0	6052.4	6092.0	6207.8	6325.0	6469.5	6630.9	6871.4	7072.3	7098.2	7016.1
62.5°	6697.9	6720.7	6807.5	6943.0	7180.4	7463.6	7758.9	8075.5	8488.1	8619.0	8579.4
65°	6474.1	6519.8	6640.1	6845.6	7162.2	7553.4	8016.2	8590.1	9142.6	9451.6	9442.5
66°	6273.2	6323.4	6471.1	6669.0	7003.8	7431.6	7937.0	8562.7	9180.7	9521.7	9543.0
67.5°	5907.9	5964.1	6108.8	6343.2	6669.0	7124.1	7667.6	8348.0	9046.7	9444.0	9500.4
70°	5197.0	5260.9	5365.9	5559.3	5880.4	6286.9	6859.3	7468.2	8200.4	8655.5	8724.0
72.5°	4344.5	4400.8	4518.0	4676.4	4939.7	5195.4	5644.5	6093.6	6617.2	7136.3	7086.1
75°	3119.1	3143.4	3213.5	3385.5	3527.0	3756.9	4117.7	4486.1	4843.8	5081.2	5114.7
77.5°	1621.2	1685.2	1784.0	1974.4	2128.1	2335.1	2569.5	2846.6	3108.4	3326.1	3266.7
80°	1061.0	1088.4	1176.7	1274.1	1386.7	1519.2	1676.0	1779.5	1813.0	1799.3	1813.0
82.5°	611.9	662.2	779.4	854.0	937.7	983.4	1108.2	1226.9	1293.9	1210.2	1179.8
85°	77.6	100.5	316.6	398.9	456.7	525.2	563.2	634.8	592.1	529.7	645.4
87.5°	16.8	15.2	21.3	45.7	47.2	39.6	74.6	79.2	48.7	24.4	30.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156489

CATALOG NUMBER: VXS-E05-LED-E1-T4-7030

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1
2.5°	1800.8	1802.4	1805.4	1809.9	1813.0	1816.1	1819.1	1823.6	1826.7	1829.7	1835.9
5°	1793.2	1799.3	1805.4	1811.5	1819.1	1831.3	1838.9	1845.0	1851.1	1863.2	1867.8
7.5°	1788.6	1799.3	1808.4	1819.1	1831.3	1842.0	1855.6	1863.2	1872.3	1880.0	1889.1
10°	1785.6	1800.8	1809.9	1825.2	1838.9	1849.5	1864.8	1873.9	1884.6	1893.7	1898.2
12.5°	1791.7	1799.3	1808.4	1823.6	1840.4	1855.6	1872.3	1880.0	1889.1	1896.7	1898.2
15°	1817.6	1817.6	1819.1	1831.3	1848.0	1860.2	1873.9	1881.5	1886.1	1890.7	1890.7
17.5°	1864.8	1854.1	1846.5	1848.0	1858.7	1866.3	1873.9	1873.9	1870.9	1869.3	1866.3
20°	1919.6	1905.9	1890.7	1880.0	1876.9	1870.9	1866.3	1851.1	1838.9	1828.2	1820.6
22.5°	1998.8	1977.4	1956.1	1936.3	1918.0	1895.2	1869.3	1838.9	1809.9	1790.2	1778.0
25°	2096.2	2079.4	2053.5	2023.1	2000.2	1957.6	1924.1	1880.0	1843.4	1817.6	1796.3
27.5°	2234.7	2214.9	2190.6	2163.1	2129.6	2082.5	2041.3	1989.5	1945.4	1907.4	1880.0
30°	2406.6	2380.8	2362.5	2329.0	2306.2	2253.0	2211.8	2147.9	2062.7	2001.8	1963.7
32.5°	2583.2	2554.3	2539.1	2513.3	2487.4	2455.4	2393.0	2294.0	2184.5	2085.5	2020.0
35°	2819.2	2788.8	2761.3	2738.5	2700.5	2641.1	2586.3	2467.6	2316.9	2178.3	2068.7
37.5°	3116.1	3065.8	2997.3	2939.5	2872.4	2787.3	2703.5	2581.8	2409.7	2230.1	2083.9
40°	3432.6	3344.4	3246.9	3138.9	3023.2	2899.9	2803.9	2680.7	2487.4	2274.2	2073.3
42.5°	3763.0	3623.0	3487.5	3335.2	3173.9	3027.8	2902.9	2767.5	2545.2	2286.4	2030.7
45°	4090.3	3933.5	3728.0	3528.6	3324.6	3143.4	3003.4	2851.2	2598.4	2291.0	1974.4
47.5°	4361.2	4199.9	3965.5	3715.9	3473.8	3268.3	3103.8	2939.5	2670.1	2323.0	1960.6
50°	4647.5	4451.1	4190.8	3895.4	3621.5	3391.6	3216.5	3046.0	2770.5	2405.2	2004.8
52.5°	4959.5	4734.2	4429.7	4099.4	3799.6	3542.3	3352.0	3176.9	2898.3	2520.8	2088.5
55°	5340.1	5064.6	4734.2	4361.2	4040.1	3755.4	3545.3	3338.3	3050.6	2657.8	2193.6
57.5°	5921.6	5583.6	5212.2	4787.5	4431.3	4094.8	3843.7	3604.7	3286.5	2861.9	2336.7
60°	6973.5	6612.6	6130.1	5615.5	5197.0	4804.2	4435.9	4139.0	3747.8	3263.7	2653.3
62.5°	8480.4	8000.9	7357.0	6637.0	6089.0	5522.7	5107.2	4665.7	4180.1	3657.9	3026.2
65°	9317.7	8736.2	7874.6	7038.9	6334.1	5719.1	5190.9	4679.4	4140.5	3641.2	3113.0
66°	9421.2	8815.3	7920.3	7040.4	6300.6	5668.9	5113.3	4583.5	4032.4	3556.0	3076.5
67.5°	9378.5	8759.1	7836.6	6908.0	6156.0	5477.1	4903.2	4353.7	3804.1	3359.6	2954.7
70°	8679.9	8092.3	7186.5	6286.9	5573.0	4903.2	4355.1	3814.7	3310.9	2930.4	2632.0
72.5°	7207.9	6705.5	5918.5	5212.2	4652.0	4099.4	3635.1	3119.1	2692.8	2411.3	2234.7
75°	5203.0	4898.7	4181.7	3776.7	3285.0	2918.1	2467.6	2161.6	1855.6	1718.7	1688.2
77.5°	3286.5	2877.1	2421.9	1994.2	1639.5	1359.4	1057.9	898.1	748.9	733.7	885.9
80°	1663.8	1497.9	1153.9	919.5	773.3	625.6	494.7	374.5	261.9	315.1	377.5
82.5°	1089.9	908.8	712.4	586.1	509.9	423.2	328.8	228.3	167.5	188.8	258.8
85°	589.1	502.4	404.9	319.7	258.8	231.4	155.2	109.6	108.1	115.6	147.7
87.5°	42.6	42.6	33.5	30.5	36.6	30.5	27.4	27.4	25.9	27.4	36.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156489

CATALOG NUMBER: VXS-E05-LED-E1-T4-7030

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1	1819.1
2.5°	1838.9	1843.4	1845.0	1852.5	1857.1	1860.2	1863.2	1863.2	1864.8	1869.3	1870.9
5°	1873.9	1881.5	1890.7	1896.7	1899.8	1908.9	1911.9	1911.9	1915.0	1921.0	1925.6
7.5°	1895.2	1905.9	1915.0	1918.0	1924.1	1927.2	1931.7	1934.8	1934.8	1940.8	1943.9
10°	1902.8	1908.9	1918.0	1918.0	1924.1	1924.1	1928.7	1930.3	1930.3	1936.3	1940.8
12.5°	1902.8	1905.9	1913.5	1913.5	1918.0	1919.6	1925.6	1930.3	1931.7	1939.4	1945.4
15°	1893.7	1896.7	1902.8	1904.4	1915.0	1921.0	1934.8	1943.9	1943.9	1951.5	1954.6
17.5°	1867.8	1875.4	1887.6	1899.8	1919.6	1933.3	1950.1	1957.6	1951.5	1946.9	1942.4
20°	1825.2	1838.9	1867.8	1898.2	1933.3	1951.5	1960.6	1953.1	1931.7	1910.5	1896.7
22.5°	1782.6	1809.9	1858.7	1904.4	1943.9	1956.1	1951.5	1924.1	1889.1	1863.2	1845.0
25°	1802.4	1834.3	1881.5	1922.6	1948.5	1945.4	1927.2	1889.1	1851.1	1817.6	1787.2
27.5°	1884.6	1919.6	1945.4	1959.2	1956.1	1934.8	1905.9	1863.2	1817.6	1773.5	1730.8
30°	1962.2	1980.4	1986.5	1975.9	1951.5	1916.5	1880.0	1831.3	1770.4	1715.5	1666.8
32.5°	1997.2	1979.0	1950.1	1921.0	1881.5	1851.1	1800.8	1747.6	1671.4	1606.0	1557.3
35°	1997.2	1924.1	1851.1	1790.2	1730.8	1692.7	1634.9	1563.3	1493.4	1438.5	1400.5
37.5°	1953.1	1813.0	1692.7	1593.8	1519.2	1478.1	1391.3	1327.4	1268.1	1249.7	1225.4
40°	1872.3	1665.4	1491.8	1362.4	1268.1	1207.2	1120.4	1076.3	1053.4	1044.2	1039.7
42.5°	1764.2	1500.9	1269.5	1109.7	1007.8	939.3	881.3	854.0	852.4	851.0	851.0
45°	1648.6	1324.4	1053.4	863.1	773.3	712.4	685.0	674.4	683.5	682.0	683.5
47.5°	1577.1	1190.4	855.5	653.1	584.6	545.0	531.3	535.9	543.4	540.4	540.4
50°	1567.9	1121.9	723.1	508.4	456.7	436.9	433.9	433.9	438.4	435.3	433.9
52.5°	1601.5	1111.2	654.6	436.9	395.8	379.1	376.0	374.5	373.0	363.8	356.2
55°	1659.3	1135.6	634.8	418.7	376.0	357.7	353.2	350.2	344.0	331.8	318.1
57.5°	1774.9	1211.7	653.1	427.8	382.1	366.8	362.3	362.3	350.2	330.4	310.6
60°	2053.5	1405.1	727.7	462.8	411.0	395.8	398.9	397.3	379.1	350.2	319.7
62.5°	2412.7	1657.7	825.1	511.5	447.6	444.5	459.7	456.7	426.2	382.1	337.9
65°	2578.7	1776.5	852.4	522.2	455.1	468.8	499.3	496.3	458.2	397.3	340.9
66°	2581.8	1776.5	840.3	513.0	444.5	461.2	491.7	490.2	452.1	391.2	334.9
67.5°	2519.3	1727.8	805.3	494.7	423.2	435.3	462.8	461.2	426.2	376.0	322.7
70°	2284.9	1546.6	715.4	462.8	394.3	388.2	397.3	391.2	368.4	333.4	296.8
72.5°	1957.6	1298.4	624.1	438.4	374.5	350.2	344.0	339.5	321.2	301.5	278.5
75°	1542.1	1027.6	548.0	420.1	356.2	324.2	313.6	307.5	295.3	281.7	263.3
77.5°	951.4	735.2	478.0	395.8	342.5	310.6	302.9	293.8	275.5	258.8	245.1
80°	424.7	455.1	392.7	345.6	306.0	277.1	264.9	251.2	233.0	222.3	214.6
82.5°	283.1	293.8	284.7	258.8	231.4	208.5	190.3	190.3	187.3	178.1	175.0
85°	181.1	182.7	176.6	159.8	149.2	135.4	127.9	129.4	135.4	134.0	132.4
87.5°	41.1	41.1	48.7	45.7	53.3	56.4	60.9	65.5	74.6	74.6	79.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156489

CATALOG NUMBER: VXS-E05-LED-E1-T4-7030

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1819.1	1819.1	1819.1	1819.1	1819.1
2.5°	1872.3	1875.4	1878.4	1873.9	1875.4
5°	1925.6	1924.1	1931.7	1927.2	1930.3
7.5°	1942.4	1943.9	1950.1	1950.1	1951.5
10°	1943.9	1946.9	1954.6	1959.2	1962.2
12.5°	1951.5	1957.6	1969.7	1972.8	1972.8
15°	1957.6	1960.6	1968.3	1971.3	1974.4
17.5°	1936.3	1930.3	1933.3	1934.8	1933.3
20°	1883.0	1876.9	1875.4	1869.3	1872.3
22.5°	1825.2	1808.4	1797.8	1785.6	1785.6
25°	1755.1	1729.3	1708.0	1686.6	1691.2
27.5°	1689.7	1656.2	1634.9	1621.2	1618.1
30°	1625.8	1590.8	1571.0	1554.2	1554.2
32.5°	1519.2	1494.8	1469.0	1458.3	1456.8
35°	1371.5	1356.4	1335.0	1330.5	1322.8
37.5°	1205.6	1201.0	1182.8	1181.2	1173.7
40°	1032.1	1035.1	1029.0	1026.0	1021.5
42.5°	858.5	873.8	870.8	869.2	866.1
45°	692.6	703.3	704.8	709.3	717.0
47.5°	545.0	548.0	551.1	549.5	551.1
50°	426.2	418.7	417.1	412.5	417.1
52.5°	344.0	331.8	325.8	319.7	316.6
55°	302.9	290.8	284.7	281.7	278.5
57.5°	292.2	280.1	271.0	264.9	263.3
60°	295.3	277.1	264.9	257.3	255.8
62.5°	302.9	278.5	261.9	254.2	252.6
65°	301.5	275.5	260.3	251.2	249.6
66°	296.8	272.4	257.3	249.6	248.1
67.5°	289.2	267.9	254.2	248.1	245.1
70°	275.5	261.9	251.2	243.5	240.5
72.5°	263.3	252.6	243.5	236.0	234.4
75°	249.6	240.5	231.4	225.3	223.7
77.5°	233.0	223.7	217.7	213.2	211.6
80°	205.5	199.4	193.4	187.3	187.3
82.5°	170.5	165.9	159.8	155.2	153.8
85°	130.9	130.9	126.3	121.8	120.2
87.5°	77.6	76.1	76.1	71.5	71.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)