

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P152172

Luminaire Tested: **VXS-E04-LED-E1-SL4-7060**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P152172
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E04-LED-E1-SL4-7060
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (84) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12124.9 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B2 - U0 - G2


Input Watts (W): 97.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P152172
 CATALOG NUMBER: VXS-E04-LED-E1-SL4-7060

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 6.5 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152172

CATALOG NUMBER: VXS-E04-LED-E1-SL4-7060

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P152172

CATALOG NUMBER: VXS-E04-LED-E1-SL4-7060


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2517.0	0.0	2517.0
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	9607.9	0.0	9607.9
	% Fixture	79.2	0.0	79.2
Total	Lumens	12124.9	0.0	12124.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.7	2.0
10°-20°	661.7	5.5
20°-30°	979.5	8.1
30°-40°	1237.8	10.2
40°-50°	1399.9	11.5
50°-60°	1992.1	16.4
60°-70°	3710.1	30.6
70°-80°	1700.3	14.0
80°-90°	201.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12124.9	100.0
0°-180°	12124.9	100.0



REPORT NUMBER: P152172


CATALOG NUMBER: VXS-E04-LED-E1-SL4-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1104.1	9.1			
FM	(30°-60°)	3552.2	29.3			
FH	(60°-80°)	4801.9	39.6			G2/5000
FVH	(80°-90°)	149.7	1.2			G2/225
BL	(0°-30°)	778.8	6.4	B2/1000		
BM	(30°-60°)	1077.6	8.9	B2/2500		
BH	(60°-80°)	608.5	5.0	B2/1000		G2/1000
BVH	(80°-90°)	52.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P152172

CATALOG NUMBER: VXS-E04-LED-E1-SL4-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2
2.5°	2626.8	2633.7	2625.5	2624.1	2624.1	2622.7	2614.5	2613.2	2602.2	2603.5	2606.3
5°	2646.0	2648.7	2643.2	2641.9	2639.2	2633.7	2626.8	2618.7	2610.4	2602.2	2595.3
7.5°	2665.2	2662.4	2658.3	2658.3	2654.2	2646.0	2632.3	2621.3	2603.5	2594.0	2581.7
10°	2692.5	2688.4	2682.9	2680.2	2673.4	2661.0	2641.9	2626.8	2605.0	2585.8	2565.3
12.5°	2718.4	2717.1	2708.9	2704.8	2693.9	2681.6	2658.3	2635.0	2606.3	2576.2	2548.8
15°	2765.0	2759.6	2751.3	2743.1	2725.3	2708.9	2673.4	2646.0	2605.0	2565.3	2522.9
17.5°	2845.7	2836.2	2828.0	2810.2	2788.3	2759.6	2707.6	2661.0	2605.0	2547.5	2499.6
20°	2993.5	2973.0	2962.1	2938.8	2900.4	2848.5	2767.8	2692.5	2609.0	2535.1	2470.9
22.5°	3160.4	3146.7	3131.7	3116.6	3056.5	2981.1	2871.7	2759.6	2633.7	2529.7	2447.6
25°	3347.9	3330.1	3321.9	3295.9	3239.8	3153.6	3004.5	2848.5	2689.7	2551.6	2447.6
27.5°	3514.7	3509.3	3507.9	3477.8	3424.5	3323.2	3146.7	2959.3	2766.4	2596.7	2468.1
30°	3666.6	3661.1	3658.4	3642.0	3580.4	3460.0	3268.5	3057.8	2849.8	2659.7	2506.4
32.5°	3828.1	3810.3	3802.1	3770.6	3700.8	3559.9	3341.0	3122.1	2915.5	2721.2	2548.8
35°	3959.4	3944.4	3928.0	3882.8	3784.2	3617.4	3372.4	3143.9	2941.5	2755.4	2570.8
37.5°	4055.1	4040.1	4016.9	3959.4	3837.6	3636.5	3371.1	3137.1	2931.9	2749.9	2574.8
40°	4097.6	4082.5	4057.9	3985.4	3847.3	3625.6	3345.1	3105.7	2903.2	2721.2	2558.4
42.5°	4081.1	4070.3	4038.8	3969.0	3817.1	3576.3	3293.2	3046.8	2848.5	2674.7	2521.5
45°	4018.2	4010.1	3979.9	3906.0	3748.7	3497.0	3216.5	2973.0	2782.8	2617.2	2472.2
47.5°	3923.8	3921.1	3891.0	3818.4	3662.5	3417.6	3137.1	2900.4	2717.1	2561.1	2431.2
50°	3819.9	3806.2	3791.1	3724.0	3581.8	3349.2	3079.7	2855.3	2680.2	2540.6	2413.4
52.5°	3754.2	3750.1	3736.4	3676.2	3539.4	3309.5	3053.7	2838.9	2677.4	2536.6	2403.8
55°	4337.0	4346.6	4220.7	3959.4	3729.5	3419.0	3131.7	2922.4	2744.5	2602.2	2505.1
57.5°	6415.2	6372.8	6156.7	5638.1	5052.5	4279.6	3722.7	3384.8	3164.6	3189.1	3238.3
60°	7474.2	7465.9	7426.2	7225.2	6835.2	6246.9	5594.3	4845.9	4607.9	4633.9	4653.1
62.5°	7947.6	7959.8	7989.9	7914.7	7812.1	7641.0	7315.4	7014.5	6695.6	6576.7	6257.8
65°	8166.4	8188.3	8256.7	8299.2	8338.9	8368.9	8497.5	8850.5	9083.1	8648.0	7635.5
67.5°	7713.6	7819.0	8044.7	8265.0	8462.0	8742.4	9177.5	9997.0	10567.6	10032.5	8564.6
70°	5623.1	5766.7	6025.3	6706.6	7434.5	8070.7	8913.5	10161.1	11021.8	10608.6	8794.4
72.5°	3525.7	3565.4	3680.3	3930.7	4471.1	5287.9	6761.3	8633.0	9626.2	9296.5	7433.1
75°	2236.9	2250.6	2246.5	2303.9	2395.6	2573.5	3156.3	5099.1	6594.4	6080.0	4142.7
77.5°	1332.5	1353.1	1361.3	1379.1	1422.9	1485.8	1533.7	1734.8	2765.0	2684.2	1503.6
80°	1116.4	1132.8	1119.2	1115.0	1087.7	1068.5	1091.8	1068.5	991.9	954.9	879.7
82.5°	591.1	589.6	585.6	625.3	706.0	768.9	816.8	805.8	729.2	621.1	526.7
85°	324.2	335.2	335.2	348.9	336.6	337.9	348.9	368.0	340.6	284.6	232.5
87.5°	27.4	42.4	34.2	42.4	57.5	41.0	39.7	39.7	34.2	24.7	21.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152172

CATALOG NUMBER: VXS-E04-LED-E1-SL4-7060

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2
2.5°	2599.5	2596.7	2591.3	2587.2	2587.2	2580.3	2576.2	2573.5	2572.1	2566.6	2566.6
5°	2591.3	2581.7	2572.1	2565.3	2561.1	2554.3	2543.4	2537.9	2531.1	2525.6	2522.9
7.5°	2573.5	2555.6	2540.6	2529.7	2516.1	2505.1	2491.4	2479.1	2466.7	2461.2	2458.5
10°	2546.1	2522.9	2499.6	2479.1	2459.9	2440.7	2423.0	2405.2	2390.2	2379.2	2368.3
12.5°	2520.1	2484.6	2454.4	2424.4	2394.2	2371.0	2346.3	2320.4	2298.4	2277.9	2272.4
15°	2484.6	2443.5	2405.2	2368.3	2331.3	2293.0	2262.9	2234.2	2198.7	2175.3	2157.5
17.5°	2451.7	2402.5	2356.0	2312.1	2267.0	2227.4	2182.2	2143.8	2108.3	2072.7	2046.7
20°	2416.2	2362.8	2313.6	2264.2	2215.0	2164.4	2112.4	2063.1	2019.4	1977.0	1934.5
22.5°	2384.7	2329.9	2282.1	2228.7	2174.0	2116.5	2056.3	1994.7	1944.1	1889.4	1840.1
25°	2365.5	2305.3	2256.1	2204.0	2143.8	2080.9	2012.5	1940.0	1878.4	1815.5	1756.7
27.5°	2365.5	2287.6	2236.9	2184.9	2123.3	2056.3	1981.0	1901.8	1831.9	1762.2	1689.6
30°	2386.0	2290.3	2221.9	2167.2	2104.2	2031.7	1948.2	1864.8	1788.2	1706.1	1636.3
32.5°	2405.2	2295.8	2210.9	2141.1	2068.6	1997.5	1912.6	1823.7	1738.9	1660.9	1587.0
35°	2417.5	2295.8	2190.4	2101.5	2019.4	1949.6	1866.1	1777.2	1691.0	1614.4	1546.0
37.5°	2418.9	2284.8	2157.5	2056.3	1970.2	1897.6	1818.2	1734.8	1652.7	1581.6	1524.1
40°	2405.2	2262.9	2124.8	2008.4	1918.1	1844.2	1771.7	1696.5	1622.6	1563.8	1514.5
42.5°	2380.5	2239.7	2093.3	1970.2	1875.8	1799.1	1732.0	1667.8	1603.4	1552.8	1511.8
45°	2343.6	2208.2	2064.6	1946.8	1853.8	1773.2	1707.5	1654.1	1599.4	1557.0	1515.9
47.5°	2310.8	2197.2	2074.1	1961.9	1864.8	1781.3	1714.3	1669.1	1626.7	1598.0	1541.9
50°	2303.9	2191.7	2078.2	1974.2	1875.8	1790.9	1732.0	1708.8	1696.5	1678.8	1592.5
52.5°	2284.8	2190.4	2108.3	2050.9	1987.9	1948.2	1886.6	1908.6	1894.9	1831.9	1676.0
55°	2485.9	2513.3	2589.8	2699.4	2800.6	2823.8	2817.0	2791.0	2652.8	2282.1	1877.1
57.5°	3417.6	3572.2	3717.2	3781.6	3773.4	3700.8	3648.8	3543.5	3343.7	2892.2	2273.9
60°	4711.9	4736.5	4659.9	4546.3	4354.8	4194.7	4023.7	3826.7	3536.7	3094.7	2517.4
62.5°	5903.5	5572.4	5231.8	4911.6	4620.2	4365.7	4127.7	3852.6	3475.0	3014.0	2485.9
65°	6745.0	6044.5	5506.7	5047.0	4635.2	4279.6	3982.7	3625.6	3200.1	2784.1	2303.9
67.5°	7178.7	6104.7	5279.7	4639.4	4055.1	3562.6	3167.3	2819.7	2503.7	2321.8	2016.7
70°	6694.3	5181.1	4031.9	3308.2	2609.0	2091.9	1652.7	1387.3	1295.6	1468.0	1526.8
72.5°	4988.3	3372.4	2398.3	1855.2	1421.5	1132.8	868.8	682.7	555.4	582.8	756.6
75°	2358.7	1455.8	1028.8	782.6	622.5	515.8	421.3	385.8	322.9	268.2	251.7
77.5°	918.0	669.0	552.7	405.0	287.4	231.2	197.0	190.2	194.3	188.8	186.1
80°	699.2	473.4	296.9	217.5	187.5	165.6	146.4	140.9	143.6	150.5	157.3
82.5°	389.9	243.5	180.6	157.3	140.9	120.4	109.4	101.2	102.6	110.8	125.9
85°	150.5	117.6	108.1	103.9	97.1	78.0	67.0	68.4	78.0	93.1	93.1
87.5°	16.4	16.4	21.9	16.4	16.4	16.4	15.0	17.8	19.2	24.7	28.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152172

CATALOG NUMBER: VXS-E04-LED-E1-SL4-7060

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2	2587.2
2.5°	2563.9	2563.9	2563.9	2561.1	2562.5	2557.1	2557.1	2553.0	2559.8	2555.6	2554.3
5°	2524.2	2522.9	2517.4	2517.4	2517.4	2517.4	2521.5	2510.6	2518.8	2518.8	2514.6
7.5°	2457.2	2457.2	2442.2	2450.4	2447.6	2451.7	2457.2	2451.7	2459.9	2465.4	2461.2
10°	2364.1	2364.1	2351.8	2361.5	2357.3	2366.8	2376.5	2371.0	2376.5	2384.7	2387.4
12.5°	2261.6	2256.1	2245.1	2249.2	2249.2	2254.7	2258.8	2265.6	2272.4	2283.4	2288.9
15°	2142.5	2134.3	2120.6	2120.6	2112.4	2115.1	2123.3	2126.1	2139.8	2154.8	2172.6
17.5°	2020.7	2000.2	1985.2	1967.4	1953.7	1964.7	1974.2	1981.0	1992.0	2015.2	2027.6
20°	1905.8	1864.8	1836.1	1812.7	1797.7	1804.6	1816.9	1825.1	1834.7	1840.1	1844.2
22.5°	1792.2	1745.7	1706.1	1677.3	1652.7	1659.6	1654.1	1649.9	1656.8	1639.1	1637.6
25°	1693.8	1639.1	1585.7	1551.5	1521.3	1511.8	1483.1	1476.3	1457.1	1442.0	1431.1
27.5°	1622.6	1551.5	1492.6	1453.0	1405.1	1369.5	1332.5	1295.6	1275.1	1250.5	1238.1
30°	1566.5	1491.3	1421.5	1354.5	1291.5	1236.8	1187.6	1139.7	1106.8	1071.3	1048.0
32.5°	1514.5	1444.8	1359.9	1268.3	1183.4	1121.9	1057.6	1002.8	950.9	904.4	870.2
35°	1479.0	1400.9	1292.8	1180.7	1085.0	1012.4	944.0	866.0	803.1	742.9	706.0
37.5°	1459.8	1364.0	1231.3	1106.8	1000.1	918.0	833.2	742.9	666.3	610.2	554.1
40°	1444.8	1327.0	1176.6	1041.1	929.0	830.5	731.9	625.3	540.4	481.6	437.8
42.5°	1428.3	1286.0	1128.7	989.1	864.7	749.7	630.7	517.2	436.5	395.4	376.3
45°	1410.6	1250.5	1083.5	939.9	801.8	662.2	525.4	420.0	372.1	358.4	358.4
47.5°	1406.4	1227.3	1050.8	892.0	730.6	560.9	428.2	362.6	348.9	351.6	357.1
50°	1422.9	1220.4	1022.0	836.0	636.2	454.2	362.6	340.6	343.4	351.6	359.8
52.5°	1462.6	1225.8	991.9	757.9	524.0	374.9	335.2	333.8	342.1	354.3	362.6
55°	1529.5	1225.8	934.4	641.7	418.7	336.6	325.6	331.1	342.1	353.0	359.8
57.5°	1673.3	1213.6	833.2	513.1	350.3	322.9	322.9	329.7	339.3	350.3	355.8
60°	1844.2	1197.1	690.9	396.8	316.1	311.9	321.6	329.7	337.9	347.5	353.0
62.5°	1855.2	1154.7	547.3	328.4	298.2	305.1	320.1	331.1	333.8	340.6	347.5
65°	1704.7	1006.9	435.0	294.2	290.1	301.0	316.1	324.2	325.6	328.4	335.2
67.5°	1492.6	820.9	351.6	277.7	281.9	294.2	302.4	309.2	313.3	320.1	321.6
70°	1225.8	659.5	301.0	261.3	265.4	279.1	285.9	292.7	301.0	309.2	305.1
72.5°	868.8	513.1	264.0	243.5	249.0	261.3	269.5	275.0	281.9	290.1	284.6
75°	369.4	358.4	228.5	220.3	228.5	236.7	244.9	253.1	259.9	264.0	264.0
77.5°	188.8	210.7	197.0	197.0	202.5	210.7	217.5	225.7	229.8	234.0	239.4
80°	160.1	162.8	165.6	171.0	176.5	184.7	191.5	198.3	199.8	201.1	203.8
82.5°	132.7	138.1	140.9	149.1	153.3	156.0	160.1	160.1	162.8	162.8	158.7
85°	95.8	102.6	106.7	108.1	106.7	108.1	109.4	112.2	119.1	119.1	113.6
87.5°	27.4	26.0	32.8	34.2	36.9	42.4	47.9	57.5	60.2	62.9	62.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152172

CATALOG NUMBER: VXS-E04-LED-E1-SL4-7060

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2587.2	2587.2	2587.2	2587.2
2.5°	2553.0	2555.6	2550.3	2551.6
5°	2514.6	2520.1	2513.3	2521.5
7.5°	2465.4	2473.6	2472.2	2470.9
10°	2394.2	2405.2	2405.2	2409.3
12.5°	2303.9	2310.8	2316.3	2319.0
15°	2182.2	2194.5	2201.3	2201.3
17.5°	2035.8	2044.0	2048.1	2042.6
20°	1849.7	1846.9	1848.4	1834.7
22.5°	1634.9	1639.1	1626.7	1629.4
25°	1424.2	1417.4	1422.9	1414.6
27.5°	1220.4	1221.8	1206.7	1213.6
30°	1026.1	1019.3	1000.1	1009.6
32.5°	838.7	820.9	800.3	788.1
35°	662.2	634.8	625.3	621.1
37.5°	519.9	489.8	480.2	469.2
40°	413.2	402.3	398.1	400.8
42.5°	370.8	370.8	373.5	374.9
45°	359.8	363.9	368.0	369.4
47.5°	361.1	365.3	370.8	372.1
50°	363.9	368.0	372.1	373.5
52.5°	365.3	365.3	368.0	369.4
55°	362.6	361.1	362.6	363.9
57.5°	357.1	354.3	355.8	359.8
60°	354.3	350.3	353.0	355.8
62.5°	347.5	346.1	348.9	350.3
65°	332.4	333.8	337.9	337.9
67.5°	318.8	320.1	321.6	322.9
70°	302.4	303.7	306.4	307.9
72.5°	283.2	288.7	292.7	298.2
75°	268.2	273.7	281.9	287.4
77.5°	242.2	246.2	255.9	262.7
80°	205.2	203.8	205.2	209.3
82.5°	157.3	157.3	156.0	154.6
85°	110.8	109.4	105.4	105.4
87.5°	60.2	58.9	57.5	54.7
90°	0.0	0.0	0.0	0.0

(END OF REPORT)