

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P156492

Luminaire Tested: **VXS-E05-LED-E1-T4-7060**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P156492
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-T4-7060
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4
Light Source: (105) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15504.7 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P156492

CATALOG NUMBER: VXS-E05-LED-E1-T4-7060

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 3.4 fc
Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156492

CATALOG NUMBER: VXS-E05-LED-E1-T4-7060

Luminous Intensity Polar Plot



REPORT NUMBER: P156492

CATALOG NUMBER: VXS-E05-LED-E1-T4-7060

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3308.3	0.0	3308.3
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	12196.4	0.0	12196.4
	% Fixture	78.7	0.0	78.7
Total	Lumens	15504.7	0.0	15504.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.4	1.3
10°-20°	602.5	3.9
20°-30°	1037.8	6.7
30°-40°	1570.2	10.1
40°-50°	2035.1	13.1
50°-60°	2805.8	18.1
60°-70°	4359.3	28.1
70°-80°	2535.0	16.3
80°-90°	360.5	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15504.7	100.0
0°-180°	15504.7	100.0

Coefficient of Utilization



REPORT NUMBER: P156492


CATALOG NUMBER: VXS-E05-LED-E1-T4-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	953.2	6.1			
FM	(30°-60°)	4977.0	32.1			
FH	(60°-80°)	5989.5	38.6			G3/7500
FVH	(80°-90°)	276.7	1.8			G3/500
BL	(0°-30°)	885.5	5.7	B2/1000		
BM	(30°-60°)	1434.1	9.2	B2/2500		
BH	(60°-80°)	904.8	5.8	B2/1000		G2/1000
BVH	(80°-90°)	83.8	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P156492

CATALOG NUMBER: VXS-E05-LED-E1-T4-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6
2.5°	2006.0	2012.8	2007.8	2009.4	2009.4	2011.2	2011.2	2012.8	2011.2	2016.3	2019.7
5°	1970.2	1973.6	1971.8	1975.2	1978.7	1985.5	1983.8	1992.3	1994.1	1999.2	2007.8
7.5°	1956.5	1953.1	1954.7	1959.9	1963.3	1966.7	1970.2	1977.0	1982.1	1994.1	2000.9
10°	1970.2	1968.4	1970.2	1973.6	1973.6	1975.2	1971.8	1978.7	1982.1	1992.3	1999.2
12.5°	2026.5	2026.5	2023.1	2023.1	2019.7	2016.3	2007.8	2002.6	2000.9	2002.6	2006.0
15°	2117.2	2113.8	2106.9	2101.8	2094.9	2083.0	2071.0	2060.7	2053.9	2043.6	2040.2
17.5°	2206.1	2201.0	2194.2	2187.4	2178.8	2166.8	2148.0	2136.0	2117.2	2105.2	2098.3
20°	2308.7	2298.4	2289.9	2281.3	2264.2	2260.8	2242.1	2221.6	2199.3	2171.9	2168.5
22.5°	2442.2	2425.1	2414.8	2409.6	2392.5	2387.4	2356.6	2327.6	2300.2	2264.2	2255.8
25°	2577.2	2560.1	2555.0	2548.2	2536.2	2529.3	2500.3	2467.8	2431.9	2382.3	2372.0
27.5°	2708.9	2710.7	2697.0	2702.1	2698.7	2686.7	2657.6	2625.1	2597.7	2539.6	2527.7
30°	2873.1	2862.8	2856.0	2866.2	2854.3	2856.0	2830.4	2813.3	2768.8	2734.6	2710.7
32.5°	3044.1	3042.4	3052.6	3059.5	3057.8	3054.4	3033.9	3016.8	2977.4	2927.8	2917.5
35°	3278.4	3288.7	3297.2	3328.0	3328.0	3350.3	3329.7	3309.2	3263.0	3203.1	3182.6
37.5°	3437.4	3440.8	3475.0	3516.2	3567.5	3615.3	3629.0	3634.1	3615.3	3570.9	3540.1
40°	3582.8	3589.6	3644.4	3707.7	3782.9	3877.0	3933.4	3959.1	3964.1	3943.6	3877.0
42.5°	3728.2	3738.4	3794.9	3887.3	3991.5	4111.3	4210.5	4273.7	4309.6	4309.6	4270.3
45°	3897.5	3911.2	3972.7	4073.7	4195.0	4345.6	4482.4	4603.8	4662.0	4665.4	4627.8
47.5°	4097.6	4109.5	4181.3	4284.0	4408.8	4561.0	4733.8	4872.3	4980.0	4986.8	4956.1
50°	4355.9	4373.0	4432.7	4525.1	4653.4	4807.3	4980.0	5173.3	5286.1	5313.5	5281.0
52.5°	4697.8	4701.2	4750.9	4836.4	4961.2	5108.3	5291.3	5501.7	5650.5	5672.6	5619.7
55°	5169.8	5164.8	5197.2	5289.5	5383.6	5498.2	5688.1	5924.0	6089.9	6124.1	6069.4
57.5°	5811.2	5806.0	5833.4	5855.6	6031.8	6142.9	6329.3	6555.1	6715.9	6815.0	6721.0
60°	6804.8	6799.7	6844.1	6974.1	7105.8	7268.3	7449.5	7719.7	7945.5	7974.5	7882.2
62.5°	7524.8	7550.5	7647.9	7800.1	8066.9	8385.0	8716.8	9072.4	9536.0	9683.0	9638.5
65°	7273.4	7324.7	7459.8	7690.7	8046.4	8485.9	9005.8	9650.6	10271.3	10618.4	10608.2
66°	7047.7	7104.0	7269.9	7492.3	7868.5	8349.1	8916.9	9619.7	10314.1	10697.1	10721.1
67.5°	6637.2	6700.5	6862.9	7126.3	7492.3	8003.6	8614.2	9378.7	10163.5	10609.9	10673.2
70°	5838.5	5910.4	6028.4	6245.6	6606.4	7063.0	7706.0	8390.2	9212.7	9724.0	9801.0
72.5°	4880.8	4944.1	5075.8	5253.7	5549.5	5836.8	6341.3	6845.8	7434.1	8017.3	7960.8
75°	3504.1	3531.5	3610.2	3803.4	3962.5	4220.7	4626.0	5039.9	5441.8	5708.6	5746.2
77.5°	1821.3	1893.2	2004.4	2218.1	2390.8	2623.4	2886.7	3198.0	3492.2	3736.7	3670.1
80°	1192.0	1222.8	1322.0	1431.4	1557.9	1706.7	1882.9	1999.2	2036.8	2021.5	2036.8
82.5°	687.5	743.9	875.6	959.4	1053.5	1104.8	1245.0	1378.4	1453.7	1359.6	1325.4
85°	87.3	112.8	355.8	448.1	513.1	590.1	632.7	713.2	665.3	595.1	725.1
87.5°	18.9	17.1	23.9	51.3	53.1	44.5	83.8	88.9	54.7	27.4	34.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156492

CATALOG NUMBER: VXS-E05-LED-E1-T4-7060

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6
2.5°	2023.1	2024.9	2028.3	2033.4	2036.8	2040.2	2043.6	2048.8	2052.2	2055.6	2062.5
5°	2014.6	2021.5	2028.3	2035.1	2043.6	2057.3	2065.9	2072.7	2079.6	2093.3	2098.3
7.5°	2009.4	2021.5	2031.7	2043.6	2057.3	2069.3	2084.7	2093.3	2103.5	2112.0	2122.3
10°	2006.0	2023.1	2033.4	2050.5	2065.9	2077.8	2094.9	2105.2	2117.2	2127.5	2132.5
12.5°	2012.8	2021.5	2031.7	2048.8	2067.6	2084.7	2103.5	2112.0	2122.3	2130.9	2132.5
15°	2042.0	2042.0	2043.6	2057.3	2076.2	2089.8	2105.2	2113.8	2118.9	2124.0	2124.0
17.5°	2094.9	2083.0	2074.4	2076.2	2088.1	2096.7	2105.2	2105.2	2101.8	2100.1	2096.7
20°	2156.6	2141.1	2124.0	2112.0	2108.6	2101.8	2096.7	2079.6	2065.9	2053.9	2045.4
22.5°	2245.5	2221.6	2197.6	2175.3	2154.8	2129.1	2100.1	2065.9	2033.4	2011.2	1997.5
25°	2354.9	2336.1	2307.0	2272.8	2247.2	2199.3	2161.7	2112.0	2071.0	2042.0	2018.0
27.5°	2510.6	2488.3	2460.9	2430.2	2392.5	2339.5	2293.4	2235.2	2185.6	2142.9	2112.0
30°	2703.8	2674.7	2654.2	2616.6	2590.9	2531.1	2484.9	2413.1	2317.3	2248.9	2206.1
32.5°	2902.2	2869.6	2852.5	2823.5	2794.4	2758.5	2688.4	2577.2	2454.1	2342.9	2269.4
35°	3167.3	3133.1	3102.3	3076.6	3033.9	2967.2	2905.6	2772.2	2602.9	2447.3	2324.1
37.5°	3500.7	3444.2	3367.4	3302.4	3227.2	3131.3	3037.3	2900.4	2707.3	2505.4	2341.2
40°	3856.5	3757.3	3647.8	3526.4	3396.4	3257.9	3150.2	3011.6	2794.4	2555.0	2329.2
42.5°	4227.6	4070.3	3918.0	3747.0	3565.7	3401.6	3261.3	3109.1	2859.4	2568.7	2281.3
45°	4595.2	4419.1	4188.2	3964.1	3735.0	3531.5	3374.2	3203.1	2919.3	2573.8	2218.1
47.5°	4899.7	4718.3	4455.0	4174.5	3902.6	3671.7	3487.0	3302.4	2999.7	2609.7	2202.7
50°	5221.1	5000.5	4708.1	4376.4	4068.5	3810.3	3613.6	3422.1	3112.5	2702.1	2252.3
52.5°	5571.7	5318.7	4976.6	4605.5	4268.6	3979.6	3765.8	3569.1	3256.2	2832.0	2346.3
55°	5999.3	5689.7	5318.7	4899.7	4538.8	4219.0	3983.0	3750.5	3427.2	2986.0	2464.4
57.5°	6652.5	6273.0	5855.6	5378.5	4978.3	4600.4	4318.2	4049.7	3692.2	3215.1	2625.1
60°	7834.3	7429.0	6886.8	6308.8	5838.5	5397.3	4983.4	4649.9	4210.5	3666.6	2980.8
62.5°	9527.4	8988.7	8265.3	7456.4	6840.7	6204.6	5737.6	5241.7	4696.2	4109.5	3399.8
65°	10468.0	9814.7	8846.7	7907.9	7116.1	6425.2	5831.7	5257.1	4651.7	4090.8	3497.3
66°	10584.2	9903.6	8898.0	7909.5	7078.4	6368.7	5744.5	5149.3	4530.3	3994.9	3456.3
67.5°	10536.4	9840.3	8803.9	7760.8	6916.0	6153.2	5508.5	4891.1	4273.7	3774.4	3319.5
70°	9751.4	9091.3	8073.8	7063.0	6260.9	5508.5	4892.8	4285.7	3719.6	3292.1	2956.9
72.5°	8097.7	7533.4	6649.1	5855.6	5226.3	4605.5	4083.9	3504.1	3025.3	2708.9	2510.6
75°	5845.4	5503.3	4697.8	4242.9	3690.6	3278.4	2772.2	2428.5	2084.7	1930.8	1896.6
77.5°	3692.2	3232.2	2720.9	2240.3	1841.9	1527.2	1188.6	1009.0	841.5	824.4	995.3
80°	1869.2	1682.8	1296.3	1033.0	868.8	702.9	555.9	420.7	294.2	354.0	424.1
82.5°	1224.5	1020.9	800.3	658.4	573.0	475.4	369.4	256.5	188.1	212.0	290.8
85°	661.9	564.4	454.9	359.2	290.8	259.9	174.4	123.1	121.5	129.9	165.9
87.5°	47.9	47.9	37.6	34.2	41.0	34.2	30.8	30.8	29.1	30.8	41.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156492

CATALOG NUMBER: VXS-E05-LED-E1-T4-7060

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6	2043.6
2.5°	2065.9	2071.0	2072.7	2081.2	2086.4	2089.8	2093.3	2093.3	2094.9	2100.1	2101.8
5°	2105.2	2113.8	2124.0	2130.9	2134.3	2144.6	2148.0	2148.0	2151.4	2158.2	2163.4
7.5°	2129.1	2141.1	2151.4	2154.8	2161.7	2165.1	2170.3	2173.7	2173.7	2180.5	2183.9
10°	2137.7	2144.6	2154.8	2154.8	2161.7	2161.7	2166.8	2168.5	2168.5	2175.3	2180.5
12.5°	2137.7	2141.1	2149.7	2149.7	2154.8	2156.6	2163.4	2168.5	2170.3	2178.8	2185.6
15°	2127.5	2130.9	2137.7	2139.4	2151.4	2158.2	2173.7	2183.9	2183.9	2192.4	2195.9
17.5°	2098.3	2106.9	2120.6	2134.3	2156.6	2171.9	2190.8	2199.3	2192.4	2187.4	2182.2
20°	2050.5	2065.9	2098.3	2132.5	2171.9	2192.4	2202.7	2194.2	2170.3	2146.3	2130.9
22.5°	2002.6	2033.4	2088.1	2139.4	2183.9	2197.6	2192.4	2161.7	2122.3	2093.3	2072.7
25°	2024.9	2060.7	2113.8	2160.0	2189.0	2185.6	2165.1	2122.3	2079.6	2042.0	2007.8
27.5°	2117.2	2156.6	2185.6	2201.0	2197.6	2173.7	2141.1	2093.3	2042.0	1992.3	1944.5
30°	2204.5	2225.0	2231.8	2219.8	2192.4	2153.2	2112.0	2057.3	1988.9	1927.4	1872.6
32.5°	2243.7	2223.2	2190.8	2158.2	2113.8	2079.6	2023.1	1963.3	1877.8	1804.2	1749.5
35°	2243.7	2161.7	2079.6	2011.2	1944.5	1901.8	1836.7	1756.4	1677.7	1616.2	1573.4
37.5°	2194.2	2036.8	1901.8	1790.6	1706.7	1660.6	1563.1	1491.3	1424.6	1404.0	1376.7
40°	2103.5	1870.9	1676.0	1530.6	1424.6	1356.2	1258.7	1209.1	1183.4	1173.2	1168.1
42.5°	1982.1	1686.2	1426.3	1246.7	1132.1	1055.1	990.2	959.4	957.7	956.0	956.0
45°	1852.1	1487.9	1183.4	969.6	868.8	800.3	769.5	757.6	767.9	766.1	767.9
47.5°	1771.7	1337.3	961.1	733.7	656.7	612.2	596.9	602.0	610.6	607.2	607.2
50°	1761.5	1260.4	812.3	571.2	513.1	490.8	487.4	487.4	492.5	489.1	487.4
52.5°	1799.1	1248.4	735.3	490.8	444.7	425.8	422.4	420.7	419.0	408.7	400.2
55°	1864.0	1275.8	713.2	470.3	422.4	401.9	396.8	393.4	386.5	372.8	357.4
57.5°	1994.1	1361.3	733.7	480.5	429.2	412.1	407.0	407.0	393.4	371.1	348.9
60°	2307.0	1578.4	817.5	519.9	461.8	444.7	448.1	446.3	425.8	393.4	359.2
62.5°	2710.7	1862.4	926.9	574.6	502.8	499.4	516.5	513.1	478.9	429.2	379.7
65°	2897.0	1995.8	957.7	586.6	511.3	526.7	560.9	557.5	514.7	446.3	383.1
66°	2900.4	1995.8	944.0	576.4	499.4	518.1	552.4	550.7	507.9	439.5	376.3
67.5°	2830.4	1941.0	904.7	555.9	475.4	489.1	519.9	518.1	478.9	422.4	362.6
70°	2566.9	1737.5	803.8	519.9	442.9	436.1	446.3	439.5	413.9	374.5	333.5
72.5°	2199.3	1458.8	701.1	492.5	420.7	393.4	386.5	381.3	360.8	338.7	313.0
75°	1732.4	1154.4	615.6	472.0	400.2	364.2	352.3	345.5	331.8	316.4	295.9
77.5°	1068.8	826.0	537.0	444.7	384.8	348.9	340.3	330.1	309.5	290.8	275.3
80°	477.1	511.3	441.2	388.2	343.7	311.3	297.6	282.2	261.7	249.6	241.1
82.5°	318.1	330.1	319.8	290.8	259.9	234.3	213.8	213.8	210.4	200.1	196.7
85°	203.5	205.2	198.3	179.6	167.6	152.2	143.6	145.4	152.2	150.5	148.8
87.5°	46.2	46.2	54.7	51.3	59.9	63.3	68.4	73.6	83.8	83.8	88.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156492

CATALOG NUMBER: VXS-E05-LED-E1-T4-7060

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	2043.6	2043.6	2043.6	2043.6	2043.6
2.5°	2103.5	2106.9	2110.4	2105.2	2106.9
5°	2163.4	2161.7	2170.3	2165.1	2168.5
7.5°	2182.2	2183.9	2190.8	2190.8	2192.4
10°	2183.9	2187.4	2195.9	2201.0	2204.5
12.5°	2192.4	2199.3	2213.0	2216.4	2216.4
15°	2199.3	2202.7	2211.3	2214.7	2218.1
17.5°	2175.3	2168.5	2171.9	2173.7	2171.9
20°	2115.4	2108.6	2106.9	2100.1	2103.5
22.5°	2050.5	2031.7	2019.7	2006.0	2006.0
25°	1971.8	1942.8	1918.9	1894.9	1900.0
27.5°	1898.3	1860.6	1836.7	1821.3	1817.9
30°	1826.4	1787.2	1764.9	1746.1	1746.1
32.5°	1706.7	1679.4	1650.4	1638.3	1636.7
35°	1540.8	1523.7	1499.8	1494.7	1486.1
37.5°	1354.5	1349.3	1328.8	1327.0	1318.5
40°	1159.5	1162.9	1156.1	1152.6	1147.6
42.5°	964.6	981.7	978.2	976.5	973.1
45°	778.1	790.1	791.8	796.9	805.5
47.5°	612.2	615.6	619.1	617.4	619.1
50°	478.9	470.3	468.6	463.4	468.6
52.5°	386.5	372.8	366.0	359.2	355.8
55°	340.3	326.6	319.8	316.4	313.0
57.5°	328.4	314.7	304.5	297.6	295.9
60°	331.8	311.3	297.6	289.0	287.4
62.5°	340.3	313.0	294.2	285.6	283.9
65°	338.7	309.5	292.4	282.2	280.5
66°	333.5	306.1	289.0	280.5	278.8
67.5°	325.0	301.0	285.6	278.8	275.3
70°	309.5	294.2	282.2	273.7	270.3
72.5°	295.9	283.9	273.7	265.1	263.3
75°	280.5	270.3	259.9	253.1	251.4
77.5°	261.7	251.4	244.6	239.4	237.7
80°	230.9	224.0	217.2	210.4	210.4
82.5°	191.5	186.4	179.6	174.4	172.7
85°	147.0	147.0	142.0	136.8	135.1
87.5°	87.3	85.5	85.5	80.4	80.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)