

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P152184

Luminaire Tested: **VXS-F05-LED-E1-SL4-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P152184
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-SL4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (35) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11136.9 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P152184

CATALOG NUMBER: VXS-F05-LED-E1-SL4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 6 fc
Type IV - Short - Full Cutoff

REPORT NUMBER: P152184

CATALOG NUMBER: VXS-F05-LED-E1-SL4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P152184

CATALOG NUMBER: VXS-F05-LED-E1-SL4-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2311.9	0.0	2311.9
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	8825.0	0.0	8825.0
	% Fixture	79.2	0.0	79.2
Total	Lumens	11136.9	0.0	11136.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.0	2.0
10°-20°	607.7	5.5
20°-30°	899.7	8.1
30°-40°	1137.0	10.2
40°-50°	1285.8	11.5
50°-60°	1829.8	16.4
60°-70°	3407.8	30.6
70°-80°	1561.8	14.0
80°-90°	185.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11136.9	100.0
0°-180°	11136.9	100.0

Coefficient of Utilization



REPORT NUMBER: P152184


CATALOG NUMBER: VXS-F05-LED-E1-SL4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1014.1	9.1			
FM	(30°-60°)	3262.7	29.3			
FH	(60°-80°)	4410.6	39.6			G2/5000
FVH	(80°-90°)	137.5	1.2			G2/225
BL	(0°-30°)	715.3	6.4	B2/1000		
BM	(30°-60°)	989.8	8.9	B1/1000		
BH	(60°-80°)	558.9	5.0	B2/1000		G2/1000
BVH	(80°-90°)	47.9	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short



REPORT NUMBER: P152184

CATALOG NUMBER: VXS-F05-LED-E1-SL4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4
2.5°	2412.7	2419.1	2411.5	2410.3	2410.3	2409.0	2401.5	2400.2	2390.2	2391.4	2393.9
5°	2430.4	2432.8	2427.9	2426.6	2424.0	2419.1	2412.7	2405.3	2397.7	2390.2	2383.8
7.5°	2448.0	2445.5	2441.7	2441.7	2437.9	2430.4	2417.8	2407.8	2391.4	2382.6	2371.3
10°	2473.1	2469.3	2464.4	2461.8	2455.5	2444.1	2426.6	2412.7	2392.6	2375.1	2356.3
12.5°	2497.0	2495.8	2488.2	2484.5	2474.4	2463.0	2441.7	2420.3	2393.9	2366.3	2341.1
15°	2539.7	2534.7	2527.2	2519.6	2503.2	2488.2	2455.5	2430.4	2392.6	2356.3	2317.3
17.5°	2613.9	2605.1	2597.5	2581.1	2561.0	2534.7	2486.9	2444.1	2392.6	2339.9	2296.0
20°	2749.5	2730.7	2720.6	2699.3	2664.1	2616.4	2542.2	2473.1	2396.5	2328.6	2269.5
22.5°	2902.9	2890.3	2876.5	2862.7	2807.4	2738.2	2637.7	2534.7	2419.1	2323.5	2248.2
25°	3075.0	3058.7	3051.2	3027.3	2975.8	2896.6	2759.6	2616.4	2470.6	2343.6	2248.2
27.5°	3228.4	3223.3	3222.1	3194.4	3145.4	3052.4	2890.3	2718.1	2540.9	2385.2	2267.0
30°	3367.9	3362.8	3360.3	3345.2	3288.7	3178.0	3002.2	2808.6	2617.6	2442.9	2302.2
32.5°	3516.2	3499.8	3492.2	3463.3	3399.3	3269.8	3068.7	2867.7	2677.9	2499.5	2341.1
35°	3636.8	3622.9	3607.9	3566.4	3476.0	3322.6	3097.6	2887.8	2701.8	2530.9	2361.2
37.5°	3724.8	3710.9	3689.5	3636.8	3524.9	3340.2	3096.4	2881.6	2693.1	2525.9	2365.1
40°	3763.7	3749.8	3727.3	3660.6	3533.7	3330.2	3072.5	2852.6	2666.6	2499.5	2349.9
42.5°	3748.6	3738.5	3709.6	3645.6	3506.1	3284.9	3024.8	2798.5	2616.4	2456.8	2316.1
45°	3690.8	3683.2	3655.6	3587.8	3443.2	3212.0	2954.4	2730.7	2556.1	2403.9	2270.8
47.5°	3604.0	3601.6	3573.9	3507.4	3364.0	3139.2	2881.6	2664.1	2495.8	2352.4	2233.1
50°	3508.6	3496.1	3482.2	3420.6	3289.9	3076.3	2828.7	2622.6	2461.8	2333.6	2216.8
52.5°	3448.3	3444.5	3431.9	3376.7	3251.0	3039.9	2804.9	2607.6	2459.3	2329.8	2208.0
55°	3983.6	3992.4	3876.8	3636.8	3425.6	3140.4	2876.5	2684.2	2520.8	2390.2	2300.9
57.5°	5892.4	5853.5	5654.9	5178.7	4640.8	3930.8	3419.4	3109.0	2906.6	2929.2	2974.5
60°	6865.1	6857.6	6821.1	6636.4	6278.2	5737.9	5138.4	4451.1	4232.4	4256.3	4273.9
62.5°	7299.9	7311.2	7338.9	7269.7	7175.5	7018.4	6719.4	6442.9	6150.1	6040.7	5748.0
65°	7500.9	7521.0	7583.9	7622.9	7659.3	7686.9	7805.1	8129.3	8342.9	7943.3	7013.4
67.5°	7085.0	7181.8	7389.1	7591.5	7772.4	8030.1	8429.6	9182.4	9706.4	9215.0	7866.6
70°	5164.9	5296.8	5534.3	6160.1	6828.7	7413.1	8187.2	9333.2	10123.6	9744.1	8077.8
72.5°	3238.4	3274.8	3380.4	3610.4	4106.7	4857.0	6210.4	7929.5	8841.9	8539.0	6827.5
75°	2054.6	2067.2	2063.4	2116.2	2200.4	2363.7	2899.1	4683.5	6057.1	5584.6	3805.2
77.5°	1223.9	1242.8	1250.4	1266.7	1306.9	1364.8	1408.7	1593.5	2539.7	2465.6	1381.0
80°	1025.4	1040.5	1028.0	1024.1	999.1	981.5	1002.8	981.5	911.1	877.1	808.0
82.5°	542.9	541.7	537.8	574.3	648.4	706.2	750.3	740.2	669.8	570.6	483.8
85°	297.8	307.9	307.9	320.4	309.1	310.4	320.4	338.0	313.0	261.3	213.7
87.5°	25.2	39.0	31.4	39.0	52.7	37.7	36.5	36.5	31.4	22.6	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152184

CATALOG NUMBER: VXS-F05-LED-E1-SL4-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4
2.5°	2387.7	2385.2	2380.1	2376.4	2376.4	2370.1	2366.3	2363.7	2362.5	2357.5	2357.5
5°	2380.1	2371.3	2362.5	2356.3	2352.4	2346.2	2336.2	2331.1	2324.8	2319.8	2317.3
7.5°	2363.7	2347.5	2333.6	2323.5	2311.0	2300.9	2288.4	2277.1	2265.7	2260.7	2258.2
10°	2338.7	2317.3	2296.0	2277.1	2259.5	2241.9	2225.5	2209.2	2195.3	2185.3	2175.2
12.5°	2314.7	2282.1	2254.4	2226.8	2199.2	2177.8	2155.1	2131.3	2111.2	2092.3	2087.3
15°	2282.1	2244.4	2209.2	2175.2	2141.3	2106.1	2078.5	2052.1	2019.5	1998.0	1981.8
17.5°	2251.9	2206.7	2163.9	2123.7	2082.3	2045.8	2004.4	1969.2	1936.5	1903.8	1880.0
20°	2219.3	2170.3	2125.0	2079.8	2034.5	1988.0	1940.3	1895.0	1854.8	1815.9	1776.9
22.5°	2190.4	2140.1	2096.1	2047.0	1996.8	1944.0	1888.7	1832.2	1785.7	1735.4	1690.2
25°	2172.7	2117.5	2072.2	2024.5	1969.2	1911.4	1848.5	1782.0	1725.4	1667.6	1613.6
27.5°	2172.7	2101.1	2054.6	2006.8	1950.4	1888.7	1819.7	1746.7	1682.7	1618.5	1552.0
30°	2191.6	2103.6	2040.8	1990.6	1932.7	1866.1	1789.4	1712.8	1642.5	1567.0	1503.0
32.5°	2209.2	2108.7	2030.8	1966.6	1900.1	1834.7	1756.8	1675.1	1597.2	1525.6	1457.7
35°	2220.5	2108.7	2011.9	1930.3	1854.8	1790.8	1714.1	1632.4	1553.3	1482.9	1420.0
37.5°	2221.8	2098.7	1981.8	1888.7	1809.5	1743.0	1670.1	1593.5	1518.0	1452.6	1399.9
40°	2209.2	2078.5	1951.6	1844.8	1761.9	1694.0	1627.4	1558.2	1490.4	1436.4	1391.1
42.5°	2186.6	2057.1	1922.7	1809.5	1722.9	1652.5	1590.9	1531.8	1472.8	1426.3	1388.6
45°	2152.6	2028.3	1896.3	1788.2	1702.8	1628.6	1568.3	1519.3	1469.0	1430.1	1392.3
47.5°	2122.5	2018.2	1905.1	1802.1	1712.8	1636.2	1574.6	1533.2	1494.2	1467.8	1416.3
50°	2116.2	2013.2	1908.9	1813.4	1722.9	1645.0	1590.9	1569.5	1558.2	1541.9	1462.8
52.5°	2098.7	2011.9	1936.5	1883.7	1825.9	1789.4	1733.0	1753.1	1740.5	1682.7	1539.4
55°	2283.3	2308.5	2378.9	2479.4	2572.3	2593.8	2587.5	2563.6	2436.7	2096.1	1724.1
57.5°	3139.2	3281.1	3414.3	3473.4	3465.9	3399.3	3351.5	3254.7	3071.3	2656.6	2088.6
60°	4327.9	4350.6	4280.2	4175.9	3999.9	3853.0	3695.9	3514.8	3248.5	2842.6	2312.2
62.5°	5422.5	5118.3	4805.5	4511.4	4243.7	4009.9	3791.3	3538.8	3191.9	2768.4	2283.3
65°	6195.3	5551.9	5058.0	4635.9	4257.5	3930.8	3658.1	3330.2	2939.3	2557.3	2116.2
67.5°	6593.7	5607.2	4849.4	4261.3	3724.8	3272.3	2909.1	2589.9	2299.7	2132.5	1852.3
70°	6148.8	4759.0	3703.3	3038.5	2396.5	1921.5	1518.0	1274.3	1190.1	1348.4	1402.4
72.5°	4581.8	3097.6	2202.9	1704.0	1305.7	1040.5	797.9	627.0	510.2	535.3	694.9
75°	2166.4	1337.1	945.0	718.8	571.8	473.8	387.0	354.4	296.6	246.3	231.2
77.5°	843.2	614.5	507.7	372.0	263.9	212.3	180.9	174.7	178.4	173.4	170.9
80°	642.2	434.8	272.7	199.8	172.1	152.0	134.5	129.4	131.9	138.2	144.6
82.5°	358.1	223.7	165.9	144.6	129.4	110.6	100.5	93.0	94.3	101.8	115.6
85°	138.2	108.1	99.3	95.5	89.2	71.6	61.6	62.8	71.6	85.5	85.5
87.5°	15.1	15.1	20.1	15.1	15.1	15.1	13.8	16.4	17.6	22.6	26.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152184

CATALOG NUMBER: VXS-F05-LED-E1-SL4-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4	2376.4
2.5°	2354.9	2354.9	2354.9	2352.4	2353.7	2348.7	2348.7	2344.9	2351.2	2347.5	2346.2
5°	2318.5	2317.3	2312.2	2312.2	2312.2	2312.2	2316.1	2306.0	2313.5	2313.5	2309.7
7.5°	2257.0	2257.0	2243.1	2250.7	2248.2	2251.9	2257.0	2251.9	2259.5	2264.5	2260.7
10°	2171.5	2171.5	2160.2	2169.0	2165.2	2174.0	2182.8	2177.8	2182.8	2190.4	2192.8
12.5°	2077.2	2072.2	2062.2	2065.9	2065.9	2071.0	2074.7	2081.0	2087.3	2097.4	2102.4
15°	1967.9	1960.4	1947.8	1947.8	1940.3	1942.8	1950.4	1952.8	1965.4	1979.3	1995.5
17.5°	1856.1	1837.2	1823.4	1807.0	1794.5	1804.6	1813.4	1819.7	1829.7	1851.1	1862.4
20°	1750.6	1712.8	1686.4	1665.1	1651.3	1657.5	1668.8	1676.4	1685.2	1690.2	1694.0
22.5°	1646.2	1603.5	1567.0	1540.6	1518.0	1524.4	1519.3	1515.5	1521.8	1505.5	1504.2
25°	1555.8	1505.5	1456.5	1425.1	1397.4	1388.6	1362.2	1356.0	1338.3	1324.6	1314.5
27.5°	1490.4	1425.1	1371.0	1334.6	1290.6	1257.9	1223.9	1190.1	1171.2	1148.6	1137.3
30°	1438.9	1369.7	1305.7	1244.0	1186.3	1136.1	1090.8	1046.8	1016.7	983.9	962.6
32.5°	1391.1	1327.0	1249.1	1164.9	1087.0	1030.5	971.4	921.1	873.4	830.7	799.3
35°	1358.4	1286.8	1187.6	1084.5	996.5	929.9	867.0	795.4	737.6	682.4	648.4
37.5°	1340.8	1252.8	1131.0	1016.7	918.7	843.2	765.3	682.4	612.0	560.5	508.9
40°	1327.0	1219.0	1080.7	956.3	853.3	762.8	672.3	574.3	496.4	442.4	402.2
42.5°	1311.9	1181.2	1036.8	908.6	794.2	688.6	579.3	475.0	400.8	363.2	345.6
45°	1295.6	1148.6	995.2	863.3	736.4	608.2	482.6	385.8	341.8	329.2	329.2
47.5°	1291.8	1127.3	965.1	819.4	671.1	515.2	393.4	333.1	320.4	323.0	328.0
50°	1306.9	1120.9	938.8	767.8	584.4	417.2	333.1	313.0	315.4	323.0	330.5
52.5°	1343.3	1126.0	911.1	696.2	481.3	344.4	307.9	306.6	314.2	325.5	333.1
55°	1405.0	1126.0	858.3	589.3	384.6	309.1	299.1	304.1	314.2	324.2	330.5
57.5°	1536.9	1114.6	765.3	471.3	321.7	296.6	296.6	302.9	311.6	321.7	326.7
60°	1694.0	1099.6	634.6	364.5	290.3	286.5	295.3	302.9	310.4	319.2	324.2
62.5°	1704.0	1060.6	502.7	301.6	274.0	280.2	294.1	304.1	306.6	313.0	319.2
65°	1565.8	924.9	399.6	270.2	266.4	276.5	290.3	297.8	299.1	301.6	307.9
67.5°	1371.0	754.0	323.0	255.1	258.9	270.2	277.7	284.0	287.8	294.1	295.3
70°	1126.0	605.7	276.5	240.0	243.8	256.4	262.6	268.9	276.5	284.0	280.2
72.5°	797.9	471.3	242.5	223.7	228.7	240.0	247.6	252.5	258.9	266.4	261.3
75°	339.3	329.2	209.8	202.3	209.8	217.4	225.0	232.4	238.8	242.5	242.5
77.5°	173.4	193.6	180.9	180.9	186.0	193.6	199.8	207.4	211.1	214.9	219.9
80°	147.0	149.5	152.0	157.1	162.1	169.6	176.0	182.2	183.5	184.8	187.3
82.5°	121.9	126.9	129.4	137.0	140.7	143.2	147.0	147.0	149.5	149.5	145.8
85°	88.0	94.3	98.0	99.3	98.0	99.3	100.5	103.0	109.3	109.3	104.4
87.5°	25.2	23.8	30.2	31.4	33.9	39.0	43.9	52.7	55.3	57.8	57.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152184

CATALOG NUMBER: VXS-F05-LED-E1-SL4-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2376.4	2376.4	2376.4	2376.4
2.5°	2344.9	2347.5	2342.4	2343.6
5°	2309.7	2314.7	2308.5	2316.1
7.5°	2264.5	2272.0	2270.8	2269.5
10°	2199.2	2209.2	2209.2	2213.0
12.5°	2116.2	2122.5	2127.6	2130.1
15°	2004.4	2015.6	2022.0	2022.0
17.5°	1869.9	1877.4	1881.2	1876.2
20°	1699.0	1696.5	1697.7	1685.2
22.5°	1501.7	1505.5	1494.2	1496.7
25°	1308.2	1301.9	1306.9	1299.4
27.5°	1120.9	1122.2	1108.4	1114.6
30°	942.5	936.2	918.7	927.5
32.5°	770.4	754.0	735.1	723.8
35°	608.2	583.1	574.3	570.6
37.5°	477.5	449.8	441.0	431.0
40°	379.5	369.4	365.7	368.2
42.5°	340.5	340.5	343.1	344.4
45°	330.5	334.3	338.0	339.3
47.5°	331.7	335.5	340.5	341.8
50°	334.3	338.0	341.8	343.1
52.5°	335.5	335.5	338.0	339.3
55°	333.1	331.7	333.1	334.3
57.5°	328.0	325.5	326.7	330.5
60°	325.5	321.7	324.2	326.7
62.5°	319.2	317.9	320.4	321.7
65°	305.4	306.6	310.4	310.4
67.5°	292.8	294.1	295.3	296.6
70°	277.7	279.0	281.5	282.8
72.5°	260.1	265.2	268.9	274.0
75°	246.3	251.3	258.9	263.9
77.5°	222.4	226.2	235.0	241.2
80°	188.5	187.3	188.5	192.2
82.5°	144.6	144.6	143.2	142.0
85°	101.8	100.5	96.8	96.8
87.5°	55.3	54.0	52.7	50.3
90°	0.0	0.0	0.0	0.0

(END OF REPORT)