

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P148257

Luminaire Tested: **VXS-F06-LED-E1-5XQ-7060**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P148257
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F06-LED-E1-5XQ-7060
Description: VISION SITE SMALL LED LUMINAIRE
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (42) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16164.1 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U0 - G3


Input Watts (W): 156.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P148257
 CATALOG NUMBER: VXS-F06-LED-E1-5XQ-7060

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.5 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148257
CATALOG NUMBER: VXS-F06-LED-E1-5XQ-7060

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P148257

CATALOG NUMBER: VXS-F06-LED-E1-5XQ-7060


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8082.1	0.0	8082.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8082.1	0.0	8082.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	16164.1	0.0	16164.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	0.9
10°-20°	431.8	2.7
20°-30°	723.0	4.5
30°-40°	1102.2	6.8
40°-50°	1760.0	10.9
50°-60°	2706.1	16.7
60°-70°	3940.2	24.4
70°-80°	4438.6	27.5
80°-90°	916.3	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16164.1	100.0
0°-180°	16164.1	100.0



REPORT NUMBER: P148257


CATALOG NUMBER: VXS-F06-LED-E1-5XQ-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	650.4	4.0			
FM	(30°-60°)	2784.2	17.2			
FH	(60°-80°)	4189.4	25.9			G2/5000
FVH	(80°-90°)	458.1	2.8			G3/500
BL	(0°-30°)	650.4	4.0	B2/1000		
BM	(30°-60°)	2784.2	17.2	B3/5000		
BH	(60°-80°)	4189.4	25.9	B4/5000		G2/5000
BVH	(80°-90°)	458.1	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3

Type V Short





REPORT NUMBER: P148257

CATALOG NUMBER: VXS-F06-LED-E1-5XQ-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5
2.5°	1534.1	1534.9	1534.5	1533.6	1534.1	1533.6	1532.7	1532.3	1529.3	1531.1	1533.7
5°	1534.1	1533.3	1532.7	1532.3	1532.3	1533.7	1532.3	1531.1	1530.7	1531.5	1530.3
7.5°	1533.3	1531.5	1530.7	1530.3	1530.7	1531.1	1529.8	1528.1	1529.4	1528.1	1526.4
10°	1530.7	1529.4	1529.8	1528.1	1528.5	1528.1	1526.4	1525.2	1526.0	1524.8	1522.6
12.5°	1531.5	1529.3	1529.0	1528.1	1527.7	1527.3	1525.2	1523.0	1523.4	1522.6	1520.5
15°	1531.5	1530.3	1529.8	1528.1	1527.7	1526.8	1524.2	1523.4	1523.4	1522.2	1519.6
17.5°	1532.4	1531.5	1531.5	1529.3	1528.5	1528.2	1525.2	1523.9	1525.2	1522.6	1520.9
20°	1534.9	1534.1	1534.5	1533.3	1531.5	1531.5	1529.4	1528.6	1529.0	1528.5	1523.9
22.5°	1540.0	1540.0	1540.8	1540.4	1540.0	1540.4	1538.7	1538.7	1539.2	1539.2	1535.3
25°	1554.3	1554.0	1554.8	1554.8	1555.2	1558.2	1556.9	1556.5	1558.7	1558.7	1554.8
27.5°	1581.6	1580.6	1581.5	1582.4	1584.5	1588.3	1587.4	1588.7	1592.1	1591.2	1587.9
30°	1612.8	1612.0	1614.1	1616.7	1618.3	1624.2	1621.7	1628.1	1631.1	1633.6	1631.1
32.5°	1658.5	1658.7	1662.4	1664.0	1667.9	1673.8	1674.7	1679.7	1683.5	1687.8	1684.9
35°	1719.6	1718.8	1721.7	1724.7	1729.3	1734.8	1737.0	1743.7	1749.6	1752.5	1747.2
37.5°	1812.7	1808.1	1813.6	1815.3	1819.1	1820.4	1826.3	1834.8	1841.1	1840.3	1836.5
40°	1938.9	1938.1	1936.0	1933.5	1939.4	1941.6	1941.6	1953.0	1963.1	1961.5	1961.0
42.5°	2086.4	2082.5	2080.0	2080.0	2083.3	2084.2	2097.4	2105.8	2113.1	2114.7	2113.0
45°	2244.8	2240.9	2241.8	2240.0	2241.3	2246.8	2254.5	2270.2	2283.7	2284.1	2276.9
47.5°	2414.9	2403.1	2412.4	2399.4	2407.4	2411.6	2430.7	2453.6	2477.3	2481.5	2475.2
50°	2587.8	2586.5	2585.7	2583.1	2586.9	2596.3	2619.6	2655.5	2678.4	2693.7	2683.5
52.5°	2776.7	2770.4	2767.4	2763.1	2767.0	2785.2	2817.8	2849.1	2890.3	2907.6	2893.7
55°	2960.6	2958.4	2947.5	2946.9	2955.0	2983.4	3019.0	3057.5	3102.0	3121.5	3116.4
57.5°	3149.4	3137.1	3133.8	3128.7	3144.8	3171.4	3215.1	3284.6	3330.7	3352.7	3340.0
60°	3334.1	3324.8	3317.6	3316.0	3326.8	3364.2	3426.8	3510.3	3567.5	3596.3	3576.0
62.5°	3532.3	3526.4	3517.9	3508.2	3531.4	3579.3	3657.2	3749.6	3833.9	3869.4	3838.5
65°	3778.9	3766.5	3757.2	3744.9	3763.9	3824.1	3922.0	4052.0	4165.1	4206.6	4184.6
67.5°	4038.9	4027.5	4028.3	4020.6	4054.5	4138.0	4264.1	4440.8	4592.4	4663.1	4621.7
70°	4265.9	4272.2	4274.0	4304.9	4363.3	4490.4	4700.4	4977.0	5206.9	5315.0	5270.5
71°	4199.0	4213.0	4234.5	4266.7	4367.6	4517.9	4804.6	5139.7	5414.1	5597.1	5535.6
72.5°	4009.2	4017.6	4028.7	4077.8	4191.7	4390.9	4686.0	5068.9	5421.7	5658.4	5587.4
75°	3734.7	3742.8	3746.6	3780.9	3884.7	4058.3	4328.5	4668.2	4979.5	5181.1	5161.2
77.5°	3320.5	3321.8	3351.5	3404.4	3520.8	3719.5	4004.1	4356.5	4649.2	4805.9	4706.3
80°	2384.5	2368.4	2399.0	2467.2	2611.1	2839.0	3130.4	3532.7	3857.6	4004.1	3849.9
82.5°	907.3	956.4	1033.8	1146.5	1195.2	1448.5	1720.4	1956.8	2230.4	2536.2	2459.5
85°	97.4	109.7	137.6	170.7	215.5	298.2	412.1	562.5	693.4	814.9	723.4
87.5°	36.5	37.3	41.5	47.9	48.7	50.9	54.2	63.1	58.9	50.8	41.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148257

CATALOG NUMBER: VXS-F06-LED-E1-5XQ-7060

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5	1531.5
2.5°	1531.5	1531.9	1531.5	1531.9	1531.9	1530.3	1530.7	1529.7
5°	1531.1	1529.8	1530.3	1530.7	1530.3	1531.1	1529.8	1530.7
7.5°	1528.9	1526.4	1527.3	1527.3	1526.4	1527.7	1526.8	1526.4
10°	1524.8	1521.3	1523.0	1522.2	1521.8	1522.2	1522.2	1522.2
12.5°	1520.9	1518.8	1519.3	1518.8	1518.3	1519.7	1519.3	1519.6
15°	1520.1	1516.7	1516.3	1515.4	1515.9	1516.7	1516.7	1517.9
17.5°	1519.2	1515.0	1514.6	1513.8	1514.2	1515.9	1516.3	1515.4
20°	1521.8	1518.3	1517.5	1516.7	1516.3	1518.3	1517.9	1517.9
22.5°	1533.6	1529.4	1529.0	1525.6	1524.4	1525.6	1524.8	1524.8
25°	1552.6	1547.6	1545.9	1541.2	1537.8	1537.8	1536.6	1535.8
27.5°	1586.9	1579.4	1577.6	1573.9	1569.2	1570.1	1567.6	1567.0
30°	1626.8	1620.1	1614.1	1608.6	1603.1	1600.9	1598.0	1597.6
32.5°	1679.0	1671.3	1664.0	1657.3	1649.6	1646.7	1641.7	1639.1
35°	1742.9	1732.6	1724.2	1719.6	1711.9	1708.2	1704.8	1708.6
37.5°	1832.2	1819.9	1815.8	1810.2	1805.1	1799.2	1800.4	1799.2
40°	1956.0	1944.9	1940.7	1930.9	1929.6	1922.8	1927.0	1922.9
42.5°	2108.8	2088.5	2085.5	2077.9	2075.3	2071.5	2073.2	2070.3
45°	2275.2	2257.0	2253.7	2241.3	2241.9	2232.8	2236.3	2236.3
47.5°	2462.4	2443.4	2427.8	2418.9	2415.4	2409.9	2413.0	2412.4
50°	2655.5	2629.7	2612.4	2595.0	2587.4	2589.5	2583.6	2593.8
52.5°	2863.1	2824.6	2800.0	2783.5	2769.1	2772.0	2772.8	2775.9
55°	3077.8	3028.7	2993.2	2971.5	2958.3	2959.3	2963.1	2966.4
57.5°	3293.9	3232.4	3184.1	3151.9	3143.5	3147.3	3147.4	3146.9
60°	3517.9	3444.2	3382.0	3345.5	3337.9	3335.8	3352.3	3346.7
62.5°	3758.4	3669.9	3605.6	3559.0	3548.0	3555.6	3570.4	3567.0
65°	4077.4	3955.0	3872.0	3825.8	3807.3	3814.8	3834.7	3833.9
67.5°	4488.6	4317.5	4207.9	4148.6	4134.9	4144.4	4155.3	4165.9
70°	5103.6	4859.3	4702.6	4574.2	4519.2	4508.6	4519.6	4520.0
71°	5320.0	5039.3	4789.8	4633.1	4542.8	4504.8	4507.8	4488.7
72.5°	5311.2	4965.2	4673.4	4509.4	4384.0	4353.6	4338.7	4315.9
75°	4953.3	4641.6	4388.3	4209.5	4088.8	4052.8	4026.5	4025.3
77.5°	4492.0	4262.1	3983.0	3793.7	3646.6	3586.9	3560.2	3559.4
80°	3611.1	3266.7	3062.6	2948.6	2771.2	2720.0	2665.8	2645.4
82.5°	2183.8	1706.4	1387.6	1233.0	1147.4	944.9	847.9	802.3
85°	508.7	361.2	249.0	163.5	117.7	93.6	72.0	63.5
87.5°	34.3	27.2	24.1	19.5	14.8	14.4	8.9	7.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)