

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P151571

Luminaire Tested: **VXS-E01-LED-E1-SL4-HSS-7050**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P151571
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E01-LED-E1-SL4-HSS-7050
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (21) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2087.9 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G1


Input Watts (W): 24.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P151571
 CATALOG NUMBER: VXS-E01-LED-E1-SL4-HSS-7050

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.7 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P151571
CATALOG NUMBER: VXS-E01-LED-E1-SL4-HSS-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P151571

CATALOG NUMBER: VXS-E01-LED-E1-SL4-HSS-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	62.2	0.0	62.2
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	2025.7	0.0	2025.7
	% Fixture	97.0	0.0	97.0
Total	Lumens	2087.9	0.0	2087.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.2	0.8
10°-20°	55.9	2.7
20°-30°	106.9	5.1
30°-40°	177.9	8.5
40°-50°	240.7	11.5
50°-60°	376.4	18.0
60°-70°	773.8	37.1
70°-80°	311.4	14.9
80°-90°	28.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2087.9	100.0
0°-180°	2087.9	100.0



REPORT NUMBER: P151571


CATALOG NUMBER: VXS-E01-LED-E1-SL4-HSS-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	155.4	7.4			
FM	(30°-60°)	766.5	36.7			
FH	(60°-80°)	1076.1	51.5			G1/1800
FVH	(80°-90°)	27.7	1.3			G1/100
BL	(0°-30°)	23.6	1.1	B0/110		
BM	(30°-60°)	28.4	1.4	B0/220		
BH	(60°-80°)	9.1	0.4	B0/110		G0/110
BVH	(80°-90°)	1.1	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type IV Short





REPORT NUMBER: P151571

CATALOG NUMBER: VXS-E01-LED-E1-SL4-HSS-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7
2.5°	210.4	208.0	205.2	205.2	201.8	201.8	199.8	194.3	193.6	190.5	187.5
5°	268.5	266.4	263.0	259.9	257.2	252.4	249.0	242.5	235.3	228.5	222.3
7.5°	325.3	324.2	318.1	317.1	312.6	304.8	297.9	288.3	276.1	266.4	255.1
10°	377.9	375.5	374.2	368.4	361.9	353.4	342.7	331.1	316.7	301.7	285.6
12.5°	419.7	418.3	412.1	409.7	402.9	394.4	381.0	366.0	351.6	332.1	313.3
15°	450.8	448.4	444.4	440.5	432.3	424.8	412.5	396.1	378.7	357.4	334.8
17.5°	476.8	472.3	471.3	465.5	457.0	448.1	434.4	419.4	398.9	377.6	353.0
20°	511.7	505.5	503.5	494.9	485.0	472.6	457.0	438.1	416.6	393.4	368.0
22.5°	552.7	548.3	543.8	536.3	523.6	506.2	483.3	462.8	435.4	409.7	382.4
25°	610.9	607.2	599.9	589.6	573.9	553.1	525.4	495.2	463.1	430.3	398.1
27.5°	667.4	663.9	658.8	650.9	633.1	610.2	576.0	537.7	497.0	457.3	421.8
30°	720.3	717.2	712.1	704.2	688.5	665.9	627.3	586.2	535.6	489.4	446.7
32.5°	777.4	776.4	770.6	759.3	745.6	715.2	673.2	629.0	577.7	524.4	474.4
35°	842.1	834.2	828.7	817.5	794.2	761.8	712.4	664.2	610.2	555.4	499.7
37.5°	896.8	889.3	882.5	868.1	839.7	798.3	742.6	689.5	633.8	578.0	521.2
40°	936.8	933.1	924.9	906.0	874.2	825.0	764.8	706.9	650.9	594.8	538.8
42.5°	966.6	960.7	951.5	932.0	894.4	838.3	773.7	714.2	658.8	605.1	549.9
45°	977.5	972.7	964.2	943.0	902.3	842.1	773.4	712.1	659.1	608.2	557.5
47.5°	971.1	966.2	958.8	938.9	898.9	837.6	767.2	706.3	655.6	609.1	564.4
50°	949.5	946.7	940.9	924.1	888.3	829.1	761.8	703.2	655.0	614.3	573.9
52.5°	947.5	945.7	938.5	921.8	885.2	826.3	761.0	705.0	660.8	620.8	580.7
55°	1157.8	1133.5	1079.2	1033.0	957.0	866.7	795.5	732.6	685.4	646.4	618.4
57.5°	1645.5	1609.3	1537.8	1449.8	1275.4	1104.0	966.9	867.8	818.9	801.0	811.6
60°	1874.0	1867.5	1856.3	1814.5	1725.2	1577.8	1413.7	1236.2	1165.0	1158.9	1180.4
62.5°	1982.5	1978.3	1981.8	1976.6	1948.9	1905.8	1858.7	1782.0	1711.5	1666.0	1569.6
65°	2032.3	2035.1	2054.6	2069.9	2073.4	2084.7	2119.3	2214.7	2284.5	2167.2	1899.3
67.5°	1905.5	1921.6	1966.3	2022.5	2088.1	2151.7	2254.4	2455.4	2598.8	2460.9	2080.6
69°	1577.5	1585.3	1694.8	1800.5	1960.9	2073.1	2221.9	2485.6	2646.6	2491.1	2066.2
70°	1242.0	1249.1	1366.4	1510.1	1781.3	1925.7	2120.3	2434.6	2601.9	2451.0	1992.3
72.5°	560.2	549.9	591.4	668.3	963.2	1192.3	1532.6	1972.5	2146.6	1963.6	1490.6
75°	391.3	386.8	391.3	391.6	437.5	564.4	712.1	1069.2	1322.3	1141.0	712.1
77.5°	303.0	300.0	296.9	293.5	299.0	334.8	349.2	379.3	492.5	465.8	271.6
80°	239.8	237.0	244.6	242.2	242.2	246.2	243.5	232.2	211.0	195.6	175.1
82.5°	111.5	112.2	112.2	121.8	146.7	171.4	179.3	168.0	149.1	126.9	102.3
85°	10.6	12.0	20.2	31.1	61.9	69.7	70.2	58.1	58.1	45.8	36.9
87.5°	0.0	0.3	0.3	0.3	3.1	8.6	7.2	2.1	1.0	1.0	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P151571

CATALOG NUMBER: VXS-E01-LED-E1-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7
2.5°	182.0	180.9	176.8	172.7	169.0	164.9	161.1	157.3	153.3	150.2	146.4
5°	212.7	205.2	196.7	188.5	180.2	171.7	162.8	154.9	146.7	139.2	132.0
7.5°	243.8	229.1	217.5	202.8	189.5	176.2	163.8	151.2	139.6	128.6	118.3
10°	270.3	252.4	234.3	215.4	196.4	178.5	161.5	146.4	131.0	117.6	105.0
12.5°	291.7	269.2	246.9	223.3	201.8	179.3	158.0	139.9	121.8	106.7	93.7
15°	311.3	285.3	258.5	231.2	203.8	178.2	154.6	132.0	113.6	96.5	81.8
17.5°	326.9	297.2	267.2	236.4	206.9	176.8	150.2	126.5	105.0	87.3	72.8
20°	340.6	309.5	277.1	242.5	209.0	176.5	146.4	119.7	97.5	78.7	64.7
22.5°	353.4	322.2	287.4	250.4	212.0	176.2	143.0	114.6	91.0	72.1	58.1
25°	367.7	334.8	298.2	258.5	217.5	177.5	140.9	110.5	85.2	66.0	53.1
27.5°	383.7	349.2	311.3	268.8	224.8	180.2	140.2	106.0	80.0	60.2	48.9
30°	406.3	366.3	324.2	279.1	231.2	183.3	139.6	103.3	74.9	55.8	44.8
32.5°	426.2	383.1	338.7	289.7	238.4	186.4	139.2	99.5	70.2	51.3	41.8
35°	447.0	398.4	350.9	300.0	244.6	189.8	138.9	96.8	65.7	46.8	38.7
37.5°	465.2	411.5	360.5	308.8	251.4	193.0	139.2	94.4	61.6	43.1	36.0
40°	480.5	424.8	371.1	317.1	258.5	197.7	139.6	92.0	57.5	39.7	33.5
42.5°	494.2	437.5	382.4	326.3	266.7	203.2	141.6	89.9	54.1	36.6	31.1
45°	504.9	449.1	394.7	339.3	280.1	212.0	145.4	88.6	50.6	33.9	29.1
47.5°	515.8	466.2	415.5	359.8	299.6	226.1	151.8	88.3	47.9	31.8	27.4
50°	530.9	483.3	434.1	380.7	317.4	240.4	159.7	88.6	44.5	29.7	25.7
52.5°	541.8	500.7	458.0	416.9	359.8	284.2	190.2	94.7	42.8	28.1	23.6
55°	606.4	599.3	600.3	607.2	563.0	483.6	318.1	136.8	50.3	31.8	23.2
57.5°	855.1	880.4	895.1	894.7	821.9	681.7	427.2	175.9	56.1	36.9	27.7
60°	1182.1	1162.9	1135.9	1069.2	972.4	778.1	477.8	189.1	48.6	29.4	25.3
62.5°	1471.1	1358.9	1259.4	1151.3	1024.4	811.6	488.1	188.1	42.4	22.3	17.8
65°	1651.3	1449.5	1288.8	1153.4	1003.8	783.6	461.8	172.7	36.0	18.1	14.7
67.5°	1694.4	1400.6	1173.2	1000.4	838.7	609.8	339.0	129.9	28.1	15.0	13.0
69°	1600.4	1245.0	972.0	776.1	610.2	404.7	209.6	82.1	21.6	13.7	12.0
70°	1472.1	1082.9	791.8	622.8	451.8	284.2	146.7	57.8	17.4	12.6	11.0
72.5°	947.0	568.8	389.2	270.9	186.4	113.3	57.5	26.0	13.4	10.6	8.9
75°	367.4	210.4	152.5	116.0	90.7	62.9	34.9	16.8	11.3	8.9	6.8
77.5°	180.9	138.5	113.3	77.6	45.2	28.1	18.9	13.0	9.2	6.5	4.5
80°	143.0	95.1	56.8	35.2	26.6	20.2	14.4	10.6	6.8	4.1	3.1
82.5°	73.2	40.0	29.4	23.9	19.8	15.8	11.6	7.6	4.5	2.7	2.4
85°	22.9	16.8	15.0	14.7	13.7	11.3	8.2	4.8	2.7	1.8	1.8
87.5°	1.8	2.4	3.1	2.4	2.7	2.4	3.1	2.1	1.3	1.3	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P151571

CATALOG NUMBER: VXS-E01-LED-E1-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7	157.7
2.5°	143.6	139.6	135.8	133.4	128.9	127.3	125.5	124.9	121.8	122.5	119.7
5°	125.5	118.3	112.8	107.4	102.3	98.5	95.4	91.7	88.6	87.3	84.5
7.5°	109.1	99.9	92.6	86.8	80.7	76.0	71.8	69.1	66.3	63.6	62.3
10°	94.7	84.9	76.6	70.8	65.0	60.9	57.8	55.8	54.1	53.1	52.6
12.5°	81.5	71.8	64.4	59.2	54.7	52.6	51.3	50.3	49.9	49.6	49.6
15°	71.2	61.6	55.8	52.0	49.9	48.9	48.6	47.9	47.2	46.8	46.8
17.5°	61.6	54.4	50.3	48.2	47.2	46.5	45.8	45.2	44.5	44.1	44.1
20°	55.0	49.2	47.2	45.8	44.8	44.1	43.1	42.4	42.1	41.8	41.3
22.5°	49.9	46.2	44.8	43.7	42.4	41.3	40.7	40.0	39.4	39.0	38.7
25°	46.2	43.7	42.8	41.3	40.0	39.0	37.9	36.9	36.3	36.0	35.2
27.5°	43.4	41.8	40.3	38.7	37.3	36.3	35.2	34.2	33.5	32.8	32.5
30°	41.0	39.4	37.6	36.3	34.5	33.5	32.1	31.1	30.8	30.1	29.4
32.5°	38.7	36.9	35.2	33.5	31.8	30.5	29.7	28.4	27.7	27.4	26.6
35°	36.0	34.2	32.1	30.8	29.1	27.7	26.6	25.7	25.0	24.2	23.9
37.5°	33.5	31.5	29.4	27.7	26.3	25.0	23.9	22.9	22.3	21.6	21.2
40°	30.8	28.7	26.6	25.0	23.6	22.6	21.6	20.5	19.8	19.5	19.5
42.5°	28.4	26.0	23.9	22.6	21.6	20.2	19.2	18.1	17.8	17.4	17.8
45°	26.0	23.6	21.9	20.5	19.5	18.1	17.1	16.4	16.1	16.4	16.8
47.5°	23.9	21.6	19.8	18.9	17.8	16.8	15.8	15.0	15.0	15.8	16.4
50°	21.9	19.5	18.1	17.4	16.4	15.4	14.0	13.7	14.0	14.7	15.4
52.5°	19.8	17.1	16.1	15.8	14.7	13.7	12.6	12.3	12.6	13.4	13.0
55°	17.8	15.0	14.7	14.4	13.4	12.0	11.0	11.0	11.0	10.6	9.9
57.5°	17.1	13.4	13.0	12.6	11.6	10.3	9.5	8.9	8.6	7.6	7.2
60°	17.8	12.0	12.0	11.3	10.3	8.9	7.9	6.8	6.1	5.5	5.5
62.5°	14.4	11.0	10.6	9.9	8.6	7.2	6.1	5.2	4.8	4.5	4.5
65°	11.6	9.9	9.2	8.2	7.2	5.8	4.8	4.1	3.7	3.7	4.1
67.5°	10.6	8.9	7.9	6.8	5.8	4.5	3.7	3.4	3.4	3.7	3.7
69°	9.9	8.2	7.2	6.1	5.2	4.1	3.4	3.4	3.4	3.4	3.7
70°	9.2	7.9	6.8	5.8	4.5	3.4	3.1	3.1	3.4	3.4	3.7
72.5°	7.2	6.1	5.8	4.8	3.4	3.1	2.7	3.1	3.1	3.4	3.4
75°	5.5	4.5	4.5	3.7	2.7	2.4	2.4	2.7	2.7	3.1	3.1
77.5°	3.7	3.1	3.1	2.7	2.4	2.1	2.1	2.4	2.7	2.7	3.1
80°	2.7	2.4	2.1	2.4	2.1	1.8	2.1	2.4	2.4	2.7	2.7
82.5°	2.1	2.1	2.1	2.1	1.8	1.8	2.1	2.1	2.4	2.7	2.7
85°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.1	2.1	2.4	2.4
87.5°	1.0	1.0	1.0	1.3	1.3	1.8	1.8	1.8	1.8	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P151571

CATALOG NUMBER: VXS-E01-LED-E1-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	157.7	157.7	157.7	157.7
2.5°	119.1	118.7	117.3	117.6
5°	83.4	81.5	82.8	82.4
7.5°	61.2	60.9	60.5	61.2
10°	52.3	52.3	52.0	52.3
12.5°	49.2	49.2	49.2	49.2
15°	46.8	46.8	46.5	46.5
17.5°	44.1	44.1	44.1	43.7
20°	41.3	41.0	41.0	41.0
22.5°	38.3	37.9	37.9	37.9
25°	35.2	34.9	34.9	34.9
27.5°	32.1	31.8	31.5	31.5
30°	29.1	28.7	28.4	28.4
32.5°	26.0	25.7	25.3	25.3
35°	23.2	23.2	22.9	22.6
37.5°	20.8	20.8	20.8	20.8
40°	19.2	19.5	19.5	19.5
42.5°	18.1	18.4	18.9	19.2
45°	17.4	18.1	18.4	18.4
47.5°	17.1	17.4	17.8	17.8
50°	15.8	15.4	15.4	15.4
52.5°	12.6	12.0	11.6	11.3
55°	9.2	8.9	8.2	8.2
57.5°	6.5	6.5	6.1	6.1
60°	5.2	5.2	4.8	5.2
62.5°	4.5	4.5	4.5	4.5
65°	4.1	4.1	4.1	4.1
67.5°	4.1	4.1	4.1	4.1
69°	3.7	3.7	3.7	3.7
70°	3.7	3.7	3.7	3.7
72.5°	3.4	3.4	3.4	3.4
75°	3.1	3.4	3.4	3.4
77.5°	3.1	3.1	3.1	3.1
80°	2.7	2.7	3.1	3.1
82.5°	2.7	2.7	2.7	2.7
85°	2.4	2.4	2.7	2.7
87.5°	2.1	2.1	2.4	2.4
90°	0.0	0.0	0.0	0.0

(END OF REPORT)