

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P155426

Luminaire Tested: **VXS-F02-LED-E1-T3-7050**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P155426
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33672)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F02-LED-E1-T3-7050
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 3
Light Source: (14) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5224.6 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type III - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P155426

CATALOG NUMBER: VXS-F02-LED-E1-T3-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 5.6 fc
 Type III - Short - Semi-Cutoff

REPORT NUMBER: P155426

CATALOG NUMBER: VXS-F02-LED-E1-T3-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 67.5-Deg Lateral - - - Horizontal Cone Through 66-Deg Vertical

REPORT NUMBER: P155426

CATALOG NUMBER: VXS-F02-LED-E1-T3-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1804.2	0.0	1804.2
	% Fixture	34.5	0.0	34.5
Street Side	Lumens	3420.4	0.0	3420.4
	% Fixture	65.5	0.0	65.5
Total	Lumens	5224.6	0.0	5224.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.0
10°-20°	159.1	3.0
20°-30°	273.5	5.2
30°-40°	444.1	8.5
40°-50°	741.5	14.2
50°-60°	1167.5	22.3
60°-70°	1592.1	30.5
70°-80°	689.2	13.2
80°-90°	103.6	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5224.6	100.0
0°-180°	5224.6	100.0



REPORT NUMBER: P155426


CATALOG NUMBER: VXS-F02-LED-E1-T3-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	244.4	4.7			
FM	(30°-60°)	1459.1	27.9			
FH	(60°-80°)	1631.8	31.2			G1/1800
FVH	(80°-90°)	85.1	1.6			G1/100
BL	(0°-30°)	242.2	4.6	B1/500		
BM	(30°-60°)	894.1	17.1	B1/1000		
BH	(60°-80°)	649.4	12.4	B2/1000		G2/1000
BVH	(80°-90°)	18.5	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P155426

CATALOG NUMBER: VXS-F02-LED-E1-T3-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0
2.5°	565.3	567.6	565.3	565.8	566.4	565.8	565.3	565.3	563.6	564.8	565.8
5°	563.0	564.8	564.1	564.8	565.3	564.8	564.1	564.8	563.6	564.1	565.8
7.5°	560.2	559.6	560.2	561.3	562.5	562.5	562.5	563.0	562.5	562.5	564.1
10°	551.7	552.3	553.5	555.1	555.6	557.4	557.4	559.1	559.6	560.7	563.0
12.5°	541.0	541.6	542.7	543.8	546.6	549.4	549.4	553.5	555.1	557.9	561.9
15°	533.1	533.7	534.8	536.0	538.1	541.0	542.7	547.3	550.1	555.1	560.7
17.5°	537.6	537.0	538.1	538.8	538.8	541.0	541.0	544.4	547.8	552.3	559.6
20°	550.6	550.6	551.7	551.7	551.2	552.3	550.1	550.1	550.6	552.8	557.9
22.5°	563.6	563.0	565.3	566.4	566.9	568.7	566.4	565.8	563.0	561.3	563.0
25°	576.1	575.4	578.2	580.0	582.8	584.5	584.5	584.5	582.2	579.4	577.7
27.5°	595.2	595.2	598.0	599.7	602.0	605.4	607.0	607.0	607.7	603.7	600.8
30°	627.4	628.0	628.5	630.8	633.1	634.2	636.5	638.1	639.8	637.6	633.1
32.5°	665.8	662.4	662.4	665.8	668.6	672.0	673.2	675.4	678.8	677.1	676.6
35°	711.5	710.4	709.3	710.4	713.8	717.7	722.3	726.2	723.9	727.4	725.7
37.5°	779.3	780.4	781.0	781.0	780.4	781.6	783.8	787.8	786.6	787.8	790.1
40°	891.1	887.2	883.2	883.7	878.1	879.3	870.3	874.2	874.7	870.8	872.5
42.5°	1002.9	1005.2	1006.8	1011.4	1007.5	1005.2	996.7	996.7	992.2	988.3	987.2
45°	1123.8	1128.3	1128.9	1137.9	1134.5	1141.9	1148.1	1146.4	1139.1	1138.4	1130.6
47.5°	1220.3	1227.7	1235.6	1246.3	1254.8	1271.2	1290.4	1300.0	1305.6	1310.2	1301.1
50°	1292.6	1296.1	1316.4	1333.3	1351.9	1379.1	1405.6	1440.0	1467.7	1480.7	1493.2
52.5°	1331.6	1340.1	1362.1	1388.6	1421.3	1462.1	1505.0	1559.8	1607.2	1638.9	1667.0
55°	1340.1	1348.5	1373.4	1407.3	1451.9	1506.6	1568.2	1642.8	1713.9	1774.9	1834.2
57.5°	1316.4	1325.9	1352.5	1391.5	1443.9	1510.6	1588.0	1685.7	1783.9	1882.8	1970.3
60°	1272.8	1284.8	1309.0	1347.5	1405.6	1480.7	1573.3	1695.9	1833.7	1985.0	2152.7
62.5°	1201.1	1213.6	1236.2	1278.5	1338.3	1421.3	1528.7	1681.1	1876.0	2114.3	2411.9
65°	1085.9	1091.6	1119.3	1162.2	1215.2	1306.7	1424.8	1608.9	1862.5	2193.9	2603.9
66°	1034.0	1043.6	1060.5	1095.0	1145.8	1231.6	1350.3	1537.2	1811.1	2166.2	2598.9
67.5°	952.6	960.0	971.3	994.5	1025.5	1088.8	1201.1	1377.9	1654.1	2026.2	2491.0
70°	770.3	773.7	788.9	796.8	807.6	828.4	869.1	970.8	1185.9	1535.4	2010.4
72.5°	525.2	534.8	551.2	573.8	603.1	631.4	650.6	663.5	709.8	916.0	1339.5
75°	385.2	395.3	416.2	446.1	497.5	556.3	617.2	645.5	626.3	599.7	746.0
77.5°	223.6	237.2	254.7	283.5	330.9	408.8	513.4	605.9	668.6	672.5	638.7
80°	94.3	96.0	106.7	121.5	150.8	205.6	286.8	420.1	559.1	652.8	674.8
82.5°	21.5	26.5	33.9	40.1	49.1	67.8	100.5	167.2	302.1	473.8	617.8
85°	7.9	7.9	10.8	15.9	18.0	20.3	26.5	42.4	72.3	133.3	277.8
87.5°	0.0	0.5	1.1	1.1	2.3	2.8	4.6	6.2	5.6	5.1	16.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155426

CATALOG NUMBER: VXS-F02-LED-E1-T3-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°	100°
0°	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0
2.5°	564.8	564.1	563.0	563.0	563.0	563.0	561.9	562.5	561.3	561.9	561.9
5°	564.1	564.1	563.6	562.5	563.0	563.0	563.6	562.5	562.5	563.0	562.5
7.5°	564.1	563.6	563.6	563.6	564.1	563.6	564.1	564.1	564.1	564.8	564.8
10°	564.1	564.1	565.3	565.8	565.8	566.4	568.1	568.1	568.7	569.2	570.4
12.5°	564.8	566.9	568.7	570.4	570.9	572.0	574.9	574.9	576.1	577.7	578.2
15°	565.3	568.7	572.0	573.2	574.3	576.6	579.4	580.5	582.2	583.9	585.1
17.5°	564.8	569.2	573.2	574.9	576.6	579.4	582.8	583.9	586.2	588.4	590.7
20°	564.1	570.4	576.6	578.9	581.1	585.1	589.5	592.4	594.6	598.0	600.3
22.5°	567.6	574.9	583.3	586.7	590.7	595.8	602.0	605.4	608.2	611.6	613.3
25°	578.2	583.9	594.1	599.7	604.8	613.3	621.8	625.7	629.1	631.9	632.4
27.5°	596.4	598.0	610.5	617.8	625.2	638.7	648.8	651.7	657.9	660.1	659.6
30°	625.7	622.9	633.1	644.4	655.0	673.7	686.1	693.5	699.2	699.2	694.6
32.5°	668.1	663.5	666.3	679.4	691.8	718.9	733.6	743.2	747.2	746.0	736.4
35°	723.4	720.6	718.9	729.0	748.8	780.4	799.7	804.8	811.0	809.8	797.4
37.5°	788.9	786.6	786.6	798.5	817.7	864.6	885.5	888.9	888.3	879.3	856.1
40°	866.3	865.2	860.1	866.8	883.2	944.2	972.4	977.0	970.8	956.1	928.9
42.5°	977.5	970.8	954.9	958.9	971.3	1030.6	1067.4	1079.7	1073.6	1058.9	1014.8
45°	1122.7	1115.3	1088.8	1085.4	1092.1	1144.1	1191.5	1194.4	1193.3	1174.6	1122.7
47.5°	1293.2	1281.9	1253.7	1244.7	1242.4	1290.4	1336.2	1340.6	1337.8	1310.2	1240.7
50°	1477.8	1461.5	1442.9	1436.7	1427.6	1462.1	1508.4	1508.9	1497.6	1459.3	1394.3
52.5°	1674.9	1669.3	1665.9	1659.7	1655.8	1685.7	1713.9	1697.0	1680.0	1639.9	1583.4
55°	1873.8	1896.9	1920.6	1922.9	1929.6	1961.9	1961.2	1914.9	1902.5	1880.5	1824.6
57.5°	2085.0	2170.8	2245.3	2268.5	2291.1	2350.9	2345.3	2299.5	2283.7	2256.6	2210.3
60°	2372.3	2603.9	2819.1	2870.5	2906.0	2977.7	2971.0	2900.4	2933.2	2930.9	2871.0
62.5°	2775.0	3160.2	3482.6	3561.7	3586.5	3594.4	3551.5	3475.2	3507.5	3543.6	3359.5
65°	3047.8	3500.7	3831.6	3892.6	3896.0	3801.7	3706.2	3616.5	3608.5	3577.5	3314.3
66°	3054.0	3517.6	3849.6	3909.0	3888.1	3759.3	3638.4	3548.1	3509.1	3440.8	3168.1
67.5°	2944.5	3412.0	3769.5	3832.1	3786.4	3604.0	3437.4	3321.1	3244.9	3134.2	2893.6
70°	2472.8	2936.6	3377.0	3493.9	3508.6	3236.4	3005.4	2868.8	2766.0	2614.1	2406.8
72.5°	1838.8	2257.7	2646.2	2758.0	2815.1	2597.7	2402.9	2299.0	2158.3	1998.5	1851.2
75°	1152.5	1448.5	1708.8	1787.4	1733.7	1565.4	1448.5	1405.0	1266.6	1171.2	1104.0
77.5°	659.1	751.6	772.5	742.6	679.4	520.1	369.8	273.9	237.7	263.1	290.3
80°	643.2	589.5	469.8	413.4	374.4	257.5	151.3	103.9	86.4	88.7	96.0
82.5°	696.9	747.7	615.5	502.1	421.2	284.7	157.0	83.6	56.5	66.6	75.1
85°	453.0	630.3	567.6	478.3	387.4	243.4	129.3	43.5	28.8	37.8	51.9
87.5°	45.7	50.3	42.9	58.1	43.5	20.3	10.2	6.2	5.6	6.7	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155426

CATALOG NUMBER: VXS-F02-LED-E1-T3-7050

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0	563.0
2.5°	562.5	562.5	563.0	563.6	564.1	564.8	564.8	564.8	564.8	565.8	565.3
5°	563.6	564.8	565.8	566.4	567.6	567.6	569.2	568.7	568.7	570.4	570.9
7.5°	565.8	567.6	569.8	569.2	571.5	570.9	572.0	572.0	570.4	570.9	569.8
10°	570.9	573.2	574.3	572.6	573.2	570.9	570.4	567.6	564.1	562.5	560.2
12.5°	579.4	581.7	581.7	578.9	575.4	570.4	566.4	560.2	555.1	552.3	549.4
15°	586.7	589.0	588.4	583.9	578.9	570.9	565.3	557.9	550.6	546.1	543.2
17.5°	592.4	593.5	591.8	585.6	580.0	572.6	566.9	559.1	550.6	545.0	539.9
20°	600.8	599.7	595.8	587.9	581.7	574.9	570.4	563.6	554.0	546.6	539.3
22.5°	613.3	608.8	601.5	593.0	586.7	580.5	576.1	568.7	559.1	550.1	541.6
25°	629.6	620.6	610.5	601.5	595.8	589.0	583.9	576.1	565.8	555.6	545.5
27.5°	653.4	637.6	624.6	616.7	610.5	602.0	595.8	585.6	574.9	563.0	551.7
30°	679.9	658.4	646.0	639.8	633.1	624.0	614.4	601.5	589.0	576.1	562.5
32.5°	714.4	688.4	676.6	670.4	661.2	649.9	638.7	624.0	606.5	589.5	573.2
35°	759.6	733.0	720.6	711.0	698.5	683.8	667.5	647.8	624.0	601.5	580.5
37.5°	808.1	779.3	767.5	757.3	738.7	719.5	696.3	667.5	635.3	605.4	579.4
40°	869.6	843.1	827.9	810.4	788.4	755.0	718.9	677.1	635.9	599.2	568.7
42.5°	947.6	921.0	898.4	870.8	832.4	781.0	729.6	675.4	625.7	583.9	551.2
45°	1051.0	1018.8	979.8	931.2	869.1	797.4	730.2	664.7	606.5	560.2	525.2
47.5°	1177.4	1128.3	1064.5	982.6	893.4	801.9	721.1	643.2	576.6	526.3	487.4
50°	1327.7	1250.3	1145.3	1025.0	905.8	795.1	698.5	611.0	534.2	480.6	434.3
52.5°	1499.3	1372.8	1218.1	1055.4	905.3	772.5	660.1	562.5	478.9	419.1	374.9
55°	1700.9	1512.8	1293.2	1078.0	889.4	730.8	601.5	494.1	410.6	355.2	314.5
57.5°	1996.3	1739.9	1424.2	1113.1	857.8	666.3	521.8	412.2	338.9	286.3	251.8
60°	2536.2	2118.9	1660.3	1183.6	809.2	572.0	428.6	324.7	263.1	220.8	197.6
62.5°	2942.7	2411.9	1787.9	1167.9	711.5	455.8	317.9	236.6	193.7	164.9	150.3
65°	2884.6	2321.0	1651.8	1005.8	557.9	321.3	211.2	160.9	133.3	119.7	111.3
66°	2753.0	2202.4	1533.8	905.3	482.3	267.2	173.9	134.9	114.6	105.1	99.4
67.5°	2503.4	1982.2	1322.6	742.1	370.5	193.7	131.0	106.7	93.2	89.2	85.3
70°	2080.9	1580.6	928.4	432.0	189.2	107.9	83.0	74.5	71.2	70.6	69.4
72.5°	1594.7	1118.7	546.6	204.5	98.2	71.7	64.4	61.6	60.4	60.4	61.0
75°	977.5	628.5	241.7	100.0	68.9	60.4	57.0	56.0	55.3	56.0	55.3
77.5°	326.4	199.9	103.3	75.6	62.7	56.0	53.7	52.5	52.5	52.5	52.5
80°	100.0	86.9	79.1	70.1	59.3	53.1	49.7	49.1	49.7	50.3	48.6
82.5°	75.1	71.2	66.6	62.1	53.7	47.5	46.3	46.3	46.3	44.7	42.4
85°	55.3	54.8	45.2	42.4	39.5	39.5	39.5	39.5	37.8	35.0	32.7
87.5°	10.2	9.6	10.2	10.8	15.9	16.9	16.9	18.0	19.8	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155426

CATALOG NUMBER: VXS-F02-LED-E1-T3-7050

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	563.0	563.0	563.0	563.0	563.0
2.5°	565.3	564.8	566.4	565.3	565.8
5°	570.4	569.8	570.9	569.8	571.5
7.5°	568.7	567.6	566.9	567.6	568.1
10°	556.8	555.6	555.1	554.5	555.1
12.5°	546.6	544.4	544.4	543.2	543.8
15°	539.3	537.6	537.0	536.0	536.5
17.5°	536.0	533.1	531.9	530.9	530.9
20°	533.7	530.3	528.6	527.5	526.8
22.5°	533.7	528.6	526.3	525.2	524.7
25°	536.0	529.7	526.3	524.7	524.0
27.5°	540.4	532.5	528.6	526.3	526.3
30°	548.3	538.1	532.5	529.7	529.1
32.5°	556.3	542.7	534.8	531.4	530.3
35°	560.2	542.7	533.1	527.5	526.3
37.5°	555.6	535.3	523.5	515.0	513.4
40°	541.6	520.1	507.2	499.2	498.0
42.5°	522.9	502.1	486.7	481.1	479.5
45°	497.5	472.6	457.4	449.5	450.1
47.5°	454.0	428.6	415.0	407.8	408.8
50°	402.7	377.8	365.9	358.0	359.7
52.5°	346.2	323.6	312.3	308.3	307.3
55°	286.8	269.3	261.5	257.0	255.2
57.5°	232.6	220.2	214.6	208.9	209.5
60°	183.5	177.3	175.6	169.4	168.8
62.5°	144.6	140.6	139.0	134.4	134.9
65°	109.5	108.4	109.5	106.7	107.9
66°	98.9	99.4	99.4	97.7	98.9
67.5°	85.3	86.4	88.1	86.4	87.6
70°	70.6	71.7	72.8	72.8	72.8
72.5°	61.6	62.7	63.2	63.2	63.2
75°	56.5	57.0	57.6	56.5	56.5
77.5°	53.1	53.1	51.9	51.4	50.8
80°	48.0	47.5	45.7	44.7	44.7
82.5°	40.1	39.0	37.8	36.2	36.2
85°	30.5	29.3	28.2	26.0	24.9
87.5°	15.9	16.4	15.9	13.0	11.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)