

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P156486

Luminaire Tested: **VXS-F04-LED-E1-T4-7050**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P156486
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F04-LED-E1-T4-7050
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 4
Light Source: (28) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10239.6 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P156486

CATALOG NUMBER: VXS-F04-LED-E1-T4-7050

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 3.5 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156486

CATALOG NUMBER: VXS-F04-LED-E1-T4-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 47.5-Deg Lateral - - - Horizontal Cone Through 66-Deg Vertical

REPORT NUMBER: P156486

CATALOG NUMBER: VXS-F04-LED-E1-T4-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2184.9	0.0	2184.9
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	8054.7	0.0	8054.7
	% Fixture	78.7	0.0	78.7
Total	Lumens	10239.6	0.0	10239.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.1	1.3
10°-20°	397.9	3.9
20°-30°	685.4	6.7
30°-40°	1037.0	10.1
40°-50°	1344.0	13.1
50°-60°	1853.0	18.1
60°-70°	2879.0	28.1
70°-80°	1674.1	16.3
80°-90°	238.1	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10239.6	100.0
0°-180°	10239.6	100.0



REPORT NUMBER: P156486


CATALOG NUMBER: VXS-F04-LED-E1-T4-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	629.5	6.1			
FM (30°-60°)	3286.9	32.1			
FH (60°-80°)	3955.6	38.6			G2/5000
FVH (80°-90°)	182.7	1.8			G2/225
BL (0°-30°)	584.8	5.7	B2/1000		
BM (30°-60°)	947.1	9.2	B1/1000		
BH (60°-80°)	597.6	5.8	B2/1000		G2/1000
BVH (80°-90°)	55.4	0.5			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P156486

CATALOG NUMBER: VXS-F04-LED-E1-T4-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6
2.5°	1324.9	1329.3	1325.9	1327.0	1327.0	1328.2	1328.2	1329.3	1328.2	1331.6	1333.9
5°	1301.1	1303.3	1302.3	1304.5	1306.7	1311.3	1310.2	1315.8	1316.9	1320.3	1325.9
7.5°	1292.1	1289.8	1291.0	1294.3	1296.6	1298.9	1301.1	1305.6	1309.0	1316.9	1321.5
10°	1301.1	1300.0	1301.1	1303.3	1303.3	1304.5	1302.3	1306.7	1309.0	1315.8	1320.3
12.5°	1338.3	1338.3	1336.2	1336.2	1333.9	1331.6	1325.9	1322.6	1321.5	1322.6	1324.9
15°	1398.2	1396.0	1391.5	1388.1	1383.5	1375.6	1367.8	1360.9	1356.5	1349.6	1347.5
17.5°	1457.0	1453.6	1449.0	1444.6	1438.9	1431.0	1418.5	1410.7	1398.2	1390.4	1385.8
20°	1524.8	1517.9	1512.3	1506.6	1495.3	1493.2	1480.7	1467.2	1452.4	1434.4	1432.1
22.5°	1612.8	1601.6	1594.7	1591.4	1580.1	1576.7	1556.4	1537.2	1519.1	1495.3	1489.7
25°	1702.1	1690.8	1687.4	1682.9	1674.9	1670.5	1651.2	1629.7	1606.0	1573.3	1566.5
27.5°	1789.0	1790.2	1781.1	1784.5	1782.3	1774.3	1755.1	1733.7	1715.6	1677.2	1669.3
30°	1897.4	1890.7	1886.1	1893.0	1885.0	1886.1	1869.2	1857.9	1828.6	1806.0	1790.2
32.5°	2010.4	2009.2	2016.1	2020.5	2019.4	2017.2	2003.6	1992.3	1966.3	1933.6	1926.8
35°	2165.1	2171.9	2177.5	2197.9	2197.9	2212.5	2199.0	2185.5	2154.9	2115.4	2101.9
37.5°	2270.2	2272.4	2295.0	2322.1	2356.0	2387.7	2396.7	2400.0	2387.7	2358.2	2337.9
40°	2366.1	2370.7	2406.8	2448.6	2498.3	2560.4	2597.7	2614.6	2618.0	2604.5	2560.4
42.5°	2462.2	2468.9	2506.2	2567.3	2636.1	2715.1	2780.6	2822.5	2846.2	2846.2	2820.2
45°	2574.0	2583.0	2623.6	2690.4	2770.5	2869.8	2960.2	3040.4	3078.9	3081.1	3056.3
47.5°	2706.1	2714.0	2761.5	2829.2	2911.7	3012.2	3126.3	3217.7	3288.9	3293.5	3273.1
50°	2876.7	2888.0	2927.5	2988.5	3073.2	3174.8	3288.9	3416.6	3491.1	3509.1	3487.7
52.5°	3102.6	3104.8	3137.6	3194.0	3276.5	3373.6	3494.5	3633.4	3731.6	3746.3	3711.3
55°	3414.3	3410.9	3432.3	3493.4	3555.4	3631.1	3756.5	3912.3	4021.9	4044.5	4008.4
57.5°	3837.8	3834.4	3852.5	3867.2	3983.5	4056.9	4180.0	4329.1	4435.3	4500.8	4438.7
60°	4494.0	4490.7	4520.0	4605.8	4692.8	4800.1	4919.8	5098.2	5247.4	5266.5	5205.6
62.5°	4969.5	4986.4	5050.9	5151.4	5327.6	5537.6	5756.7	5991.6	6297.7	6394.8	6365.5
65°	4803.5	4837.4	4926.6	5079.1	5314.0	5604.2	5947.6	6373.4	6783.4	7012.6	7005.9
66°	4654.4	4691.7	4801.2	4948.1	5196.5	5513.9	5888.9	6353.1	6811.6	7064.6	7080.4
67.5°	4383.3	4425.1	4532.4	4706.3	4948.1	5285.8	5688.9	6193.8	6712.2	7007.0	7048.8
70°	3855.9	3903.3	3981.2	4124.7	4363.0	4664.6	5089.2	5541.0	6084.2	6422.0	6472.7
72.5°	3223.4	3265.2	3352.1	3469.6	3665.0	3854.7	4188.0	4521.1	4909.6	5294.8	5257.5
75°	2314.2	2332.3	2384.2	2511.8	2616.9	2787.5	3055.1	3328.4	3593.9	3770.1	3794.9
77.5°	1202.8	1250.3	1323.7	1464.9	1579.0	1732.5	1906.5	2112.0	2306.3	2467.8	2423.7
80°	787.3	807.6	873.1	945.3	1028.9	1127.2	1243.5	1320.3	1345.2	1335.0	1345.2
82.5°	454.0	491.3	578.2	633.6	695.8	729.6	822.3	910.4	960.0	897.9	875.3
85°	57.6	74.5	234.9	296.0	338.9	389.6	417.9	471.0	439.4	393.1	478.9
87.5°	12.4	11.3	15.9	33.9	35.0	29.3	55.3	58.8	36.2	18.0	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156486

CATALOG NUMBER: VXS-F04-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6
2.5°	1336.2	1337.2	1339.5	1342.9	1345.2	1347.5	1349.6	1353.1	1355.3	1357.6	1362.1
5°	1330.5	1335.0	1339.5	1344.0	1349.6	1358.8	1364.4	1368.9	1373.4	1382.4	1385.8
7.5°	1327.0	1335.0	1341.8	1349.6	1358.8	1366.6	1376.8	1382.4	1389.2	1394.8	1401.7
10°	1324.9	1336.2	1342.9	1354.2	1364.4	1372.2	1383.5	1390.4	1398.2	1405.0	1408.4
12.5°	1329.3	1335.0	1341.8	1353.1	1365.5	1376.8	1389.2	1394.8	1401.7	1407.3	1408.4
15°	1348.5	1348.5	1349.6	1358.8	1371.1	1380.2	1390.4	1396.0	1399.4	1402.8	1402.8
17.5°	1383.5	1375.6	1370.1	1371.1	1379.1	1384.7	1390.4	1390.4	1388.1	1386.9	1384.7
20°	1424.2	1414.1	1402.8	1394.8	1392.6	1388.1	1384.7	1373.4	1364.4	1356.5	1350.8
22.5°	1482.9	1467.2	1451.3	1436.7	1423.1	1406.1	1386.9	1364.4	1342.9	1328.2	1319.2
25°	1555.2	1542.8	1523.6	1501.0	1484.0	1452.4	1427.6	1394.8	1367.8	1348.5	1332.7
27.5°	1658.0	1643.3	1625.3	1605.0	1580.1	1545.1	1514.6	1476.2	1443.4	1415.1	1394.8
30°	1785.6	1766.4	1752.8	1728.1	1711.1	1671.6	1641.0	1593.7	1530.4	1485.2	1457.0
32.5°	1916.7	1895.2	1883.9	1864.7	1845.5	1821.8	1775.4	1702.1	1620.7	1547.4	1498.8
35°	2091.7	2069.1	2048.8	2031.8	2003.6	1959.6	1918.9	1830.8	1719.0	1616.3	1534.9
37.5°	2311.9	2274.7	2223.8	2180.9	2131.2	2068.0	2005.9	1915.5	1787.9	1654.6	1546.2
40°	2546.8	2481.3	2409.1	2328.9	2243.0	2151.6	2080.4	1988.9	1845.5	1687.4	1538.2
42.5°	2791.9	2688.1	2587.6	2474.6	2354.8	2246.4	2153.8	2053.3	1888.4	1696.4	1506.6
45°	3034.8	2918.4	2766.0	2618.0	2466.7	2332.3	2228.4	2115.4	1928.0	1699.8	1464.9
47.5°	3235.9	3116.1	2942.2	2757.0	2577.4	2424.9	2302.9	2180.9	1981.0	1723.5	1454.7
50°	3448.2	3302.5	3109.3	2890.3	2686.9	2516.4	2386.5	2260.0	2055.5	1784.5	1487.5
52.5°	3679.7	3512.5	3286.6	3041.6	2819.1	2628.2	2487.0	2357.1	2150.5	1870.4	1549.5
55°	3962.1	3757.6	3512.5	3235.9	2997.5	2786.3	2630.5	2476.9	2263.4	1972.0	1627.6
57.5°	4393.5	4142.8	3867.2	3552.0	3287.8	3038.1	2851.8	2674.5	2438.4	2123.3	1733.7
60°	5174.0	4906.2	4548.2	4166.5	3855.9	3564.5	3291.2	3070.9	2780.6	2421.6	1968.6
62.5°	6292.1	5936.3	5458.5	4924.4	4517.7	4097.6	3789.2	3461.8	3101.5	2714.0	2245.3
65°	6913.3	6481.9	5842.6	5222.5	4699.6	4243.3	3851.4	3471.9	3072.0	2701.7	2309.7
66°	6990.1	6540.5	5876.5	5223.6	4674.7	4206.0	3793.8	3400.7	2991.9	2638.3	2282.6
67.5°	6958.4	6498.8	5814.3	5125.4	4567.5	4063.7	3637.9	3230.2	2822.5	2492.6	2192.2
70°	6440.0	6004.0	5332.0	4664.6	4134.8	3637.9	3231.3	2830.4	2456.5	2174.2	1952.7
72.5°	5347.9	4975.1	4391.2	3867.2	3451.5	3041.6	2697.1	2314.2	1997.9	1789.0	1658.0
75°	3860.4	3634.5	3102.6	2802.2	2437.3	2165.1	1830.8	1603.8	1376.8	1275.1	1252.5
77.5°	2438.4	2134.6	1796.9	1479.6	1216.4	1008.6	785.0	666.3	555.6	544.4	657.3
80°	1234.5	1111.4	856.1	682.2	573.8	464.2	367.0	277.8	194.3	233.8	280.1
82.5°	808.7	674.3	528.6	434.8	378.3	314.0	243.9	169.4	124.2	140.0	192.0
85°	437.1	372.7	300.4	237.2	192.0	171.7	115.2	81.3	80.2	85.8	109.5
87.5°	31.6	31.6	24.9	22.6	27.2	22.6	20.3	20.3	19.2	20.3	27.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156486

CATALOG NUMBER: VXS-F04-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6	1349.6
2.5°	1364.4	1367.8	1368.9	1374.5	1377.9	1380.2	1382.4	1382.4	1383.5	1386.9	1388.1
5°	1390.4	1396.0	1402.8	1407.3	1409.5	1416.3	1418.5	1418.5	1420.8	1425.4	1428.7
7.5°	1406.1	1414.1	1420.8	1423.1	1427.6	1429.8	1433.3	1435.5	1435.5	1440.0	1442.3
10°	1411.8	1416.3	1423.1	1423.1	1427.6	1427.6	1431.0	1432.1	1432.1	1436.7	1440.0
12.5°	1411.8	1414.1	1419.7	1419.7	1423.1	1424.2	1428.7	1432.1	1433.3	1438.9	1443.4
15°	1405.0	1407.3	1411.8	1413.0	1420.8	1425.4	1435.5	1442.3	1442.3	1448.0	1450.2
17.5°	1385.8	1391.5	1400.5	1409.5	1424.2	1434.4	1446.8	1452.4	1448.0	1444.6	1441.1
20°	1354.2	1364.4	1385.8	1408.4	1434.4	1448.0	1454.7	1449.0	1433.3	1417.4	1407.3
22.5°	1322.6	1342.9	1379.1	1413.0	1442.3	1451.3	1448.0	1427.6	1401.7	1382.4	1368.9
25°	1337.2	1360.9	1396.0	1426.4	1445.7	1443.4	1429.8	1401.7	1373.4	1348.5	1325.9
27.5°	1398.2	1424.2	1443.4	1453.6	1451.3	1435.5	1414.1	1382.4	1348.5	1315.8	1284.1
30°	1455.9	1469.4	1473.9	1466.0	1448.0	1422.0	1394.8	1358.8	1313.6	1272.8	1236.7
32.5°	1481.9	1468.3	1446.8	1425.4	1396.0	1373.4	1336.2	1296.6	1240.1	1191.5	1155.4
35°	1481.9	1427.6	1373.4	1328.2	1284.1	1256.0	1213.1	1159.9	1108.0	1067.4	1039.1
37.5°	1449.0	1345.2	1256.0	1182.5	1127.2	1096.7	1032.3	984.9	940.8	927.3	909.2
40°	1389.2	1235.6	1106.8	1010.9	940.8	895.6	831.3	798.5	781.6	774.8	771.4
42.5°	1309.0	1113.6	942.0	823.3	747.7	696.9	654.0	633.6	632.4	631.4	631.4
45°	1223.2	982.6	781.6	640.4	573.8	528.6	508.3	500.3	507.2	506.0	507.2
47.5°	1170.1	883.2	634.7	484.6	433.7	404.4	394.2	397.5	403.2	400.9	400.9
50°	1163.3	832.4	536.5	377.2	338.9	324.1	321.9	321.9	325.3	323.0	321.9
52.5°	1188.2	824.5	485.7	324.1	293.7	281.2	279.0	277.8	276.7	269.9	264.2
55°	1231.1	842.6	471.0	310.6	279.0	265.4	262.1	259.8	255.2	246.2	236.1
57.5°	1316.9	899.1	484.6	317.4	283.5	272.2	268.8	268.8	259.8	245.1	230.4
60°	1523.6	1042.5	539.9	343.3	305.0	293.7	296.0	294.8	281.2	259.8	237.2
62.5°	1790.2	1229.9	612.1	379.5	332.0	329.8	341.1	338.9	316.3	283.5	250.8
65°	1913.3	1318.0	632.4	387.4	337.7	347.9	370.5	368.2	340.0	294.8	253.0
66°	1915.5	1318.0	623.4	380.6	329.8	342.2	364.8	363.6	335.4	290.3	248.5
67.5°	1869.2	1281.9	597.5	367.0	314.0	323.0	343.3	342.2	316.3	279.0	239.5
70°	1695.2	1147.5	530.9	343.3	292.5	288.0	294.8	290.3	273.4	247.4	220.2
72.5°	1452.4	963.4	463.1	325.3	277.8	259.8	255.2	251.8	238.3	223.6	206.7
75°	1144.1	762.4	406.6	311.7	264.2	240.5	232.6	228.2	219.1	208.9	195.4
77.5°	705.9	545.5	354.6	293.7	254.1	230.4	224.8	218.0	204.5	192.0	181.9
80°	315.1	337.7	291.4	256.4	227.0	205.6	196.5	186.3	172.8	164.9	159.3
82.5°	210.1	218.0	211.2	192.0	171.7	154.7	141.1	141.1	139.0	132.1	129.8
85°	134.4	135.5	131.0	118.5	110.7	100.5	94.9	96.0	100.5	99.4	98.2
87.5°	30.5	30.5	36.2	33.9	39.5	41.8	45.2	48.6	55.3	55.3	58.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156486

CATALOG NUMBER: VXS-F04-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1349.6	1349.6	1349.6	1349.6	1349.6
2.5°	1389.2	1391.5	1393.7	1390.4	1391.5
5°	1428.7	1427.6	1433.3	1429.8	1432.1
7.5°	1441.1	1442.3	1446.8	1446.8	1448.0
10°	1442.3	1444.6	1450.2	1453.6	1455.9
12.5°	1448.0	1452.4	1461.5	1463.7	1463.7
15°	1452.4	1454.7	1460.3	1462.6	1464.9
17.5°	1436.7	1432.1	1434.4	1435.5	1434.4
20°	1397.1	1392.6	1391.5	1386.9	1389.2
22.5°	1354.2	1341.8	1333.9	1324.9	1324.9
25°	1302.3	1283.0	1267.3	1251.4	1254.8
27.5°	1253.7	1228.8	1213.1	1202.8	1200.6
30°	1206.2	1180.2	1165.6	1153.2	1153.2
32.5°	1127.2	1109.1	1089.9	1082.0	1080.8
35°	1017.6	1006.3	990.5	987.2	981.5
37.5°	894.5	891.1	877.6	876.5	870.8
40°	765.8	768.0	763.5	761.2	757.8
42.5°	637.0	648.3	646.0	644.9	642.7
45°	513.9	521.8	522.9	526.3	531.9
47.5°	404.4	406.6	408.8	407.8	408.8
50°	316.3	310.6	309.4	306.1	309.4
52.5°	255.2	246.2	241.7	237.2	234.9
55°	224.8	215.8	211.2	208.9	206.7
57.5°	216.9	207.8	201.0	196.5	195.4
60°	219.1	205.6	196.5	190.9	189.7
62.5°	224.8	206.7	194.3	188.6	187.5
65°	223.6	204.5	193.2	186.3	185.2
66°	220.2	202.2	190.9	185.2	184.1
67.5°	214.6	198.8	188.6	184.1	181.9
70°	204.5	194.3	186.3	180.7	178.4
72.5°	195.4	187.5	180.7	175.0	173.9
75°	185.2	178.4	171.7	167.2	166.0
77.5°	172.8	166.0	161.6	158.1	157.0
80°	152.4	148.0	143.4	139.0	139.0
82.5°	126.5	123.1	118.5	115.2	114.1
85°	97.1	97.1	93.8	90.4	89.2
87.5°	57.6	56.5	56.5	53.1	53.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)