

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P156496

Luminaire Tested: **VXS-F05-LED-E1-T4-7050**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P156496
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-T4-7050
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4
Light Source: (35) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12799.5 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P156496

CATALOG NUMBER: VXS-F05-LED-E1-T4-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 4.4 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156496

CATALOG NUMBER: VXS-F05-LED-E1-T4-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P156496

CATALOG NUMBER: VXS-F05-LED-E1-T4-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2731.1	0.0	2731.1
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	10068.4	0.0	10068.4
	% Fixture	78.7	0.0	78.7
Total	Lumens	12799.5	0.0	12799.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.8	1.3
10°-20°	497.4	3.9
20°-30°	856.7	6.7
30°-40°	1296.2	10.1
40°-50°	1680.1	13.1
50°-60°	2316.3	18.1
60°-70°	3598.7	28.1
70°-80°	2092.7	16.3
80°-90°	297.6	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12799.5	100.0
0°-180°	12799.5	100.0

Coefficient of Utilization



REPORT NUMBER: P156496


CATALOG NUMBER: VXS-F05-LED-E1-T4-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	786.9	6.1			
FM	(30°-60°)	4108.6	32.1			
FH	(60°-80°)	4944.4	38.6			G2/5000
FVH	(80°-90°)	228.4	1.8			G3/500
BL	(0°-30°)	731.0	5.7	B2/1000		
BM	(30°-60°)	1183.9	9.2	B2/2500		
BH	(60°-80°)	747.0	5.8	B2/1000		G2/1000
BVH	(80°-90°)	69.2	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P156496

CATALOG NUMBER: VXS-F05-LED-E1-T4-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0
2.5°	1656.1	1661.7	1657.4	1658.9	1658.9	1660.3	1660.3	1661.7	1660.3	1664.5	1667.4
5°	1626.4	1629.2	1627.8	1630.6	1633.5	1639.1	1637.7	1644.8	1646.1	1650.4	1657.4
7.5°	1615.1	1612.2	1613.7	1617.9	1620.7	1623.5	1626.4	1632.0	1636.3	1646.1	1651.8
10°	1626.4	1625.0	1626.4	1629.2	1629.2	1630.6	1627.8	1633.5	1636.3	1644.8	1650.4
12.5°	1673.0	1673.0	1670.2	1670.2	1667.4	1664.5	1657.4	1653.2	1651.8	1653.2	1656.1
15°	1747.8	1745.0	1739.4	1735.1	1729.4	1719.6	1709.6	1701.2	1695.5	1687.0	1684.2
17.5°	1821.2	1817.0	1811.3	1805.7	1798.7	1788.7	1773.2	1763.3	1747.8	1737.9	1732.2
20°	1905.9	1897.4	1890.4	1883.3	1869.2	1866.4	1850.9	1833.9	1815.5	1793.0	1790.2
22.5°	2016.1	2002.0	1993.5	1989.2	1975.1	1970.9	1945.5	1921.5	1898.9	1869.2	1862.2
25°	2127.6	2113.5	2109.2	2103.5	2093.7	2088.1	2064.0	2037.2	2007.6	1966.6	1958.1
27.5°	2236.3	2237.7	2226.4	2230.7	2227.8	2217.9	2193.9	2167.2	2144.6	2096.5	2086.6
30°	2371.8	2363.3	2357.7	2366.1	2356.3	2357.7	2336.5	2322.4	2285.7	2257.4	2237.7
32.5°	2513.0	2511.6	2520.0	2525.7	2524.2	2521.5	2504.6	2490.4	2457.9	2417.0	2408.5
35°	2706.4	2714.9	2722.0	2747.4	2747.4	2765.7	2748.8	2731.8	2693.7	2644.2	2627.4
37.5°	2837.7	2840.5	2868.8	2902.7	2945.0	2984.6	2995.9	3000.1	2984.6	2947.8	2922.4
40°	2957.7	2963.3	3008.5	3060.7	3122.9	3200.5	3247.2	3268.3	3272.5	3255.5	3200.5
42.5°	3077.7	3086.2	3132.7	3209.0	3295.1	3394.0	3475.9	3528.1	3557.7	3557.7	3525.3
45°	3217.5	3228.8	3279.6	3362.9	3463.1	3587.4	3700.3	3800.5	3848.5	3851.4	3820.3
47.5°	3382.7	3392.5	3451.8	3536.6	3639.6	3765.3	3907.9	4022.2	4111.2	4116.8	4091.4
50°	3595.9	3609.9	3659.4	3735.6	3841.5	3968.6	4111.2	4270.7	4363.8	4386.4	4359.6
52.5°	3878.2	3881.0	3922.0	3992.5	4095.6	4217.0	4368.1	4541.8	4664.6	4682.9	4639.2
55°	4267.9	4263.6	4290.5	4366.6	4444.4	4539.0	4695.6	4890.5	5027.4	5055.6	5010.5
57.5°	4797.3	4793.1	4815.6	4834.0	4979.4	5071.2	5225.1	5411.4	5544.1	5626.0	5548.4
60°	5617.5	5613.3	5649.9	5757.3	5866.0	6000.1	6149.7	6372.8	6559.2	6583.2	6506.9
62.5°	6211.9	6233.1	6313.6	6439.2	6659.4	6922.0	7196.0	7489.5	7872.1	7993.6	7956.9
65°	6004.4	6046.7	6158.2	6348.8	6642.5	7005.3	7434.5	7966.7	8479.3	8765.8	8757.3
66°	5818.0	5864.6	6001.6	6185.1	6495.6	6892.3	7361.0	7941.3	8514.5	8830.8	8850.6
67.5°	5479.2	5531.4	5665.5	5882.9	6185.1	6607.2	7111.2	7742.3	8390.3	8758.8	8811.0
70°	4819.9	4879.2	4976.6	5155.9	5453.8	5830.7	6361.6	6926.2	7605.3	8027.5	8091.0
72.5°	4029.2	4081.5	4190.2	4337.0	4581.2	4818.4	5234.9	5651.4	6137.1	6618.4	6571.9
75°	2892.7	2915.3	2980.3	3139.8	3271.1	3484.4	3818.9	4160.5	4492.3	4712.5	4743.6
77.5°	1503.5	1562.9	1654.6	1831.1	1973.7	2165.7	2383.1	2640.1	2882.9	3084.8	3029.7
80°	984.0	1009.4	1091.3	1181.7	1286.1	1409.0	1554.4	1650.4	1681.5	1668.7	1681.5
82.5°	567.6	614.1	722.8	792.0	869.6	912.0	1027.8	1137.9	1200.0	1122.4	1094.1
85°	72.0	93.2	293.7	369.8	423.5	487.0	522.4	588.7	549.2	491.3	598.5
87.5°	15.5	14.1	19.8	42.4	43.7	36.7	69.2	73.4	45.2	22.6	28.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156496

CATALOG NUMBER: VXS-F05-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0
2.5°	1670.2	1671.6	1674.4	1678.7	1681.5	1684.2	1687.0	1691.3	1694.2	1697.0	1702.6
5°	1663.1	1668.7	1674.4	1680.0	1687.0	1698.3	1705.5	1711.1	1716.8	1728.1	1732.2
7.5°	1658.9	1668.7	1677.2	1687.0	1698.3	1708.3	1720.9	1728.1	1736.5	1743.5	1752.0
10°	1656.1	1670.2	1678.7	1692.7	1705.5	1715.3	1729.4	1737.9	1747.8	1756.3	1760.5
12.5°	1661.7	1668.7	1677.2	1691.3	1706.8	1720.9	1736.5	1743.5	1752.0	1759.1	1760.5
15°	1685.7	1685.7	1687.0	1698.3	1713.9	1725.2	1737.9	1745.0	1749.2	1753.5	1753.5
17.5°	1729.4	1719.6	1712.5	1713.9	1723.8	1730.9	1737.9	1737.9	1735.1	1733.7	1730.9
20°	1780.3	1767.6	1753.5	1743.5	1740.7	1735.1	1730.9	1716.8	1705.5	1695.5	1688.5
22.5°	1853.7	1833.9	1814.2	1795.8	1778.9	1757.7	1733.7	1705.5	1678.7	1660.3	1649.0
25°	1944.0	1928.5	1904.6	1876.3	1855.1	1815.5	1784.5	1743.5	1709.6	1685.7	1665.9
27.5°	2072.5	2054.2	2031.6	2006.1	1975.1	1931.3	1893.3	1845.2	1804.2	1769.0	1743.5
30°	2232.0	2208.1	2191.1	2160.0	2138.9	2089.4	2051.3	1992.0	1913.0	1856.5	1821.2
32.5°	2395.9	2369.0	2354.8	2330.9	2306.8	2277.2	2219.4	2127.6	2025.9	1934.2	1873.5
35°	2614.6	2586.4	2561.0	2539.8	2504.6	2449.4	2398.7	2288.5	2148.7	2020.3	1918.7
37.5°	2889.9	2843.3	2779.8	2726.2	2664.0	2585.0	2507.4	2394.4	2234.8	2068.3	1932.7
40°	3183.6	3101.7	3011.4	2911.1	2803.8	2689.4	2600.5	2486.2	2306.8	2109.2	1922.9
42.5°	3489.9	3360.1	3234.4	3093.3	2943.6	2808.1	2692.3	2566.6	2360.5	2120.5	1883.3
45°	3793.5	3648.1	3457.5	3272.5	3083.3	2915.3	2785.5	2644.2	2409.9	2124.8	1831.1
47.5°	4044.8	3895.1	3677.7	3446.2	3221.8	3031.1	2878.7	2726.2	2476.3	2154.4	1818.3
50°	4310.2	4128.1	3886.6	3612.7	3358.7	3145.5	2983.1	2825.0	2569.4	2230.7	1859.4
52.5°	4599.6	4390.7	4108.3	3802.0	3523.8	3285.3	3108.8	2946.4	2688.1	2337.9	1937.0
55°	4952.5	4697.0	4390.7	4044.8	3746.9	3482.9	3288.1	3096.1	2829.2	2465.0	2034.4
57.5°	5491.9	5178.4	4834.0	4440.1	4109.7	3797.7	3564.8	3343.1	3048.1	2654.2	2167.2
60°	6467.5	6132.8	5685.3	5208.1	4819.9	4455.6	4114.0	3838.7	3475.9	3026.8	2460.7
62.5°	7865.1	7420.4	6823.2	6155.4	5647.2	5122.0	4736.6	4327.2	3876.8	3392.5	2806.6
65°	8641.6	8102.3	7303.2	6528.1	5874.5	5304.1	4814.2	4339.9	3840.1	3377.0	2887.2
66°	8737.6	8175.6	7345.6	6529.5	5843.4	5257.5	4742.2	4250.9	3739.8	3297.9	2853.3
67.5°	8698.0	8123.4	7267.9	6406.7	5709.3	5079.6	4547.4	4037.7	3528.1	3115.9	2740.3
70°	8050.1	7505.1	6665.1	5830.7	5168.6	4547.4	4039.2	3537.9	3070.7	2717.7	2441.0
72.5°	6684.9	6219.0	5489.0	4834.0	4314.4	3802.0	3371.4	2892.7	2497.5	2236.3	2072.5
75°	4825.5	4543.1	3878.2	3502.7	3046.6	2706.4	2288.5	2004.8	1720.9	1593.9	1565.7
77.5°	3048.1	2668.3	2246.1	1849.4	1520.5	1260.7	981.2	833.0	694.6	680.5	821.7
80°	1543.1	1389.2	1070.2	852.7	717.2	580.2	458.9	347.3	242.8	292.2	350.2
82.5°	1010.9	842.8	660.7	543.5	473.0	392.4	305.0	211.8	155.3	175.0	240.0
85°	546.3	465.9	375.5	296.5	240.0	214.6	144.0	101.7	100.2	107.3	137.0
87.5°	39.5	39.5	31.1	28.2	33.9	28.2	25.4	25.4	24.0	25.4	33.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156496

CATALOG NUMBER: VXS-F05-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0	1687.0
2.5°	1705.5	1709.6	1711.1	1718.1	1722.4	1725.2	1728.1	1728.1	1729.4	1733.7	1735.1
5°	1737.9	1745.0	1753.5	1759.1	1762.0	1770.4	1773.2	1773.2	1776.1	1781.7	1785.9
7.5°	1757.7	1767.6	1776.1	1778.9	1784.5	1787.4	1791.6	1794.4	1794.4	1800.0	1802.9
10°	1764.8	1770.4	1778.9	1778.9	1784.5	1784.5	1788.7	1790.2	1790.2	1795.8	1800.0
12.5°	1764.8	1767.6	1774.6	1774.6	1778.9	1780.3	1785.9	1790.2	1791.6	1798.7	1804.2
15°	1756.3	1759.1	1764.8	1766.1	1776.1	1781.7	1794.4	1802.9	1802.9	1809.9	1812.7
17.5°	1732.2	1739.4	1750.7	1762.0	1780.3	1793.0	1808.5	1815.5	1809.9	1805.7	1801.5
20°	1692.7	1705.5	1732.2	1760.5	1793.0	1809.9	1818.3	1811.3	1791.6	1771.8	1759.1
22.5°	1653.2	1678.7	1723.8	1766.1	1802.9	1814.2	1809.9	1784.5	1752.0	1728.1	1711.1
25°	1671.6	1701.2	1745.0	1783.1	1807.0	1804.2	1787.4	1752.0	1716.8	1685.7	1657.4
27.5°	1747.8	1780.3	1804.2	1817.0	1814.2	1794.4	1767.6	1728.1	1685.7	1644.8	1605.2
30°	1819.8	1836.8	1842.4	1832.5	1809.9	1777.4	1743.5	1698.3	1641.9	1591.1	1545.9
32.5°	1852.2	1835.3	1808.5	1781.7	1745.0	1716.8	1670.2	1620.7	1550.2	1489.4	1444.2
35°	1852.2	1784.5	1716.8	1660.3	1605.2	1569.9	1516.3	1449.9	1385.0	1334.1	1298.9
37.5°	1811.3	1681.5	1569.9	1478.1	1409.0	1370.9	1290.4	1231.1	1176.1	1159.1	1136.5
40°	1736.5	1544.5	1383.5	1263.5	1176.1	1119.6	1039.1	998.1	977.0	968.5	964.2
42.5°	1636.3	1392.0	1177.4	1029.2	934.6	871.1	817.4	792.0	790.6	789.2	789.2
45°	1529.0	1228.3	977.0	800.5	717.2	660.7	635.3	625.4	633.9	632.4	633.9
47.5°	1462.6	1104.0	793.5	605.7	542.2	505.4	492.7	497.0	504.0	501.1	501.1
50°	1454.2	1040.5	670.6	471.5	423.5	405.2	402.4	402.4	406.6	403.7	402.4
52.5°	1485.2	1030.6	607.0	405.2	367.0	351.5	348.7	347.3	345.9	337.4	330.4
55°	1538.9	1053.2	588.7	388.3	348.7	331.8	327.6	324.7	319.1	307.8	295.0
57.5°	1646.1	1123.8	605.7	396.7	354.4	340.2	336.0	336.0	324.7	306.3	288.0
60°	1904.6	1303.1	674.8	429.2	381.1	367.0	369.8	368.5	351.5	324.7	296.5
62.5°	2237.7	1537.4	765.2	474.4	415.0	412.2	426.3	423.5	395.3	354.4	313.4
65°	2391.6	1647.6	790.6	484.2	422.2	434.8	463.1	460.2	425.0	368.5	316.3
66°	2394.4	1647.6	779.3	475.8	412.2	427.8	456.0	454.6	419.3	362.8	310.6
67.5°	2336.5	1602.4	746.8	458.9	392.4	403.7	429.2	427.8	395.3	348.7	299.3
70°	2119.1	1434.4	663.5	429.2	365.7	360.0	368.5	362.8	341.7	309.2	275.3
72.5°	1815.5	1204.2	578.9	406.6	347.3	324.7	319.1	314.8	297.9	279.6	258.3
75°	1430.2	953.0	508.3	389.6	330.4	300.7	290.9	285.2	273.9	261.1	244.2
77.5°	882.4	681.9	443.3	367.0	317.6	288.0	280.9	272.4	255.5	240.0	227.3
80°	393.9	422.2	364.2	320.5	283.7	257.0	245.7	233.0	216.0	206.1	199.1
82.5°	262.6	272.4	264.0	240.0	214.6	193.4	176.5	176.5	173.7	165.2	162.4
85°	168.0	169.4	163.7	148.2	138.3	125.7	118.5	120.0	125.7	124.2	122.8
87.5°	38.1	38.1	45.2	42.4	49.4	52.2	56.5	60.7	69.2	69.2	73.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156496

CATALOG NUMBER: VXS-F05-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	1687.0	1687.0	1687.0	1687.0	1687.0
2.5°	1736.5	1739.4	1742.2	1737.9	1739.4
5°	1785.9	1784.5	1791.6	1787.4	1790.2
7.5°	1801.5	1802.9	1808.5	1808.5	1809.9
10°	1802.9	1805.7	1812.7	1817.0	1819.8
12.5°	1809.9	1815.5	1826.8	1829.6	1829.6
15°	1815.5	1818.3	1825.5	1828.3	1831.1
17.5°	1795.8	1790.2	1793.0	1794.4	1793.0
20°	1746.4	1740.7	1739.4	1733.7	1736.5
22.5°	1692.7	1677.2	1667.4	1656.1	1656.1
25°	1627.8	1603.8	1584.0	1564.2	1568.5
27.5°	1567.0	1536.1	1516.3	1503.5	1500.7
30°	1507.8	1475.3	1457.0	1441.5	1441.5
32.5°	1409.0	1386.4	1362.4	1352.5	1351.1
35°	1272.0	1257.9	1238.1	1233.9	1226.8
37.5°	1118.1	1113.9	1097.0	1095.5	1088.5
40°	957.2	960.0	954.4	951.5	947.4
42.5°	796.3	810.4	807.6	806.1	803.3
45°	642.4	652.2	653.7	657.9	665.0
47.5°	505.4	508.3	511.1	509.6	511.1
50°	395.3	388.3	386.8	382.6	386.8
52.5°	319.1	307.8	302.1	296.5	293.7
55°	280.9	269.6	264.0	261.1	258.3
57.5°	271.1	259.8	251.3	245.7	244.2
60°	273.9	257.0	245.7	238.5	237.2
62.5°	280.9	258.3	242.8	235.8	234.4
65°	279.6	255.5	241.5	233.0	231.5
66°	275.3	252.7	238.5	231.5	230.2
67.5°	268.3	248.5	235.8	230.2	227.3
70°	255.5	242.8	233.0	225.9	223.1
72.5°	244.2	234.4	225.9	218.9	217.4
75°	231.5	223.1	214.6	208.9	207.6
77.5°	216.0	207.6	201.9	197.6	196.3
80°	190.6	185.0	179.3	173.7	173.7
82.5°	158.1	153.9	148.2	144.0	142.6
85°	121.5	121.5	117.2	113.0	111.5
87.5°	72.0	70.6	70.6	66.3	66.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)