

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P156506

Luminaire Tested: **VXS-F06-LED-E1-T4-7050**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P156506
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F06-LED-E1-T4-7050
Description: VISION SITE SMALL LED LUMINAIRE
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 4
Light Source: (42) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15359.4 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 156.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P156506

CATALOG NUMBER: VXS-F06-LED-E1-T4-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 3.4 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156506

CATALOG NUMBER: VXS-F06-LED-E1-T4-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P156506

CATALOG NUMBER: VXS-F06-LED-E1-T4-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3277.3	0.0	3277.3
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	12082.1	0.0	12082.1
	% Fixture	78.7	0.0	78.7
Total	Lumens	15359.4	0.0	15359.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.6	1.3
10°-20°	596.9	3.9
20°-30°	1028.1	6.7
30°-40°	1555.5	10.1
40°-50°	2016.1	13.1
50°-60°	2779.5	18.1
60°-70°	4318.5	28.1
70°-80°	2511.2	16.3
80°-90°	357.1	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15359.4	100.0
0°-180°	15359.4	100.0

Coefficient of Utilization



REPORT NUMBER: P156506


CATALOG NUMBER: VXS-F06-LED-E1-T4-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	944.3	6.1			
FM	(30°-60°)	4930.4	32.1			
FH	(60°-80°)	5933.3	38.6			G3/7500
FVH	(80°-90°)	274.1	1.8			G3/500
BL	(0°-30°)	877.2	5.7	B2/1000		
BM	(30°-60°)	1420.7	9.2	B2/2500		
BH	(60°-80°)	896.3	5.8	B2/1000		G2/1000
BVH	(80°-90°)	83.0	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P156506

CATALOG NUMBER: VXS-F06-LED-E1-T4-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6
2.5°	1987.3	1994.0	1988.9	1990.7	1990.7	1992.3	1992.3	1994.0	1992.3	1997.4	2000.8
5°	1951.7	1955.0	1953.4	1956.8	1960.1	1966.9	1965.2	1973.7	1975.3	1980.4	1988.9
7.5°	1938.1	1934.7	1936.4	1941.5	1944.9	1948.3	1951.7	1958.4	1963.5	1975.3	1982.2
10°	1951.7	1949.9	1951.7	1955.0	1955.0	1956.8	1953.4	1960.1	1963.5	1973.7	1980.4
12.5°	2007.6	2007.6	2004.1	2004.1	2000.8	1997.4	1988.9	1983.8	1982.2	1983.8	1987.3
15°	2097.4	2094.0	2087.2	2082.1	2075.3	2063.5	2051.6	2041.5	2034.7	2024.6	2021.1
17.5°	2185.5	2180.4	2173.6	2166.8	2158.3	2146.5	2127.9	2116.0	2097.4	2085.5	2078.8
20°	2287.2	2276.9	2268.5	2260.0	2243.0	2239.7	2221.0	2200.7	2178.7	2151.6	2148.2
22.5°	2419.3	2402.3	2392.1	2387.0	2370.2	2365.1	2334.5	2305.7	2278.7	2243.0	2234.6
25°	2553.1	2536.2	2531.1	2524.2	2512.4	2505.7	2476.9	2444.7	2409.1	2360.0	2349.7
27.5°	2683.5	2685.2	2671.7	2676.8	2673.4	2661.6	2632.7	2600.5	2573.4	2515.9	2503.9
30°	2846.2	2836.0	2829.2	2839.4	2827.6	2829.2	2803.8	2786.8	2742.8	2708.9	2685.2
32.5°	3015.5	3013.9	3024.0	3030.9	3029.1	3025.8	3005.4	2988.5	2949.5	2900.4	2890.3
35°	3247.7	3257.8	3266.3	3296.8	3296.8	3318.9	3298.5	3278.1	3232.4	3173.2	3152.8
37.5°	3405.3	3408.6	3442.5	3483.2	3534.0	3581.5	3595.0	3600.1	3581.5	3537.4	3506.9
40°	3549.2	3556.1	3610.3	3673.0	3747.5	3840.6	3896.6	3922.0	3927.0	3906.7	3840.6
42.5°	3693.3	3703.4	3759.3	3850.8	3954.2	4072.7	4171.0	4233.7	4269.2	4269.2	4230.3
45°	3860.9	3874.5	3935.5	4035.4	4155.8	4304.9	4440.4	4560.6	4618.2	4621.7	4584.4
47.5°	4059.2	4071.1	4142.2	4243.8	4367.6	4518.3	4689.4	4826.6	4933.4	4940.1	4909.6
50°	4315.0	4331.9	4391.2	4482.7	4609.7	4762.3	4933.4	5124.8	5236.6	5263.7	5231.5
52.5°	4653.8	4657.2	4706.3	4791.1	4914.7	5060.4	5241.7	5450.1	5597.5	5619.5	5566.9
55°	5121.5	5116.4	5148.5	5240.0	5333.2	5446.7	5634.7	5868.5	6032.8	6066.7	6012.5
57.5°	5756.7	5751.6	5778.8	5800.7	5975.2	6085.4	6270.1	6493.7	6653.0	6751.2	6658.0
60°	6741.0	6736.0	6780.0	6908.7	7039.2	7200.1	7379.7	7647.4	7871.0	7899.8	7808.4
62.5°	7454.3	7479.7	7576.3	7727.0	7991.3	8306.4	8635.1	8987.5	9446.6	9592.3	9548.2
65°	7205.2	7256.1	7389.8	7618.5	7971.0	8406.4	8921.5	9560.1	10175.0	10519.0	10508.8
66°	6981.6	7037.5	7201.9	7422.1	7794.8	8270.9	8833.3	9529.6	10217.4	10596.9	10620.6
67.5°	6575.0	6637.7	6798.7	7059.5	7422.1	7928.6	8533.5	9290.7	10068.3	10510.5	10573.2
70°	5783.8	5855.0	5971.9	6187.0	6544.5	6996.9	7633.9	8311.5	9126.4	9633.0	9709.2
72.5°	4835.1	4897.8	5028.3	5204.5	5497.5	5782.2	6281.9	6781.7	7364.5	7942.2	7886.3
75°	3471.3	3498.4	3576.4	3767.8	3925.4	4181.1	4582.7	4992.6	5390.8	5655.0	5692.3
77.5°	1804.2	1875.4	1985.6	2197.3	2368.4	2598.9	2859.7	3168.1	3459.5	3701.8	3635.6
80°	1180.8	1211.3	1309.5	1418.0	1543.4	1690.8	1865.3	1980.4	2017.7	2002.5	2017.7
82.5°	681.0	737.0	867.4	950.5	1043.6	1094.4	1233.4	1365.5	1440.0	1346.8	1313.0
85°	86.4	111.8	352.4	443.8	508.3	584.5	626.8	706.4	659.1	589.5	718.3
87.5°	18.7	16.9	23.7	50.8	52.5	44.0	83.0	88.1	54.2	27.2	33.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156506

CATALOG NUMBER: VXS-F06-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6
2.5°	2004.1	2005.9	2009.2	2014.3	2017.7	2021.1	2024.6	2029.6	2033.0	2036.4	2043.1
5°	1995.8	2002.5	2009.2	2016.1	2024.6	2038.0	2046.5	2053.3	2060.1	2073.7	2078.8
7.5°	1990.7	2002.5	2012.6	2024.6	2038.0	2049.9	2065.2	2073.7	2083.8	2092.2	2102.5
10°	1987.3	2004.1	2014.3	2031.3	2046.5	2058.3	2075.3	2085.5	2097.4	2107.6	2112.6
12.5°	1994.0	2002.5	2012.6	2029.6	2048.2	2065.2	2083.8	2092.2	2102.5	2110.9	2112.6
15°	2022.8	2022.8	2024.6	2038.0	2056.7	2070.3	2085.5	2094.0	2099.1	2104.1	2104.1
17.5°	2075.3	2063.5	2055.0	2056.7	2068.6	2077.0	2085.5	2085.5	2082.1	2080.4	2077.0
20°	2136.4	2121.0	2104.1	2092.2	2088.9	2082.1	2077.0	2060.1	2046.5	2034.7	2026.2
22.5°	2224.5	2200.7	2177.0	2154.9	2134.6	2109.2	2080.4	2046.5	2014.3	1992.3	1978.8
25°	2332.8	2314.2	2285.4	2251.5	2226.1	2178.7	2141.5	2092.2	2051.6	2022.8	1999.1
27.5°	2487.0	2465.0	2437.9	2407.4	2370.2	2317.6	2271.8	2214.3	2165.1	2122.8	2092.2
30°	2678.4	2649.6	2629.3	2592.0	2566.6	2507.4	2461.6	2390.5	2295.5	2227.8	2185.5
32.5°	2875.0	2842.8	2825.8	2797.0	2768.3	2732.6	2663.2	2553.1	2431.1	2321.0	2248.2
35°	3137.6	3103.7	3073.2	3047.8	3005.4	2939.4	2878.3	2746.2	2578.5	2424.4	2302.4
37.5°	3468.0	3412.0	3335.8	3271.4	3196.9	3102.0	3008.8	2873.3	2681.9	2482.0	2319.3
40°	3820.3	3722.1	3613.6	3493.4	3364.6	3227.4	3120.6	2983.4	2768.3	2531.1	2307.5
42.5°	4188.0	4032.1	3881.3	3711.9	3532.3	3369.6	3230.8	3080.0	2832.6	2544.7	2260.0
45°	4552.2	4377.7	4149.0	3927.0	3700.0	3498.4	3342.6	3173.2	2891.9	2549.7	2197.3
47.5°	4853.8	4674.2	4413.3	4135.4	3866.0	3637.3	3454.4	3271.4	2971.5	2585.3	2182.1
50°	5172.2	4953.7	4664.0	4335.3	4030.4	3774.6	3579.8	3389.9	3083.3	2676.8	2231.2
52.5°	5519.6	5268.8	4929.9	4562.4	4228.6	3942.3	3730.6	3535.6	3225.7	2805.5	2324.4
55°	5943.1	5636.5	5268.8	4853.8	4496.3	4179.5	3945.7	3715.2	3395.1	2958.0	2441.2
57.5°	6590.3	6214.2	5800.7	5328.1	4931.7	4557.3	4277.7	4011.7	3657.7	3185.0	2600.5
60°	7760.9	7359.4	6822.4	6249.7	5783.8	5346.7	4936.8	4606.4	4171.0	3632.2	2953.0
62.5°	9438.1	8904.5	8187.9	7386.5	6776.6	6146.4	5683.8	5192.5	4652.1	4071.1	3368.0
65°	10369.9	9722.7	8763.8	7833.8	7049.3	6365.0	5777.1	5207.8	4608.1	4052.4	3464.6
66°	10485.1	9810.9	8814.7	7835.4	7012.1	6309.0	5690.7	5101.1	4487.8	3957.5	3423.8
67.5°	10437.6	9748.2	8721.5	7688.1	6851.2	6095.5	5456.9	4845.3	4233.7	3739.0	3288.4
70°	9660.0	9006.1	7998.1	6996.9	6202.3	5456.9	4846.9	4245.5	3684.8	3261.2	2929.2
72.5°	8021.8	7462.7	6586.8	5800.7	5177.3	4562.4	4045.6	3471.3	2997.0	2683.5	2487.0
75°	5790.6	5451.8	4653.8	4203.2	3656.0	3247.7	2746.2	2405.7	2065.2	1912.7	1878.9
77.5°	3657.7	3202.0	2695.4	2219.4	1824.6	1512.8	1177.4	999.6	833.5	816.6	986.0
80°	1851.7	1667.0	1284.1	1023.3	860.6	696.3	550.6	416.8	291.4	350.7	420.1
82.5°	1213.1	1011.4	792.8	652.2	567.6	471.0	365.9	254.1	186.3	210.1	288.0
85°	655.6	559.1	450.7	355.8	288.0	257.5	172.8	122.0	120.3	128.7	164.4
87.5°	47.5	47.5	37.3	33.9	40.6	33.9	30.5	30.5	28.8	30.5	40.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156506

CATALOG NUMBER: VXS-F06-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6	2024.6
2.5°	2046.5	2051.6	2053.3	2061.8	2066.8	2070.3	2073.7	2073.7	2075.3	2080.4	2082.1
5°	2085.5	2094.0	2104.1	2110.9	2114.3	2124.5	2127.9	2127.9	2131.2	2138.0	2143.1
7.5°	2109.2	2121.0	2131.2	2134.6	2141.5	2144.8	2149.8	2153.3	2153.3	2160.0	2163.4
10°	2117.7	2124.5	2134.6	2134.6	2141.5	2141.5	2146.5	2148.2	2148.2	2154.9	2160.0
12.5°	2117.7	2121.0	2129.5	2129.5	2134.6	2136.4	2143.1	2148.2	2149.8	2158.3	2165.1
15°	2107.6	2110.9	2117.7	2119.4	2131.2	2138.0	2153.3	2163.4	2163.4	2171.9	2175.3
17.5°	2078.8	2087.2	2100.7	2114.3	2136.4	2151.6	2170.3	2178.7	2171.9	2166.8	2161.8
20°	2031.3	2046.5	2078.8	2112.6	2151.6	2171.9	2182.1	2173.6	2149.8	2126.1	2110.9
22.5°	1983.8	2014.3	2068.6	2119.4	2163.4	2177.0	2171.9	2141.5	2102.5	2073.7	2053.3
25°	2005.9	2041.5	2094.0	2139.7	2168.5	2165.1	2144.8	2102.5	2060.1	2022.8	1988.9
27.5°	2097.4	2136.4	2165.1	2180.4	2177.0	2153.3	2121.0	2073.7	2022.8	1973.7	1926.2
30°	2183.7	2204.0	2210.9	2199.0	2171.9	2133.0	2092.2	2038.0	1970.3	1909.3	1855.1
32.5°	2222.7	2202.4	2170.3	2138.0	2094.0	2060.1	2004.1	1944.9	1860.2	1787.4	1733.2
35°	2222.7	2141.5	2060.1	1992.3	1926.2	1883.9	1819.5	1739.9	1662.0	1600.9	1558.7
37.5°	2173.6	2017.7	1883.9	1773.8	1690.8	1645.0	1548.5	1477.3	1411.2	1390.9	1363.8
40°	2083.8	1853.4	1660.3	1516.3	1411.2	1343.4	1246.9	1197.7	1172.3	1162.2	1157.1
42.5°	1963.5	1670.5	1413.0	1235.0	1121.6	1045.3	980.9	950.5	948.7	947.0	947.0
45°	1834.7	1473.9	1172.3	960.6	860.6	792.8	762.4	750.5	760.7	759.0	760.7
47.5°	1755.1	1324.9	952.1	726.8	650.6	606.5	591.3	596.4	604.8	601.5	601.5
50°	1745.0	1248.6	804.8	565.8	508.3	486.2	482.8	482.8	487.9	484.6	482.8
52.5°	1782.3	1236.7	728.5	486.2	440.5	421.9	418.4	416.8	415.0	404.9	396.5
55°	1846.6	1263.8	706.4	465.9	418.4	398.1	393.1	389.6	382.9	369.3	354.1
57.5°	1975.3	1348.5	726.8	476.1	425.2	408.3	403.2	403.2	389.6	367.7	345.6
60°	2285.4	1563.7	809.8	515.0	457.4	440.5	443.8	442.2	421.9	389.6	355.8
62.5°	2685.2	1845.0	918.2	569.2	498.0	494.7	511.6	508.3	474.4	425.2	376.1
65°	2869.8	1977.1	948.7	581.1	506.5	521.8	555.6	552.3	509.9	442.2	379.5
66°	2873.3	1977.1	935.1	570.9	494.7	513.4	547.3	545.5	503.2	435.4	372.7
67.5°	2803.8	1922.9	896.2	550.6	471.0	484.6	515.0	513.4	474.4	418.4	359.2
70°	2542.9	1721.2	796.3	515.0	438.8	432.0	442.2	435.4	409.9	371.0	330.4
72.5°	2178.7	1445.1	694.6	487.9	416.8	389.6	382.9	377.8	357.5	335.4	310.1
75°	1716.2	1143.5	609.8	467.6	396.5	360.8	349.0	342.2	328.7	313.4	293.1
77.5°	1058.9	818.2	531.9	440.5	381.1	345.6	337.1	326.9	306.6	288.0	272.7
80°	472.6	506.5	437.1	384.6	340.5	308.3	294.8	279.6	259.2	247.4	238.9
82.5°	315.1	326.9	316.8	288.0	257.5	232.1	211.8	211.8	208.4	198.2	194.8
85°	201.6	203.3	196.5	177.9	166.0	150.8	142.3	144.0	150.8	149.1	147.4
87.5°	45.7	45.7	54.2	50.8	59.3	62.7	67.8	72.8	83.0	83.0	88.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P156506

CATALOG NUMBER: VXS-F06-LED-E1-T4-7050

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	2024.6	2024.6	2024.6	2024.6	2024.6
2.5°	2083.8	2087.2	2090.6	2085.5	2087.2
5°	2143.1	2141.5	2149.8	2144.8	2148.2
7.5°	2161.8	2163.4	2170.3	2170.3	2171.9
10°	2163.4	2166.8	2175.3	2180.4	2183.7
12.5°	2171.9	2178.7	2192.2	2195.6	2195.6
15°	2178.7	2182.1	2190.6	2193.9	2197.3
17.5°	2154.9	2148.2	2151.6	2153.3	2151.6
20°	2095.6	2088.9	2087.2	2080.4	2083.8
22.5°	2031.3	2012.6	2000.8	1987.3	1987.3
25°	1953.4	1924.6	1900.8	1877.1	1882.2
27.5°	1880.5	1843.2	1819.5	1804.2	1800.9
30°	1809.3	1770.4	1748.4	1729.7	1729.7
32.5°	1690.8	1663.6	1634.8	1623.0	1621.3
35°	1526.4	1509.5	1485.8	1480.7	1472.2
37.5°	1341.8	1336.7	1316.4	1314.6	1306.2
40°	1148.6	1152.0	1145.3	1141.9	1136.8
42.5°	955.5	972.4	969.0	967.4	963.9
45°	770.9	782.7	784.4	789.4	797.9
47.5°	606.5	609.8	613.3	611.6	613.3
50°	474.4	465.9	464.2	459.1	464.2
52.5°	382.9	369.3	362.6	355.8	352.4
55°	337.1	323.6	316.8	313.4	310.1
57.5°	325.3	311.7	301.6	294.8	293.1
60°	328.7	308.3	294.8	286.3	284.7
62.5°	337.1	310.1	291.4	282.9	281.2
65°	335.4	306.6	289.7	279.6	277.8
66°	330.4	303.2	286.3	277.8	276.2
67.5°	321.9	298.1	282.9	276.2	272.7
70°	306.6	291.4	279.6	271.1	267.7
72.5°	293.1	281.2	271.1	262.6	260.9
75°	277.8	267.7	257.5	250.8	249.0
77.5°	259.2	249.0	242.3	237.2	235.4
80°	228.7	222.0	215.1	208.4	208.4
82.5°	189.7	184.7	177.9	172.8	171.1
85°	145.7	145.7	140.6	135.5	133.9
87.5°	86.4	84.7	84.7	79.6	79.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)